


5

FED. MFR. CODE 91929

CIRCUIT DIAGRAM



△

- MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000±.002 CENTERS.

2 - SUITABLE ONLY FOR APPLICATIONS IMPARTING A RAPID STROKE TO THE SWITCH PLUNGER.

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS. HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS		ELECTRICAL DATA		SCALE	FULL
OPERATING FORCE	----- 8 OZ MAX	CONTACT ARRANGEMENT		DO NOT SCALE PRINT	
RELEASE FORCE	----- 1 1/2 OZ MIN	SINGLE POLE DOUBLE THROW		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±	
PRETRAVEL	----- .250 MAX	DOUBLE BREAK			
DIFFERENTIAL TRAVEL	----- .050 MAX	30 VOLTS DC RATING (SEA LEVEL TO 50,000 FT)			
OVERTRAVEL	----- .030 MIN	INDUCTIVE ----- 25 AMP RESISTIVE ----- 30 AMP MAXIMUM INRUSH ----- 75 AMP (BASED ON LIFE OF 25,000 OPERATIONS)			
		25A 125, <u>250</u> , OR 480 VAC L58 3/4 HP 125 VAC, 1 1/2 HP <u>250</u> VAC 1A 125 VDC, 0.5A 250 VDC			
				WEIGHT	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BA-2SV22T](#)