




Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51742-ABBCC00EF--
NOTE: ①



mat'l code				SEE NOTE 2		tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
litr	ecn no.	dr	date	linear		.XX±.01/0.X±0.3		COPY		projection		title	
H	DG05-0132	SJ	06/02/05			.XXX±.005/0.XX±0.13						VERTICAL RECEPTACLE W/GUIDE PIN	
J	DG05-0153	SJ	06/10/05			.XXX±.0020/.XX±.051						POWER / SIGNAL	
K	DG06-0362	JULIA	08/30/06	angles		0°±2°						product family	PWRBLADE
L	DG08-0239	JC	09/11/08	dr		D. EATON	05-25-99					code	213
				enr		J. BROWN	05-24-99					size	dwg no
				chr		J. BROWN	05-26-99					scale	51742
				appd		J. BROWN	05-26-99					sheet	1 of 3
sheet index	revision sheet	L	L	L									
		1	2	3									

Pro/E

cage code 22526



PRODUCT NUMBER	DIM	LENGTH FORMULAS (SEE NOTE 10)
51742-ABBCCC00EF-- NOTE: ①	DIM "A"	.100 [2.54] x (CCC/4) + .250 [6.35] x BB + .650 [16.51] (NOTE 10)
	DIM "B"	.100 [2.54] x (CCC/4) + .250 [6.35] x BB + .350 [8.89]
	DIM "C"	.100 [2.54] x (CCC/4) + .250 [6.35] x BB + .300 [7.62]
	DIM "E"	.100 [2.54] x (CCC/4) + .450 [11.43]
	DIM "F"	.100 [2.54] x (CCC/4) + .250 [6.35] x BB + .680 [17.27]
	DIM "H"	.100 [2.54] x (CCC/4) + .250 [6.35]

CONNECTOR NOTES

- PRODUCT NUMBER CODE:
51742 - A BB CCC 00 E F LF
NO THIS SUFFIX: 100u"/2.54um SnPb ON PCB INTERFACE
ADD THIS SUFFIX: 78u"/2.00um Sn ON PCB INTERFACE
RETENTION TO PCB (NOTE 8)
TAIL OPTIONS (NOTE 7)
ALWAYS '00' (ZERO, ZERO) (NOTE 6)
NUMBER OF SIGNAL CONTACTS (NOTE 5)
NUMBER OF RIGHT POWER CONTACTS (NOTE 4)
PLATING (NOTE 3)
BASE NUMBER
 - HOUSING MATERIAL: GLASS FILLED V-O HIGH TEMP THERMO PLASTIC.
SIGNAL CONTACT MATERIAL: COPPER ALLOY
POWER CONTACT MATERIAL: COPPER ALLOY
 - PLATING OPTION:
SEE PRINT 10064183 FOR PLATING SPEC OF 51742-1BBCCC00EF; 51742-1BBCCC00EFLF
 - RIGHT END POWER CONTACT, 01 TO 20 AVAILABLE.
MAXIMUM OF 20 POWER CONTACTS PER CONNECTOR.
 - SIGNAL CONTACTS, 004 TO 148 AVAILABLE.
 - THIS PART NOT AVAILABLE WITH LEFT SIDE POWER CONTACTS.
 - TAIL OPTIONS:
A = .135 ±.010[3.43±.25] SOLDER TO BOARD
C = .135 ±.010[3.43±.25] PRESS FIT
 - RETENTION TO PCB OPTIONS:
A = BOARD LOCK (REQUIRES .098 + .002, -.001 [2.49 +0.05, -0.03] THRU HOLE IN PCB) (NOT AVAILABLE WITH PRESS FIT).
BOARD LOCK TO BE USED IN CONJUNCTION WITH AN .092 PCB OR THICKER.
C = NO RETENTION FEATURE (ALL PRESS FIT).
 - MANUFACTURE'S NAME, P/N, AND DATE CODE TO APPEAR ON THIS SURFACE.
 - THE MAXIMUM OVERALL LENGTH (DIM A) OF A PART IS 8.00 [203.2].
 - PRODUCT SPECIFICATION GS-12-149.
 - REFERENCE 51698 FOR SPECIALS WORKSHEET.
- PCB NOTES:
- ALL DIMENSIONS ARE BASIC UNLESS OTHERWISE SPECIFIED.
 - ALL THROUGH HOLES ARE LOCATED WITH A TRUE POSITION OF .004 [0.01]
 - ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.
 - 0.0453±.001 [1.151±.02] DRILLED HOLES PLATED WITH 0.0003 [0.007] MIN SnPb OVER 0.001 [1.03] TO .003 [0.08] PLATING TO ACHIEVE A .040 ±.003 [1.02 ±.08] HOLE.
 - THE VOID CORING IN BETWEEN POWER MODULES, SIGNAL MODULES AND END MODULES ARE OPTIONAL AND THE SHAPE MAY BE DIFFERENT FOR OPTIMIZING THE MOLDING PROCESS. THE VOID CORING WILL NOT EFFECT TO PRODUCT FUNCTION.
 - A SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

mat'l code				SEE NOTE 2		tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
litr	ecn no.	dr	date			.XX±.01/0.X±0.3		COPY					
L						linear .XXX±.005/0.XX±0.13		projection					
						angles .XXX±.0020/.XX±.051							
						0°±2°		INCH/MM					
						dr D. EATON 05-25-99							
						enrg J. BROWN 05-24-99							
						chr J. BROWN 05-26-99							
						appd J. BROWN 05-26-99							
sheet index	revision sheet												


cage code 22526

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.


PRODUCT NUMBER
51742-ABBCCC00EF--
NOTE: ①




SECTION B-B
SCALE 2:1



SECTION C-C
SCALE 2:1



SECTION A-A
SCALE 2:1



RECOMMENDED PCB LAYOUT

mat'l code				SEE NOTE 2		tolerances unless otherwise specified		CUSTOMER		FCI		www.fciconnect.com	
litr	ecn no.	dr	date			linear	.XX±.01/.0.X±0.3	COPY		projection		title	
L							.XXX±.005/.0.XX±0.13					VERTICAL RECEPTACLE W/GUIDE PIN	
						angles	.XXX±.0020/.XX±.051					POWER / SIGNAL	
						dr	0°±2°					product family	
						enrg	D. EATON 05-25-99					PWRBLADE	
						chr	J. BROWN 05-24-99					code	
						appd	J. BROWN 05-26-99					213	
							J. BROWN 05-26-99					sheet	
												3 of 3	
sheet index	revision sheet												

Pro/E

cage code 22526