




FIG. 11




FIG. III




FIG. 1

NOTE:

1. DO NOT SOLDER TO PIN: USE SNAP ON SOCKET ONLY.
2. RECOMMENDED "O"RING .612 I.D. X .103 WIDE WHEN REQUIRED (SUPPLIED BY CUSTOMER).
3. USE AMP CRIMP TOOL #90204-1.
4. NUT IS SUPPLIED WITH KIT BUT NOT ASSEMBLED.

861611-4	WITH GOLD PLATED STRAIGHT ON SOCKET	II
861611-3	AS SHOWN, WITH RIGHT ANGLE SOCKET	III
861611-2	AS SHOWN, WITH STRAIGHT ON SOCKET	II
861611-1	AS SHOWN, NO SOCKET	I
PART NO.	DESCRIPTION	FIG. NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN J. KAISER		1/12/04		 Tyco Electronics Corporation Harrisburg, PA 17105-3608								
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		D. EABY		APVD D. EABY		NAME							
		0 PLC ± -		PRODUCT SPEC		RECEPTACLE, LGH - -									
		1 PLC ± -		-											
		2 PLC ± .01		APPLICATION SPEC											
		3 PLC ± .005		-											
4 PLC ± -		ANGLES ± - ± -		-		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
MATERIAL POLYESTER		FINISH BLACK		WEIGHT -		A2		00779		C-861611		-			
CUSTOMER DRAWING										SCALE 5:1		SHEET 1 of 1		REV	