





Part Number	Contact Area Plating Finish	Insulator Color	Packaging
KUSBL-SMTAS1NW	Gold Flash (standard)	White	Bulk (trays, standard)
KUSBL-SMTAS1NW30	30u" Gold (30 option)	White	Bulk (trays, standard)
KUSBL-SMTAS1NB	Gold Flash (standard)	Black	Bulk (trays, standard)
KUSBL-SMTAS1NB30	30u" Gold (30 option)	Black	Bulk (trays, standard)
KUSBL-SMTAS1NWTR	Gold Flash (standard)	White	Tape & Reel (TR option)
KUSBL-SMTAS1NW30TR	30u" Gold (30 option)	White	Tape & Reel (TR option)
KUSBL-SMTAS1NBTR	Gold Flash (standard)	Black	Tape & Reel (TR option)
KUSBL-SMTAS1NB30TR	30u" Gold (30 option)	Black	Tape & Reel (TR option)

REV.	DATE	DESCRIPTION	REV. BY	CHK. BY	DRAWN BY	DATE
A0	1/22/03	New Drawing	T. Gokcek	C. Leiva	T. Gokcek	1/20/03
A1	3/13/03	Release Drawing	T. Gokcek	H. MA		
A2	6/25/04	ECO#04-029	H. MA	C. Leiva		
						UNITS
						mm

KUSBL-SMTAS1Nxyzz

x - insulator color
yy - plating option
zz - packaging option



Surface Mount A-Type USB Socket

Low Profile Mount, w/ Tape & Reel Option

Material and Finish

Insulator: HTN thermoplastic,
UL94V-0 rated, black or white color,
Reflow Process Compatible-
Recommended Soldering Temperature:
230°C for 30 seconds, 260°C max.

Shield: brass, 0.30mm thick

Shield Finish: 120u" nickel plated
over 50u" copper underplate

Contact Material: phosphor bronze

Contact Plating Options:

Standard: gold flash on contact area,
120u" min. tin/lead on soldertails,
all over 50u" min. nickel underplate

-30 Option: 30u" gold on contact area,
120u" min. tin/lead on soldertails,
all over 50u" min. nickel underplate

Specifications:

Contact Current Rating: 1A max.

Contact Resistance: 30 milliohms max.

Insulation Resistance: 1000 Megohms min.

Dielectric Withstanding Voltage: 500V AC

Insertion Force: 3.57kg max.

Extraction Force: 1.02kg min.

Operating Temperature: -25°C to +80°C

Durability: 1500 mating cycles min.

Tolerances

X.X $\pm$ 0.35
X.XX $\pm$ 0.25
Unless Stated
Otherwise



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[KUSBL-SMTAS1NB](#) [KUSBL-SMTAS1NB30](#) [KUSBL-SMTAS1NW](#) [KUSBL-SMTAS1NW30](#)