


*** UNCONTROLLED DOCUMENT * FOR REFERENCE ONLY**

STEWARD



CORE DIMENSIONS

UNCOATED CORE 35T0501-100				
	MM	INCHES	MM	INCHES
OD	12.70	(.500)	± .25	(.010)
ID	7.14	(.281)	± .25	(.010)
TH	6.35	(.250)	± .18	(.007)
EPOXY COATING 35T0501-10H				
OD	13.72	(.540)	± max	
ID	6.12	(.241)	± min	
TH	7.29	(.287)	± max	

WEIGHT / K 2.7216 KGS 6.0000 LBS
INITIAL PERMEABILITY **5000**

ELECTRICAL SPECIFICATIONS

	MIN (μ H)	MIN TOL.	NOM (μ H)	MAX (μ H)	MAX TOL.	FREQ. (kHz)	VOLT. (V)	TURNS
L1	2.927	(-20%)	3.659	4.391	+20%	100	≤ .0076	1
L2	292.7	(-20%)	365.9	439.1	+20%	100	≤ .0763	10
Q	10	-	-	-	-	100	≤ .0076	1

COATING SPECIFICATIONS

		Max. Coating Thickness (mm)	Min. DLB VAC	Min. DLB VDC	TEST FORCE (LB)
TYPE					
35T0501-100	UNCOATED	-	-	-	-
35T0501-10H	EPOXY	0.76	1000	1333	1.34

NOTES

Steward

THIS DOCUMENT CONTAINS INFORMATION WHICH IS PROPRIETARY TO STEWARD. NO PRODUCTION OR PUBLICATION OF THIS DOCUMENT IN WHOLE OR IN PART SHALL BE MADE WITHOUT WRITTEN AUTHORIZATION FROM STEWARD.

Date:	01/05/2006	DWG #:	35T0501-10H-E	Title:	35T0501-10H	REV:	E
Drawn By:	JRK						

REV	Description	ECN #	Date	INT
E	Change coating description from Poly to Epoxy add kgs to weight		01/05/2006	JRK