





AD4506 SERIES

External Dimensions



Frame:Plastic(UL:94V-0)
Impeller:Plastic(UL:94V-0)
Lead wire:UL1571AWG28

Specifications(Nominal)


*:Noise is measured at the distance of one (1) meter from the axis of intake.

Bearing type: ◎=Ball ※=Sleeve ●=Hypro bearing

Frame size (mm)	Model No.	Bearing System Type	Rated Voltage (VDC)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum AirFlow (CMM) (CFM)	Maximum Pressure (InAq) (mmAq)	*Noise Level (dB/A)	Weight (g)
45x45x06	AD4505LX-K90(X)	●	5	0.05	0.25	4500	0.164 5.800	0.056 1.422	23.0	11.0
	AD4505MX-K90(X)	●	5	0.07	0.35	5500	0.203 7.200	0.080 2.032	27.4	
	AD4505HX-K90(X)	●	5	0.10	0.50	6200	0.233 8.250	0.100 2.540	32.6	
	AD4512LX-K90(X)	●	12	0.04	0.48	4500	0.164 5.800	0.056 1.422	23.0	
	AD4512MX-K90(X)	●	12	0.05	0.60	5500	0.203 7.200	0.080 2.032	27.4	
	AD4512HX-K90(X)	●	12	0.06	0.72	6200	0.233 8.250	0.100 2.540	32.6	

Specifications subject to change without notice.

The specification for bearing type is for reference only , for more bearing types information, please contact with your ADDA sales representative, thanks!!
(網頁上呈現產品軸承資訊均以參考為主，若需其他產品資訊請聯絡您在ADDA的業務代表，謝謝！！)



*Motor protective circuit and third lead wire functions

0	1	2	3	4	6	7	8	9	A	B
✓					✓					

*Safety approvals

				✓

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADDA:](#)

[AP4512MX-J90-4P-TA-LF](#) [AP4512MX-G90-LF](#) [AP4512MB-G90\(S\)-LF](#) [AP4512HX-G90-LF](#) [AD4512LX-K90 \(X\)](#)