



PC board drilling dimensions(after plating)
(thickness $\leq 3.20 \pm 0.30$ mm)



Notes:

1) The nut can protrude above the surface of insulator but maintaining the footprint dimension 6.0 ± 0.15 mm.

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0001

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S91C4PL00LF	D09S91C6PL00LF	D09S91C8PL00LF
15	39.14	33.32	25.18	24.54	19.18	D15S91C4PL00LF	D15S91C6PL00LF	D15S91C8PL00LF
25	53.03	47.04	39.12	38.25	33.12	D25S91C4PL00LF	D25S91C6PL00LF	D25S91C8PL00LF
37	69.32	63.50	55.68	54.71	49.68	D37S91C4PL00LF	D37S91C6PL00LF	D37S91C8PL00LF
						gold flash	0.76µ gold	1.25µ gold

mat'l. code				surface	tolerance	projection	product family		
-				ISO 1302	ISO 406 ISO 1101	MM	D-SUB		
ltr	ecn no	dr	date	tolerances unless otherwise specified			title		
K	ELX-I-21256	AB	2015/07/14	angles	linear	MM	FEMALE CONNECTOR DELTA-D		
				0°±2°	.0±0.1	scale 2:1	STRAIGHT PRESS FIT		
					.00±0.1		dwg no		
				dr	JOUBERT	1995/03/24	sheet 1 of 1		
				enr	ALIAS BABU	2015/07/14	C01-8646-0128		
				chr	MITHUN PAUL	2015/07/14	A3		
				app	BIJU K PAUL	2015/07/14	type Product Customer Drawing		
sheet index	revision	K							
	sheet	1							