

PRODUCT NUMBER
69167-XXXXXXHLF





LEAD FREE OPTION
NOTE 1, 2, 7

POLARIZATION
NOTE 10

NO. OF POS.
SEE TABLE

PIN PLATING

BASE P/N



mat'l. code				surface ISO 1302		tolerance ISO 406 ISO 1101	projection ISO 1001	product family HEADER	
ltr	ecn no	dr	date	tolerances unless otherwise specified	angles	linear	INCH/MM	title	
T	ELX-N-011896	JZ	05/31/12					FRICTION LATCH HEADER	
U	ELX-N-20592	JH	03/30/15					SINGLE ROW VERTICAL	
N	M05-0134	MHT	6/17/05	dr	M.CLOUSER	11/27/90	scale 4:1	dwg no	
P	M05-0176	ERE	08/05/05	enr	C.TREXTLER	11/27/90		69167	
R	M06-0256	MHT	9/07/06	chr	C.TREXTLER	11/27/90		A3	
S	M08-0291	MHT	10/06/08	appd	C.TREXTLER	11/27/90		type Product Customer Drawing	
sheet	revision	U	U	U	U				
index	sheet	1	2	3	4				



FCIconnect.com

Copyright FCI

PRODUCT NUMBER	NO OF POS	DIM K	DIM L	TAIL LENGTH DIM M
69167-X03	1 X 3	.300/7.62	.200/5.08	.120/3.05
69167-X04	1 X 4	.400/10.16	.300/7.62	.120/3.05
69167-X05	1 X 5	.500/12.70	.400/10.16	.120/3.05
69167-X06	1 X 6	.600/15.24	.500/12.70	.120/3.05
69167-X07	1 X 7	.700/17.78	.600/15.24	.120/3.05
69167-X08	1 X 8	.800/20.32	.700/17.78	.120/3.05
69167-X09	1 X 9	.900/22.86	.800/20.32	.120/3.05
69167-X10	1 X 10	1.000/25.40	.900/22.86	.120/3.05
69167-X11	1 X 11	1.100/27.94	1.000/25.40	.120/3.05
69167-X12	1 X 12	1.200/30.48	1.100/27.94	.120/3.05
69167-X13	1 X 13	1.300/33.02	1.200/30.48	.120/3.05
69167-X14	1 X 14	1.400/35.56	1.300/33.02	.120/3.05
69167-X15	1 X 15	1.500/38.10	1.400/35.56	.120/3.05
69167-X16	1 X 16	U N A V A I L A B L E		
69167-X17	1 X 17	U N A V A I L A B L E		
69167-X18	1 X 18	U N A V A I L A B L E		
69167-X19	1 X 19	U N A V A I L A B L E		
69167-X20	1 X 20	U N A V A I L A B L E		
69167-X21	1 X 21	U N A V A I L A B L E		
69167-X22	1 X 22	U N A V A I L A B L E		
69167-X23	1 X 23	U N A V A I L A B L E		
69167-X24	1 X 24	U N A V A I L A B L E		
69167-X25	1 X 25	U N A V A I L A B L E		
69167-X26	1 X 26	U N A V A I L A B L E		
69167-X27	1 X 27	U N A V A I L A B L E		
69167-X28	1 X 28	U N A V A I L A B L E		
69167-X29	1 X 29	U N A V A I L A B L E		
69167-X30	1 X 30	U N A V A I L A B L E		
69167-X31	1 X 31	U N A V A I L A B L E		
69167-X32	1 X 32	U N A V A I L A B L E		
69167-X33	1 X 33	U N A V A I L A B L E		
69167-X34	1 X 34	U N A V A I L A B L E		
69167-X35	1 X 35	U N A V A I L A B L E		
69167-X36	1 X 36	U N A V A I L A B L E		

PIN PLATING CODES

XXXXX-1YY	30u"/0.76u MIN (SEE NOTE 8) OVER 50u"/1.27u MIN Ni
XXXXX-2YY	15u"/0.38u MIN (SEE NOTE 8) OVER 50u"/1.27u MIN Ni
XXXXX-3YY	50u"/1.27u MIN (SEE NOTE 8) OVER 50u"/1.27u MIN Ni
XXXXX-4YY	100u"/2.54u MIN Sn OVER 50u"/1.27u MIN Ni (SEE NOTE 9)
XXXXX-4YYHLF	
XXXXX-5YY	15u"/0.38u MIN (SEE NOTE 8) OVER 50u"/1.27u MIN Ni
XXXXX-6YY	30u"/0.76u MIN (SEE NOTE 8) OVER 50u"/1.27u MIN Ni
XXXXX-7YY	30u"/0.76u MIN (SEE NOTE 8) OVER 50u"/1.27u MIN Ni
XXXXX-8YY	15u"/0.38u MIN (SEE NOTE 8) OVER 50u"/1.27u MIN Ni

NOTES:

1. PART NUMBER OPTIONS:

PIN PLATING CODES (SEE ABOVE)

LEAD FREE:

ADD "HLF" AT THE END OF PART NUMBER FOR LEAD FREE OPTION, NOT AVAILABLE FOR -5YY, -5YYH, -6YY, -6YYH.

2. BODY MATERIAL:

GLASS REINFORCED PCT COLOR: BLACK

FLAME RETARDANT PER UL 94 V-0

MAXIMUM OPERATING TEMPERATURE: 130° C

OR

MINERAL FILLED LCP, COLOR BLACK

FLAME RETARDANT PER UL 94 V-0

PART NUMBERS WITH "H" SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.

PART NUMBERS WITHOUT "H" SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR WAVE SOLDER PROCESS.

3. PIN MATERIAL: 3/4 HARD PHOS-BRONZE.

4. NO SLOTS ON 1 X 5 POSITION OR SMALLER PRODUCT. THE CENTER KEY SLOT WILL BE ON ALL HEADERS REGARDLESS OF SIZE.

5. TWO NON-CRITICAL SIDES OF PIN TIP NOT PLATED, BOTH ENDS

6. COMPANY LOGO MAY APPEAR IN THIS AREA.

7. THESE PRODUCTS MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.

8. PLATING OPTIONS:

PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT ON CONTACT OR TAIL, OPTIONALLY (78~295u"/2~7.5u) TIN ON TAIL.

9. "THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT ENVIRONMENTS."

10. FOR POLARIZATION, SPECIFY POSITION NUMBER (i.e. A03=ROW A POSITION 03) TO OMIT PIN.

OMIT FROM PRODUCT NUMBER IF THIS FEATURE IS NOT APPLICABLE.

PRODUCT MANAGEMENT APPROVAL REQUIRED PRIOR TO RELEASE OR SALE OF POLARIZED PRODUCT.

mat'l. code		surface ☒ ISO 1302 ☐ ISO 406 ☐ ISO 1101		tolerance		projection		product family	
ltr		ecn no		dr		date		title	
U								FRICION LATCH HEADER	
				angles		linear		INCH/MM	
				0°±2°		XXX±.01/XX±.03		scale 4:1	
				dr		M.CLOUSER 11/27/90		dwg no	
				enrg		C.TREXTLER 11/27/90		sheet 2 of 4	
				chr		C.TREXTLER 11/27/90		size	
				appd		C.TREXTLER 11/27/90		A3	
sheet		revision						type	
index		sheet						Product Customer Drawing	



FCIconnect.com

Copyright FCI

D

PRODUCT NUMBER	NO OF POS	DIM K	DIM L	TAIL LENGTH DIM M	POLARIZATION PIN POSITION	
69167-X43	1 X 3	.300/7.62	.200/5.08	.190/4.83		
69167-X44	1 X 4	.400/10.16	.300/7.62	.190/4.83		
69167-X45	1 X 5	.500/12.70	.400/10.16	.190/4.83		
69167-X46	1 X 6	.600/15.24	.500/12.70	.190/4.83		
69167-X47	1 X 7	.700/17.78	.600/15.24	.190/4.83		
69167-X48	1 X 8	.800/20.32	.700/17.78	.190/4.83		
69167-X49	1 X 9	.900/22.86	.800/20.32	.190/4.83		
69167-X50	1 X 10	1.000/25.40	.900/22.86	.190/4.83		
69167-X51	1 X 11	1.100/27.94	1.000/25.40	.190/4.83		
69167-X52	1 X 12	1.200/30.48	1.100/27.94	.190/4.83		
69167-X53	1 X 13	1.300/33.02	1.200/30.48	.190/4.83		
69167-X54	1 X 14	1.400/35.56	1.300/33.02	.190/4.83		
69167-X55	1 X 15	1.500/38.10	1.400/35.56	.190/4.83		
69167-X56	1 X 16	U N A V A I L A B L E				
69167-X57	1 X 17	U N A V A I L A B L E				
69167-X58	1 X 18	U N A V A I L A B L E				
69167-X59	1 X 19	U N A V A I L A B L E				
69167-X60	1 X 20	U N A V A I L A B L E				
69167-X61	1 X 21	U N A V A I L A B L E				
69167-X62	1 X 22	U N A V A I L A B L E				
69167-X63	1 X 23	U N A V A I L A B L E				
69167-X64	1 X 24	U N A V A I L A B L E				
69167-X65	1 X 25	U N A V A I L A B L E				
69167-X66	1 X 26	U N A V A I L A B L E				
69167-X67	1 X 27	U N A V A I L A B L E				
69167-X68	1 X 28	U N A V A I L A B L E				
69167-X69	1 X 29	U N A V A I L A B L E				
69167-X70	1 X 30	U N A V A I L A B L E				
69167-X71	1 X 31	U N A V A I L A B L E				
69167-X72	1 X 32	U N A V A I L A B L E				
69167-X73	1 X 33	U N A V A I L A B L E				
69167-X74	1 X 34	U N A V A I L A B L E				
69167-X75	1 X 35	U N A V A I L A B L E				
69167-X76	1 X 36	U N A V A I L A B L E				
69167-X77	1 X 10	1.000/25.40	.900/22.86	.120/3.05		2/3/5/6/8/9
69167-X78	1 X 4	1.000/25.40	.900/22.86	.120/3.05		2/3

mat'l. code				surface ISO 1302 ☒		tolerance ISO 406 ISO 1101		projection 		product family HEADER	
ltr		ecn no		dr		date		tolerances unless otherwise specified		title	
U								angles linear XX±.01/XX±.03 XXX±.005/XXX±0.13 XXXX±.0020/XXX±0.05		INCH/MM scale 4:1	
								dr		M.CLOUSER 11/27/90	
								enr		C.TREXTLER 11/27/90	
								chr		C.TREXTLER 11/27/90	
								appd		C.TREXTLER 11/27/90	
sheet index		revision sheet								type Product Customer Drawing	