


HDM40216L

Dimensional Drawing

40 Character x 2 Lines, LED Backlight



Dimension tolerance: +/- 0.3mm

(-1) = Thick version

Features

Character Format 5x7 Dots with Cursor
Backlight..... White or Yellow LED
Options..... TN/Gray STN/Yellow STN, FSTN
12 o'Clock/6 o'Clock View
Normal/Extended Temperature
Normal/Negative Displays

Physical Data

Module Size 182.0W x 33.5H x 13.0T mm
Thick version..... 182.0W x 33.5H x 15.0T mm
Viewing Area Size..... 154.4W x 15.8H mm
Weight..... 70g


Absolute Maximum Ratings

PARAMETER	SYMBOL	MIN	MAX	UNIT
SUPPLY VOLTAGE	$V_{DD}-V_{SS}$	0	7.0	V
SUPPLY VOLTAGE FOR LCD	$V_{DD}-V_L$	0	13.5	V
OPERATING TEMPERATURE	T_{OP}	0	50	°C
STORAGE TEMPERATURE	T_{STG}	-20	70	°C
LED FORWARD CURRENT (White)	I_F	-	50	mA
(Yellow)		-	700	
LED REVERSE VOLTAGE (White)	V_R	-	5	V
(Yellow)		-	8	
LED POWER CONSUMPTION (White)	P_D	-	200	mW
(Yellow)		-	3200	

Electrical Characteristics (VDD=5.0±0.25V 25°C)

PARAMETER	SYM	CONDITION	MIN	TYP	MAX	UNIT
POWER SUPPLY CURRENT	I _{DD}	V _{DD} =5.0V	-	1.73	3.0	mA
POWER SUPPLY FOR LCD	V _{DD} -V _L	T _A =25°C	4.2	4.7	5.2	V
LED FORWARD Vtg (White)	V _F	I _F =40mA	3.0	3.3	3.6	V
(Yellow)		I _F =360mA	4.0	4.2	4.6	
BRIGHTNESS (White LED)	L	I _F =40mA	-	135	-	cd/m ²
(Yellow LED)		I _F =360mA	-	90	-	
DRIVE METHOD	1/16 Duty					

Block Diagram



Pin Connections

PIN NO.	SYMBOL	LEVEL	FUNCTION
1	V_{SS}	-	0V
2	V_{DD}	-	5V
3	V_L	-	-
4	RS	H/L	H: Data input L: Instruction data input
5	R/W	H/L	H: Data read L: Data write
6	E	H, H->L	Enable signal
7	D0	H/L	Data bus
8	D1	H/L	
9	D2	H/L	
10	D3	H/L	
11	D4	H/L	
12	D5	H/L	
13	D6	H/L	
14	D7	H/L	
15	A	-	Anode for LED backlight
16	K	-	Cathode for LED backlight

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hantronix:](#)

[HDM40216L-1-L30S](#)