

SmartOnline 6kVA On-Line Double-Conversion UPS, 6U Rack/Tower, 200-240V Hardwire output

MODEL NUMBER: **SU6000RT3UHVXL**



Description

Tripp Lite Smart Online UPS systems offer high performance power protection ideal for critical server and network equipment in data centers, computer rooms and network closets. Online, double-conversion Uninterruptible Power Supply (UPS) maintains perfectly regulated output power by continuously converting raw AC input to DC, then re-converting output back to AC. Fully regulated sine wave AC output with $\pm 2\%$ voltage regulation powers network equipment continuously, even during severe brownouts and overvoltages, all without depleting UPS battery reserves. Maintains battery-derived AC output during power failures with zero transfer time. Extended runtime options available. Interactive LCD interface reports UPS operating mode, detailed UPS and site-power data, plus enables a variety of UPS setup and configuration options. Highly efficient operation in optional economy mode saves BTU heat output and energy costs. Network management interfaces support communications via RS-232, contact-closure and optional SNMP WEB CARD network interface. Built-in DB9 port offers both enhanced RS-232 data and basic contact closure monitoring ability. Includes PowerAlert monitoring software and complete cabling. Emergency Power Off (EPO) interface. LED display reports UPS operating mode, line power availability, battery mode operation, inverter operation, ECO mode status and output power availability. Audible alarm with push-button momentary alarm-cancel and silent-mode LCD configuration options. Programmable self-test. Fault-tolerant auto-bypass mode. Field-replaceable, hot-swappable internal batteries and external battery packs.

Features

- True on-line, double conversion UPS provides pure, sine wave AC output at all times
- World-wide compatibility with Euro 50Hz and High Voltage North American 60Hz power
- Maintains continuous operation through blackouts, voltage fluctuations and surges with zero transfer time
- Removes harmonic distortion, electrical impulses, frequency variations and other hard to solve power problems
- 6000VA/4200 watt power capacity with hardwire input/output connections
- Accepts input voltages between 156 and 276, regulating output within 2% of selectable 200/208/220/230/240V AC output
- 30 minutes runtime at half load (2100W) / 12 minutes at full load (4200W) with included BP240V10RT3U external battery pack
- Expandable runtime with multiple external battery packs

Highlights

- 6000VA / 6kVA / 4200W on-line double-conversion UPS
- 200/208/220/230/240V 50/60Hz output, Economy mode option
- 6U Rack/Tower compatible; Hot-swappable battery modules
- RS232 & EPO ports; support for SNMP/WEB card options
- Front panel LEDs with detailed LCD monitoring and control screen
- Ships with high capacity BP240V10RT3U battery pack
- Hardwire input (3 wire); Hardwire output

Package Includes

- SU6000RT3UPM 3U UPS Power Module
- BP240V10RT3U 3U external battery pack
- PowerAlert UPS management software and complete cabling
- Mounting hardware to support each 3U module in 4 post rack enclosures
- 2-9U STAND tower stand set
- Warranty information
- Instruction manual



- Innovative design makes unit adaptable for rackmount, tower, or stacking applications
- Power module and battery pack require only 3 rack spaces each (6U total rack space usage)
- DB9 serial port for network interface; SNMP compatible
- Slot for optional SNMP/web card (part# SNMPWEBCARD)
- PowerAlert unattended shutdown software and 6 ft. network cable included
- Fault tolerant electronic bypass maintains utility output during a variety of UPS fault conditions
- Diagnostic LEDs
- Mounting hardware included with each 3U module for 4 post rackmount installation, 2 post telecom rack compatible with separate purchase 2POSTRMKITWM (2 required)
- Includes RJ11 EPO (emergency power off) port and interconnection cable
- \$250,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

General Info	
Product Group	UPS SYSTEMS
OUTPUT	
Output Volt Amp Capacity (VA)	6000
Output kVA Capacity (kVA)	6
Output Watt Capacity (Watts)	4200
Output kW Capacity (kW)	4.2
Power Factor	0.7
Crest Factor	3:1
Nominal Output Voltage(s) Supported	200V; 208V; 220V; 230V; 240V
Nominal Voltage Details	Voltage selection via front panel LCD interface
Frequency Compatibility	50 / 60 Hz
Frequency Compatibility Details	Output frequency matches input nominal on startup
Output Voltage Regulation (Line Mode)	+/- 2%
Output Voltage Regulation (Economy Line Mode)	+/- 10%
Output Voltage Regulation (Battery Mode)	+/- 2%
UPS Output Receptacles	Hardwire
Output Receptacle Backplate Options	Optional SUPDM11 backplate adds 2 L6-30R outlets and L6-30P input cord
Output Circuit Breakers	40A double-pole
Output AC Waveform (AC Mode)	Sine wave



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Output AC Waveform (Battery Mode)	Pure Sine wave
INPUT	
Rated input current (Maximum Load)	30A
Nominal Input Voltage(s) Supported	200V AC; 208V AC; 220V AC; 230V AC; 240V AC
UPS Input Connection Type	Hardwire
UPS Input Connection Description	3 wire single phase input (L1, L2, G); optional, country-specific SUPDM11 backplate adds 2 L6-30R outlets and L6-30P input cord
Input Circuit Breakers	40A double-pole
Recommended Electrical Service	30A 208/220/230/240V
Input Phase	Single-Phase
BATTERY	
Full Load Runtime (min.)	12 min. (4200w)
Half Load Runtime (min.)	30 min. (2100w)
Expandable Battery Runtime	Includes one expandable BP240V10RT3U external battery pack; built-in daisychain throughput connected supports the connection of multiple additional BP240V10RT3U external battery packs
External Battery Pack Compatibility	BP240V10RT3U
DC System Voltage (VDC)	240
Battery Recharge Rate (Included Batteries)	Less than 6 hours from 10% to 80% (typical, full load discharge)
Battery Replacement Description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage Regulation Description	Online, double-conversion power conditioning
Overvoltage Correction	2% output voltage regulation during overvoltages to 276
Undervoltage Correction	2% output voltage regulation during undervoltages to 156
LEDS ALARMS & SWITCHES	
LED Indicators	6 LEDs indicate line power, online mode, economy/bypass mode, on-battery, charger and AC output status; LCD screen offers additional information and control options
Front Panel LCD Display	Selectable LCD display with scroll and selection buttons enables UPS control and detailed monitoring options; LED/LCD panel rotates for viewing in rack/tower formats (see manual)
Audible Alarm	Unique audible alarms for all major UPS, environmental and power conditions (see manual)
Alarm Cancel Operation	Alarm cancel switch
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation; 2 additional switches support set and execute scrolling LCD functions
SURGE / NOISE SUPPRESSION	



UPS AC Suppression Joule Rating	480
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Included Mounting Accessory Description	2 sets of adjustable 4 post rack rails included
Installation Form Factors Supported with Optional Accessories	2 post rackmount (2POSTRMKITWM)
Optional Mounting Accessory Notes	2 sets of 2POSTRMKITWM required for 2 post rackmount installation of separate power module and battery pack
Primary Form Factor	Rackmount
UPS Power Module Dimensions (hwd, in.)	5.2 x 17.5 x 26
UPS Power Module Dimensions (hwd, cm)	13.3 x 44.4 x 66
Installed Whole System Maximum Rack Depth (in.)	26
Installed Whole System Maximum Rack Depth (cm)	66
Rack Height	6U
Secondary Form Factor	Tower (requires 2-9USTAND)
UPS Power Module Weight (lbs.)	43.8
UPS Power Module Weight (kg)	19.9
UPS Dimensions Details	Includes 3U power module and 3U battery pack
Included Battery Pack Dimensions (hwd / in.)	5.2 x 17.5 x 25
Included Battery Pack Dimensions (hwd / cm)	13.3 x 44.4 x 63.5
Included Battery Pack Weight (lbs.)	136.5
Included Battery Pack Weight (kg)	62
UPS Shipping Dimensions (hwd / in.)	27.5 x 40 x 48
UPS Shipping Dimensions (hwd / cm)	69.9 x 101.6 x 121.9
Shipping Weight (lbs.)	323
Shipping Weight (kg)	146.6
Cooling Method	Fan
UPS Housing Material	Steel



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius.
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius.
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	1412.3
AC Economy Mode BTU / Hr. (Full Load)	911.5
Battery Mode BTU / Hr. (Full Load)	1586.7
AC Mode Efficiency Rating (100% Load)	91%
AC Economy Mode Efficiency Rating (100% Load)	94%
Audible Noise	60 dBA at front side 1 meter
COMMUNICATIONS	
Communications Interface	DB9 Serial; Contact closure; EPO (emergency power off); Slot for SNMP/Web interface
Network Monitoring Port Description	RS232 and contact closure communications are located on two separate DB9 ports
PowerAlert Software	Included
Communications Cable	DB9 cable included
LINE / BATTERY TRANSFER	
Transfer Time	No transfer time (0 ms.) in online, double-conversion mode
Low Voltage Transfer to Battery Power (Setpoint)	156
High Voltage Transfer to Battery Power (Setpoint)	276
SPECIAL FEATURES	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Automatic inverter bypass; Hot swappable batteries
Green Energy-Saving Features	High efficiency economy mode operation; Schedulable daily hours of economy mode operation
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); CE; Tested to GOST (Russia); Tested to SASO (Saudi Arabia); Tested to IRAM (Argentina); Meets FCC Part 15 Category A (EMI); ROHS (Restriction of Hazardous Substances)
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	2-year limited warranty
-------------------------------------	-------------------------

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.