





1. MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOKTM PLUG.
2. RECOMMENDED PANEL THICKNESS 0.76 – 2.29.
3. PANEL MUST BE PUNCHED SO THAT THE HOUSING ENTERS THE PANEL IN THE SAME DIRECTION AS THE PUNCH.
4. OPTIONAL FOR KEYING HOUSING IN PANEL.
5. CIRCUIT NUMBER 1 LOCATION.
6. DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION. ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.
7. FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION. NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.
8. UNDERWRITERS RECOGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE EACH ON SIDE OF HOUSING.



DETAIL A
OPTIONAL CONSTRUCTIONS



3-DIMENSIONAL MODEL
NTS

6.35	.250	—	—
4.45	.175	27.43	1.080
2.79	.110	26.16	1.030
2.54	.100	25.91	1.020
2.29	.090	20.70	.815
0.76	.030	20.32	.800
0.38	.015	12.19	.480
0.25	.010	8.13	.320
0.13	.005	6.99	.275
MM	IN	MM	IN

CONVERSION TABLE

THIS DRAWING IS A CONTROLLED DOCUMENT.		D/W K. WHITAKER 17JUN92	NAME TE Connectivity									
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: R. SWING 17JUN92										
<table border="1"> <tr> <td>0 PLC</td> <td>± -</td> </tr> <tr> <td>2 PLC</td> <td>± -</td> </tr> <tr> <td>3 PLC</td> <td>± -</td> </tr> <tr> <td>4 PLC</td> <td>± 0.38</td> </tr> <tr> <td>5 PLC</td> <td>± - 10°</td> </tr> </table>		0 PLC	± -	2 PLC	± -	3 PLC	± -	4 PLC	± 0.38	5 PLC	± - 10°	APVO D. SELF
0 PLC	± -											
2 PLC	± -											
3 PLC	± -											
4 PLC	± 0.38											
5 PLC	± - 10°											
		PRODUCT SPEC	CAP.9 CIRCUIT, UNIVERSAL MATE-N-LOK(TM)									
		APPLICATION SPEC										
MATERIAL NYLON,UL 94V-0		SIZE CAGE CODE DRAWING NO A1 00779 C 350782	RESTRICTED TO									
FINISH		WEIGHT	—									
REVISIONS		CUSTOMER DRAWING	SCALE 4:1 SHEET 1 OF 1 REV V4									