

NUMBER
201609


USED ON

PRINT DIST. 47
DIMENSIONS IN INCHES. DO NOT SCALE PRINT
PROPOSAL NO

NOTES:


1 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	201609-1	1. AS SHOWN.
OBSOLETE	201609-2	1. SAME AS -1 EXCEPT; 2. FINISH OF ITEM #1, SILVER OVER NICKEL
OBSOLETE	201609-3	1. SAME AS -1 EXCEPT; 2. FINISH OF ITEM #1, .0001 MIN GOLD OVER .0001 MIN SILVER
OBSOLETE	201609-4	1. SAME AS -1 EXCEPT; 2. MTD ON TAPE.
	201609-5	1. SAME AS -1 EXCEPT; 2. FINISH -.000050 MIN GOLD OVER .000050 MIN NICKEL.
OBSOLETE	201609-6	1. SAME AS -5 EXCEPT; 2. MTD ON TAPE.



ITEM #1
SOCKET BODY
COPPER ALLOY
.00003 MIN GOLD OVER
.00005 MIN NICKEL

WHEN ORDERING CONTACT ON TAPE, ORDER BY THE TAPE NUMBER PLUS THE PACKAGING CODE AS FOLLOWS:
1. FOR USE WITH AMP TAPETRONIC, PNEUMATIC TOOL -
A. 1000 PARTS TO A BOX ADD PACKAGING CODE: 1MBOX
2. FOR USE WITH 4/8 INDENT STRIPPER CRIMPER -
A. 1000 PARTS TO A REEL ADD PACKAGING CODE: 1MREEL
B. 5000 PARTS TO A REEL ADD PACKAGING CODE: 5MREEL



TAPE MTD ASS'Y
201609-4 AND
201609-6 ONLY.

TOLERANCES
EXCEPT AS NOTED
DECIMALS: ± .008
FRACTIONS: ± 1/64
ANGLES: ± 1/2°

© 1961 BY AMP INCORPORATED
AMP PRODUCTS COVERED BY PATENTS
AND/OR PATENTS PENDING

MATERIAL SEE CALL OUT	DR J. Kaufman 12-1-61	ENGR J. B. M. 12-5-61
HEAT TREAT -H-	CHK G. L. Williams 12-5-61	APP J. B. M. 12-5-61
FINISH SEE CALL OUT	AMP AMP INCORPORATED HARRISBURG, PENNA.	
NAME #20 SOCKET CONTACT ASS'Y WIRE SIZE 28-24-.035-.055 INS. DIA.		
SCALE 10:1	LOC FT B	NO 201609
		REV P1

CUSTOMER DRAWING