







SECTION A-A



- NOTES
- 1 SWITCH SEALED PER MIL-PRF-8805, SYMBOL 4
 - 2 PRINT CIRCUIT DIAGRAM, CATALOG LISTING, DATE CODE, FEDERAL MANUFACTURING CODE AND CUSTOMER PART NUMBER 13212969 ON NAMEPLATE
 - 3 RECEPTACLE PART NUMBER MS27468T9B35P
 - 4 ENCLOSURE: CONVERSION COAT PER MIL-C-5541, CLASS 1A (ALODINE). APPLY PAINT IN ACCORDANCE WITH MIL-C-53039A AND COLOR NUMBER 34094 (FOREST GREEN)
 - 5 ENCLOSURE UNSEALED
 - 6 SWITCH IS TYPE "HS" SELF ADJUSTING, TECHNICAL BROCHURE FOR INFORMATION
 - 7 3X M6-1.0 INTERNAL THREADED HELICOIL, SEE "BACK VIEW SIDE" FOR LOCATION
 - 8 - LEVER PRETRAVEL = $2^{\circ} \pm 1^{\circ}$
 - 9 CABLE, SWITCH AND BACKSHELL, CABLE INTERFACE COVERED WITH HEAT SHRINK IAW M23053/4, CLASS 3 HEAT SHRINK
 - 10 6X LEAD WIRES PER M22759/16-22 GAGE, DOUBLE SHIELDED PER QQ-B-575 GROUNDED TO SWITCH HOUSING AND ENCASED IN HEAT SHRINK PER M23053/1, CLASS 2
 - 11 - SHIELD, SWITCH HOUSING, AND BACKSHELL TERMINATIONS: 2.5m OHMS UNDER 0.10 AMP LOAD EACH JOINT

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

CHARACTERISTICS		ELECTRICAL DATA	
PRETRAVEL		CONTACT ARRANGEMENT	
OPERATING FORCE		2X S P D T GOLD	
TOTAL TRAVEL		LOAD AMPS	28 VDC AT SEA LEVEL
CLICK DISTANCE		RESISTIVE	1 AMP
RELEASE FORCE		INDUCTIVE	1/2 AMP
ACTUATOR FORCE			

THIRD ANGLE PROJECTION	
SCALE	NONE
DO NOT SCALE PRINT	
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
ONE PLACE	(.0) ±.030
TWO PLACE	(.00) ±.015
THREE PLACE	(.000) ±.005
ANGLES	± 4°
WEIGHT	