



HONEYWELL
PART NUMBER

12SX22

PRODUCT CODE
VDK1200JG-NUMBER
JG-81322

REV	DOCUMENT	CHANGED BY	CHECK
7	0038449	VS 28APR08	BLR



NOTES

- (1) MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .188±.002 CENTERS
2 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F
3 - MOVABLE CONTACT MATERIAL - 24K SOLID GOLD
4 - STATIONARY CONTACT MATERIAL - GOLD ALLOY
5 - TERMINALS ARE SOLDER DIPPED WITH RoHS-COMPLIANT TIN/COPPER/SILVER SOLDER
(6) .035^{+.002}_{-.001} DIA PRIOR TO SOLDER COATING

RELEASE NO.	PR-14211
REPLACES	X82907-SX

CHARACTERISTICS

OPERATING FORCE - - - - 5 OZ MAX

RELEASE FORCE - - - - - 1 OZ MIN

DIFFERENTIAL TRAVEL - - - .003 MAX

OVERTRAVEL - - - - - .004 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
SPDT

30 VOLTS DC RATING

	SEA LEVEL	50,000 FT
INDUCTIVE	0.5 AMP	0.5 AMP
RESISTIVE	1 AMP	1 AMP

MAXIMUM INRUSH 2 AMP

APPROVALS	KEMA, CE	1A 250 V ~ T125 25E3	CE
	UL, CSA	1A 125 VAC	UL

DESIGN UNITS: INCH

TOLERANCES UNLESS NOTED:

NO PLACE	X	±
ONE PLACE	.X	±
TWO PLACE	.XX	±
THREE PLACE	.XXX	±
FOUR PLACE	.XXXX	±
ANGLES		±

THIRD ANGLE PROJECTION



DRAWN	SPK	14FEB08
CHECK	RJ	14FEB08
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		

RASTER

Honeywell

TITLE

SWITCH - BASIC

SIZE	TYPE	DRAWING NAME	REV
B	I	12SX22	7
SCALE	-	WEIGHT:.003 LB MAX	SHEET 1 OF 1