




Features

- Economical method of storing static sensitive electronics devices
- Wide choice of sizes
- Shipped knocked-down; easy to assemble



Item No.	Size O.D. - L x W x D
37100	5-3/4 x 3-3/4 x 2-11/16
37101	9 x 4 x 4-1/2
37102	12 x 2 x 4-1/2
37103	12 x 4 x 4-1/2
37104	12 x 6 x 4-1/2
37105	12 x 8 x 4-1/2
37106	12 x 12 x 4-1/2
37115	18 x 2 x 4-1/2
37107	18 x 4 x 4-1/2

Item No.	Size O.D. - L x W x D
37108	18 x 6 x 4-1/2
37109	18 x 8 x 4-1/2
37110	18 x 12 x 4-1/2
37117	24 x 12 x 6-3/8
37116	24-3/4 x 2-1/4 x 4-1/2
37111	24-3/4 x 4-1/4 x 4-1/2
37112	24-3/4 x 6-1/4 x 4-1/2
37113	24-3/4 x 8-1/4 x 4-1/2
37114	24-3/4 x 12 x 4-1/2

Meets the required limits of ANSI/ESD S20.20, and Packaging standard ANSI/ESD S541.

SPECIFICATIONS

Properties

Surface Resistance

Sloughing Test

Recyclability

Typical Values

1×10^6 to $< 1 \times 10^9$ ohms

Negligible surface damage at 10 cycles and <5% of surface damage at 200 cycles in Taber Abrasion Test.

No conductive particles abraded from surface

Complete recyclability of package

Test Procedures/Method

ANSI/ESD STM11.11

ASTM D4060 at 70 rpm with CS-17 abrasive-coated wheels and 1000 grams load

Rockwell International Test Report of January 8, 1992

Rockwell International Test Report of January 8, 1992

RoHS 2, REACH, and Conflict Minerals Statement

None of the RoHS 2 restricted materials, or REACH substances of very high concern as of 2015/06/15, or Conflict Minerals are intentionally added in manufacturing this product. Ref: European Union Directive 2011/65/EU and Regulation (EC) No. 1907/2006/CE. See Protektive Pak [terms and conditions](#).

Specifications and procedures subject to change without notice



Made in the
United States of America

Unless otherwise noted, tolerance is $\pm 10\%$

PROTEKTIVE PAK
BURIED SHIELDING LAYER

OPEN BIN BOXES

PROTEKTIVE PAK
13520 MONTE VISTA AVENUE, CHINO, CA 91710
PHONE (909) 627-2578
ProtektivePak.com

DRAWING NUMBER
37100

DATE:
December
2024