


Line Filters and Connectors


AC Power Inlet with Fuseholder



Series 4707 for "cold" connections 70°C, protection Class 1 (with ground pin). Terminals are 6.3 × 0.8 mm or 4.8 × 0.8 mm quick-connect or solder. Approved by UL, CSA, and VDE up to 10 amps 250 volt.

Stock No.	Mfr.'s Type	Mounting	Fusing	Terminals	D × H × W (mm)	EACH	
						1-24	25-Up
509-2001	4707.1000	Screw-on	1-pole	Quick-connect, 6.3 × 0.8 mm	41.0 × 34 × 44	16.02	11.64
509-2005	4707.2000	Screw-on	1-pole	Quick-connect, 6.3 × 0.8 mm	41.0 × 34 × 44	16.02	11.64
509-2011	4707.2100	Screw-on	2-pole	Quick-connect, 4.8 × 0.8 mm	31.7 × 34 × 44	16.02	11.64
509-2011	4707.1300	Screw-on	2-pole	Solder	37.6 × 34 × 44	16.02	11.64
509-2013	4707.2300	Screw-on	2-pole	Solder	37.6 × 34 × 44	16.02	11.64


AC Line Filter with AC Inlet



Series 5110 for "cold" connections 65°C, protection class I. Terminals are 6.3 × 0.8 mm quick-connect. Screw-on or snap-in panel mounting. Approved up to 15 A/250 V.

Stock No.	Mfr.'s Type	Fig.	Mounting	Filter (Amps)	Leakage Current	D × H × W (mm)	EACH	
							1-24	25-Up
509-3200	5110.0132.1	1	Screw-on	1 A Standard	<0.5 mA	55 × 21 × 48	11.61	10.08
509-3202	5110.0333.1	1	Screw-on	3 A Standard	<0.5 mA	55 × 21 × 48	11.61	10.08
509-3204	5110.0633.1	1	Screw-on	6 A Standard	<0.5 mA	55 × 21 × 48	11.61	10.08
509-3205	5110.0833.1	1	Screw-on	8 A Standard	<0.5 mA	55 × 21 × 48	11.61	10.08
509-3208	5110.1033.1	1	Screw-on	10 A Standard	<0.5 mA	55 × 21 × 48	11.61	10.08
509-3210	5110.1533.1	1	Screw-on	15 A Standard	<0.5 mA	55 × 21 × 48	11.61	10.08
509-3212	5110.0143.1	1	Snap-in	1 A Standard	<0.5 mA	55 × 21 × 48	11.61	10.08
509-3214	5110.0343.1	2	Snap-in	3 A Standard	<0.5 mA	55 × 21 × 36	11.61	10.08
509-3216	5110.0643.1	2	Snap-in	6 A Standard	<0.5 mA	55 × 21 × 36	11.61	10.08
509-3218	5110.0843.1	2	Snap-in	8 A Standard	<0.5 mA	55 × 21 × 36	11.61	10.08
509-3219	5110.1043.1	2	Snap-in	10 A Standard	<0.5 mA	55 × 21 × 36	11.61	10.08
509-3221	5110.1543.1	2	Snap-in	15 A Standard	<0.5 mA	55 × 21 × 36	11.96	10.38
509-3222	5110.0133.3	1	Screw-on	1 A Medical	<0.0 μA	55 × 21 × 48	11.61	10.08
509-3224	5110.0333.3	1	Screw-on	3 A Medical	<0.0 μA	55 × 21 × 48	11.61	10.08
509-3226	5110.0633.3	1	Screw-on	6 A Medical	<0.0 μA	55 × 21 × 48	11.61	10.08
509-3228	5110.0833.3	1	Screw-on	8 A Medical	<0.0 μA	55 × 21 × 48	11.61	10.08
509-3229	5110.1033.3	1	Screw-on	10 A Medical	<0.0 μA	55 × 21 × 48	16.21	14.06
509-3232	5110.1533.3	1	Screw-on	15 A Medical	<0.0 μA	55 × 21 × 48	11.61	10.08
509-3234	5110.0143.3	2	Snap-in	1 A Medical	<0.0 μA	55 × 21 × 36	11.61	10.08
509-3236	5110.0343.3	2	Snap-in	3 A Medical	<0.0 μA	55 × 21 × 36	11.61	10.08
509-3238	5110.0643.3	2	Snap-in	6 A Medical	<0.0 μA	55 × 21 × 36	11.61	10.08
509-3240	5110.0843.3	2	Snap-in	8 A Medical	<0.0 μA	55 × 21 × 36	11.61	10.08
509-3242	5110.1043.3	2	Snap-in	10 A Medical	<0.0 μA	55 × 21 × 36	11.96	10.38
509-3244	5110.1543.3	2	Snap-in	15 A Medical	<0.0 μA	55 × 21 × 36	11.61	10.08

High Current Line Filter — 20 A



Series C20F for cold connections 65°C, Protection Class I. Screw mount, solder/quick connect terminals 6.3 × 0.8 mm. RFI filter in medical or standard. UL, CSA approved 20 A/125V. VDE approved 16 A/250 V.

Stock No.	Mfr.'s Type	Filter (Amps)	Leakage Current	D × H × W (mm)	EACH	
					1-24	25-Up
509-5070	C20F.0001	20 A / 16A Standard	<0.5 mA	80.8 × 53 × 30	22.17	18.14
509-5070	C20F.0002	20 A / 16A Medical	<5.0 μA	80.8 × 53 × 30	22.17	18.14

509-5074. 0888.0220. Cordset; C19 plug mates to C20 inlet; NEMA 5-15P end. 1-24...
25-Up..... EACH 24.29
EACH 19.43

Check Pricing And Availability Of All Items On The Internet At www.alliedelec.com

ALLIED ► 757


Filtered AC Inlet/Circuit Breaker for Equipment



Series PEM 45 power entry module combines an AC inlet, circuit breaker for equipment, and optional RFI filter. The circuit breaker provides manual reset of the circuit, 1 or 2-pole thermal overload protection, or no bi-metal for on/off switching only (white switch I/O embossed lettering). Optional undervoltage release. Approved by UL, CSA up to 15 amps at 125 and 250 volt, and VDE up to 10 amps 250 volt.

Stock No.	Mfr.'s Type	Fig.	Overload Protection	Rated Current CBE/Filter	Leakage Current	D × H × W (mm)	EACH	
							1-24	25-Up
509-3246	5-ABTWFO50CO-511	3	1-pole	5 A/6 A	<0.5 mA	51.7 × 91.5 × 36	26.34	18.17
509-3248	5-ABTWFO50CO-531	3	1-pole	5 A/15 A	<0.5 mA	51.7 × 91.5 × 36	18.71	
509-3250	5-ABTWFO50CO-531	3	1-pole	5 A/6 A	<0.5 μA	51.7 × 91.5 × 36	26.34	18.17
509-3252	5-ABTWFO50CO-831	3	1-pole	15 A/15 A	<0.5 μA	51.7 × 91.5 × 36	29.66	20.46
509-3254	5-ABDWFO50CO-511	3	2-pole	5 A/5 A	<0.5 mA	51.7 × 91.5 × 36	29.66	20.46
509-3256	5-ABDWFO50CO-811	3	2-pole	15 A/15 A	<0.5 mA	51.7 × 91.5 × 36	29.66	20.46
509-3260	5-ABDWFO50CO-831	3	2-pole	15 A/15 A	<0.5 μA	51.7 × 91.5 × 36	30.55	21.07

AC Line Filters with Fuseholders



Series KFA for cold connections 65°C, Protection Class I. Quick connect terminals 6.3 × 0.8 mm. Available 2 pos. voltage selector 115/230 or without and with medical or standard RFI filter. Approved up to 10 A/250 V. Fusedrawers ordered separately below.

Stock No.	Mfr.'s Type	Fig.	Fusing	Voltage Selector	Filter (Amps)	Leakage Current	D × H × W (mm)	EACH	
1-24	25-Up								

<tbl_r cells="10" ix="5" max