

ADAPTERS, BETWEEN-SERIES

Type N / 2.4mm, DC - 18 GHz

SPECIFICATIONS:

Models: 5155, 5156, 5157, 5158

RoHS
Compliant

AEROFLEX
A passion for performance.

Electrical:



Frequency Range _____ DC - 18.0 GHz
VSWR _____ 1.15:1 Max.
Impedance _____ 50 Ohms
Operating Temp Range _____ -65°C to +125°C

Mechanical:

Connectors _____ Passivated Stainless Steel
Mates with MIL-STD-348
Conductors _____ Gold Plated Beryllium Copper



Model Number: **5155**
Type N Female to 2.4mm Male

Model Number: **5156**
Type N Female to 2.4mm Female



Model Number: **5157**
Type N Male to 2.4mm Male

Model Number: **5158**
Type N Male to 2.4mm Female



Note: Dimensions in Brackets are Expressed in Millimeters and are for Reference Only.

5155: REV C

AEROFLEX
INMET

Aeroflex / Inmet, Inc. • 300 Dino Drive, Ann Arbor, MI 48103 • U.S.A.
888-244-6638 or 734-426-5553 • FAX: 734-426-5557
www.aeroflex.com/inmet • inmetsales@aeroflex.com