

## SAC-5P-10,0-PUR/AD-2L

Order No.: 1435111



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1435111>

Sensor/Actuator cable, 5-position, PUR, halogen-free, Black RAL 9005, Free conductor end, on Valve plug A (pressure switch), with 2 LEDs, Cable length: 10 m

Commercial data	
GTIN (EAN)	4046356413473
sales group	D113
Pack	1 pcs.
Customs tariff	85444290
Weight/Piece	0.4505 KG
Catalog page information	Page 106 (PC-2009)

### Product notes

WEEE/RoHS-compliant since:  
01/08/2009



<http://www.download.phoenixcontact.com>  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data	
<b>General data</b>	
Rated current at 40°C	4 A
Rated voltage	24 V
Number of positions	5
Volume resistance	≤ 5 mΩ

Insulation resistance	≥ 100 MΩ
Length of cable	10 m
Stripping length of the free conductor end	50 mm
Ambient temperature (operation)	-20 °C ... 85 °C (valve plug)

#### General characteristics

Surge voltage category	III
Pollution degree	3
Degree of protection	IP65/IP67
Contact material	CuSn
Contact surface material	Sn
Valve plug contact insert material	PA 6
Material, housing, valve plug	TPU
Sealing material	TPU (Seal molded)
Status display	2 LEDs


#### Conductor data

Cable type	PUR halogen-free black
Cable type (abbreviation)	PUR
Cable abbreviation	Li9Y11Y-HF
Conductor cross section	0.5 mm <sup>2</sup>
AWG signal line	20
Conductor structure signal line	28x 0.15 mm
Core diameter including insulation	1.5 mm ±0.05 mm
External cable diameter	5.30 mm
Wire colors	Black 1, black 2, black 3, black 4, green/yellow
External sheath, color	Black-gray RAL 7021
Insulation resistance	≥ 20 MΩ*km
Conductor resistance	≤ 39 Ω/km
Nominal voltage, conductor	300 V
Test voltage, conductor	1200 V
Overall twist	5 cores, twisted
Outer sheath, material	PUR
Material conductor insulation	PP
Conductor material	Bare Cu litz wires
Smallest bending radius, fixed installation	26.5 mm


Number of bending cycles	4000000
Bending radius	45 mm
Traversing path	10 m
Traversing rate	3 m/s
Acceleration	10 m/s <sup>2</sup>
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -20 °C ... 80 °C (cable, flexible installation)
Special properties	Flexible cable conduit capable Silicone-free Free of substances which would hinder coating with paint or varnish
Flame resistance	in accordance with DIN UL-Style 20549
Halogen-free	in accordance with DIN VDE 0472 part 815
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	Highly resistant to acids, alkaline solutions and solvents hydrolysis and microbe resistant

### Diagrams/Drawings

#### Dimensioned drawing




Valve plug type AD




Valve connector, type AD, side view

Circuit diagram



Contact assignment of valve connector

Schematic diagram



Valve plug connector pin assignment, type AD

**Address**

PHOENIX CONTACT Ltd  
Halesfield 13  
Telford Shropshire TF7 4PG,GB  
Phone 01952 681 700  
Fax 01952 681 799  
<http://www.phoenixcontact.co.uk>



© 2010 Phoenix Contact  
Technical modifications reserved;