



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	ALUM. WIRE SIZE	COPPER PIGTAIL SIZE	WIRE STRIP LENGTH	DIMENSIONS			CAP COLOR
				C	L	O.D.	
BPC6-L	6 AWG	8 AWG		.88	2.45	.64	TAN
BPC4-L	4 AWG	6 AWG	1.00	.88	2.45	.64	
BPC2-L	2 AWG	4 AWG	1.00	.88	2.45	.64	
BPC1-X	1 AWG	3 AWG	1.00	1.00	2.58	.64	
BPC1/0-X	1/0AWG	2 AWG	1.25	1.25	3.33	.91	RED
BPC2/0-X	2/0AWG	1 AWG	1.25	1.25	3.33	.91	
BPC3/0-X	3/0AWG	1/0 AWG	1.25	1.38	3.45	.91	
BPC4/0-X	4/0AWG	2/0 AWG	1.25	1.38	3.45	.91	
BPC250-X	250 MCM	3/0 AWG	1.38	1.50	3.70	1.16	GREEN
BPC300-X	300 MCM	4/0 AWG	1.38	1.63	4.11	1.16	
BPC350-X	350 MCM	4/0 AWG	1.38	1.63	4.11	1.16	
BPC400-X	400 MCM	250 MCM	1.38	1.88	4.34	1.32	BLACK
BPC500-X	500 MCM	350 MCM	1.38	1.88	4.34	1.32	
BPC600-6	600 MCM	350 MCM	1.88	1.88	4.78	1.50	RED
BPC750-6	750 MCM	500 MCM	1.88	2.00	4.91	1.50	

NOTES:

1. BARREL MATERIAL: ALUMINUM A-A
OR ALUMINUM ALLOY 1100.
2. WIRE MATERIAL: HIGH CONDUCTIVITY GRADE,
STRANDED COPPER.
3. USER TO ASSEMBLE CONNECTORS
TO ALUMINUM STRANDED WIRE ONLY
4. OXIDE INHIBITING JOINT COMPOUND
PREFILLED IN EACH BARREL.
5. CONNECTOR UL LISTED, RATED FOR 90° C AND 600V.
OPERATION.INSULATING SLEEVES ARE TO BE
RATED FOR 90° C - 600V. OPERATION
6. INSULATING SLEEVE INCLUDED (EPDM)
7. PACKAGE QTY: -L=50
-X=10

COLOR CODED
PLASTIC CAP



LISTED
E52164

C41292_01

								PANDUIT CORP. TINLEY PARK, ILLINOIS			
01	9/08	JHNU	JHNU	REVISED COPPER PIGTAIL SIZE FOR BPC1-X: 3 AWG WAS 2 AWG				BI-METAL SPLICE			
00	1/01	EJS		DRAWING RELEASED							
REV	DATE	BY	CHK	DESCRIPTION	ECN #	SUP	PM	DRAWN BY EJS	CHK'D	SCALE NONE	DRAWING NO. C41292