

Panasonic
 ideas for life

1a1b/2a 8A polarized power
 relays

ST RELAYS



RoHS compliant

FEATURES

1. Even with small form factor, sensitive enough for direct IC- driving

The dimensions of this high-density 4-
 gap balanced armature are 31 mm ×
 14 mm × 11 mm 1.220 inch × .551 inch
 × .433 inch. Despite this small size,
 high sensitivity is achieved by a
 mechanism that incorporates high-
 efficiency polarized magnetic circuits
 along with our exclusive spring
 alignment method. With an minimum
 operating power of about 150 mW,
 nominal operating power of 240 mW,
 this relay can be directly driven by
 transistor or chip controllers.

2. High switching capability

High contact pressure, low contact
 bounce, and forced separation
 structure that radically improves
 resistance to contact welding
 (1 Form A 1 Form B type equivalent to
 TV-3). Strong against lamp inductive
 loads, maximum switching capacity
 has reached 3,040 VA (8A 380V AC).

3. High breakdown voltage – Optimal for control in 250 V power circuits

High breakdown voltage has been
 achieved. Between contacts and coil of
 3,750 Vrms; Surge breakdown voltage
 between coil and contact of 6,000 V,
 and between open contacts of 1,200
 Vrms mean that these relays are
 suitable even for 250 V power circuit
 control.

4. Improved stability

**Conforms to all types of safety
 standards.**

Insulating distance of more than 3 mm
 secured. Complies with Japan
 Electrical Appliance and Material
 Safety Law requirements for operating
 200 V power supply circuits, and
 conforms with UL, CSA and VDE
 standards.

5. Latching types available

In addition to single side stable types,
 convenient 2 coil latching types with
 memory functions are also available.
 Moreover, we offer 2 Form A
 specifications which, with double pole
 switching for applications such as 250
 V power circuit switching, can enable
 safer designs.

6. Automatic cleaning possible

The sealed design means that these
 relays can undergo immersion in
 automatic washing systems and are
 suitable for automatic soldering. Even
 in difficult environments, the contacts
 remain reliable.

7. Easy to design PC board patterns

Features 4/10 dual-in-line terminals.
 Because the lead spacing has a pitch
 greater than 7.54 mm .297 inch,
 designers can make easy adjustments
 with the width of the land size. This,
 along with the large insulation
 distance, simplifies the drawing of PC
 board patterns.

8. To improve soldering efficiency, preapplication of solder to the terminals is recommended.

9. Sockets are available.

ORDERING INFORMATION

ST - - - F

Contact arrangement
 1: 1 Form A 1 Form B
 2: 2 Form A

Operating function
 Nil: Single side stable
 L2: 2 coil latching

Nominal coil voltage
 DC 3, 5, 6, 9, 12, 24, 48 V

Contact material
 F: AgSnO₂ type contact

Note: Certified by UL, CSA, VDE and SEV

ST

TYPES

Contact arrangement	Nominal coil voltage	Single side stable	2 coil latching
		Part No.	Part No.
1 Form A 1 Form B	3V DC	ST1-DC3V-F	ST1-L2-DC3V-F
	5V DC	ST1-DC5V-F	ST1-L2-DC5V-F
	6V DC	ST1-DC6V-F	ST1-L2-DC6V-F
	9V DC	ST1-DC9V-F	ST1-L2-DC9V-F
	12V DC	ST1-DC12V-F	ST1-L2-DC12V-F
	24V DC	ST1-DC24V-F	ST1-L2-DC24V-F
	48V DC	ST1-DC48V-F	ST1-L2-DC48V-F
2 Form A	3V DC	ST2-DC3V-F	ST2-L2-DC3V-F
	5V DC	ST2-DC5V-F	ST2-L2-DC5V-F
	6V DC	ST2-DC6V-F	ST2-L2-DC6V-F
	9V DC	ST2-DC9V-F	ST2-L2-DC9V-F
	12V DC	ST2-DC12V-F	ST2-L2-DC12V-F
	24V DC	ST2-DC24V-F	ST2-L2-DC24V-F
	48V DC	ST2-DC48V-F	ST2-L2-DC48V-F

Standard packing: Carton: 50 pcs.; Case: 500 pcs.
* For sockets, see page 113.

RATING

1. Coil data

1) Single side stable

Nominal coil voltage	Pick-up voltage (at 20°C 68°F)	Drop-out voltage (at 20°C 68°F)	Nominal operating current [±10%] (at 20°C 68°F)	Coil resistance [±10%] (at 20°C 68°F)	Nominal operating power	Max. applied voltage (at 20°C 68°F)
3V DC	80%V or less of nominal voltage (Initial)	10%V or more of nominal voltage (Initial)	75mA	38Ω	240mW	150%V of nominal voltage
5V DC			47mA	105Ω		
6V DC			40mA	150Ω		
9V DC			25mA	360Ω		
12V DC			20mA	600Ω		
24V DC			10mA	2,400Ω		
48V DC			4.7mA	9,000Ω		

2) 2 coil latching

Nominal coil voltage	Set voltage (at 20°C 68°F)	Reset voltage (at 20°C 68°F)	Nominal operating current [±10%] (at 20°C 68°F)		Coil resistance [±10%] (at 20°C 68°F)		Nominal operating power		Max. applied voltage (at 20°C 68°F)
			Set coil	Reset coil	Set coil	Reset coil	Set coil	Reset coil	
3V DC	80%V or less of nominal voltage (Initial)	80%V or less of nominal voltage (Initial)	75mA	75mA	40Ω	40Ω	240mW	240mW	150%V of nominal voltage
5V DC			45mA	45mA	110Ω	110Ω			
6V DC			37.5mA	37.5mA	155Ω	155Ω			
9V DC			25mA	25mA	360Ω	360Ω			
12V DC			18.8mA	18.8mA	640Ω	640Ω			
24V DC			10mA	10mA	2,400Ω	2,400Ω			
48V DC			4.7mA	4.7mA	10,200Ω	10,200Ω			

2. Specifications

Characteristics	Item		Specifications
Contact	Arrangement		1 Form A 1 Form B, 2 Form A
	Contact material		Au-flashed AgSnO ₂ type
	Contact resistance (Initial)		Max. 30 mΩ (By voltage drop 6 V DC 1A)
Rating	Max. switching power (resistive load)		3,040 VA, 150 W
	Max. switching voltage		380 V AC, 250 V DC
	Max. switching current		8 A
	Minimum operating power		150mW (Single side stable, 2 coil latching)
	Nominal operating power		240mW (Single side stable, 2 coil latching)
	Min. switching capacity (Reference value)*1		100 mA 5V DC
Electrical characteristics	Insulation resistance (Initial) (at 25°C, 50% relative humidity)		Min. 1,000MΩ (at 500V DC) Measurement at same location as "Breakdown voltage" section.
	Breakdown voltage (Initial)	Between open contacts	1,200 Vrms for 1 min. (Detection current: 10 mA)
		Between contact sets	2,000 Vrms for 1 min. (Detection current: 10 mA)
		Between contact and coil	3,750 Vrms for 1 min. (Detection current: 10 mA)
	Surge breakdown voltage (Initial)*2		6,000 V (Between contact and coil)
	Operate time [Set time] (at 20°C 68°F)		Max. 15 ms [Max. 15 ms] (Nominal coil voltage applied to the coil, excluding contact bounce time.)
	Release time [Reset time] (at 20°C 68°F)		Max. 10 ms [Max. 15 ms] (Nominal coil voltage applied to the coil, excluding contact bounce time.) (without diode)
	Temperature rise (coil) (at 60°C 140°F)		Max. 55°C (By resistive method, nominal voltage applied to the coil; contact carrying current: 8A.)
Mechanical characteristics	Shock resistance	Functional	Min. 196 m/s ² (Half-wave pulse of sine wave: 11 ms; detection time: 10μs.)
		Destructive	Min. 980 m/s ² (Half-wave pulse of sine wave: 6 ms.)
	Vibration resistance	Functional	10 to 55 Hz at double amplitude of 2 mm (Detection time: 10μs.)
		Destructive	10 to 55 Hz at double amplitude of 3 mm
Expected life	Mechanical		Min. 10 ⁷ (at 180 times/min.)
	Electrical		Min. 10 ⁵ (8 A 250 V AC resistive) (ON : OFF = 1 s : 5 s)
Conditions	Conditions for operation, transport and storage*3		Ambient temperature: -40°C to +60°C -40°F to +140°F; Humidity: 5 to 85% R.H. (Not freezing and condensing at low temperature)
	Max. operating speed		30 cps
Unit weight			Approx. 10g .353 oz


Notes: *1. This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load.

*2. Wave is standard shock voltage of $\pm 1.2 \times 50\mu\text{s}$ according to JEC-212-1981


*3. The upper limit of the ambient temperature is the maximum temperature that can satisfy the coil temperature rise value. Refer to Usage, transport and storage conditions in NOTES.

REFERENCE DATA


1. Max. switching power



2. Coil temperature rise



3. Influence of adjacent mounting




DIMENSIONS (mm inch)

CAD Data


The CAD data of the products with a **CAD Data** mark can be downloaded from: <http://industrial.panasonic.com/ac/e/>

External dimensions




General tolerance: $\pm 0.5 \pm .020$

PC board pattern (Bottom view)



Tolerance: $\pm 0.1 \pm .004$

Schematic (Bottom view)




SAFETY STANDARDS

UL/C-UL (Recognized)		CSA (Certified)		VDE (Certified)		TV rating (UL/CSA)		SEV	
File No.	Contact rating	File No.	Contact rating	File No.	Contact rating	File No.	Rating	File No.	Contact rating
E43028	8A 250V AC 1/4HP 125, 250V AC 5A 30V DC	LR26550 etc.	8A 250V AC 1/4HP 125, 250V AC 5A 30V DC	1017	8A 250V AC ($\cos\phi=1.0$) 4A 250V AC ($\cos\phi=0.4$) 5A 30V DC	UL: E43028 CSA: LR26550	—	98-1 10289	8A 380V AC

NOTES

1. PC board patterns for 2 coil latching types

When applying relays in power supply operation circuits for finished products regulated by the Electrical Appliance and Material Safety Law, use the pattern shown below.



2. Soldering should be done under the following conditions:

- 1) 250°C 482°F within 10s
300°C 572°F within 5s
350°C 662°F within 3s
- 2) For automatic cleaning, the boiling method is recommended. Avoid ultrasonic cleaning which subjects the relays to high frequency vibrations, which may cause the contacts to stick. It is recommended that a fluorinated hydrocarbon or other alcoholic solvents be used.

3. When using, please be aware that the a contact and b contact sides of 1 Form A and 1 Form B types may go on simultaneously at operate time and release time.

For Cautions for Use.