







NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING: 4A @125VAC/28VDC, 2A @250VAC
5. DIELECTRIC STRENGTH: 1kV RMS min. at sea level
6. ELECTRICAL LIFE: 10,000 make-and-break cycles at full load.
7. MATERIALS:


CONTACTS: Silver Plated Cu (Q Contact material)
TERMINALS: GOLD Plated Cu (Q Contact material)
MOUNTING NUT: Nickel Plated zinc alloy
CONTACT SPRING: Piano Wire
KEYS (2): Brass with code no. A126
LOCK: Bright Ni plated zinc alloy with Ni facing
TUMBLER Mechanism: 4-disc tumbler cylinder.



RECOMMENDED PANEL LAYOUT

SWITCH FUNCTION		
CONNECTED TERMINAL #		
POS. 1	POS. 2	POS. 3
8-1	1-2	2-3

CIRCUIT: SP (45° INDEXING)
CONTACT CONFIGURATION



LEGEND

- = Detent Positions (45° or 90°)
- ⊙ = Key pull possible in these positions

TITLE			
E-SWITCH®			
K0130C-A126			
K200212			
REV.	ECN NO.	DATE	CHKD
C	11722	10/10/01	CJB
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
REVISIONS		DATE	BY
REVISED NOTES		10/10/01	CJB
DESCRIPTION		DATE	CHKD
SCALE		DATE	DR
1:1		10/10/01	CJB
		DATE	DWG
		10/10/01	CJB
		DATE	REV
		10/10/01	C