


200V

V _{RM} (V)	Package	Part Number	I _F (A) () is with Heatsink	I _{FSM} (A)	T _j (°C)	T _{stg} (°C)	V _F (V) max		I _R (μA)	I _R (H) (μA)	R _{th} (j-ℓ) R _{th} (j-c) (°C/W)	Mass (g)	Fig. No.	Page where characteristic curve is shown
				50Hz Half-cycle Sinewave Single Shot				I _F (A)	V _R = V _{RM} max	T _a (°C)				
200	Surface Mount	SFPM-52	0.9	30	-40 to +150	1.0	1.0	10	50	100	20	0.072	1	48
		SFPM-62	1.0	45	-40 to +150	0.98	1.0	10	50	100	20	0.072		
	Axial	AM01Z	1.0	35	-40 to +150	0.98	1.0	10	50	100	22	0.13	2	48
		EM01Z	1.0	45	-40 to +150	0.97	1.0	10	50	100	20	0.2		
		EM 1Z	1.0	45	-40 to +150	0.97	1.0	10	50	100	17	0.3	4	
		RM 1Z	1.0	50	-40 to +150	0.95	1.0	5	50	100	15	0.4		
		RM 10Z	1.5	120	-40 to +150	0.91	1.5	10	50	100	15	0.4		
		RO 2Z	1.2	80	-40 to +150	0.92	1.5	10	50	100	12	0.61	6	50
		RM 2Z	1.2	100	-40 to +150	0.91	1.5	10	50	100	12	0.6		49
		RM 4Z	1.7 (3.0)	200	-40 to +150	0.95	3.0	10	50	100	8	1.2	7	50
		Center-tap	FMM-22S, R	10	100	-40 to +150	1.1	5.0	10	100	100	4.0	2.1	8
	FMM-32S, R		20	120	-40 to +150	1.1	10	10	100	100	2.0	5.5	9	51
	Bridge	RBV-402	4.0	80	-40 to +150	1.05	2.0	10	100	100	5.0	4.05	10	51
		RBV-602	6.0	120	-40 to +150	1.0	3.0	10	100	100	3.0	6.45	11	52
		RBV-4102	10	80	-40 to +150	1.1	5.0	10	100	150 (T _j)	2.0	4.05	10	—




■ External Dimensions

Flammability: UL94V-0 or Equivalent (Unit: mm)






Characteristic Curves Rectifier Diodes




RBV-406H






RBV-601, 602



RBV-604, 606



RBV-608



RBV-606H

