


ST series

Miniature toggle switches

Distinctive features and specifications



- ☐ Dry circuit through power ratings.
- ☐ Ultra-rugged construction SPDT & DPDT models with numerous options.
- ☐ PC and panel mount models.

ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load :
 - gold over nickel plated brass contacts : 0.4VA - 20V Max.
 - coin silver contacts: 6A 125VAC, 3A 250VAC, 7A 30VDC
- Initial contact resistance: 3 milliohms max. at 3VDC, 0.1 Amp.
- Insulation resistance: 2,000 MΩ min. between terminals & case ground.
- Dielectric strength: 2,000 VAC for 1 minute between terminals & case ground.
- Electrical life: 100,000 cycles at full load for ST1-1 and ST2-1, all other models 40,000 cycles

MATERIALS

- Case : Diallylphthalate (DAP), color blue
- Actuator : Brass, bright nickel or chrome plated.
- Bushing: nickel plated brass
- Strap: stainless steel
- Contacts
 - B: Gold
 - Q: Coin silver
 - G: Gold over silver
- Terminal seal: epoxy

GENERAL SPECIFICATIONS

- Operating temperature : -30°C to +85°C

AGENCY APPROVAL




Availability: All models with coin silver contacts (Q) only.

Marking: To order switches marked UL use "UL" prefix for series designation. For CSA marking, complete appropriate box on ordering format.

ST series

Miniature toggle switches



SERIES	
ST1-	Single Pole
UL1	S.P. UL Model
ST2-	Double Pole
UL2	D.P. UL Model

Actuators	
K	Standard
F1	Flatted
F3	Sm Flatted
T4	Long round

Terminations	
Z	Solder lug
C	Printed circuit board
V30	Straight w/bracket, non-crimped
V31	Straight w/bracket, crimped

Sealing	
E	Epoxy

Electrical Functions				
1	ON	NONE	ON	
2	ON	OFF	ON	
6	ON	ON	ON	▲
▲ FUNCTION 6: DOUBLE POLE ONLY				

Bushing	
M	Standard 1/4" thd'd.
H	Splashproof 1/4" thd'd.
Y	Long 1/4" thd'd.
M4	15/32" thd'd.

Contact Material	
B	Gold
Q	Coin Silver
G	Gold over Silver

Agency approval	
No approval	
/CSA	CSA Approval
	(Q contact material only)
Note: for UL, Select UL1 or UL2 series above	

ABOUT THIS SERIES

On the following pages, you will find successively :

- model structure of switches
- options in the same order as in above chart

Dimensions : first dimensions are in mm while inches are shown as bracketed numbers.



Sealing boots are available to protect the switches against dust and water. They are presented in section H



Mounting accessories : standard hardware supplied with all models with Ø 6,35 (1/4) threaded bushing : 2 - 5/16" hex nuts , 1 locking ring and 1 lockwasher. Standard and special hardware available are presented in section I.



Packaging unit : 25 pieces for double pole
50 pieces for single pole





NOTICE : please note that not all combinations of above numbers are available. Refer to the following pages for further information.

ST series

Miniature toggle switches

Terminations:


- Solder lug or straight PC terminals
- Epoxy sealed terminals standard



Single pole panel mount with solder lug terminals → Keyway




MODEL NO.	UL NO.	I	II	III
		1-2		2-3
ST1-1KMZQE	UL11KMZQE	ON	-	ON
ST1-2KMZQE	UL12KMZQE	ON	OFF	ON




Double pole panel mount with solder lug terminals → Keyway




MODEL NO.	UL NO.	I	II	III
		1-2	1-2	2-3
		4-5	5-6	5-6
ST2-1KMZQE	UL21KMZQE	ON	-	ON
ST2-2KMZQE	UL22KMZQE	ON	OFF	ON
ST2-6KMZQE	UL26KMZQE	ON	ON	ON



Single pole straight PC terminals




MODEL NO.	UL NO.	I	II	III
		1-2		2-3
ST1-1KMCBE	UL11KMCQE	ON	-	ON
ST1-2KMCBE	UL12KMCQE	ON	OFF	ON




Miniature toggle switches


MODEL NO.	UL NO.	I	II	III
		1-2 4-5	1-2 5-6	2-3 5-6
ST2-1KMCBE	UL21KMCQE	ON	-	ON
ST2-2KMCBE	UL22KMCQE	ON	OFF	ON
ST2-6KMCBE	UL26KMCQE	ON	ON	ON




MODEL NO.	UL NO.	I 1-2	II 1-2	III 2-3
ST1-1F1MZQE	UL11F1MZQE	ON	-	ON
ST1-2F1MZQE	UL12F1MZQE	ON	OFF	ON



MODEL NO.	UL NO.	I	II	III
		1-2 4-5	1-2 5-6	2-3 5-6
ST2-1F1MZQE	UL21F1MZQE	ON	-	ON
ST2-2F1MZQE	UL22F1MZQE	ON	OFF	ON
ST2-6F1MZQE	UL26F1MZQE	ON	ON	ON



MODEL NO.	UL NO.	I 1-2	II	III 2-3
ST1-1KHZQE	UL11KHZQE	ON	-	ON
ST1-2KHZQE	UL12KHZQE	ON	OFF	ON




ST series

Miniature toggle switches


Double pole panel mount with splashproof bushing → "D" flat




MODEL NO.	UL NO.	I	II	III
		1-2	1-2	2-3
		4-5	5-6	5-6
ST2-1KHZQE	UL21KHZQE	ON	-	ON
ST2-2KHZQE	UL22KHZQE	ON	OFF	ON
ST2-6KHZQE	UL26KHZQE	ON	ON	ON




Actuator




Flatted




Short flatted




Round




Bushing options




Splashproof




Threaded



Long threaded



15/32" threaded




Bushing Option	Bushing Dims.		Actuator length Dim C			
	Dim A	Dim B	F1	F3	K	T4
H	7.37 (.290)	1.52 (.060)	N/A	N/A	10.41 (.410)	N/A
M	7.04 (.277)	1.52 (.060)	11.43 (.450)	6.35 (.250)	10.41 (.410)	N/A
Y	8.38 (.330)	1.02 (.040)	N/A	N/A	10.41 (.410)	N/A
M4	11.38 (.448)	-	N/A	N/A	N/A	17.45 (.687)


ST series

Miniature toggle switches

V30 bracket option




Panel cut-outs




Hardware


Anti-rotate ring A107
Nickel plated brass




5/16" Hex nut A112
Nickel plated brass 1/4-40



Anti-rotate ring A158
Nickel plated brass



9/16" Hex nut A465
Nickel plated brass 15/32-32



ST series

Miniature toggle switches

Contact material specs.

- B** Dry circuit - gold over nickel over brass.
RATING: 0.4 Volt-Amps (VA) max. at 20 V max.
ELECTRIC LIFE: 100,000 cycles min. (ST1-1 & ST2-1 only - other models 40,000 cycles min.)
- Q** Power circuit - coin silver.
RATING: 6 Amps at 125 VAC, 3 Amps at 250 VAC or 7 Amps at 30 VDC (resistive loads).
ELECTRIC LIFE: 100,000 cycles min. (ST1-1 & ST2-1 only - other models 40,000 cycles min.)
- G** Dry circuit or power circuit - gold over nickel over coin silver.
RATINGS & ELECTRIC LIFE: Same as B & Q above - i.e. - can be used in either dry circuit or power circuit, however once used in power circuit, switch cannot be re-used in dry circuit. This option satisfies those customers who have both dry circuit and power circuit requirements, but prefer to inventory only one switch for both.

A

UL & CSA options




- UL** For power circuits - coin silver
RATING: 6 Amps at 125 VAC or 3 Amps at 250 VAC (75% power factor).
Underwriter Laboratories file no. E66367. Note - applicable only to terminations with coin silver contacts (Q option).
- CSA** For power circuits - coin silver
RATING: 6 Amps at 125 VAC or 3 Amps at 250 VAC (75% power factor). Canadian Standards Association file no. LR54592-1. Note - applicable only to terminations with coin silver contacts (Q option) as CSA recognizes switches for power applications only.
Note- Double pole switches with solder lug terminals are not CSA recognized .

ST series

Miniature rocker switches

Distinctive features and specifications



- ☐ Dry circuit through power ratings.
- ☐ Ultra-rugged construction SPDT & DPDT models with numerous options.
- ☐ Panel, panel & PC and PC mounting models.

ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load :
 - gold over nickel plated brass contacts : 0.4VA - 20V Max.
 - coin silver contacts : 6A 125VAC, 3A 250VAC, 7A 30VDC
- Initial contact resistance : 3 milliohms max. at 3VDC, 0.1 Amp.
- Insulation resistance : 2,000 MΩ min. between terminals & case ground.
- Dielectric strength : 2,000 VAC for 1 minute between terminals & case ground.
- Electrical life : 40,000 cycles for function 6, all other models are 100,000 cycles at full load

MATERIALS

- Case : Melamine Phenolic, color, blue
- Actuator :
 - J1 & J2: Glass filled polyester
 - J3 & J4: Nylon or acetal
- Bushing: nickel plated brass
- Strap: stainless steel
- Contacts
 - B: Gold
 - Q: Coin silver
 - G: Gold over silver
- Terminal seal: epoxy
- Spring Bracket: Stainless steel
- Bezel: Nylon

GENERAL SPECIFICATIONS

- Operating temperature : -30°C to +85°C

AGENCY APPROVAL




Availability: All models with coin silver contacts (Q) only.

Marking: To order switches marked UL use "UL" prefix for series designation. For CSA marking, complete appropriate box on ordering format.

ST series

Miniature rocker switches



ABOUT THIS SERIES

On the following pages, you will find successively :

- model structure of switches
- options in the same order as in above chart

Dimensions : first dimensions are in mm while inches are shown as bracketed numbers.



Sealing boots are available to protect the switches against dust and water. They are presented in section H.



Mounting accessories : standard hardware supplied with all models with Ø 6,35 (1/4) threaded bushing : 2 - 5/16" hex nuts , 1 locking ring and 1 lockwasher.
Standard and special hardware available are presented in section I.






NOTICE : please note that not all combinations of above numbers are available. Refer to the following pages for further information.

ST series

Miniature rocker switches

Terminations



- Solder lug or straight PC terminals
- Epoxy sealed terminals standard



Solder lug terminals with snap-in bezel




MODEL NO.	I	II	III
SINGLE POLE	1-2		2-3
ST1-1L5S5ZQJ4J9022	ON	-	ON
ST1-2L5S5ZQJ4J9022	ON	OFF	ON
DOUBLE POLE	1-2	1-2	2-3
	4-5	5-6	5-6
ST2-1L5S5ZQJ4J9022	ON	-	ON
ST2-2L5S5ZQJ4J9022	ON	OFF	ON
ST1-6L5S5ZQJ4J9022	ON	ON	ON



Double pole straight PC terminals with bracket




MODEL NO.	I	II	III
	1-2	1-2	2-3
	4-5	5-6	5-6
ST2-1L4S4V30BJ12	ON	-	ON
ST2-2L4S4V30BJ12	ON	OFF	ON
ST2-6L4S4V30BJ12	ON	ON	ON



Single pole straight PC terminals with bracket




MODEL NO.	I	II	III
	1-2		2-3
ST1-1L4S4V30BJ12	ON	-	ON
ST1-2L4S4V30BJ12	ON	OFF	ON




ST series

Miniature rocker switches

Straight PC terminals with PC mounting bezel




MODEL NO.	I	II	III
SINGLE POLE	1-2		2-3
ST1-1L5S5CBJ3J9322	ON	-	ON
ST1-2L5S5CBJ3J9322	ON	OFF	ON
DOUBLE POLE	1-2	1-2	2-3
ST2-1L5S5CBJ3J9322	ON	-	ON
ST2-2L5S5CBJ3J9322	ON	OFF	ON
ST2-6L5S5CBJ3J9322	ON	ON	ON




Straight PC terminals with bracket & PC mounting bezel




MODEL NO.	I	II	III
SINGLE POLE	1-2		2-3
ST1-1L5S5CV30J3J9322	ON	-	ON
ST1-2L5S5CV30J3J9322	ON	OFF	ON
DOUBLE POLE	1-2 4-5	1-2 5-6	2-3 5-6
ST2-1L5S5CV30J3J9322	ON	-	ON
ST2-2L5S5CV30J3J9322	ON	OFF	ON
ST2-6L5S5CV30J3J9322	ON	ON	ON



Panel cut-out



With bezel J90




With bezel J93

ST series


Miniature rocker switches

V30 & V31 bracket options




Printed circuit mounting


Actuators




J1 Rocker



J2 Lever



J3 Rocker



J4 Lever

ST series

Miniature rocker switches

Contact material specs.

- B** Dry circuit - gold over nickel over brass.
RATING: 0.4 Volt-Amps (VA) max. at 20 V max.
ELECTRIC LIFE: 100,000 cycles min. (ST1-1 & ST2-1 only - other models 40,000 cycles min.)
- Q** Power circuit - coin silver.
RATING: 6 Amps at 125 VAC, 3 Amps at 250 VAC or 7 Amps at 30 VDC (resistive loads).
ELECTRIC LIFE: 100,000 cycles min. (ST1-1 & ST2-1 only - other models 40,000 cycles min.)
- G** Dry circuit or power circuit - gold over nickel over coin silver.
RATINGS & ELECTRIC LIFE: Same as B & Q above - i.e. - can be used in either dry circuit or power circuit, however once used in power circuit, switch cannot be re-used in dry circuit. This option satisfies those customers who have both dry circuit and power circuit requirements, but prefer to inventory only one switch for both.

UL & CSA options



- UL** For power circuits - coin silver
RATING: 6 Amps at 125 VAC or 3 Amps at 250 VAC (75% power factor).
Underwriter Laboratories file no. E66367. Note - applicable only to terminations with coin silver contacts (Q option).
- CSA** For power circuits - coin silver
RATING: 6 Amps at 125 VAC or 3 Amps at 250 VAC (75% power factor). Canadian Standards Association file no. LR54592-1. Note - applicable only to terminations with coin silver contacts (Q option) as CSA recognizes switches for power applications only.
Note- Double pole switches with solder lug terminals are not CSA recognized .

300 & 400 series

Miniature pushbutton switches

Distinctive features and specifications



- ☐ Dry circuit through power ratings .
- ☐ Compact size.
- ☐ Panel, panel & PC and PC mounting models.

C

ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load :
 - gold over nickel plated brass contacts : 0.4VA - 20V Max.
 - coin silver contacts : 1A 125VAC or 28VDC, 0.5A 250VAC, 3A 125VAC or 28VDC,
- Initial contact resistance : 10 milliohms max. at 3VDC, 0.1 Amp.
- Insulation resistance : 10,000 MΩ min.
- Dielectric strength : 1,000 Vrms min at sea level.
- Electrical life :

Model	Contacts	Rating	Number of cycles
300	(Q) coin silver	1A 125VAC or 28 VDC	250,000
300	(Q) coin silver	3A 125VAC or 28VDC	10,000
300	(B) gold	0.4VA max. at 20V	250,000
400	(Q) coin silver	1A 125VAC or 28 VDC	40,000
400	(Q) coin silver	3A 125VAC or 28VDC	10,000
400	(B) gold	0.4VA max. at 20V	40,000

GENERAL SPECIFICATIONS

- Operating temperature : -30°C to +85°C

MATERIALS

- Base: diallyphthalate (DAP)
- Actuator: nylon
- Bushing: nickel plated brass
- Contacts
 - B:** Gold
 - Q:** Coin silver
- Terminal seal: epoxy
- Spring bracket: stainless steel
- Support bracket: tin plated brass or steel
- Bezel and cap: nylon

AGENCY APPROVAL




Availability: All models with coin silver contacts (Q) only.

Marking: To order switches marked UL, complete appropriate box on ordering format.

300 & 400 series

Miniature pushbutton switches



ABOUT THIS SERIES

On the following pages, you will find successively :

- model structure of switches
- options in the same order as in above chart


Dimensions : first dimensions are in mm while inches are shown as bracketed numbers.



NOTICE : please note that not all combinations of above numbers are available. Refer to the following pages for further information.


300 & 400 series

Miniature pushbutton switches



Terminations

- Solder lug or straight PC terminals
- Epoxy sealed terminals standard



Normally open with overtravel: 301



Solder lug terminals

301ZQE  Normally Open

301ZBE  Normally Open


PC terminals

301CQE  Normally Open

301CBE  Normally Open

Total travel: 2.7 (.110)
Over travel: 0.51 (.020)

Actuation force: 8.5oz. $\pm$ 4oz.



Normally open no overtravel: 302



Solder lug terminals

302ZQE  Normally Open

302ZBE  Normally Open


PC terminals

302CQE  Normally Open

302CBE  Normally Open

Total travel: 1.52 (.060)

Actuation force: 10oz. $\pm$ 4oz.



Normally open with greater overtravel: 305



Solder lug terminals

305ZQE  Normally Open

305ZBE  Normally Open


PC terminals

305CQE  Normally Open

305CBE  Normally Open

Total travel: 2.7 (.110)
Over travel: 1.20 (.075)

Actuation force: 8oz. $\pm$ 4oz.



300 & 400 series

Miniature pushbutton switches

Normally open with sealed contact area: 306



Solder lug terminals

306ZQE  Normally Open


306ZBE  Normally Open

PC terminals

306CQE  Normally Open

306CBE  Normally Open

Total travel: 8.74 (.310)
Over travel: 6.35 (.250)
Actuation force at full travel: 9oz.




Normally open snap-action mechanism: 400



401  Alternate Action

402  Normally Open
Pretravel: 0.66 (.026)
Actuation travel: 2.60 (.106)
Total travel: 3.48 (.137)
Over travel: 0.79 (.031)
Actuation force: 22oz.




▲ For complete part number, and full list of options see part number breakdown at the beginning of this section

Snap-in bezel




Model no.	Dim A	Dim B
301	2.74 (.108)	23.60 (.929)
302	2.16 (.085)	20.75 (.817)
305	2.74 (.108)	23.60 (.929)
401	3.68 (.145)	29.00 (1.142)
402	3.68 (.145)	29.00 (1.142)



Right angle terminal with bracket



Model no.	Dim B	Dim C	Dim D
301	11.15 (.439)	13.97(.550)	16.51 (.650)
302	8.30 (.327)	11.43 (.450)	13.97(.550)
305	11.15 (.439)	13.97(.550)	16.51 (.650)
401	16.59 (.653)	19.05 (.750)	21.59 (.850)
402	16.59 (.653)	19.05 (.750)	21.59 (.850)




300 & 400 series

Miniature pushbutton switches

T1 option with 15/32 bushing




Model no.	Dim A
301	6.35 (.250)
305	6.35 (.250)




T1 option available only for 301 and 305 models

C


Option S long actuator



301 & 305




302




401 & 402


Panel cut-outs



1/4" threaded
bushings



15/32" threaded
bushings



Snap-in bezel

UL option



UL For power circuits - coin silver


RATING: 0.5 Amps at 125 VAC (75% power factor).

Underwriter Laboratories file no. E66367. Note - applicable only to terminations with coin silver contacts (Q option).

800 series

Snap-action momentary pushbutton switches

Distinctive features and specifications



- ☐ Panel and PC mount models
- ☐ Snap-in panel mounting version
- ☐ Tactile feedback

ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load :
 - gold over nickel plated brass contacts : 0.4VA - 20V max.
 - coin silver contacts : 6A 125VAC, 3A 250VAC, 7A 30VDC
- Initial contact resistance : 20 mΩ max.
- Insulation resistance : 2,000 MΩ min. between terminals & case ground.
- Dielectric strength : 1,500 VAC for 1 minute between terminals & case ground.
- Electrical life : 60.000 cycles at full load

MATERIALS

- Case : DAP
- Actuator : polyamide, glass filled
- Bushing : brass, nickel plated
- Strap : stainless steel
- Bracket : tin plated steel or brass
- Contacts
 - B: Gold
 - Q: Coin Silver
- Terminal seal : epoxy

GENERAL SPECIFICATIONS

- Total travel : 0.9mm (.035)
- Actuation force:
 - Single pole: 290+/- 75g
 - Double pole: 550+/- 75g
- Operating temperature : -30°C to +85°C
- Soldering : 300°C, 3 sec. max.

AGENCY APPROVAL




Availability: All models with coin silver contacts (Q) only.

Marking: To order switches marked UL, complete appropriate box on ordering format.

800 series

Snap-action momentary pushbutton switches

D



ABOUT THIS SERIES

On the following pages, you will find successively :

- model structure of switches
- options in the same order as in above chart

Dimensions: first dimensions are in mm while inches are shown as bracketed numbers.



Sealing boots are available to protect the switches against dust and water. They are presented in section H.



Mounting accessories: standard hardware supplied with all models with Ø 6,35 (1/4) threaded bushing :
2 - 5/16" hex nuts , 1 locking ring and 1 lockwasher.
Standard and special hardware available are presented in section I.




Packaging unit: 25 pieces for double pole
50 pieces for single pole



NOTICE: please note that not all combinations of above numbers are available. Refer to the following pages for further information.


800 series

Snap-action momentary pushbutton switches



Terminations

- Solder lug or straight PC terminals
- Epoxy sealed terminals standard





Shown with standard plunger (K)

Solder lug terminals




810KMZ



Solder lug terminals




820KMZ



Horizontal right angle




810KSA-1



800 series

Snap-action momentary pushbutton switches


Horizontal angle



820KSA-1



→ Keyway




Straight PC terminals with bracket



810KSV30



→ Keyway




Straight PC terminals with bracket




820KSV30



→ Keyway




Solder lug terminals with snap-in bezel



→ Keyway

MODEL NUMBER	DIM. A
810K2M1ZQJ8122	2.54 (.100)
810K1M1ZQJ8122	0.25 (.010)




800 series



Snap-action momentary pushbutton switches

Actuator & bushing options

M & M1




S




BUSHING OPTION	DIM. B	DIMENSION A ACTUATOR OPTION		
		K	K1	K2
M	6.35 (.250)	5.84 (.230)	.069 (1.75)	4.27 (.168)
S	6.35 (.250)	5.84 (.230)	.069 (1.75)	4.27 (.168)
M1	3.91 (.154)	8.18 (.322)	4.91 (.165)	6.70 (.264)


Panel cut-outs




Without keying




With A107 anti-rotate
ring



With A158 anti-rotate
ring



With slotted keyway



Accepts all 1/4" non-
threaded bushings

Contact materials

B

Dry circuit - gold over nickel over brass.

RATING: 0.4 Volt-Amps (VA) max. at 20 V max.

ELECTRIC LIFE: 60,000 cycles minimum. MECHANICAL LIFE: 500,000 cycles minimum.

Q

Power circuit - coin silver.

RATING: 6 Amps at 125 VAC, 3 Amps at 250 VAC or 7 Amps at 30 VDC (resistive loads).

ELECTRIC LIFE: 60,000 cycles minimum at full load.

Approvals

/UL

For power circuits - coin silver

RATING: 6 Amps at 125 VAC or 3 Amps at 250 VAC (75% power factor).

Underwriter Laboratories file no. E66367. Note - applicable only to terminations with coin silver contacts (Q option).

AV series

Anti-vandal and security pushbutton switches




- ☐ 19mm bushing
- ☐ Single pole ON-OFF, Alternate Action, & Momentary functions
- ☐ Standard sealing IP54, IP65 models available
- ☐ Extremely rugged and durable

Specifications


For all 400 series models, see section "C".

For all 800 series models, see section "D"

Panel cut-out



SEALING (OPTION K)



Front panel sealing (IP65)

① internal gasket ② external gasket

AV

Z

SERIES

Switch Model

401 Alternate Action
402 Momentary
810KM Momentary (SPDT)
820KM Momentary (DPDT)

Contact material

B Gold
Q Coin Silver

Sealing

K IP54
K IP65

Mushroom cap color

0 Natural
6 Red
6P Powder coated red

Actuators/Bushing Configurations

09 19mm w/flat actuator
19 19mm w/curved actuator
49 19mm w/mushroom cap

Terminations


Z Solder lug

Terminal sealing


E Epoxy ▲
 ▲ For 400 series models only, all 800 series models built with sealed terminals standard.

Agency approval


(None)
/UL UL approved




09 flat actuator & curved bushing



19 800 series w/curved actuator & bushing



19 400 series w/ curved actuator & bushing



49 Thd. actuator with mushroom cap & curved bushing