

# Features

## Regulated Converters

- Compact AC-DC Power Supply
- 10 Watt PCB Mount Package
- Universal Input Voltage Range
- 3000VAC Isolation
- Low Output Ripple and Noise
- Short Circuit Protected
- UL Certified, CE Marked

### Description

Compact UL certified switching AC/DC power module for PCB, screw-terminal connection or DIN-rail mounting.

### Selection Guide

| Part Number | Input Range (VAC) | Output Voltage (VDC) | Output Current (mA) | Efficiency (%) | Max. Capacitive Load |
|-------------|-------------------|----------------------|---------------------|----------------|----------------------|
| RAC10-3.3SA | 90-264            | 3.3                  | 3000                | 65             | 70000µF              |
| RAC10-05SA  | 90-264            | 5                    | 2000                | 71             | 35000µF              |
| RAC10-12SA  | 90-264            | 12                   | 833                 | 76             | 11000µF              |
| RAC10-15SA  | 90-264            | 15                   | 666                 | 75             | 7000µF               |
| RAC10-24SA  | 90-264            | 24                   | 426                 | 76             | 2300µF               |
| RAC10-05DA  | 90-264            | ±5                   | ±800                | 73             | ±22000µF             |
| RAC10-12DA  | 90-264            | ±12                  | ±380                | 75             | ±3000µF              |
| RAC10-15DA  | 90-264            | ±15                  | ±300                | 74             | ±2000µF              |

\*add suffix "-E" for extended temperature range, e.g. RAC10-05SA-E

\*add suffix "-ST" for screw terminal module e.g. RAC10-05SA-ST, RAC010-05DA-E-ST

### Specifications (typical at 25°C and after warm up time unless otherwise specified )

|                                                                  |                                 |                             |
|------------------------------------------------------------------|---------------------------------|-----------------------------|
| Input Voltage Range                                              | 90-264VAC or 120-370VDC         |                             |
| Rated Power                                                      | 10 Watts max.                   |                             |
| Input Frequency Range (for AC Input)                             | 47-440Hz                        |                             |
| Input Current (full load)                                        | 115VAC/230VAC                   | 200mA / 130mA max.          |
| No Load Power Consumption                                        | 115VAC/230VAC                   | 1.65W max.                  |
| Inrush Current (<2ms)                                            | 115VAC                          | 10A max. (-E = 23A max.)    |
|                                                                  | 230VAC                          | 20A max. (-E = 46A max.)    |
| Leakage Current                                                  | 0.75mA max.                     |                             |
| Output Voltage Accuracy (Full load)                              | ±2%                             |                             |
| Line Voltage Regulation (low line, high line at full load)       | ±0.3% typ.                      |                             |
| Load Voltage Regulation ( 5% to 100% full load )                 | ±0.5% typ.                      |                             |
| Output Ripple and Noise (20MHz limited)                          | Noise                           | 0.5% Vout + 50mVp-p max.    |
|                                                                  | Ripple                          | <0.2% Vout + 40mVp-p max.   |
| Operating Frequency                                              | 100kHz typ.                     |                             |
| Efficiency at Full Load                                          | see table                       |                             |
| RMS Isolation Voltage (input to output)                          | 3kVAC / 1minute                 |                             |
| Temperature Coefficient                                          | ±0.02%/°C typ.                  |                             |
| Isolation Resistance                                             | 100 MΩ min.                     |                             |
| Short Circuit Protection                                         | Hiccup, Automatic Restart       |                             |
| Operating Temperature Range (free air convection, with derating) | Standard                        | -25°C to +70°C              |
|                                                                  | Suffix -E                       | -40°C to +70°C              |
| Storage Temperature Range                                        | -40°C to +85°C                  |                             |
| Humidity                                                         | 95% RH max.                     |                             |
| Case Material                                                    | Epoxy with Fibreglass (UL94V-0) |                             |
| Package Weight                                                   | 92g                             |                             |
| Packing Quantity                                                 | 5 pcs (-ST Version: 1 pc)       |                             |
| EMC                                                              | EN 55022 Class B / EN 50082-1   |                             |
| MTBF (+25°C)                                                     | using MIL-HDBK-217F             | 250 x 10 <sup>3</sup> hours |

# POWERLINE

## AC/DC-Converter

with 3 year Warranty

RECOM


## 10 Watt Single/Dual Output



UL-60950-1 Certified

## RAC10-A

## Derating-Graph (Ambient Temperature)



Refer to Application Notes


# POWERLINE

## AC/DC-Converter

# RAC10-S\_DA

## Series

### Screw Terminal Module Option (suffix -ST)





#### Pin Connections

| Pin # | Single Out | Dual Out   |
|-------|------------|------------|
| 1     | FG         | FG         |
| 2     | VAC in (N) | VAC in (N) |
| 3     | VAC in (L) | VAC in (L) |
| 4     | NC         | NC         |
| 5     | -VDC out   | -VDC out   |
| 6     | NC         | Com        |
| 7     | +VDC out   | +VDC out   |
| 8     | NC         | NC         |

NC = No Connction

### Standard Package Style and Pinning




#### Pin Connections

| Pin # | Single Out | Dual Out   |
|-------|------------|------------|
| 1     | FG         | FG         |
| 2     | VAC in (N) | VAC in (N) |
| 3     | VAC in (L) | VAC in (L) |
| 4     | -VDC out   | -VDC out   |
| 5     | No Pin     | Com        |
| 6     | +VDC out   | +VDC out   |

XX.X ± 0.5 mm


XX.XX ± 0.25 mm



### Standard Application Circuit

Suggested fuse rating

2A Slow Blow



The product information and specifications are subject to change without prior notice. RECOM products are not authorized for use in safety-critical applications (such as life support) without RECOM's explicit written consent. A safety-critical application is defined as an application where a failure of a RECOM product may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The buyer shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.