

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	REDRAWN PER ECR 09-016745	28JUL09	JR	TM
	B2	REVISED PER ECO-17-007400	27NOV2017	RS	DR

D

D

C


C

B

B

A

A



AMP WIRE RANGE	FILE E13288
12-10 AWG STRANDED	12-10 AWG STRANDED

- 1 WIRE INSUL ϕ 3.810-5.842[ϕ .150-.230]
- 2 MATERIAL: BODY - CU PER ASTM B152
SLEEVE - CU PER ASTM B152
INSULATION - NYLON ASTM D4066 TYPE 1.
- 3 FINISH: BODY & SLEEVE: TIN PER ASTM B-545
INSULATION - COLOR: YELLOW.
- 4 STAMP AMP 12-10* 6-9 APPROX AS SHOWN.

500	LOOSE PIECE	320620
QTY	PACKAGE TYPE	PART NO

MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr_ruth 12JUN09	TE Connectivity		
			CHK TOM MICHIELUTTI 12JUN09			
	DIMENSIONS: mm [INCHES]		APVD TOM MICHIELUTTI 12JUN09	NAME TERMINAL, PIDG, KNIFE DISCONNECT, WIRE SIZE: 12-10		
VOLTAGE RATING: 300 V MAX		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127[.005] 4 PLC ± - ANGLES ± 5°	PRODUCT SPEC UL 486A-B	SIZE A3		
CIRCULAR MIL AREA: 2.62-6.64mm² [5,180-13,100] STRANDED			APPLICATION SPEC 114-2157			
	MATERIAL 2	FINISH 3	WEIGHT -	CAGE CODE 00779	DRAWING NO C=320620	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 5:1	SHEET 1 OF 1	REV B2	