

Intel® Server Board S5500WB

SPECIFICATIONS

- All
- Essentials
- Memory Specifications
- Graphics Specifications
- Expansion Options
- I/O Specifications
- Package Specifications
- Advanced Technologies

COMPATIBLE PRODUCTS

ORDERING / SSPECS / STEPPINGS

Specifications

Essentials

Status	Launched
Launch Date	Q2 2009
Expected Discontinuance	1H 2013
Limited 3-year Warranty	Yes
Extended Warranty Available for Purchase (Select Countries)	Yes
# of QPI Links	2
Board Form Factor	SSI EATX (12 x 13)
Chassis Form Factor	Rack
Socket	LGA1366
Integrated Systems Available	Yes
Integrated BMC with IPMI	IPMI 2.0 w/ DCMI
Rack-Friendly Board	Yes
Supplemental SKU	No
Max TDP	95 W
Recommended Customer Price	N/A

Description

A rack-optimized server board, purpose-built energy efficiency and lowest total cost of ownership in dense computing applications

Target Market

Cloud/Datacenter

Additional Information URL

[Link](#)

Memory Specifications

Max Memory Size (dependent on memory type)	128 GB
Memory Types	DDR3 ECC UDIMM, RDIMM
# of Memory Channels	3
Max Memory Bandwidth	1066 GB/s
# of DIMMs	8
ECC Memory Supported	Yes

Graphics Specifications

Integrated Graphics	Yes
Dual Display Capable	Yes

Expansion Options

# of PCI Express Ports	2
PCIe x8 Gen 2.x	1
PCIe x16 Gen 2.x	1
IO Expansion x4 Gen 2.x	2

I/O Specifications

USB Revision	USB 2.0
# of USB Ports	4
USB 2.0 Configuration (Back + Internal)	6
# of SATA Ports	6
RAID Configuration	Intel(R) Embedded RAID (0,1); upgradeable to RAID5
# of Serial Ports	2
# of LAN Ports	2
Integrated LAN	Dual, GbE
Integrated SAS Ports	0

Package Specifications

Max CPU Configuration	2
Low Halogen Options Available	See MDDDS

Advanced Technologies

Intel® Remote Management Module Support	AXXRMM3
Intel® Intelligent Power Node Manager	Yes

COMPARE PRODUCTS

- [Add to Compare](#)
- [Compare Now \(0\)](#)

QUICK LINKS

- [Products formerly Willowbrook](#)
- [Download Datasheet](#)
- [Additional Information](#)
- [Search Distributors](#)

ADDITIONAL INFORMATION

SUPPORT AND DOWNLOADS

- [Software Downloads >](#)
- [Support Overview >](#)

PCN/MDDDS INFORMATION



"Announced" SKUs are not yet available. Please refer to the Launch Date for market availability.

The Recommended Customer Price ("RCP") is pricing guidance for Intel products. Prices are for direct Intel customers and are subject to change without notice. Taxes and shipping, etc. not included. Prices may vary for other package types and shipment quantities, and special promotional arrangements may apply. Listing of these RCP does not constitute a formal pricing offer from Intel. Please work with your appropriate Intel representative to obtain a formal price quotation.

"Intel classifications" consist of Export Control Classification Numbers (ECCN) and Harmonized Tariff Schedule (HTS) numbers. Any use made of Intel classifications are without recourse to Intel and shall not be construed as a representation or warranty regarding the proper ECCN or HTS. Your company may be the exporter of record, and as such, your company is responsible for determining the correct classification of any item at the time of export.

Intel processor numbers are not a measure of performance. Processor numbers differentiate features within each processor family, not across different processor families. See http://www.intel.com/products/processor_number for details.

Hyper-Threading Technology (HT Technology) requires a computer system with an Intel® processor supporting HT Technology and an HT Technology enabled chipset, BIOS and operating system.

Performance will vary depending on the specific hardware and software you use. See www.intel.com/products/ht/hyperthreading_more.htm for more information including details on which processors support HT Technology.

64-bit computing on Intel® architecture requires a computer system with a processor, chipset, BIOS, operating system, device drivers and applications enabled for Intel® 64 architecture. Processors will not operate (including 32-bit operation) without an Intel 64 architecture-enabled BIOS. Performance will vary depending on your hardware and software configurations. Consult with your system vendor for more information.

Max Turbo Frequency refers to the maximum single-core frequency that can be achieved with Intel® Turbo Boost Technology, which requires a PC with a processor with Intel Turbo Boost Technology capability. Intel Turbo Boost Technology performance varies depending on hardware, software, and overall system configuration. Check with your PC manufacturer on whether your system delivers Intel Turbo Boost technology. See www.intel.com/technology/turboboost for more information.

Enabling Execute Disable Bit functionality requires a PC with a processor with Execute Disable Bit capability and a supporting operating system. Check with your PC manufacturer on whether your system delivers Execute Disable Bit functionality.

Intel® Virtualization Technology requires a computer system with a processor, chipset, BIOS, virtual machine monitor (VMM) and for some uses, certain platform software, enabled for it. Functionality, performance or other benefit will vary depending on hardware and software configurations. Intel Virtualization Technology-enabled VMM applications are currently in development.

System and Maximum TDP is based on worst case scenarios. Actual TDP may be lower if not all I/Os for chipsets are used.

All information provided is subject to change at any time, without notice. Intel may make changes to manufacturing life cycle, specifications, and product descriptions at any time, without notice. The information herein is provided "as-is" and Intel does not make any representations or warranties whatsoever regarding the accuracy, completeness, or timeliness of the information, nor on the product features, availability, functionality, or compatibility of the products listed. Please contact system vendor for more information on specific products or systems.

Low Halogen: Applies only to brominated and chlorinated flame retardants (BFRs/CFRs) and PVC in the final product. Intel components as well as purchased components on the finished assembly meet IEC 61249-2-21 requirements, and the PCB / substrate meet IEC 61249-2-21 requirements. The replacement of halogenated flame retardants and/or PVC may not be better for the environment.

Some products can support AES New Instructions with a Processor Configuration update, in particular, i7-2630QM/7-2635QM, i7-2670QM/7-2675QM, i5-2430M/5-2435M, i5-2410M/5-2415M. Please contact OEM for the BIOS that includes the latest Processor Configuration update.