


SPACERS

Buy One or
Buy Bulk & SAVESWI & MSW Series
Special Spacers

Specifications:

- Material: Nylon
- Color: See Chart for Part-Specific Details

Features:

- Will not rust, corrode or deteriorate
- Act as an electrical insulator by preventing metal-to-metal contact
- Low-friction coefficient

Imperial

Item No.	A		B		C		Screw Size	Bulk Pack Qty.
	In	mm	In	mm	In	mm		
SWI1240A	0.125	3.20	0.305	7.70	0.500	12.70	#4	2000
SWS1810A	0.194	4.90	0.500	12.70	0.125	3.20	#10	1000
SWI1550A	0.194	4.90	0.500	12.70	1.000	25.40	#10	1000
SWI1570A	0.205	5.20	0.500	12.70	0.510	13.00	#10	1000
SWI1610A	0.250	6.40	0.740	18.80	0.250	6.40	#12	5000
SWI1620A	0.253	6.40	0.500	12.70	0.125	3.20	1/4	15000
SWI1760A	0.286	7.30	0.500	12.70	0.103	2.60	1/4	6000
SWI1840A	0.335	8.50	0.750	19.10	0.250	6.40	5/16	7400
SWI1860A	0.375	9.50	0.750	19.10	0.065	1.70	5/16	10000
SWI1880A	0.375	9.50	0.875	22.20	0.375	9.50	5/16	3500
SWI1910A	0.376	9.60	0.557	14.10	0.503	12.78	5/16	2000
SWI1930A	0.380	9.70	0.625	15.90	0.062	1.60	3/8	5000
SWI1960A	0.380	9.70	0.750	19.10	0.187	4.70	3/8	1000
SWI2020A	0.500	12.70	0.750	19.10	0.375	9.50	7/16	1000
SWI2040A	0.500	12.70	1.000	25.40	0.100	2.50	7/16	8000
SWI2050A	0.500	12.70	1.250	31.80	0.063	1.60	7/16	1000
SWI2090A	0.505	12.80	0.750	19.10	0.125	3.20	1/2	1000
SWI2100A	0.512	13.00	1.258	32.00	0.064	1.60	1/2	6000
SWI2150A	0.629	16.00	1.125	28.60	0.128	3.30	9/16	1000

Metric

Item No.	Color	A		B		C		Screw Size	Bulk Pack Qty.
		In	mm	In	mm	In	mm		
MSW1000A	Natural	0.122	3.10	0.236	6.00	0.295	7.50	M3	1000
MSW1010A	Natural	0.165	4.20	0.315	8.00	0.394	10.00	M4	1000
MSW1020A	Natural	0.169	4.40	0.354	9.00	0.055	1.40	M4	1000
MSW1040A	Natural	0.205	5.20	0.394	10.00	0.295	7.50	M5	1000
MSW1050A	Natural	0.205	5.20	0.394	10.00	0.394	10.00	M5	1000
MSW1060A	Natural	0.205	5.20	0.394	10.00	0.591	15.00	M5	1000
MSW1080A	Natural	0.205	5.20	0.394	10.00	0.197	5.00	M5	1000
MSW1090A	Natural	0.248	6.30	0.591	15.00	0.295	7.50	M6	1000
MSW1100C	Black	0.248	6.30	0.591	15.00	0.299	7.60	M6	1000
MSW1110A	Natural	0.248	6.30	0.591	15.00	0.394	10.00	M6	1000
MSW1120A	Natural	0.248	6.30	0.591	15.00	0.591	15.00	M6	1000
MSW1130A	Black	0.252	6.40	1.338	34.00	0.039	1.00	M6	1000
MSW1150A	Natural	0.252	6.40	0.500	12.70	0.193	4.90	M6	1000
MSW1160A	Natural	0.252	6.40	0.500	12.70	0.500	12.70	M6	1000
MSW1170A	Natural	0.252	6.40	0.563	14.30	0.063	1.60	M6	1000
MSW1180A	Natural	0.252	6.40	0.563	14.30	0.126	3.20	M6	1000
MSW1190A	Natural	0.252	6.40	0.709	18.00	0.079	2.00	M6	1000
MSW1200A	Natural	0.252	6.40	1.181	30.00	0.118	3.00	M6	1000
MSW1210A	Natural	0.256	6.50	0.591	15.00	0.118	3.00	M6	1000
MSW1220A	Natural	0.323	8.20	0.472	12.00	0.394	10.00	M8	1000
MSW1230A	Natural	0.323	8.20	0.472	12.00	0.984	25.00	M8	500
MSW1240A	Natural	0.323	8.20	0.709	18.00	0.394	10.00	M8	1000
MSW1250A	Natural	0.323	8.20	0.709	18.00	0.787	20.00	M8	1000
MSW1260A	Natural	0.331	8.40	0.669	17.00	0.079	2.00	M8	1000
MSW1270A	Natural	0.402	10.20	0.669	17.00	0.079	2.00	M10	1000
MSW1280A	Natural	0.406	10.30	0.591	15.00	0.394	10.00	M10	1000
MSW1290A	Natural	0.406	10.30	0.591	15.00	0.787	20.00	M10	1000
MSW1300A	Natural	0.413	10.50	0.827	21.00	0.098	2.50	M10	1000
MSW1320A	Natural	0.504	12.80	0.709	18.00	0.394	10.00	M12	1000
MSW1340A	Natural	0.827	21.00	1.457	37.00	0.118	3.00	M20	1000
MSW1350A	Natural	0.874	22.20	1.339	34.00	0.059	1.50	M20	3000