




Diagram illustrating the recommended mounting hole dimensions:

- Horizontal dimension: 5.10 [.201]
- Vertical dimension: 4.50 [.177]
- Text: RECOMMENDED MOUNTING HOLE



1. CRIMPED FERRULE HEX CRIMP SIZE .128"
2. CONTACT PIN TO SOLDER
3. MAX. PANEL THICKNESS = 6.8mm

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS; DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex						
8						DRAWN	G.R.S.	07/08/07								
7	FERRULE	COPPER	GOLD	1		CHECKED										
6	HEX NUT	BRASS	GOLD	1		ISSUED				PART DESCRIPTION MCX BULKHEAD CRIMP JACK (FOR RG-174/U, 188A/U, 316/U)						
5	LOCK WASHER	BRASS	GOLD	1		SHEET	1 OF 1									
4	CONTACT PIN	BER. COPPER	GOLD	1												
3	BARREL	BRASS	GOLD	1					PART NO. 252145							
2	INSULATOR	TEFLON	NATURAL	2												
1	BODY	BRASS	GOLD	1												
	DESCRIPTION	MATERIAL	FINISH	QTY	CAD FILE C:/252/252145.DWG			DWG. NO.	252145.DWG		REV.	A	SIZE	A	SCALE	NA