


Actual Size



LTR	REVISION	DATE	APPD
-	RELEASED	08-02-96	
A	WARNING NOTE ADDED	10-31-01	RM

**WARNING: DO NOT LOOK AT LED DIRECTLY WHEN POWER IS ON, USE IR CAMERA TO VIEW LED**

**NOTES:**

1. ALL DIMS ARE IN INCHES (MILLIMETERS).
2. TOLERANCE IS  $\pm 0.010"$  ( $\pm 0.25\text{mm}$ ) UNLESS OTHERWISE SPECIFIED.
3. LEAD SPACING IS MEASURED WHERE LEADS EMERGE FROM THE PACKAGE.
4. LEADS TO BE SOLDERABLE AND CAPABLE OF MEETING THE SOLDERABILITY REQUIREMENTS OF MIL-STD-202, METHOD 208.
5. MANUFACTURE DATE SHALL NOT BE OLDER THAN 26 WEEKS (6 MONTHS).

LEDTRONICS PART NO.	L.E.D. RADIATION COLOR	L.E.D. APPEARANCE	ABSOLUTE MAXIMUM RATINGS ( $T_a=25^\circ\text{C}$ )						ELECTRO-OPTICAL CHARACTERISTICS ( $T_a=25^\circ\text{C}$ )				Ifp=20mA PW=10 $\mu$ S DC=10%		VIEW ANGLE 2 $\theta_{1/2}$	$\Delta\lambda$ nm	$\lambda_P$ nm
			Pd mW	Ifp A	If mA	Vr V	Topr ( $^\circ\text{C}$ )		If mA	Vf=V typ/max	Ir $\mu$ A	Radiant Power mW/typ	Tr (ns)	Tf (ns)			
L200CWIR881	IR	WATER CLEAR	150	1.0	50	5	-45 TO +100		100	1.7/2.0	100	10/15	500	200	18	50	880

Tstg:  $-45^\circ\text{C}$  TO  $+100^\circ\text{C}$

Radiant Power Unit: ( $\text{mW}/\text{cm}^2$ )

**LED<sup>®</sup>**  
**LEDTRONICS, INC.<sup>™</sup>**  
23105 KASHIWA COURT  
TORRANCE, CA 90505

PROPRIETARY.  
This document contains Proprietary  
Information of LEDTRONICS, INC.  
It may not be copied, used or disclosed  
for any purpose without the prior express  
written consent of LEDTRONICS, INC.

.XXX  $\pm$  .010 TOLERANCE PER ANSI-Y14.5  
.XX  $\pm$  .025 (UNLESS OTHERWISE STATED)  
ANGLES  $\pm$  0°.30°  
FRACT.  $\pm$  1/32

TITLE							
L120CWIR881							
DWG NO		SCALE		SHEET		DATE	
DSDC0037		2:1		1 OF 1		08-02-96	
CODE IDENT NO.	DWG BY	CHK BY	QA	PL	MNFG	CUSTOMER	
8Z410	SMA	10-31-01					