

PM30-48S DC-DC Converters

The PM30 is a DC-DC converter which provides a regulated output at power levels up to 30 watts. It accepts a wide range DC input and provides a fully isolated, regulated output. In operation, either (or neither) input pin, as well as either (or neither) output pin can be grounded. * PM30 units provide full output power for ambient temperatures up to 50°C, with linear derating from 50°C to zero power at 105°C. In forced air applications, full output power can be maintained as long as the chassis temperature, as measured in the center of the unit's label, is maintained at less than or equal to 100°C.


Note: For safety agency approval of the end use equipment to safety standards (such as UL 1950 3rd Edition, CAN/CSA C22.2 No. 950-95, DIN VDE 0805 and EN 60950), the output of the converter is ELV if the input to the converter is ELV; the output of the converter is SELV only if its input is SELV: (when the output is between 60Vdc and 75Vdc, the output may be SELV only if the DC input is reinforced insulated from the – AC mains, and, SELV reliability fault tests are successfully conducted on the DC power source in combination with the converters; these test have already been performed on the converters). The input and output are to be both floating or both grounded. The converter is to be protected by the specified fuse, provided in the ungrounded leg. The CE mark on the product is applied to show conformance to the requirements outlined in the European Union's low voltage directive (72/23/EEC) as amended by the CE mark directive (93/68/EEC).

Specifications:

ITEMS		MODELS	PM30-48S Series			
			PM30-48S03	PM30-48S05	PM30-48S12	PM30-48S15
Nominal Output Voltage	V	3.3	5	12	15	
Voltage Accuracy	-	± 1%				
Output Current (Power) @ 50°C	A/W	7.50 (24.80)	6.00 (30.0)	2.50 (30.0)	2.00 (30.0)	
Operating Temperature	-	-25°C to + 105°C. Derate linearly above + 50°C to 0 watts at 105°C				
Output Voltage Adjustment Range	V	3.3 – 3.6	4.5 – 5.5	10.8 – 13.2	13.5 – 16.5	
Output Ripple (20MHz BW)	mV	20mV RMS / 75 mV p-p		25mV RMS / 100 mV p-p		
Line Regulation	mV	6.6	10	24	30	
Load Regulation (10% - 100%)	mV	33	50	120	150	
Remote On /Off	-	Logic 1 or open enables unit, logic 0 or short shuts unit down. Referenced to -Vin				
Temperature Coefficient	-	± 0.01% / °C				
Overshoot	-	No overshoot at turn on, turn off, power failure or removal of a short circuit				
Input Voltage Range	-	36 – 75 Vdc				
Efficiency (Typical)	%	72	80			
No Load Input Power	W	0.4				
Conducted EMI	-	EN55022 Level B, FCC Level B with external filter				
Short Circuit Protection	-	Continuous				
Overvoltage Clamp Point (fixed)	V	4.7 max.	6.5 max.	14 max.	17.5 max	
Isolation (Input to Output)	-	900Vac, 1500Vdc, 10MΩ				
Regulatory Agency Compliance**	-	ETSI-300-132-2, Bellcore GR-1089, UL1950 3 rd Edition, CAN/CSA C22.2 No. 950-95, EN 60950, VDE 0805				
Mounting & Connections	-	0.040" diameter, 0.22" long solderable pins				
Cover	-	0.032" anodized aluminum				
Size (W.H.D.)	in	2.5" x 3.0" x 0.335"				
Storage Temperature	-	-40°C to + 105°C				
Cooling	-	Convection cooling allows full o/p rating. Contact factory for rating w/external forced air				
Vibration	-	2.5G RMS, 10Hz – 50 Hz, random vibration, 10 minutes per axis				
Relative Humidity	-	5% - 95%, non-condensing				
Altitude	-	10,000 feet max. operating / 45,000 feet max. storage				
Fungus Proofing	-	Units are inherently fungus inert				
Thermal Cycling	-	1 hour @ -25°C ramped to 1 hour @ +25°C ramped to 1 hour @ +100°C, 10 cycles ramp = 5°C/ minute				
Warranty	-	2 year warranty includes parts and labor				


****Regulatory Agency compliance testing is in process. Check individual unit's label for appropriate agency logos.**

Note: Regulation values pertain to operation with output currents above 10% of rated load current on main output.

Total Output Power vs. Ambient Operating Temperature





PM30-48S DC-DC Converters

Recommended Circuit Hook up:



Notes:

1. Input can have -Vin, +Vin or neither terminal grounded. Input ground connection should be placed as close to PM unit input as possible.
2. Output can have -Vo, +Vo or neither terminal grounded. Output ground connection should be placed as close to PM unit input as possible.
3. Recommended input fusing: 2A (Buss PCB2, or equivalent).
4. Remote on/off control: low impedance path, or logic 0, referenced to -Vin disables unit output. Open circuit, or logic 1, referenced to -Vin enables output.
5. Output voltage programming: Resistor connected from Pin 5 to either -V or +V will generate increased or decreased output voltages, respectively, as follows.



Mechanical Information:

PM30 units are designed for installation on printed wiring boards. The chassis has four tabs built in to provide clearance between the unit body and the PCB to allow for wave soldering. During wave soldering, the top surface of the board to which the PM unit is mounted (measured 1/2" from the edge of the PM unit) should be maintained at a temperature of no more than 180°C for no more than 30 seconds. The chassis of the PM unit is electrically isolated from both the input and output circuitry and should be left floating in a typical installation.

