


2	GREY	SICMA RCPT CONN SLD W/ 1.5 GRY 10CKT	0987881108
1	BLACK	SICMA RCPT CONN SLD W/ 1.5 BLK 10CKT	0987881101
CODING	COLOR	DESCRIPTION	MATERIAL NUMBER

SUPPORT AREA


WIRE INTERFACE SUPPORT



AREA

$\pm 0.3B$

AREA




LATCHING AREA


AREA

$\pm 0.3B$

SICMA 2 TERMINAL POSITION AND CAVITIES POSITION



MATING / UNMATING OVERALL DIMENSIONS




PIN CONN.

28.9 MAXI

24.75 MAXI

1.8 MINI


3.2 MINI



78.80 MAXI


35.8 MAXI

OVERALL DIMENSION AFTER LOCK



58.2 MAXI

OVERALL DIMENSION BEFORE LOCK




65.1 MAXI

NOTES:



1. MATERIALS: SEE CHART
2. FINISHES: N/A
3. PRODUCT SPECIFICATION: AS-98788-001
4. PACKAGING INFORMATION: PK-98788-002
5. MATES WITH: 0987891101(BLACK), 0987891108(GREY)
6. 2MM2 WIRES NOT ALLOWED FOR THIS PRODUCT
7. CONNECTOR TIGHTENING STRENGTH ON WIRING INTERFACE:
 - 200 TO 250 N WITH PUSH TEST
 - 50 TO 250 WITHOUT PUSH TEST
8. AREAS SHOWN AS: AREA
 - DO NOT LOCK WIRING INTERFACE
 - DO NOT DAMAGE THE PART

ISOMETRIC VIEW




REVISED (MINOR) EC NO: G2008-0313 DRAWN: VLOUVANCOUR 2008/02/12 CHKD: YIGEL 2008/02/12 APPR: LSTICKEIR 2008/02/13 A1	QUALITY SYMBOLS ▽=0 ▽=0 DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	 FIRST ANGLE PROJECTION	
			mm	INCH	DRAWN BY VLOUVANCOUR	DATE 2007/08/02	TITLE SICMA RCPT CONN SLD W/ 1.5 10CKT		
		4 PLACES	± ---	± ---	CHECKED BY	DATE			
		3 PLACES	± ---	± ---	YIGEL	2007/08/02			
		2 PLACES	± ---	± ---	APPROVED BY	DATE			
		1 PLACE	± 0.2	± ---	LSTICKEIR	2007/08/02	MOLEX INCORPORATED		
		ANGULAR ± 2 °		MATERIAL NO.		DOCUMENT NO.			
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-98788-005			
				SIZE A2		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			SHEET NO. 1 OF 2

CAVITY MARKING


③ TPA STROKE 6.1 ± 0.3 

Z-Z


CAVITY MARKING



VIEW WITHOUT TPA



VIEW WITH TPA LOCKED

CUSTOMER P/N
CUSTOMER LOGOSUPPLIER TPA REV LEVEL
TPA PRINT MARKING


AREA FOR ITG CODE

CONN RAW MATERIAL

SUPPLIER CONN P/N


SUPPLIER REV LEVEL
LOF EQUIPED CONN

TPA RAW MATERIAL



TPA SUPPLIER MARKING

SUPPLIER CONN REV LEVEL



DATUM YEAR / MONTH

CONN SUPPLIER MARKING

CONN PRINT MARKING

3	1	Piece	SICMA RCPT CONN SLD 10CKT	0987880206	-	SILICONE		0.642g					
2	1	Piece	SICMA RCPT CONN TPA YEL 10CKT	0987880114	-	POLYESTER	YELLOW	1.469g					
1	1	Piece	SICMA RCPT CONN 1.5 GRY 10CKT	0987880108	-	(PBT),	GREY	7.459g					
			SICMA RCPT CONN 1.5 BLK 10CKT	0987880101	-	UL94 HB	BLACK						
Item	Amount	Unit	Description	Material-Number	Packing	Material		Weight Calculated					
REVISED (MINOR) EC NO: G2008-0313 DRAWN: VLOUVANCOUR 2008/02/12 CHKD: YIGEL 2008/02/12 APPR: LSTICKEIR 2008/02/13 A1			QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	FIRST ANGLE PROJECTION			
			▽=0 ▽=0			MM ONLY				2:1	METRIC		
						DRAWN BY DATE		TITLE		SICMA RCPT CONN SLD W/ 1.5 10CKT			
						VLOUVANCOUR 2007/08/02							
						CHECKED BY DATE							
						YIGEL 2007/08/02							
					APPROVED BY DATE		MOLEX INCORPORATED						
					LSTICKEIR 2007/08/02								
					ANGULAR ± 2 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-98788-005		2 OF 2		
				SIZE A2		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							