

Magnet Wire Terminals Systems

IDC MAG-MATE Wire , SIAMEZE, AMPLIVAR and Cluster Blocks

TE connectivity

Table of Contents

Standard MAG-MATE Terminals

Introduction ... 1
Interconnection System ... 2
Termination Sequence ... 2
Test Results ... 3
300 Box Poke-In Terminals ... 4
500 Box Poke-In Terminals ... 6
Poke-In Tab Terminals ... 7
MAG-MATE Terminals with extended leaf-spring ... 8
300 Box Poke-In Terminals ... 9
Tab Receptacle Terminals ... 9
187 Box F-Crimp Terminals ... 10
300 Box F-Crimp Terminals ... 10
Posted PCB Terminals ... 11
300 Box Posted PCB Terminals ... 11
MAG-MATE Edge Leaf Terminals ... 12
187 Box Posted PCB Terminals ... 13
187 Box Tab Terminals ... 13
300 Box Tab Terminals ... 14
Pin Receptacle Terminals ... 15
Pin I/O Terminals ... 16
110 Series FASTON Tab Terminals ... 17
187 Series FASTON Tab Terminals ... 18
187 Series Combination Poke-In FASTON Terminals ... 18
250 Series FASTON Tab Terminals ... 21
Typical Plastic Cavity ... 23

Slim Line MAG-MATE Terminals

Introduction ... 25
187 Series FASTON Tab Terminals ... 26
250 Series FASTON Tab Terminals ... 26
Posted PCB SOLDER Terminal ... 26
Offset Tab Terminals ... 27

Mini MAG-MATE Terminals

Introduction ... 29
Poke-In Terminal ... 30
Posted Terminal ... 31
FASTON Tab Terminals ... 31
Crimp Wire Barrel Terminal 31

SIAMEZE Terminals

Introduction ... 32
Lead Lok Terminals Introduction ... 33
SIAMEZE Interconnection System ... 34
Lead Lok Interconnection System ... 35
Wire-to-Wire Terminals ... 36
Receptacle Terminals (Wire to Blade) ... 37
Pin Terminals ... 37
Post Terminals ... 38
110 Series (2.8 mm wide) FASTON Tab Terminals ... 39
187 Series (4.75 mm wide) FASTON Tab Terminals ... 40
250 Series (6.3 mm wide) FASTON Tab Terminals ... 41
Typical Plastic Cavity Pockets ... 42

MAG-MATE and SIAMEZE Application Tooling

Introduction ... 44
MPT-5S/L Machine for Mag Wire Coil Termination utilizing SIAMEZE and Lead Lok terminals ... 45
Application Tooling for MAG-MATE Terminals ... 46
Hand Tools ... 46
Application Tooling for MAG-MATE Terminals ... 47
LPT-522 Linear Product Terminator ... 48

Table of Contents

AMPLIVAR Splices
Introduction ... 50
General Application Guidelines ... 52
Suggested Splice Selection Procedure ... 52
Technical Documents ... 52
9 Serrations —Pigtail Type ... 53
7 Serrations —Pigtail Type ... 53
5 Serrations —Thru Type ... 54
5 Serrations —Pigtail Type ... 55
Miniature Splice —Pigtail Type ... 55

AMPLIVAR Terminals
Introduction ... 56
Ring Tongue Terminals ... 57
Stud Retaining Terminals ... 58
Alternator Eyelet Terminal ... 58
125 Series Blade ... 59
187 Series FASTON Tabs1 ... 59
250 Series FASTON Tabs1 ... 59
250 Series FASTON Receptacles1 ... 60
187 Series FASTON Flag Receptacles ... 61
250 Series FASTON Flag Receptacles ... 61
Pin Receptacles ... 61
250 Series Stator Receptacles —7 Serrations ... 62
Stator Terminal —Receptacle .250 x .032 [6.35 x 0.81] ... 62

Cluster Blocks
Introduction ... 63
Cluster Blocks 2.29 [.090] Pin Size (Lead Wire and Direct Connect) ... 64
Cluster Blocks 3.18 [.125] Pin Size (Lead Wire and Direct Connect) ... 66
AMPLIVAR and Cluster Blocks Application Tooling
AMPLIVAR Product Terminator (APT) ... 68
AMP-O-LECTRIC Termination Machines ... 70
Crimp Quality Monitor ... 70
Model G Splice Terminating Machine, P/N 356462-2 & Applicator ... 71
Standard G Splice Applicator ... 71
Entry Level Terminator (ELT), 1338600-(x) ... 71
Applicators ... 72
AMPOMATOR CLS IV+ Lead-Making Machines, 356500-1, -2 ... 73
Gamma 333 PC Lead-Making Machine, Three Stations, 1-528324-1 ... 73

MTM Crimpband Splices
Introduction ... 74
MTM Crimpband Interconnection System ... 75
11 Serrations ... 76
9 Serrations ... 76
7 Serrations ... 77

RTM Crimpband Splices
Introduction ... 78
RTM Crimpband Interconnection System ... 79
20 Ridges ... 80
14 Ridges ... 80
10 Ridges ... 80
9 Ridges ... 81
8 Ridges ... 81
7 Ridges ... 81
6 Ridges ... 84
3 Ridges ... 85
Crimpband Application Tooling ... 86

Table of Contents

Power Splice

Introduction 87
Power Splice Application Tooling 89
Technical Information 90
Terminal Stud Hole Size 94
Engineering Notes 95

Standard MAG-MATE Terminals

Product Facts

- Terminates film-insulated copper and aluminum magnet wire
- Eliminates need for pre-stripping conductors
- Eliminates need to post insulate termination
- Excess magnet wire is automatically trimmed during the termination process
- Simultaneously terminates two magnet wires of the same size in one terminal (for splicing or bi-filing)
- Various lead wire attachment options available
- Available in strip form for semi-automatic or fully automatic insertions
- Available in loose piece form for hand tool insertions
- Varnish resist tab terminals are available for special applications
- High speed, fully automated integrated systems provide uniform terminations reliably at the lowest possible applied cost
- Clean metal-to-metal interface produces stable, gas-tight electrical terminations free of oxides and other contaminants
- Recognized under the Component Recognition Program of Underwriters Laboratories Inc., File No. E13288,Vol. 1, Sec 29

Applications

- **Motor windings and connections**
- **Coil connections**
- **Transformer windings and connections**
- **Bobbin connections**
- **Lighting ballasts**
- **Power supplies**



TE offers a full selection of AMP Standard MAG-MATE Insulation Displacement Crimp (IDC) terminals for magnet wire terminations.

MAG-MATE terminals are available in poke-in, poke-in tab, splice, crimp wire barrel, solder post, quick connect tab, pin and receptacle styles.

Standard MAG-MATE terminates magnet wire ranging from 34-12 AWG [0.16 -2.05 mm].

Each IDC slot size terminates a range of up to four consecutive magnet wire sizes.



Two magnet wires with the same diameter can be terminated in one terminal except as noted.

According to TE specifications MAG-MATE cavities are either integrated into coil bodies or specially designed cavity housings. The magnet wires are precisely positioned in the plastic cavity slots.

The MAG-MATE Inserter cuts the terminals from the strip and places the terminals over the magnet wire into the plastic cavities.

During this operation, small stripping shoulders in the IDC slot remove the film insulation from the magnet wire.

Wiping action between the wire and terminal removes oxides or other contaminants present on both the conductor and the terminal slot side walls, producing a clean, stable, gas-tight electrical termination.

Residual spring energy in the terminal causes the side walls of each IDC slot to function as opposing cantilever beams.

This constant pressure results in an intimate metal-to-metal interface, providing a reliable, long-term connection.

The AMP MAG-MATE Inserter may be used as a semi-automatic bench machine or integrated into production lines for fully-automatic applications.

*Contact TE Engineering for guidance regarding aluminum

Standard MAG-MATE Terminals (Continued)

Standard MAG-MATE Interconnection System

How the System Operates

① Trim Blade

This part cuts off the excess magnet wire and the wire support at the front of the cavity.

② Insertion Finger

The insertion finger is part of the MAG-MATE Inserter. It pushes the terminal that was sheared from the carrier strip through the inserter "tube" into the positioned cavity.

③ Contact

Various wire attachments in three different sizes,.187, .300,.500 cavity height (see tables).

④ IDC Slot

In different sizes for magnet wire diameters from 34-12 AWG [0.16-2.05 mm]. Strain relief slots available for high vibration applications.

⑤ Stripping Shoulders

During the insertion process, these shoulders strip the film insulation from the magnet wire in four areas.

⑥ Locking Barbs

Terminal retention is secured in the cavity by four locking barbs.

⑦ Plastic Cavity

Integration of plastic cavities into final unit must be in accordance with TE Application Specifications. **Consulting TE is required for design in.**

⑧ Cavity Slot for Wire

The width has to be in accordance with the wire size (see Application Specification).

⑨ Magnet Wire

The magnet wire is positioned down into the plastic cavity slots.

⑩ Wire Support Block

The block supports the magnet wire during the cutting process. The magnet wire is cut flush to the cavity front side.

⑪ Support Anvil

The anvil supports the wire during the insertion process.





Termination Sequence

A = Prepare
B = Insert
C = Finish



① Trim Blade
② Insertion Finger
③ Poke-In Contact
④ Plastic Cavity
⑤ Magnet Wire
⑥ Support Anvil

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

Standard MAG-MATE Terminals (Continued)

Test Results

Standard and Slim Line MAG-MATE products have been submitted to the following tests without significant millivolt increase:

Current Cycling—
480 cycles with each cycle consisting of 15 minutes "ON" followed by 15 minutes "OFF"

Thermal Shock—
25 cycles with each cycle consisting of 30 minutes at 125°C followed by 30 minutes at -65°C

Humidity—Temperature Cycling
10 cycles between 25°C and 65°C at 95% RH

Heat Age—
33 days at 118°C

Mini MAG-MATE products have been submitted to the following tests in addition to those listed without significant millivolt increase:

Vibration—
10-55-01- Hz traversed in 1 minute at .06 inches total excursion; 2 hours in each of 3 mutually perpendicular directions.

Industrial Gas with Chlorine—
1000 exposure to 200 ppb each of sulphur dioxide, nitrogen dioxide, hydrogen sulphide and 50 ppb chlorine.



Resistance vs Thermal Shock (Copper Wire)



Resistance vs Current Cycles (Copper Wire)



Test Current produces 100°C Magnet Wire Operating Temperature



Current Rating Curves

The diagram shows the temperature rise of the contact, depending on the magnet wire size being applied.

Product Specifications

describe technical performance characteristics and verification tests. They are intended for the Design, Test and Quality Engineer.

108-2012	Standard .187 and .300 MAG-MATE Terminals
108-2053	Standard .500 Box MAG-MATE Terminals
108-1484	Slim Line MAG-MATE Terminals
108-2016	Mini MAG-MATE Terminals

Note: For all applications, TE recommends that samples of the magnet wire to be used be submitted for engineering evaluation.

Standard MAG-MATE Terminals (Continued)

300 Box Poke-In Terminals

Material
Tin plated brass

Typical Cavity Size 2
(See page 23)



A



B

Type	Copper Magnet Wire Range[1] AWG	mm	Lead Wire Range[3] AWG	mm²	Mating[5] Tab	Stock Thickness	Strip	Part Number*
A 300 Box Standard IDC Locking Poke-in	34-33	0.16-0.18	20-18	0.5-0.9	.135 x .020 3.40 x 0.50	.010 0.25		63662-1
	33-31	0.18-0.23	20-18	0.5-0.9	.135 x .020 3.40 x 0.50	.010 0.25		62431-1
	31-28	0.23-0.32	20-18	0.5-0.9	.135 x .020 3.40 x 0.50	.012 0.30		1217234-1
	30-27	0.25-0.36	20-18	0.5-0.9	.135 x .020 3.40 x 0.50	.012 0.30		62429-1
	27-23	0.36-0.57	20-18	0.5-0.9	.135 x .020 3.40 x 0.50	.016 0.41		62935-1
	25-22[2]	0.45-0.64	20-18	0.5-0.9	.135 x .020 3.40 x 0.50	.016 0.41		63658-1
	22-20[2]	0.64-0.81	20-18	0.5-0.9	.135 x .020 3.40 x 0.50	.016 0.41		62420-1
	20[2]	0.81	20-18	0.5-0.9	.135 x .020 3.40 x 0.50	.016 0.41		63591-1
	19-17[2]	0.91-1.15	20-18	0.5-0.9	.135 x .020 3.40 x 0.50	.016 0.41		62833-1
B[4] 300 Box Standard IDC w/ Strain Relief Slot Locking Poke-In	30	0.25	20-18	0.5-0.9	.135 x .020 3.40 x 0.50	.012 0.30		63786-1
	29-28	0.29-0.32	20-18	0.5-0.9	.135 x .020 3.40 x 0.50	.012 0.30		1217011-1
	28-26	0.32-0.40	20-18	0.5-0.9	.135 x .020 3.40 x 0.50	.012 0.30		1217368-1
	27-23	0.36-0.57	20-18	0.5-0.9	.135 x .020 3.40 x 0.50	.016 0.41		63789-1

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.
2 Single magnet wire only; 22 AWG [0.64 mm] or larger unless otherwise noted.
3 Solid or overcoated stranded lead wire only. Product will also accept Poke-In Tab Terminal shown on page 7.
4 Strain relief slot for high vibration applications.
5 See page 7 for mating tab options.
* Recognized under the Component Program of Underwriters Laboratories, Inc.



POKE-IN SYSTEM: SOLID WIRE CONNECTION



POKE-IN SYSTEM: STRANDED LEAD WIRE AND POKE-IN TAB CONNECTION

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

www.te.com/appliances

Standard MAG-MATE Terminals (Continued)



A



B



C



D

Type	Copper Magnet Wire Range[1] AWG	mm	Mating Tab[3]	Stock Thickness	Strip Part Number*
A 300 Box Standard IDC Non-Locking Poke-In MKI	35-32	0.14-0.20	.135 x .020 3.40 x 0.50	.010 0.25	969082-1
	33-30	0.18-0.265	.135 x .020 3.40 x 0.50	.010 0.25	926850-2
	30-26	0.265-0.40	.135 x .020 3.40 x 0.50	.013 0.32	926851-2
	26-21.5[2]	0.40-0.67	.135 x .020 3.40 x 0.50	.016 0.41	926852-2
	21.5-18.5[2]	0.67-0.95	.135 x .020 3.40 x 0.50	.016 0.41	928770-2
	19.5-17[2]	0.91-1.13	.135 x .020 3.40 x 0.50	.016 0.41	1-928771-4
B 300 Box Standard IDC Non-Locking Poke-In MKII	33-30	0.18-0.265	.135 x .020 3.40 x 0.50	.013 0.32	964337-2
	30-26	0.265-0.40	.135 x .020 3.40 x 0.50	.013 0.32	964338-2
	26-22[2]	0.40-0.63	.135 x .020 3.40 x 0.50	.013 0.32	964339-2
	22-19.5[2]	0.63-0.85	.135 x .020 3.40 x 0.50	.013 0.32	964340-2
	19.5-17[2]	0.85-1.12	.135 x .020 3.40 x 0.50	.013 0.32	964341-2

Type	Copper Magnet Wire Range[1] AWG	mm	Feature	Stock Thickness	Strip Part Number
C 433 Box Standard IDC with Receptacle for Tabs .110 x .020 [2.8 mm x 0.5 mm] or .110 x .032 [2.8 mm x 0.8 mm]	33-30	0.18-0.265	w/o Dimple Dimple	.013 0.32	1-964114-1 964114-1
	30-26	0.265-0.40	w/o Dimple Dimple	.013 0.32	1-964108-1 964108-1
	26-22	0.40-0.63	w/o Dimple Dimple	.013 0.32	1-928854-1 928854-1
	22-19.5[2]	0.63-0.85	w/o Dimple Dimple	.013 0.32	1-964106-1 964106-1
D 433 Box Standard IDC with Receptacle for Tabs .187 x .020 [4.8 mm x 0.5 mm] or .187 x .032 [4.8 mm x 0.8 mm]	33-31	0.18-0.265	Dimple	.013 0.32	1740574-1
	26-23	0.40-0.57	w/o Dimple	.013 0.32	964252-1
	22.5 - 20[2]	0.60-0.80	w/o Dimple	.013 0.32	964110-1
	19-17[2]	0.90-1.13	w/o Dimple	.013 0.32	964111-1
	19-17[1]	0.90-1.12	w/o Dimple	.013 0.32	1534234-1

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.
2 Single magnet wire only; 22 AWG [0.64 mm] or larger unless otherwise noted.
3 See page 7 for mating tab options.
* Recognized under the Component Program of Underwriters Laboratories, Inc.

Standard MAG-MATE Terminals (Continued)

300 Box Poke-In Terminals

(Continued)

Material

Tin plated brass

Typical Cavity Size 2

(See page 23)

Note: Special cavity required for Tri-slot splice terminal. See Application Spec. 114-2046.



A



B

Type	Copper Magnet Wire Range[1] AWG	mm	Mating Tab[4]	Stock Thickness	Strip Part Number
A[3] 300 Box Standard IDC w/Strain Relief Slot Non-Locking Poke-In	27-26	0.36-0.40	.135 x .020 3.40 x 0.50	.016 0.41	1217691-1
	25.5-24	0.43-0.51	.135 x .020 3.40 x 0.50	.016 0.41	1217690-1
	23.5-22[2]	0.54-0.64	.135 x .020 3.40 x 0.50	.016 0.41	1217689-1
	21.5-20[2]	0.68-0.81	.135 x .020 3.40 x 0.50	.016 0.41	1217688-1
B 300 Box Standard IDC Non-Locking Poke-In	30-27	0.25-0.36	.135 x .020 3.40 x 0.50	.016 0.41	1217221-1
	27-23	0.36 -0.57	.135 x .020 3.40 x 0.50	.016 0.41	63632-1
	23-20[2]	0.57-0.81	.135 x .020 3.40 x 0.50	.016 0.41	1217533-1
	19-17	0.91-1.15	.135 x .020 3.40 x 0.50	.016 0.41	1742347-1
	27-23[2] 19-17[2] 18[2]	0.36-0.57 0.91-1.15 0.8-0.9	.135 x .020 3.40 x 0.50	.016 0.41	63975-1

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.
2 Single magnet wire only; 22 AWG [0.64 mm] or larger.
3 Strain relief slot for high vibration applications.
4 See page 7 for mating small tab options.
* Recognized under the Component Program of Underwriters Laboratories, Inc.

500 Box Poke-In Terminals

Material

Tin plated brass

Typical Cavity Size 4

(See page 23)

Note: Mating poke-in tab 1217324-1 (See Type H, Page 7)



C



D

Type	Copper Magnet Wire Range[1] AWG	mm	Stock Thickness	Strip Part Number
C 500 Box Standard IDC Non-Locking Poke-In	23-19.5	0.57-0.86	.016 0.41	1217069-1
	19-17	0.91-1.15	.016 0.41	1217068-1
	16-15	1.29-1.45	.016 0.41	1217067-1
D[3] 500 Box Standard IDC w/ Strain Relief Slot Non-Locking Poke-In	23-21.5	0.57-0.68	.016 0.41	1217358-1
	21-19.5	0.72-0.86	.016 0.41	1217357-1
	19-17	0.91-1.15	.016 0.41	1217356-1
	17-16	1.15-1.29	.016 0.41	1742203-1
	16-15	1.29-1.45	.016 0.41	1217355-1
	14-13[2]	1.61-1.83	.016 0.41	1217579-1

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.
2 Single magnet wire only.
3 Strain relief slot for high vibration applications.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

www.te.com/appliances

Standard MAG-MATE Terminals (Continued)

Poke-In Tab Terminals

Material

Tin plated brass



A



B



C



D



E

Type	Lead Wire Size[1] AWG	Lead Wire Size[1] mm²	Ins. O.D.	Stock Thickness	Strip Part Number
A 90° Up	22-18	0.3-0.9	—	.018 0.46	62895-1*
				.020 0.51	63410-1
B 90° Up w/Ins. Sup.	24	0.2	.040-.060 1.02-1.52	.018 0.46	1742828-1
	22-18	0.3-0.9	.060-.100 1.52-2.54	.018 0.46	62896-1*
	18-14	0.8-2.0	.090-.140 2.29-3.56	.018 0.46	63218-1
C Straight	22-18	0.3-0.9	—	.020 0.51	62897-1*
	18-14	0.8-2.0	—	.020 0.51	63775-1
D Straight w/Ins. Sup.	22-18	0.3-0.9	.060-.100 1.52-2.54	.020 0.51	62898-1*
	18-14	0.8-2.0	.090-.140 2.29-3.56	.020 0.51	63397-1
	22-17	0.3-1.0	.118 MAX. 3.00 MAX.	.018 0.45	281622-2[2]
	22-17	0.3-1.0	.118 MAX. 3.00 MAX.	.018 0.45	281623-2[2]
	20-17	0.5-1.0	.063-.090 1.60-2.30	.018 0.45	964101-2[3]
	20-17	0.5-1.0	.063-.090 1.60-2.30	.018 0.45	964290-1[4]
E 90° Down	22-18	0.3-0.9	—	.018 0.46	63364-1
	18-14	0.8-2.0	—	.018 0.46	1742125-1

1 Stranded, fused stranded or solid lead wire.
2 Can be selectively bent inside applicator. With support flanges, can only be used in combination with modified cavity IA-84-5157
3 Can be selectively bent inside applicator, Non-locking
4 Can be selectively bent inside applicator. Non-locking;use with housing
* Recognized under the Component Program of Underwriters Laboratories, Inc.

Note: All tab terminals accept stranded, fused stranded or solid lead wire.

Standard MAG-MATE Terminals (Continued)

Poke-In Tab Terminals

Material

Tin plated brass

Pre-Tin plated brass



K



L



F



I



J

Type	Lead Wire Size[1] AWG	Lead Wire Size[1] mm²	Ins. O.D.	Stock Thickness	Strip Part Number
F 90° Down w/Ins. Sup.	24-20	0.2-0.5	.048-.078 1.22-1.98	.020 0.51	1742410-1
	22-18	0.3-0.9	.060-.100 1.52-2.54	.020 0.51	1742211-1
	18-14	0.8-2.0	.090-.140 2.29-3.56	.020 0.51	63458-1
I Flag - 300 Box only	20-16	0.5-1.4	—	.020 0.51	1217406-1
J Flag - 500 Box only	18-14	0.8-2.0	.080-.120 2.03-3.05	.020 0.51	1217324-1
K Bridge Contact	—	—	—	.020 0.51	1987199-1
L PCB Contact	—	—	—	.020 0.51	1217041-1

Note: All tab terminals accept stranded, fused stranded or solid lead wire.

MAG-MATE Terminals with extended leaf-spring

Material

Pre-tinned copper alloy



M

Type	Copper Magnet Wire Range AWG	Copper Magnet Wire Range mm	Stock Thickness	Strip Part Number
M Mag-Mate Terminal with extended Leaf-Spring	33-30	0.18-0.265	.013 0.32	1740603-1
	30-26	0.265-0.40	.013 0.32	1740698-2
	26.5-22.5	0.375-0.60	.013 0.32	1534110-1
	22.5-20	0.60-0.80	.013 0.32	969125-1*
	19.5-17	0.85-1.12	.013 0.32	1418686-1

*Single magnet wire

Note: Special cavity is required,contact TE connectivity for information.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

Standard MAG-MATE Terminals (Continued)

300 Box Poke-In Terminals

Material

Tin plated brass

.300 [7.62] Series Box

Typical Cavity Size 2

(See page 23)

Note: Special cavity required for Tri-slot splice terminal. See application SPEC 114-2046



A



B

Type	Copper Magnet Wire Range[1] AWG	mm	Stock Thickness	Strip Part Number
A 300 Box Standard IDC Splice	22-20	0.64-0.81	.016 0.41	1217973-1
	19-17	0.91-1.15	.020 0.51	1742159-1[4]
B 300 Box Standard IDC Tri-Slot Splice	28-24	0.32-0.51	.016 0.41	1217858-1
	23-20[2]	0.57-0.81	.016 0.41	1217853-1
	27-23	0.36-0.57	.016 0.41	1217613-1
	18[4]	0.8-0.9		
	19-17[2]	0.91-1.15		
	25-22[3]	0.45-0.64	.016 0.41	1217209-1
	18[4]	0.8-0.9		
	23.5-20[2]	0.54-0.81		

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.
2 Single magnet wire only; 22 AWG [0.64 mm] or larger.
3 Single solid or fused stranded lead wire only.
4 Special cavity required for 1742159-1.

Tab Receptacle Terminals

Material

Tin plated phos. bronze

Note: Special cavity required. Contact TE Engineering for details.



C

Type	Copper Magnet Wire Range[1] AWG	mm	Mating Tab	Stock Thickness	Strip Part Number
C 185 Box Standard IDC Tab Receptacle	32-31	0.20-0.23	.070 x .020 1.78 x 0.51	.010 0.25	1217538-1
	30-28	0.25-0.32	.070 x .020 1.78 x 0.51	.010 0.25	1217457-1
	29-28	0.29-0.32	.070 x .020 1.78 x 0.51	.010 0.25	1217458-1
	28-27	0.32-0.36	.070 x .020 1.78 x 0.51	.010 0.25	1742781-1

1 Two magnet wires may be terminated in the same slot if diameters are equal.

Standard MAG-MATE Terminals (Continued)

187 Box F-Crimp Terminals

Material

Tin plated brass

.187 [4.75] Series Box

Typical Cavity Size 1

(See page 23)



A



B

Type	Copper Magnet Wire Range[1] AWG	Copper Magnet Wire Range[1] mm	Lead Wire Range[3] AWG	Lead Wire Range[3] mm²	Ins. O.D.	Stock Thickness	Strip Part Number
A 187 Box Standard IDC F-Crimp	33-31	0.18-0.23	26-22	0.12-0.3	—	.010 0.25	63039-1
	30-28	0.25-0.32	26-22	0.12-0.3	—	.012 0.30	63036-1
	27-25	0.36-0.46	26-22	0.12-0.3	—	.012 0.30	62609-1[4]
	26-24	0.40-0.51	22-18	0.3-1.0	—	.012 0.30	1217146-1
	24-22[2]	0.51-0.64	26-22	0.12-0.3	—	.012 0.30	62610-1[4]
B 187 Box F-Crimp w/Ins Sup.	27-25	0.36-0.46	22-18	0.3-1.0	.071-.088 1.80 -2.23	.012 0.30	63856-1

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.
2 Single magnet wire only.
3 Stranded, fused stranded or solid lead wire.
4 Strip rereeled to feed through mini-applicator to crimp lead wire first, magnet wire termination is secondary operation.

300 Box F-Crimp Terminals

Material

Tin plated brass

.300 [7.62] Series Box

Typical Cavity Size 2, when "C" dimension is .120 [3.05]

(See page 23)

Typical Cavity Size 6, when "C" dimension is .070 [1.78]

(See page 23)



C

Type	Copper Magnet Wire Range[1] AWG	Copper Magnet Wire Range[1] mm	Dim. C	Lead Wire Range[3] AWG	Lead Wire Range[3] mm²	Stock Thickness	Strip Part Number
C 300 Box Standard IDC F-Crimp	33-31	0.18-0.23	.070 1.78	22-18	0.3-1.0	.012 0.30	63235-1
			.120 3.05	24-20	0.2-0.6	.012 0.30	63420-1
	31-28	0.23-0.32	.070 1.78	22-18	0.3-1.0	.012 0.30	63236-1
			.070 1.78	24-20	0.2-0.6	.012 0.30	1742614-1
	30-27	0.25-0.36	.120 3.05	24-20	0.2-0.6	.012 0.30	62992-1
	28-24	0.32-0.51	.120 3.05	24-20	0.2-0.6	.012 0.30	63641-1
	27-24	0.36-0.51	.070 1.78	22-18	0.3-1.0	.012 0.30	63237-1
	27-23	0.36-0.57	.120 3.05	24-20	0.2-0.6	.016 0.41	62459-1
	25-22	0.45-0.64	.070 1.78	22-18	0.3-1.0	.012 0.30	63690-1
	22-20[2]	0.64-0.81	.120 3.05	24-20	0.2-0.6	.016 0.41	62458-1
	19-17[2]	0.91-1.15	.120 3.05	22-18	0.3-1.0	.016 0.41	63504-1

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.
2 Single magnet wire only; 22 AWG [0.64 mm] or larger.
3 Stranded, fused stranded or solid lead wire.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

www.te.com/appliances

Standard MAG-MATE Terminals (Continued)

300 Box Posted PCB Terminals

Multi-Spring Solderless Terminal

Material
Tin over Copper Alloy

Cavity Size
Application Spec.
114-74109 with 114-74109-5



A

Type	Copper Magnet Wire Range[1] AWG	mm	Dim L	Stock Thickness Tab Section	Mag Wire Section	Strip Part Number
A Multi-Spring Solderless PCB Tab Terminal	33-29.5	0.18-0.265	.583 14.80	.031 0.80	.013 0.32	1247000-2
	29.5-26	0.265-0.40	.583 14.80	.031 0.80	.013 0.32	1247001-2
	26-22.5	0.40-0.63	.583 14.80	.031 0.80	.013 0.32	1247002-2
	22.5-19.5[2]	0.63-0.85	.583 14.80	.031 0.80	.013 0.32	1247003-2
	19.5-17[2]	0.85-1.12	.583 14.80	.031 0.80	.013 0.32	1247004-2

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.
2 Single magnet wire only. 22 awg [0.63 mm] and larger.

Note: PC Board hole size .057 [1.45].

300 Box Posted PCB Terminals Solder Terminal

Material
Tin over copper plated brass

Typical Cavity Size
(See page 23)
Type C—Cavity Size 2
Type D—Cavity Size 6



B



C

Type	Copper Magnet Wire Range[1] AWG	mm	Dim. L	Stock Thickness Tab Section	Mag Wire	Strip Part Number
B 300 Box Standard IDC PCB Post	33-31	0.18-0.23	.540 13.72	.010 0.25	.010 0.25	63253-1
	31-28	0.23-0.32	.540 13.72	.010 0.25	.010 0.25	62928-1*
	29-26	0.29-0.40	.540 13.72	.012 0.30	.012 0.30	62958-1*
	27-23	0.36-0.57	.460 11.68	.016 0.41	.016 0.41	63659-1
	22-20[2]	0.64-0.81	.460 11.68	.016 0.41	.016 0.41	63660-1
	19-17[2]	0.91-1.15	.460 11.68	.016 0.41	.016 0.41	63661-1
	19-17[2]	0.91-1.15	.570 14.48	.016 0.41	.016 0.41	1742708-1
C PCB Post Shallow Box	33-31	0.18-0.23	.475 12.07	.020 0.51	.012 0.30	1217302-1

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.
2 Single magnet wire only.
* Recognized under the Component Program of Underwriters Laboratories, Inc.

Note: PC Board hole size .050 [1.27].

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

www.te.com/appliances

Standard MAG-MATE Terminals (Continued)

MAG-MATE Edge Leaf Terminal

Material

Pre-tinned brass

Brass

Cavity

411-18517



A

	Copper Magnet Wire Range		Cavity Size	Stock Thickness	Strip Part Number
	AWG	mm			
A MAG-MATE Contact RAST 5D	33-30	0.18-0.265	2	.013 0.32	1394429-2
	30-26	0.265-0.40	2	.013 0.32	1394430-2
	26-22	0.40-0.63	2	.013 0.32	1394431-2
	22-20	0.63-0.80	2	.013 0.32	1394432-2
	20-17	0.85-1.12	2	.013 0.32	1394433-2

Note: Special cavity required. Contact TE Connectivity for information

Material

Unplated brass

Cavity

411-18517



B

Type	Copper Magnet Wire Range		Cavity Size	Stock Thickness	Strip Part Number
	AWG	mm			
B MAG-MATE Edge-Leaf Contact	33-30	0.18-0.265	2	.013 0.32	1-1987143-1

Note: Special cavity required. Contact TE Connectivity for information

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

Standard MAG-MATE Terminals (Continued)

187 Box Posted PCB Terminals

Material

Tin plated brass

Typical Cavity Size 1

(See page 23)



A

Type	Copper Magnet Wire Range[1] AWG	Copper Magnet Wire Range[1] mm	Dim. L	Stock Thickness	Strip Part Number
A 185 Box Standard IDC PCB Post	33-31	0.18-0.23	.267 6.78	.010 0.25	63565-1
			.330 8.38	.010 0.25	62938-1
	30-28	0.25-0.32	.267 6.78	.012 0.30	63160-1
			.287 7.29	.012 0.30	63818-1
			.330 8.38	.012 0.30	62430-1
	27-25	0.36-0.46	.330 8.38	.012 0.30	62438-1
	24-22[2]	0.51-0.64	.287 7.29	.012 0.30	63819-1
			.330 8.38	.012 0.30	62439-1

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.
2 Single magnet wire only.

187 Box Tab Terminals

Material

Tin plated brass

Typical Cavity Size 1

(See page 23)



B

Type	Copper Magnet Wire Range[1] AWG	Copper Magnet Wire Range[1] mm	Dim. L	Tab Size	Stock Thickness Tab Section	Stock Thickness Mag Wire	Strip Part Number
B 187 Box Standard IDC F-Crimp	30-28	0.25-0.32	.432 10.97	.110 x .020 2.79 x 0.51	.020 0.51	.012 0.30	63702-1
	29-27	0.29-0.36	.432 10.97	.110 x .020 2.79 x 0.51	.020 0.51	.012 0.30	1217196-1
	30-28	0.25-0.32	.512 13.00	.110 x .020 2.79 x 0.51	.020 0.51	.012 0.30	160810-2
	27-25	0.25-0.32	.512 13.00	.110 x .020 2.79 x 0.51	.020 0.51	.012 0.30	160809-2
	24-22	0.25-0.32	.512 13.00	.110 x .020 2.79 x 0.51	.020 0.51	.012 0.30	160897-2
	30	0.25	.550 14.00	.071 x .025 1.80 x 0.63	.025 0.63	.012 0.30	1217405-1
	29-27	0.29-0.36	.700 17.78	.059 x .032 1.50 x 0.81	.032 0.81	.012 0.30	1742605-1
	25-22[2]	0.46-0.64	.700 17.78	.059 x .032 1.50 x 0.81	.032 0.81	.012 0.30	1217013-1

1 Two magnet wires may be terminated in the same terminal if diameters are equal.
2 Single magnet wire only.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

www.te.com/appliances

Standard MAG-MATE Terminals (Continued)

300 Box Tab Terminals

Material
Tin plated brass

Typical Cavity Size 2
(See page 23)



Type	Copper Magnet Wire Range[1] AWG	mm	Dim. L	Tab Size	Stock Thickness Tab Section	Mag Wire	Strip Part Number
A 300 Box Standard IDC Straight Tab	20	0.79	.750 19.05	.063 x .025 1.60 x 0.63	.025 0.63	.016 0.41	63965-1[2]
			.895 22.73	.063 x .025 1.60 x 0.63	.025 0.63	.016 0.41	1217595-1[2]
	31	0.23	.870 22.10	.062 x .032 1.57 x 0.81	.032 0.81	.010 0.25	63810-1

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.
2 Tinsel wire only.

Typical Cavity Size 2
when "C" dimension is.120[3.05]
(See page 23)
Typical Cavity Size 6
when "C" dimension is.070[1.78]
(See page 23)

Type	Copper Magnet Wire Range[1] AWG	mm	Dim. C	Tab Size	Stock Thickness Tab Section	Mag Wire	Strip Part Number
B 300 Box Standard IDC Twisted Tab	33-31	0.18-0.23	.070 1.78	.125 x .020 3.17 x 0.51	.020 0.51	.012 0.30	63806-1
	31-28	0.23-0.32	.070 1.78	.125 x .020 3.17 x 0.51	.020 0.51	.012 0.30	63807-1
	27-24	0.36-0.50	.070 1.78	.125 x .020 3.17 x 0.51	.020 0.51	.012 0.30	63808-1
	21[2]	0.72	.120 3.05	.118 x .030 3.00 x 0.76	.030 0.76	.016 0.41	63463-1
	19.5[2]	0.86	.120 3.05	.118 x .030 3.00 x 0.76	.030 0.76	.016 0.41	63216-1

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.
2 Single magnet wire only.

Material
Tin plated brass

Typical Cavity Size 2
(See page 23)



Type	Copper Magnet Wire Range[1] AWG	mm	Dim. L	Tab Size	Stock Thickness Tab Section	Mag Wire	Strip Part Number
C 300 Box Standard IDC Timer Tab	33-31	0.18-0.23	.585 14.86	.118 x .020 3.00 x 0.51	.020 0.51	.010 0.25	1217746-1
	30 -28	0.25-0.32	.585 14.86	.118 x .020 3.00 x 0.51	.020 0.51	.010 0.25	1217745-1
	27-23	0.36-0.57	.585 14.86	.118 x .020 3.00 x 0.51	.020 0.51	.016 0.41	63973-1
			.585 14.86	.125 x .020 3.17 x 0.51	.020 0.51	.016 0.41	63489-1
	25-22[2]	0.45-0.64	.585 14.86	.118 x .020 3.00 x 0.51	.020 0.51	.016 0.41	1217596-1
	23.5-21.5[2]	0.54-0.68	.585 14.86	.118 x .020 3.00 x 0.51	.020 0.51	.016 0.41	1217593-1
	27-23	0.36-0.57	.775 19.68	.125 x .020 3.17 x 0.51	.020 0.51	.016 0.41	1742167-1
	23-20[2]	0.57-0.81	.775 19.68	.125 x .020 3.17 x 0.51	.020 0.51	.016 0.41	63899-1
	19-17[2]	0.91-1.15	.585 14.86	.118 x .020 3.00 x 0.51	.020 0.51	.016 0.41	63972-1
	18 Lead	1.02	.585 14.86	.118 x .020 3.00 x 0.51	.020 0.51	.016 0.41	63974-1

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.
2 Single magnet wire only; 22 AWG [0.64 mm] or larger.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.
Dimensions are shown for reference purposes only. Specifications subject to change.
www.te.com/appliances

Standard MAG-MATE Terminals (Continued)

Pin Receptacle Terminals

Material

A: Tin plated brass
B: Unplated brass

Typical Cavity Size 2

(See page 23)





Type	Copper Magnet Wire Range[1] AWG	mm	Mating Pin Dia.	Stock Thickness	Strip Part Number
A Pin Receptacle	30-27	0.25-0.36	.079 2.00	.013 0.32	1394403-1
	26-23	0.40-0.57	.079 2.00	.013 0.32	1394475-1
	21-18[2]	0.72-1.00	.079 2.00	.013 0.32	1394476-1
	26-23	0.40-0.57	.150 3.80	.013 0.32	1394638-1
	21-18[2]	0.72-1.00	.150 3.80	.013 0.32	1394639-1
B Pin Receptacle	30-27	0.25-0.36	.150 3.80	.013 0.32	1740417-1
	26-23	0.40-0.57	.150 3.80	.013 0.32	1740418-1
	21-18[3]	0.72-1.00	.150 3.80	.013 0.32	1740419-1

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.
2 Single magnet wire only; 20.5 AWG [0.76 mm] or larger.
3 Single magnet wire only

Standard MAG-MATE Terminals (Continued)

Pin I/O Terminals

Material

Tin plated brass

.300 [7.62] Series Box

Styles A, B and C

Typical Cavity Size 2

(See page 23)

.500 [12.7] Series Box

Style D

Typical Cavity Size 4

(See page 23)



A



B



C



D

Type	Copper Magnet Wire Range[1]		Pin Dia.	Stock Thickness		Strip Part Number
	AWG	mm		I/O	Mag Wire	
A 300 Box Straight Pin	27-23	0.36-0.57	.060 1.52	.010 0.25	.010 0.25	63722-1
B 300 Box Offset Pin-R.H.	33-31	0.18-0.23	.048 1.22	.010 0.25	.010 0.25	63443-1
C 300 Box Offset Pin-L.H.	33-31	0.18-0.23	.048 1.22	.010 0.25	.010 0.25	63444-1
	31-28	0.23-0.32	.048 1.22	.010 0.25	.010 0.25	63569-1
	27-23	0.36-0.57	.048 1.22	.010 0.25	.016 0.25	63570-1
	25-22[2]	0.45-0.64	.048 1.22	.010 0.25	.016 0.41	63788-1
D 500 Box Straight Pin	27-23	0.86-1.15	.090 2.29	.016 0.41	.016 0.41	63278-1
	22-20	0.64-0.81	.090 2.29	.016 0.41	.016 0.41	63277-1

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.

2 Single magnet wire only; 22 AWG [0.64 mm] or larger.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

www.te.com/appliances

Standard MAG-MATE Terminals (Continued)

110 Series FASTON Tab Terminals

Material

Tin plated brass

Typical Cavity Size 2

(See page 23)

Note: .110 [2.79] Tab Terminals mate with compatible FASTON receptacles. Request AMP Catalog 82004.



Type	Copper Magnet Wire Range[1] AWG	Copper Magnet Wire Range[1] mm	Tab Size	Stock Thickness Tab	Stock Thickness Mag Wire	Strip Part Number
A[4] 300 Box Standard IDC .110[2.79] FASTON Tab	30-27	0.25-0.36	.110 x .020 2.79 x 0.51	.020 0.51	.012 0.30	63777-1
	27-23	0.36-0.57	.110 x .020 2.79 x 0.51	.020 0.51	.016 0.41	63746-1
	23-20[2]	0.45-0.64	.110 x .020 2.79 x 0.51	.020 0.51	.016 0.41	63486-1
	19-17	0.91-1.15	.110 x .020 2.79 x 0.51	.020 0.51	.020 0.51	63145-1
B[4,5] 300 Box Single IDC w/ Strain Relief Slot	27-23	0.36-0.57	.110 x .020 2.79 x 0.51	.020 0.51	.016 0.41	63827-1
	3.5-20[2]	0.54-0.81	.110 x .020 2.79 x 0.51	.020 0.51	.016 0.41	1217783-1
C[3,4] Poke-In Combination Tab	28-24	0.32-0.51	.110 x .020 2.79 x 0.51	.020 0.51	.012 0.30	63062-1
	25-22[2]	0.45-0.64	.110 x .020 2.79 x 0.51	.020 0.51	.012 0.30	63063-2

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.
2 Single magnet wire only; 22 AWG [0.64 mm] or larger.
3 Poke-In feature accepts 20-18 AWG [0.5-0.8 mm2] Solid or overcoated stranded lead wire or 90° Poke-In tab.
4 After insertion into plastic cavity, tab portion must be bent over 45°-90° or potted in to prevent pullout when mating receptacle is disconnected.
5 Strain relief slot for high vibration applications.

Standard MAG-MATE Terminals (Continued)

187 Series FASTON Tab Terminals

Material

Tin plated brass

Typical Cavity Size

(See page 23)

Type A—Cavity Size 2



A

Type	Copper Magnet Wire Range[1] AWG	mm	Dim. L	Tab Feature	Tab Size	Stock Thickness Tab Section	Stock Thickness Mag. Wire Section	Strip Part Number
A[3] 300 Box Standard IDC .187 [4.75] FASTON Tab	33-31	0.18-0.23	.630 16.00	Dimple	.187 x .020 4.75 x 0.51	.020 0.51	.010 0.25	62513-1*
			.660 16.76	Hole	.187 x .020 4.75 x 0.51	.020 0.51	.012 0.30	63584-1
	30-27	0.25-0.36	.630 16.00	Dimple	.187 x .020 4.75 x 0.51	.020 0.51	.012 0.30	62512-1*
				Dimple	.187 x .032 4.75 x 0.81	.032 0.81	.012 0.30	62678-1†*
	27-23	0.36-0.57	.630 16.00	Dimple	.187 x .020 4.75 x 0.51	.020 0.51	.016 0.41	62514-1*
				Hole	.187 x .020 4.75 x 0.51	.020 0.51	.016 0.41	63664-1
				—	.187 x .020 4.75 x 0.51	.020 0.51	.016 0.41	63461-1
			.660 16.76	Hole	.187 x .020 4.75 x 0.51	.020 0.51	.016 0.41	63585-1
	23	0.57	.630 16.00	—	.187 x .020 4.75 x 0.51	.020 0.51	.016 0.41	63776-1
	22-20[2]	0.64-0.81	.630 16.00	Dimple	.187 x .020 4.75 x 0.51	.020 0.51	.016 0.41	62511-1*
				Hole	.187 x .020 4.75 x 0.51	.020 0.51	.016 0.41	63663-1
				Dimple	.187 x .032 4.75 x 0.81	.032 0.81	.016 0.41	1217065-1
				Hole	.187 x .032 4.75 x 0.81	.032 0.81	.016 0.41	1217128-1
	20-18[2]	0.81-1.02	.630 16.00	Dimple	.187 x .020 4.75 x 0.51	.020 0.51	.020 0.51	62904-1[4]
				Hole	.187 x .020 4.75 x 0.51	.020 0.51	.020 0.51	63670-1
	19-17	0.91-1.15	.630 16.00	Dimple	.187 x .020 4.75 x 0.51	.020 0.51	.020 0.51	63273-1[2] 1742160-1[1]
				Hole	.187 x .020 4.75 x 0.51	.020 0.51	.020 0.51	63665-1

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.
2 Single magnet wire only.
3 After insertion into plastic cavity, tab portion must be bent over 45°-90° or potted in to prevent pullout when mating receptacle is disconnected.
4 Single bare copper wire only.
* Recognized under the Component Program of Underwriters Laboratories, Inc.
† These part numbers are available upon special request; contact TE Engineering for details.

187 Series Combination Poke-In FASTON Terminals

Material

Tin plated brass

Typical Cavity Size

(See page 23)

Type B—Cavity Size 2



B

Type	Copper Magnet Wire Range[1] AWG	mm	Dim. L	Tab Feature	Tab Size	Stock Thickness Tab Section	Stock Thickness Mag. Wire Section	Strip Part Number
B[3,4] Poke-In Combination Tab	33-31	0.81-0.23	.630 16.00	Hole	.187 x .020 4.75 x 0.51	.020 0.51	.010 0.25	63018-1
	27-22[2]	0.35-0.63	.630 16.00	Hole w/o Hole	.187 x .020 4.75 x 0.51	.020 0.51	.016 0.41	316300-4 2-316300-7
	22-19[2]	0.64-0.89	.630 16.00	Hole w/o Hole	.187 x .020 4.75 x 0.51	.020 0.51	.016 0.41	316300-5 2-316300-8
	19-17[2]	0.90-1.15	.630 16.00	Hole w/o Hole	.187 x .020 4.75 x 0.51	.020 0.51	.016 0.41	316300-6 2-316300-9
	17-16[2]	1.20-1.30	.630 16.00	Hole	.187 x .020 4.75 x 0.51	.020 0.51	.016 0.41	6-316300-7

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.
2 Single magnet wire only; 22 AWG [0.64 mm] or larger.
3 Poke-In feature accepts 20-18 AWG [0.5-0.8 mm^2] solid, fused stranded lead wire or 90° poke-in tab terminal.
4 After insertion into plastic cavity, tab portion must be bent over 45°-90° or potted in to prevent pullout when mating receptacle is disconnected.

Note: .187 [4.75] Tab Terminals mate with compatible FASTON receptacles. Request AMP Catalog 82004.

Chart continued on next page

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

www.te.com/appliances

Standard MAG-MATE Terminals (Continued)

187 Series FASTON Tab Terminals
(Continued)

Material
Tin plated brass

Typical Cavity Size
(See page 23)
Type A—Cavity Size 5
Type B—Cavity Size 5



Type	Copper Magnet Wire Range[1] AWG	mm	Dim. L	Tab Feature	Tab Size	Stock Thickness Tab Section	Stock Thickness Mag. Wire Section	Strip Part Number
A 300 Box Standard IDC Narrow Body Latch Type	33-31	0.18-0.23	.630 16.00	Dimple	.187 x .020 4.75 x 0.51	.020 0.51	.010 0.25	63108-1†
	31-28	0.23-0.32	.630 16.00	Dimple	.187 x .020 4.75 x 0.51	.020 0.51	.010 0.25	62743-1†
	30-27	0.25-0.36	.630 16.00	Dimple	.187 x .020 4.75 x 0.51	.020 0.51	.012 0.30	63109-1†
	27-23	0.36-0.57	.630 16.00	Dimple	.187 x .020 4.75 x 0.51	.020 0.51	.016 0.41	63107-1
				Dimple	.187 x .020 4.75 x 0.51	.020 0.51	.016 0.41	1217493-1
	23-20[2]	0.57-0.81	.630 16.00	Dimple	.187 x .020 4.75 x 0.51	.020 0.51	.016 0.41	63340-1
	22-20[2]	0.64-0.81	.630 16.00	Dimple	.187 x .020 4.75 x 0.51	.020 0.51	.016 0.41	63429-1
	19-17[2]	0.91-1.15	.630 16.00	Dimple	.187 x .020 4.75 x 0.51	.020 0.51	.016 0.41	62888-1
				Hole	.187 x .020 4.75 x 0.51	.020 0.51	.016 0.41	63782-1
	18 lead[2]	0.80-0.92 mm[2]	.630 16.00	—	.187 x .020 4.75 x 0.51	.020 0.51	.016 0.41	1217592-1†
B[3] Narrow Body Latch Type w/ Strain Relief Slot	23.5-20[2]	0.54-0.81	.630 16.00	Dimple	.187 x .020 4.75 x 0.51	.020 0.51	.016 0.41	1217004-1

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.
2 Single magnet wire only; 22 AWG [0.64 mm] or larger.
3 Strain relief slot for high vibration applications.
† These part numbers are available upon special request; contact TE Engineering for details.

Chart continued on next page

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.
Dimensions are shown for reference purposes only. Specifications subject to change.
www.te.com/appliances

Standard MAG-MATE Terminals (Continued)

187 Series
FASTON Tab Terminals
(Continued)

Material
Tin plated brass

Typical Cavity Size
(See page 23)
Type A—Cavity Size 4
Type B—Cavity Size 4



A



B

Type	Copper Magnet Wire Range[1] AWG	Copper Magnet Wire Range[1] mm	Dim. L	Tab Feature	Tab Size	Stock Thickness Tab Section	Stock Thickness Mag. Wire Section	Strip Part Number
A[3] 500 Box Standard IDC	22-20	0.64-0.81	.830 21.08	Hole	.187 x .020 4.75 x 0.51	.020 0.51	.020 0.51	1742819-1
	19-17	0.91-1.15	.830 21.08	Hole	.187 x .020 4.75 x 0.51	.020 0.51	.020 0.51	1742820-1
	17.5-16	1.09-1.29	.830 21.08	Hole	.187 x .020 4.75 x 0.51	.020 0.51	.020 0.51	63667-1
				Hole	.187 x .020 4.75 x 0.51	.020 0.51	.020 0.51	63427-1
				Hole	.187 x .032 4.75 x 0.81	.032 0.81	.020 0.51	1217075-1
	16-15	1.29-1.45	.830 21.08	Hole	.187 x .020 4.75 x 0.51	.020 0.51	.020 0.51	63666-1
				Hole	.187 x .020 4.75 x 0.51	.020 0.51	.020 0.51	63762-1
				Dimple	.187 x .020 4.75 x 0.51	.020 0.51	.020 0.51	63353-1
	14.5-13[2]	1.54-1.83	.830 21.08	Hole	.187 x .020 4.75 x 0.51	.020 0.51	.020 0.51	1217902-1
B[3,4] 500 Box Single IDC w/ Strain Relief Slot	27-23	0.36-0.57	.830 21.08	Hole	.187 x .020 4.75 x 0.51	.020 0.51	.020 0.51	1217042-1
	22-20	0.64-0.81	.830 21.08	Hole	.187 x .020 4.75 x 0.51	.020 0.51	.020 0.51	63983-1
				Hole	.187 x .032 4.75 x 0.81	.032 0.81	.020 0.51	1217339-1
	19-17	0.91-1.15	.830 21.08	Hole	.187 x .020 4.75 x 0.51	.020 0.51	.020 0.51	63995-1
				Hole	.187 x .032 4.75 x 0.81	.032 0.81	.020 0.51	1217090-1
	16-15	1.29-1.45	.830 21.08	Hole	.187 x .020 4.75 x 0.51	.020 0.51	.020 0.51	63996-1

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.
2 Single magnet wire only.
3 After insertion into plastic cavity, tab portion must be bent over 45°-90° or potted in to prevent pullout when mating receptacle is disconnected.
4 Strain relief slot for high vibration applications.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.
Dimensions are shown for reference purposes only. Specifications subject to change.
www.te.com/appliances

Standard MAG-MATE Terminals (Continued)

250 Series FASTON Tab Terminals

Material

Tin plated brass

Typical Cavity Size

(See page 23)

Type A—Cavity Size 2

Type B—Cavity Size 5

Type C—Cavity Size 3

Note: .250 [6.35] tab terminals mate with compatible FASTON receptacles. Request AMP Catalog 82004.



A



B



C

Type	Copper Magnet Wire Range[1] AWG	mm	Dim. L	Tab Feature	Tab Size	Stock Thickness Tab Section	Stock Thickness Mag. Wire Section	Strip Part Number
A[3] 300 Box Standard IDC .250 [6.35] FASTON Tab	33-31	0.18-0.23	.750 19.05	Dimple	.250 x .032 6.35 x 0.81	.032 0.81	.010 0.25	62600-1*
	30-27	0.25-0.36	.750 19.05	Dimple	.250 x .032 6.35 x 0.81	.032 0.81	.012 0.30	62651-1*
	28-24	0.32-0.51	.750 19.05	Hole	.250 x .032 6.35 x 0.81	.032 0.81	.016 0.41	63607-1
	27-23	0.36-0.57	.750 19.05	Dimple	.250 x .032 6.35 x 0.81	.032 0.81	.016 0.41	62652-1*
	22-20	0.64-0.81	.750 19.05	Dimple	.250 x .032 6.35 x 0.81	.032 0.81	.016 0.41	1217924-1
	19-17	0.91-1.15	.750 19.05	Dimple	.250 x .032 6.35 x 0.81	.032 0.81	.020 0.51	1742398-1
B Narrow Body Latch Type	33-31	0.18-0.23[1]	.750 19.05	Dimple	.250 x .032 6.35 x 0.81	.032 0.81	.010 0.25	63026-1
	30-27	0.25-0.36[1]	.750 19.05	Dimple	.250 x .032 6.35 x 0.81	.032 0.81	.012 0.30	63027-1
	27-23	0.36-0.57	.750 19.05	Dimple	.250 x .032 6.35 x 0.81	.032 0.81	.016 0.41	1217860-1
	23-20[2]	0.57-0.81	.750 19.05	Dimple	.250 x .032 6.35 x 0.81	.032 0.81	.016 0.41	1217870-1
C Wide Body Latch Type	33-31	0.18-0.23	.750 19.05	Hole	.250 x .032 6.35 x 0.81	.032 0.81	.010 0.25	63309-1
	31-28	0.23-0.32	.750 19.05	Dimple	.250 x .032 6.35 x 0.81	.032 0.81	.012 0.30	63403-2
	30-28	0.25-0.32	.750 19.05	Hole	.250 x .032 6.35 x 0.81	.032 0.81	.012 0.30	1217152-1
	30-27	0.25-0.36	.750 19.05	Dimple Hole	.250 x .032 6.35 x 0.81	.032 0.81	.012 0.30	63132-1 63499-1
	27-23	0.36-0.57	.750 19.05	Hole Dimple	.250 x .032 6.35 x 0.81	.032 0.81	.016 0.41	63571-1 63128-1
	22-20[2]	0.64-0.81	.750 19.05	Dimple	.250 x .032 6.35 x 0.81	.032 0.81	.016 0.41	63601-2
	19-17[2]	0.91-1.15	.750 19.05	Hole	.250 x .032 6.35 x 0.81	.032 0.81	.016 0.41	63614-1

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.
2 Single magnet wire only; 22 AWG [0.64 mm] or larger.
3 After insertion into plastic holder, tab portion must be bent over 45°-90° or potted in to prevent pullout when mating receptacle is disconnected.

* Recognized under the Component Program of Underwriters Laboratories, Inc.

Chart continued on next page

Standard MAG-MATE Terminals (Continued)

250 Series FASTON Tab Terminals
(Continued)

Material
Tin plated brass

Typical Cavity Size
(See page 23)
Type A—Cavity Size 4
Type B—Cavity Size 4



A



B

Type	Copper Magnet Wire Range[1] AWG	mm	Dim. L	Tab Feature	Tab Size	Stock Thickness Tab Section	Stock Thickness Mag. Wire Section	Strip Part Number
A[3] 500 Box Standard IDC Wide Neck	22-20	0.64-0.81	.952 24.18	Hole	.250 x .032 6.35 x 0.81	.032 0.81	.020 0.51	63495-1
	19-17	0.91-1.15	.952 24.18	Hole	.250 x .032 6.35 x 0.81	.032 0.81	.020 0.51	63464-3
	16-15	1.29-1.45	.952 24.18	Hole	.250 x .032 6.35 x 0.81	.032 0.81	.020 0.51	63459-2
	14-13[2]	1.61-1.83	.952 24.18	Dimple	.250 x .032 6.35 x 0.81	.032 0.81	.020 0.51	63460-1
				Hole	.250 x .032 6.35 x 0.81	.032 0.81	.020 0.51	63816-1
B[3] 500 Box Standard IDC Narrow Neck	22-20	0.64-0.81	.952 24.18	Dimple	.250 x .032 6.35 x 0.81	.032 0.81	.020 0.51	63155-1
	19-17	0.91-1.15	.952 24.18	Dimple	.250 x .032 6.35 x 0.81	.032 0.81	.020 0.51	62923-1
	16-15	1.29-1.45	.952 24.18	Dimple	.250 x .032 6.35 x 0.81	.032 0.81	.020 0.51	63064-1
	14-13[2]	1.61-1.83	.952 24.18	Dimple	.250 x .032 6.35 x 0.81	.032 0.81	.020 0.51	63465-1
	12[2]	2.05	.952 24.18	Dimple	.250 x .032 6.35 x 0.81	.032 0.81	.020 0.51	63425-1

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.
2 Single magnet wire only.
3 After insertion into plastic holder, tab portion must be bent over 45°-90° or potted in to prevent pullout when mating receptacle is disconnected.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.
Dimensions are shown for reference purposes only. Specifications subject to change.
www.te.com/appliances

Standard MAG-MATE Terminals (Continued)

Typical Plastic Cavity

Illustrations shown are for reference only. They are not a purchased item. Manufacture only according to TE Specification.

Technical Documents

Application Specifications describe requirements for using the product in its intended application and or crimping information. They are intended for the Packaging and Design Engineer and the Machine Setup Person.

114-2050 —Poke-In Tab MAG-MATE Terminals
114-2069 —Standard MAG-MATE.187 [4.75] Box Height Terminals
114-2046 —Standard MAG-MATE.300 [7.62] Box Height Terminals
114-2066 —Standard MAG-MATE.500 [12.7] Box Height Terminals
114-2067 —Standard MAG-MATE .300 [7.62] Box Height Latch-In Terminals Narrow Body
114-2094 —Standard MAG-MATE .300 [7.62] Box Height Latch-In Terminals Wide Body



Cavity Size 1
187 [4.75] Box
MAG-MATE
(Application Spec. 114-2069)



Cavity Size 2
.300 [7.62] Box
MAG-MATE
(Application Spec. 114-2046)



Cavity Size 3
.300 [7.62] Box
Latch-In MAG-MATE Wide Body
(Application Spec. 114-2094)



Cavity Size 4
.500 [12.70] Box
MAG-MATE
(Application Spec. 114-2066)



Cavity Size 5
.300 [7.62] Box
Latch-In MAG-MATE,
Narrow Body
(Application Spec. 114-2067)



Cavity Size 6
.300 [7.62] Box
MAG-MATE
(Application Spec. 114-2046)

Note: The MAG-MATE typical plastic cavities shown above are for reference only. They are not a purchased item. Refer to appropriate TE application specification for details.

Plastic cavities, designed to TE specifications, may be molded as part of the coil bobbin or attached to a lamination stack in the area of the magnet wire coil.

Each cavity is a rectangular box with two narrow slots on opposing walls and a plastic post or anvil extending upward from the bottom surface. During or after the winding process, the magnet wire is placed across the plastic cavities and into the slots, either manually or by coil winding equipment.

Unraveling is prevented by a slight friction fit, suitable bend or by wrapping the magnet wire around a tie-off post.

During insertion, two insulation displacing terminal slots strip the film insulation from the magnet wire producing a stable electrical termination.

The plastic anvil supports the magnet wire, helping to prevent it from being dragged down when the terminal is inserted.

Terminal retention is secured in the plastic cavities by either locking barbs or locking latches in addition to locking barbs for quick disconnect FASTON tab terminals.

Excess magnet wire is trimmed flush with the outside of the plastic cavity by a shear blade traveling with the terminal insertion ram.

The sheared wire end can be tucked inside the plastic cavity, if necessary, by cutting the wire off before the terminal is fully seated allowing the terminal to drag the severed end of the wire into the pocket inside the cavity.

TE will provide design and mold engineering resources to manufacture any specifically designed MAG-MATE cavity housing.

Standard MAG-MATE Terminals (Continued)

Typical Plastic Cavities

Illustrations shown are for reference only. They are not a purchased item. Manufacture only according to TE Specification.



Slim Line MAG - MATE
Reference Application
Spec. 114-2147



Mini MAG - MATE
Reference Application
Spec. 114-2047

Technical Documents
Application Specifications

describe requirements for using the product in its intended application and or crimping information. They are intended for the Packaging and Design Engineer and the Machine Setup Person.

114-2140—Slim Line MAG-MATE Terminals

Technical Documents
Application Specifications

describe requirements for using the product in its intended application and or crimping information. They are intended for the Packaging and Design Engineer and the Machine Setup Person.

114-2047—Mini MAG-MATE Terminals

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

Slim Line MAG-MATE Terminals

Product Facts

- Terminates all magnet wire film insulations
- Eliminates need for pre-stripping conductors
- Eliminates need to post-insulate terminations
- Excess magnet wire is automatically trimmed during the termination process
- 187 and 250 Series Faston Tab and posted PCB Tab terminals available
- Terminates 33-17 AWG [0.18-1.15 mm] magnet wire
- Simultaneously terminates two magnet wires of the same size in one terminal from 33-23 AWG [0.18-0.57 mm]
- Available in strip form for semi-automatic or fully automatic insertions
- High speed, fully automated integrated systems provide uniform terminations reliably at the lowest possible applied cost
- Clean metal-to-metal interface produces stable, gas-tight electrical terminations free of oxides and other contaminants
- Recognized under the Component Recognition Program of Underwriters Laboratories Inc., File No. E13288

Applications

- Motor windings and connections
- Coil Connections
- Transformer windings and connections
- Bobbin connections
- Lighting Ballasts
- Power Supplies



TE offers a full selection of 187 and 250 Series Faston and posted PCB Slim Line MAG-MATE Tab insulation displacement (IDC) terminals for magnet wire terminations.

Slim Line MAG-MATE terminals with a single IDC slot terminate 33-17 AWG [0.18 to 1.15 mm].

Each IDC slot terminates a range of up to four consecutive magnet wire sizes.

Two magnet wires with the same diameter can be terminated in one terminal. Except as noted.

MAG-MATE cavities are either integrated into coil bodies or especially designed cavity housings. The magnet wires are precisely positioned in the plastic cavity slots.

The MAG-MATE Inserter cuts the terminals from the strip and places the terminals over the magnet wire into the plastic cavities.

During this operation, small stripping shoulders in the IDC slot remove the film insulation from the magnet wire.

Wiping action between the wire and terminals removes oxides or other contaminants present on both the conductor and the terminal slot side walls, producing a clean, stable, gas-tight electrical termination.

Residual spring energy in the terminal causes the side walls of each IDC slot to function as opposing cantilever beams.

This constant pressure results in an intimate metal-to-metal interface, providing a reliable, long-term connection.

The AMP MAG-MATE Inserter may be used as a semi-automatic bench machine or integrated in production lines for fully-automatic applications.

Slim Line MAG-MATE Terminals (Continued)

187 Series
FASTON Tab Terminals

Material

Tin plated brass



A

Type	Copper Magnet Wire Range[1] AWG	mm	Dim. L	Tab Feature	Tab Size	Stock Thickness Tab Section	Stock Thickness Mag.Wire Section	Strip Part Number
A .187 [4.75] FASTON Tab	33-31	0.18-0.23	.630 16.00	Hole Dimple	.187 x .020 4.75 x 0.51	.020 0.51	.012 0.30	63710-2 63738-2
				Hole	.187 x .032 4.75 x 0.81	.032 0.81	.012 0.30	1217666-1
	30-28	0.25-0.32	.630 16.00	Hole Dimple	.187 x .020 4.75 x 0.51	.020 0.51	.012 0.30	63711-2 63737-2
	27-24	0.36-0.51	.630 16.00	Hole Dimple	.187 x .020 4.75 x 0.51	.020 0.51	.016 0.41	63712-2 63736-2
			.760 19.31	Plain	.187 x .020 4.75 x 0.51	.020 0.51	.016 0.41	1217497-1
	23-20[2]	0.57-0.81	.630 16.00	Hole Dimple	.187 x .020 4.75 x 0.51	.020 0.51	.016 0.41	63713-2 63735-2
				Hole	.187 x .032 4.75 x 0.81	.032 0.81	.016 0.41	1217516-1
	19-17[2]	0.91-1.15	.630 16.00	Hole Dimple	.187 x .020 4.75 x 0.51	.020 0.51	.016 0.41	63714-2 63734-2

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.
2 Single magnet wire only; 22 AWG [0.64] or larger.

250 Series
FASTON Tab Terminals

Material

Tin plated brass



B

Type	Copper Magnet Wire Range[1] AWG	mm	Dim. L	Tab Feature	Tab Size	Stock Thickness Tab Section	Stock Thickness Mag.Wire Section	Strip Part Number
B .250 [6.35] FASTON Tab	33-31	0.18-0.23	.752 19.10	Hole Dimple	.250 x .032 6.35 x 0.81	.032 0.81	.012 0.30	63716-2 63744-2
	30-28	0.25-0.32	.752 19.10	Hole Dimple	.250 x .032 6.35 x 0.81	.032 0.81	.012 0.30	63717-2 63743-2
	27-24	0.36-0.51	.752 19.10	Hole Dimple	.250 x .032 6.35 x 0.81	.032 0.81	.016 0.41	63718-2 63742-2
	23-20[2]	0.57-0.81	.752 19.10	Hole Dimple	.250 x .032 6.35 x 0.81	.032 0.81	.016 0.41	63719-2 63741-2
	19-17[2]	0.91-1.15	.752 19.10	Hole Dimple	.250 x .032 6.35 x 0.81	.032 0.81	.016 0.41	63720-2 63740-2

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.
2 Single magnet wire only; 22 AWG [0.64] or larger.

Posted PCB
SOLDER Terminal

Material

Tin plated brass



C

Type	Copper Magnet Wire Range[1] AWG	mm	Dim. L	Tab Feature	Tab Size	Stock Thickness Tab Section	Stock Thickness Mag.Wire Section	Strip Part Number
C .040 [1.00] PCB Tab	33.5-30	0.17-0.25	.323 8.20	Embossment	.040 x .024 1.00 x 0.60	.024 0.60	.013 0.32	1534684-1
	29.5-26	0.27-0.40	.323 8.20	Embossment	.040 x .024 1.00 x 0.60	.024 0.60	.013 0.32	1534685-1
	26-22	0.40-0.63	.323 8.20	Embossment	.040 x .024 1.00 x 0.60	.024 0.60	.013 0.32	1534686-1
	22-20	0.63-0.81	.323 8.20	Embossment	.040 x .024 1.00 x 0.60	.024 0.60	.013 0.32	1740829-1
	21.5-19.5	0.67-0.85	.323 8.20	Embossment	.040 x .024 1.00 x 0.60	.024 0.60	.013 0.32	1534687-1

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.
2 Single magnet wire only; 22 AWG [0.64] or larger.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

Slim Line MAG-MATE Terminals (Continued)

Offset Tab Terminals

Material

Tin Plated Brass

Applications where I/O Tab spacing must be less than IDC connection spacing

Example: automotive accessory coils



A

Type	Copper Magnet Wire Range[1] AWG	mm	Dim. L	Diode Size	Tab Size	Stock Thickness Tab Section	Mag.Wire Section	Strip Part Number
A Combination Diode Slot/Tab	33-31	0.18-0.23	.725 18.42	#20 0.8	.059 x .032 1.50 x 0.81	0.032 0.81	0.012 0.30	63888-1
	33-31	0.18-0.23	.725 18.42	#22.5 0.6	.059 x .032 1.50 x 0.81	0.032 0.81	0.012 0.30	63903-1

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.

Posted PCB Terminals

Multi-Spring Solderless Terminal

Material

Tin Plated Copper Alloy

Cavity Size

Application Spec.

Contact TE Engineering



B

Type	Copper Magnet Wire Range[1] AWG	mm	Dim. L	Stock Thickness Tab Section	Mag.Wire Section	Strip Part Number
B Multi-Spring Solderless PCB Tab Terminal	33-29.5	0.18-0.265	.583 14.80	.031 0.81	.013 0.32	2120743-2
	29.5-26	0.265-0.40	.583 14.80	.031 0.81	.013 0.32	2120744-2
	26-22.5	0.40-0.63	.583 14.80	.031 0.81	.013 0.32	2120745-2
	22.5-19.5[2]	0.63-0.85	.583 14.80	.031 0.81	.013 0.32	2120746-2
	19.5-17[2]	0.85-1.12	.583 14.80	.031 0.81	.013 0.32	2120747-2

1 Two magnet wires may be terminated in the same terminal slot if diameters are equal.

2 Single magnet wire only. 22 awg [0.63 mm] and larger.

Note: PC Board hole size .057 [1.45]

Slim Line MAG-MATE Terminals (Continued)

Posted PCB Solder Terminals

Material
Unplated brass



A

Type	Copper Magnet Wire Range AWG	Copper Magnet Wire Range mm	Stock Thickness	Strip Part Number
A MAG-MATE-MQS Terminal	33-30 33[1]	0.256-0.40 0.40-0.56[1]	Varied thickness	1-1987222-1
	30-26 30-26[1]	0.256-0.40 0.40-0.56[1]	Varied thickness	1-1987223-1
	26-22 26-23[1]	0.40-0.63 0.40-0.56[1]	Varied thickness	1-1987224-1
	22-20	0.63-0.80	Varied thickness	1-1987225-1
	20-17	0.85-1.12	Varied thickness	1-1987226-1

1 For double magnet wires

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

www.te.com/appliances

Mini MAG-MATE Terminals

Product Facts

- Terminates all fine gauge magnet wire film insulations
- Eliminates need to pre-strip conductors
- Eliminates need to post insulate terminations
- Terminates 52-30 AWG [0.02-0.25 mm] diameter copper magnet wire
- Poke-In leaf style accepts 22 -18 AWG [0.3-0.9 mm] overcoated stranded or solid lead wire
- Available in strip form for semi-automatic or fully automatic insertions
- High speed, fully automated integrated systems provide uniform terminations and reliability at the lowest possible applied cost
- Recognized under the Component Recognition Program of Underwriters Laboratories Inc, File No. E13288

Applications

- Ignition coils
- Small motors
- Synchronist timers
- Electric meter coils
- Solenoids
- Relays



TE offers AMP Mini MAG-MATE poke-in, crimp wire barrel, post and quick disconnect tab insulation displacement (IDC) terminals for fine gauge magnet wire terminations.

Mini MAG-MATE terminals are designed to terminate 52-30 AWG [0.02-0.25 mm] diameter copper magnet wire.

Poke-in leaf terminals accept 22-18 AWG [0.3-0.9 mm2] overcoated stranded or solid lead wire.

The terminal design uses the AMPLIVAR serrated burr technology to penetrate the film insulation of copper magnet wire.

Mini MAG-MATE cavity pockets, designed to TE specifications, include a wire receiving slot and wire tie-off post that is either integrated into coil bodies or specially designed cavity housings.

The magnet wire is wrapped around the tie-off post and placed across the cavity slot. After the coil is wound, the finish end of the magnet wire is dressed through the second cavity slot and tied to its tie-off post.

The Mini MAG-MATE Inserter shears the terminal from the carrier strip and inserts the terminal into the cavity by a dual ram insertion mechanism.

As the unexpanded terminal approaches the bottom of the cavity, the upper ram stops. The lower ram continues to push to a prescribed depth to expand the terminal and complete the termination process.

The fully seated terminal fits squarely into the cavity,while the serrated leg of the terminal cams against the pre-positioned magnet wire to penetrate the film insulation and provide a stable electrical termination.

Mini MAG-MATE Terminals (Continued)







Termination Complete

Poke-In Terminal

Material

.010 [0.25] tin plated brass



A



B



C

Type	Copper Magnet Wire Range AWG	Copper Magnet Wire Range mm	Lead Wire Range[1] AWG	Lead Wire Range[1] mm²	Mating Tab	Stock Thickness Poke-In Beam	Stock Thickness Mag Wire	Strip Part Number
A Lead Wire Poke-In	52-42	0.02-0.06	22-18	0.3-0.9	—	0.010 0.25	0.010 0.25	62781-1
	44-36	0.05-0.13	22-18	0.3-0.9	—	0.010 0.25	0.010 0.25	62780-1
	38-30	0.10-0.25	22-18	0.3-0.9	—	0.010 0.25	0.010 0.25	62606-1
B Tab Poke-In	52-42	0.02-0.06	—	—	.060 x .020 1.52 x 0.51	0.010 0.25	0.010 0.25	63613-1
	44-36	0.05-0.13	—	—	.060 x .020 1.52 x 0.51	0.010 0.25	0.010 0.25	63795-1[2]
	38-30	0.10-0.25	—	—	.060 x .020 1.52 x 0.51	0.010 0.25	0.010 0.25	63844-2[2]
C Skinny Mini	40-34.5	0.08-0.15	—	—	.040 x .020 1.00 x 0.51	0.010 0.25	0.010 0.25	1718165-1

1 Solid or overcoated stranded lead wire only.
2 Radius on beam leaf tip.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

Mini MAG-MATE Terminals (Continued)

Posted Terminal

Material

Tin over premilled brass



A

Type	Copper Magnet Wire Range		Post Size	Stock Thickness		Strip Part Number
	AWG	mm		Post	Mag Wire	
A PCB Post	38-30	0.10-0.25	.024 x .020 0.62 x 0.51	0.020 0.51	0.010 0.25	63675-4

FASTON Tab Terminals

Material

Tin over premilled brass



B

Type	Copper Magnet Wire Range G W A m m	Tab Size	Stock Thickness		Strip Part Number
			Post	Mag Wire	
B .187 [4.75] FASTON Tab	44-36 0.05-0.13	.187 x .020 4.75 x 0.51	.020 0.51	.010 0.25	63778-1
	38-30 0.10-0.25	.187 x .020 4.75 x 0.51	.020 0.51	.010 0.25	1217529-1

Crimp Wire Barrel Terminal

Material

Tin plated brass



C

Type	Copper Magnet Wire Range		Lead Wire Range		Stock Thickness		Strip Part Number
	AWG	mm	AWG	mm²	Crimp Barrel	Mag Wire	
C Crimp Wire Barrel	38-30	0.10-0.25	22-18	0.3-0.9	0.010 0.25	0.010 0.25	63199-1[1]

1 Wire and insulation barrel reversed so lead wire exits over magnet wire termination area.

SIAMEZE Terminals

Product Facts

- Terminates all copper magnet wire film insulations
- Eliminates need for pre-stripping conductors
- Moving Beam contact design connects a wide range of magnet wire sizes with a single terminal
- Standard range terminals connect 34-18 AWG [0.16-1.0 mm] magnet wire
- Fine range terminals connect 36-27 AWG [0.13-0.38 mm] magnet wire
- Medium range terminals connect 23-12 AWG [0.56-2.03 mm] magnet wire
- Excess magnet wire is automatically trimmed during the termination process
- Available in strip form for semi-automatic or fully automatic insertions
- Loose piece terminals available for manual tool insertions
- High-speed automatic coil winding machine terminations provide uniform reliability at the lowest possible applied cost
- Clean metal-to-metal interface produces stable, gas-tight electrical terminations free of oxides and other contaminants
- Recognized under the Component Program of Underwriters Laboratories Inc.,File No. E13288

Applications

- Motor windings and connections
- Coil connections
- Transformer windings and connections
- Ballasts
- Power supplies
- Solenoids
- Actuators



TE offers a full selection of AMP SIAMEZE insulation displacement (IDC) terminals for interconnecting copper magnet wires, lead wires, and other components.

The AMP SIAMEZE insulation displacement (IDC) technology eliminates the need to strip the film insulation from copper magnet wires and lead wires.

Terminals are available in wire-to-wire, Lead Lok, quick disconnect tabs, posts, pin and receptacle terminals.



Available with either Moving Beam contacts whereby a single terminal connects toa very wide range of magnet wire sizes, or a Compliant Beam for contacting two magnet wires of the same diameter in one terminal for splicing or bi-filar applications.

Tab terminals are available with single barbs or multiple retention barbs for higher retention.

According to TE specifications SIAMEZE cavities are either integrated into coil bodies or specially designed cavity housings.

The magnet wires are positioned in the “U”shaped slots.

The SIAMEZE Inserter cuts the terminals from the strip and places the terminals over the magnet wire into the plastic cavities.

During this operation the small stripping devices penetrate the film insulation from the magnet wire.

Residual spring energy in the terminal causes the side walls of the IDC slot to function as opposing cantilever beams.

This constant pressure results in an intimate metal-to-metal interface, providing a reliable, long-term connection.

The wiping action between the wire and terminals remove all oxides or other contaminants present on both the conductor and the terminal slot side walls, producing a clean, stable, gas-tight electrical termination.

The AMP SIAMEZE Inserter may be used as a semi-automatic bench machine or integrated in production lines for fully-automatic applications.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

SIAMEZE Terminals (Continued)

Lead Lok Terminals Product Facts

- Provides perpendicular and parallel lead wire strain relief retention forces in excess of 20 lbs (90 N).
- AMP Inserter automatically positions and secures lead wire during insertion
- Manual, semi-automated, fully automated systems allow for lead wire termination
- Accepts #18-#22 [0.3mm 2-0.8 mm2] AWG solid or stranded lead wire with .115 [2.92] max.insulation diameter
- No lead wire stripping required



TE features the AMP Lead Lok strain relief terminal system that provides optimum lead wire retention when used in conjunction with SIAMEZE insulation displacement terminals.

After the one-step insertion of AMP SIAMEZE wire-to-wire terminals into TE specified plastic cavities, the application is ready for the secondary lead wire attachment.

The lead wire is manually positioned over the magnet wire terminated SIAMEZE wire-to-wire terminal.

The AMP Lead Lok Inserter cuts the Lead Lok terminals from the strip and places the terminal over the lead wire in the plastic cavities.

During this operation, the lead wire is automatically seated, the insulation pierced and the exposed solid or stranded conductor is terminated in the IDC slot of the SIAMEZE wire-to-wire terminal.

Residual spring energy in the terminal causes the side walls of the IDC slot to function as opposing cantilever beams.

This constant pressure results in an intimate metal-to-metal interface, providing a reliable, long-termconnection.

Perpendicular and parallel lead wire strain relief retention forces in excess of 20 lbs are achieved.

The AMP Lead Lok Inserter may be a secondary station in the AMP SIAMEZE Wire-to-Wire semi-automatic bench machine.

Information regarding terminal insertion equipment may be found in Magnet Wire Termination Overview #138516.

TECHNICAL DOCUMENTS

Cavity Specifications - Provide dimensional design guidelines & criteria for a cavity to be used with a SIAMEZE IDC terminal. The appropriate Cavity Specification number is shown on the following pages adjacent to the terminal number. As a general reference, overall dimensions are shown at the end of this section.

■ **Product Specifications** (These describe the performance characteristics and verification tests)

108-2085	Standard Range SIAMEZE Insulation Displacement
108-2293	High Temperature Standard Range SIAMEZE Insulation Displacement
108-2244	Fine Range SIAMEZE Insulation Displacement
108-2239	Medium Range SIAMEZE Insulation Displacement
108-2316	Heavy Range SIAMEZE Insulation Displacement

■ **Application Specifications** (These describe the requirements for using the product in its intended application)

114-13166	Standard and Fine Range SIAMEZE Insulation Displacement
114-13210	Medium and Heavy Range SIAMEZE Insulation Displacement

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

SIAMEZE Terminals (Continued)

SIAMEZE Interconnection System

How the System Operates

① **Magnet Wire**
The magnet wire is positioned in “U” slot manually or automatically by coil winding equipment.

② **Terminal Insertion Finger**
The terminal insertion finger is part of the SIAMEZE Inserter. It pushes the terminal that was sheared from the carrier strip through the“tube” into the cavity.

③ **Contact**
Various wire attachments in standard, fine, mediumand heavy duty terminals are available (See tables).

④ **IDC Slot**
The IDC slot in the terminal will terminate a wide range of magnet wire sizes.

⑤ **Stripping Burrs**
During the insertion process, these burrsstrip the film insulation from the magnet wire.

⑥ **Retention Barbs**
Terminal retention is provided in the cavity by single or multiple locking barbs.

⑦ **Plastic Cavity**
Design must comply with TE connectivity specifications(for cavity drawing numbers see tables). **ConsultingTE is required for design in.**

⑧ **Cavity Slot for Wire**
The width has to be in accord ance with the wire size (see cavity drawings).

⑨ **Wire Cutoff Block**
The wire cutoff block supports the magnet wire during the trimming process. The magnet wire is cut plain to the cavity front side.

⑩ **Trim Blade**
The trim blade cuts the excess magnet wire and the wire cutoff block at the front of the cavity.

⑪ **Terminal Insertion Complete**
The magnet wire termination is complete when the terminal is fully seated in the cavity.



Test Results

SIAMEZE products have been submitted to the following tests without significant millivolt increase:

Current Cycling—
250 cycles with each cycle consisting of 15 minutes “ON” followed by 15 minutes “OFF”

Thermal Shock—
25 Cycles -40°C to +125°C, 25 Cycles -40°C to +175°C for High Temperature terminals

Humidity—
Temperature Cycling
10 cycles between 25°C and 65°C at 80 to 100% RH

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

SIAMEZE Terminals (Continued)

Lead Lok Interconnection System

How the System Operates

① **Lead Lok Insertion Finger**
The Lead Lok insertion finger pushes the Lead Lok that was sheared from the carrier strip and positions the Lead Lok and lead wire into the IDC slot.

② **Lead Lok Terminal**
The Lead Lok terminal provides maximum lead wire retention in the cavity.

③ **Retention Barbs**
The Lead Lok multiple barbs provide retention in the cavity.

④ **Lead Wire**
Stranded, solid and bonded lead wire with 105°C PVC insulation can be used. Contact TE Engineering for other lead wires and insulation under consideration.

⑤ **IDC Slot**
The IDC slot will pierce the lead wire during insertion.

⑥ **Lead Wire Insertion Complete**
The lead wire termination is complete when the Lead Lok is fully seated in the cavity.



HOW TO CONNECT MULTIPLE MAGNET WIRES OR OTHER COMPONENTS

① **Bussed High Carrier Terminals**
Bridging of two SIAMEZE terminals that is accomplished by leaving the carrier strip between two adjacent terminals intact.

② **Bussed High Carry SIAMEZE Plastic Cavity**
Bussed cavity pocket designs are available for double or triple bussed terminals.

③ **Magnet Wire**
Magnet wire may be equal or differ in size for bi-filar applications.



Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

SIAMEZE Terminals (Continued)

Wire-to-Wire Terminals

Material
Brass



Type	Recommended Pocket[7]	Copper Magnet Wire Range		Lead Wire Range		Part Number	
		AWG	mm	AWG	mm²	Reeled	Loose
A Moving Beam	1601421	18-34	1.02-0.16	18-22[6]	0.8-0.3	1601000-1 1601000-2[5]	4-1601000-1[2] 4-1601000-2[2,5]
		27–36	0.36–0.13	18-22[6]	0.8-0.3	1601117-1 2-1601117-1[1]	4-1601117-1[2]
B Wire Specific[8]	1601421	18-34	1.02–0.16	20	0.5	1601056-1 2-1601056-1[1]	4-1601056-1[2]
		18-34	1.02-0.16	18	0.8	1601074-1 2-1601074-1[1]	4-1601074-1[2]
C High Carrier	1601433 1601440	18-34	1.02-0.16	18-22[6]	0.8-0.3	1601046-1 2-1601046-1[1]	4-1601046-1[2] 6-1601046-1[3] 8-1601046-1[4]
D High Carrier Specific[8]	1601433	27–36	0.36-0.13	20	0.5	1601237-1 2-1601237-1[1]	4-1601237-1[2] 6-1601237-1[3]
E Medium Range	1601436	12-23	2.06-0.56	16-20	1.3-0.5	1601136-1 2-1601136-1[1]	4-1601136-1[2] 6-1601136-1[3]
F Lead Lok	1601421 1601433 1601440			18-22	0.8-0.3	1601140-1 2-1601140-1[1]	4-1601140-1

1 Reversed Reeled—Consult TE drawing for orientation.
2 Loose Single.
3 Loose Bussed (Bridged) Double.
4 Loose Bussed (Bridged) Triple.
5 Finish is Post Plated Tin over Copper (Consult TE drawing for specifics).
6 Lead wire may be stranded, solid or bonded with 105°C PVC insulation. Contact TE Engineering when using other types of insulation.
7 Magnet wire 30 AWG [0.25 mm] and smaller also requires a wrap post per drawing 1601447.
8 Wire Specific terminals have a top contact designed to penetrate difficult Lead Wire Insulation (e.g Irradiated types).

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.
Dimensions are shown for reference purposes only. Specifications subject to change.
www.te.com/appliances

SIAMEZE Terminals (Continued)

Receptacle Terminals (Wire to Blade)

Material

Brass



A



B



C



D

Type	Recommended Pocket[5]	Copper Magnet Wire Range AWG	Copper Magnet Wire Range mm	L[8] Dim.	Mating Tab Size	Part Number Reeled	Part Number Loose
A Wire2Blade In Line	1601425	18-34	1.02-0.16	.300 7.62	.020 0.51	1601075-1 2-1601075-1[1]	4-1601075-1[2]
						1601075-2[6] 2-1601075-2[1,6]	4-1601075-2[2,6]
						2-1601075-3[1,7]	–
B Wire2Blade High Carrier In Line	1601426	18-34	1.02-0.16	.300 7.62	.020 0.51	1601196-1 2-1601196-1[1]	4-1601196-1[2] 6-1601196-1[3] 8-1601196-1[4]
C Wire2Blade In Line Medium Range	1601436	15-23	1.47-0.56	.550 13.97	.032 0.81	1601232-2[7] 2-1601232-2[1,7]	4-1601232-2[2,7]
D Wire2Blade Off Line Medium Range	1601437	15-23	1.47-0.56	.310 7.87	.032 0.81	1601137-2[6] 2-1601137-2[1,6]	4-1601137-2[2,6]

1 Reverse Reeled –Consult TE drawing for orientation.
2 Loose Single.
3 Loose Bussed (Bridged) Double.
4 Loose Bussed (Bridged) Triple.
5 Magnet wire 30 AWG [0.25] and smaller also requires a wrap post per Specification 1601447.
6 Finish is Pre Plated Tin (Consult TE drawing for specifics).
7 Finish is Post Plated Tin over Nickel (Consult TE drawing for specifics).
8 Overall Height of terminal does not include inserted Blade (Tab).

Pin Terminals

Material

Brass



E

Type	Recommended Pocket[2]	Copper Magnet Wire Range AWG	Copper Magnet Wire Range mm	L Dim.	Pin Dia.	Part Number Reeled	Part Number Loose
E Round Pin	1601424	18-34	1.02-0.16	.718 18.24	.084 2.13	1601077-1 2-1601077-1[1]	4-1601077-1[3]

1 Reverse Reeled –Consult TE drawing for orientation.
2 Magnet wire 30 AWG [0.25 mm] and smaller also requires a wrap post per drawing 1601447.
3 Loose piece single.

SIAMEZE Terminals (Continued)

Post Terminals

Material
Brass



Type	Recommended Pocket[7]	Copper Magnet Wire Range AWG	Copper Magnet Wire Range mm	Tab Size	L Dim.	Part Number Reeled	Part Number Loose
A PC Tab	1601424	18-34	1.02-0.16	.040 x .020 1.02 x 0.51	.345 8.76	1601009-4[5] 2-1601009-4[1,5]	4-1601009-4[2,5]
				.040 x .020 1.02 x 0.51	.405 10.29	1601214-2[5] 2-1601214-2[1,5]	4-1601214-2[2,5]
		29**	0.29	.040 x .020 1.02 x 0.51	.345 8.76	1601155-3[5] 2-1601155-3[1,5]	4-1601155-3[2,5]
		27-36	0.36-0.13	.040 x .020 1.02 x 0.51	.345 8.76	1601120-4[5] 2-1601120-4[1,5]	4-1601120-4[2,5]
B Extended PC Tab	1601425	18-34	1.02-0.16	.040 x .020 1.02 x 0.51	.456 11.57	1601095-2[4] 2-1601095-2[2,4]	4-1601095-2[2,4]
				.040 x .020 1.02 x 0.51	.485 12.32	1601041-3[5] 2-1601041-3[1,5]	4-1601041-3[2,5]
		27-36	0.36-0.13	.040 x .020 1.02 x 0.51	.485 12.32	1601128-3[5] 2-1601128-3[1,5]	4-1601128-3[2,5]
C Long Narrow Blade	1601431	18-34	1.02-0.16	.047 x .032 1.20 x. 0.81	.754 19.16	1601110-2[6] 2-1601110-2[1,6]	4-1601110-2[2,5]
				.059 x .032 1.50 x. 0.81	.669 17.00	1601099-2[5] 2-1601099-2[1,5]	4-1601099-2[2,5]
				.059 x .032 1.50 x. 0.81	.756 19.21	1601063-2[6] 2-1601063-2[1,6]	4-1601063-2[2,6]
				.059 x .032 1.50 x. 0.81	.904 22.96	1601037-2[6] 2-1601037-2[1,6]	4-1601037-2[2,6]
				.059 x .032 1.50 x. 0.81	1.005 25.53	1601066-2[6] 2-1601066-2[1,6]	4-1601066-2[2,6]
				.071 x .025 1.80 x 0.64	.974 24.74	1601104-2[6] 2-1601104-2[1,6]	4-1601104-2[2,6]
D Long Narrow Blade Mult-Barb	1601425	18-34	1.02-0.16	.059 x .032 1.50 x 0.81	.805 20.45	293214-1 2-293214-1[1]	—
E Medium Width Blade Mult-Barb	1601475	18-34	1.02-0.16	.118 x .020 3.00 x 0.51	.533 13.54	1601243-2[3] 2-1601243-2[1,3]	4-1601243-2[2,3]
		27-36	0.36-0.13	.118 x .025 3.00 x 0.64	.952 24.18	1601119-2[6] 2-1601119-2[1,6]	4-1601119-2[2,6]
F Medium Width Blade Medium wire range	1601438	12-23	0.56-2.06	.130 x .032 3.30 x 0.81	.872 22.15	1601138-1 2-1601138-1[1]	4-1601138-1[2]

1 Reverse Reeled –Consult TE drawing for orientation.
2 Loose Piece Single.
3 Finish is Post Plated Tin (Consult TE drawing for specifics).
4 Finish is Post Plated Tin over Copper (Consult TE drawing for specifics).
5 Finish is Post Plated Tin over Nickel (Consult TE drawing for specifics).
6 Finish is Pre Plated Tin (Consult TE drawing for specifics)
7 Magnet wire 30 AWG [0.25] and smaller also requires a wrap post per Specification 1601447
** Compliant contact can connect 2 wires of the same diameter.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

SIAMEZE Terminals (Continued)

110 Series (2.8 mm wide) FASTON Tab Terminals

Material

Brass



Type	Recommended Pocket[8]	Copper Magnet Wire Range AWG	Copper Magnet Wire Range mm	Thickness	L Dim.	Part Number Reeled	Part Number Loose
A Single Barb	1601425	18-34	1.02-0.16	.020 0.51	.640 16.26	1601005-1 2-1601005-1[1]	4-1601005-1[2]
				.020 0.51	.640 16.26	1601204-2[6,7] 2-1601204-2[1,6,7]	4-1601204-2[2,6,7]
				.020 0.51	.846 21.49	1601045-1 2-1601045-1[1]	4-1601045-1[2]
				.020 0.51	.846 21.49	1601059-1[7] 2-1601059-1[1,7]	4-1601059-1[2,7]
				.020 0.51	.925 23.50	1601073-1 2-1601073-1[1]	4-1601073-1[2]
B Single Barb Low Transition	1601431	18-34	1.02-0.16	.032 0.81	.945 24.00	1601097-3[6,7] 2-1601097-3[1,6,7]	4-1601097-3[2,6,7]
				.032 0.81	1.195 30.35	1601194-2[3,7] 2-1601194-2[1,3,7]	4-1601194-2[2,3,7]
C Multi-Barb	1601425	18-34	1.02-0.16	.020 0.51	.655 16.63	1601039-1 2-1601039-1[1]	4-1601039-1[2]
				.020 0.51	.655 16.63	1601039-2[6] 2-1601039-2[1,6]	4-1601039-2[2,6]
				.032 0.81	.630 15.99	1601064-1[7] 2-1601064-1[1,7]	4-1601064-1[2,7]
				.032 0.81	1.240 31.50	1601112-2[6,7] 2-1601112-2[1,6,7]	4-1601112-2[2,6,7]
		27-36	0.36-0.13	.032 0.81	1.240 31.50	1601133-2[6,7] 2-1601133-2[1,6,7]	4-1601133-2[2,6,7]

1 Reverse Reeled-Consult TE drawing for orientation.
2 Loose Piece Single.
3 Finish is Post Plated Tin over Nickel (Consult TE drawing for specifics).
4 Finish is Post Plated Tin (Consult TE drawing for specifics).
5 Finish is Pre-Plated Tin over Copper (Consult TE drawing for specifics).
6 Finish is Pre-Plated Tin (Consult TE drawing for specifics).
7 No hole in Tab.
8 Magnet wire 30 AWG [0.25] and smaller also requires a wrap post per Specification 1601447.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

www.te.com/appliances

SIAMEZE Terminals (Continued)

187 Series (4.75 mm wide)
FASTON Tab Terminals

Material

Brass

(except High Temp listed below)



Type	Recommended Pocket[8]	Copper Magnet Wire Range AWG	Copper Magnet Wire Range mm	Thickness	L Dim.	Part Number Reeled	Part Number Loose
A Single Barb	1601425	18-34	1.02-0.16	.020 0.51	.605 15.37	1601006-2[5] 2-1601006-2[1,5]	4-1601006-2[2,5]
B Single Barb Short Pocket	1601427	18-34	1.02-0.16	.020 0.51	.505 12.83	1601011-1 2-1601011-1[1]	4-1601011-1[2]
				.020 0.51	.590 14.99	1601018-2[5,6] 2-1601018-2[1,5,6]	4-1601018-2[2,5,6]
				.020 0.51	.985 25.02	1601033-2[5,6] 2-1601033-2[1,5,6]	4-1601033-2[2,5,6]
C Multi-Barb	1601425	18-34	1.02-0.16	.020 0.51	.618 15.70	1601021-2[5,6] 2-1601021-2[1,5,6]	4-1601021-2[2,5,6]
				.020 0.51	.655 16.64	1601013-1 2-1601013-1[1]	4-1601013-1[2]
				.020 0.51	.791 20.09	3-1601072-2[5,6]	4-1601072-2[2,5,6]
				.020 0.51	0.832 21.14	1601068-2[5,6] 2-1601068-2[1,5,6]	4-1601068-2[2,5,6]
				.032 0.81	.625 15.88	1601174-2[5,6] 2-1601174-2[1,5,6]	4-1601174-2[2,5,6]
				.032 0.81	.655 16.64	1601035-1 2-1601035-1[1]	4-1601035-1[2]
				.032 0.81	.655 16.64	1601035-2[5] 2-1601035-2[1,5]	4-1601035-2[2,5]
				.032 0.81	.745 18.92	293029-1[5] 2-293029-1[1,5]	–
		20-23**	0.58-0.81	.020 0.51	.655 16.64	1601142-1 2-1601142-1[1]	4-1601142-1[2]
D Multi-Barb Short Profile	1601434	18-34	1.02-0.16	.032 0.81	0.492 12.50	1601058-2[5,7] 2-1601058-2[1,5,7]	4-1601058-2[2,5,7]
				.032 0.81	0.571 14.50	1601226-1[3,6] 2-1601226-1[1,3,6]	4-1601226-1[2,3,6]
E Multi-Barb .187/.250 Profile	1601425	18-34	1.02-0.16	.020 0.51	.655 16.64	1601020-1 2-1601020-1[1]	4-1601020-1[2]
				.020 0.51	.655 16.64	1601020-2[5] 2-1601020-2[1,5]	4-1601020-2[2,5]
		18-34	1.02-0.16	.020 0.51	.805 20.45	1601049-2[5] 2-1601049-2[1,5]	4-1601049-2[2,5]

1 Reverse Reeled-Consult TE drawing for orientation.
2 Loose Piece Single.
3 High Temperature Copper Alloy.
4 Finish is Post Plated Tin (Consult TE drawing for specifics).
5 Finish is Pre Plated Tin (Consult TE drawing for specifics).
6 No hole in Tab.,
7 Extra Short Tab-Does not meet UL & NEMA length requirements.
8 Magnet wire 30 AWG [0.25] and smaller also requires a wrap post per Specification 1601447.
** Compliant contact can connect 2 wires of the same diameter

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.
Dimensions are shown for reference purposes only.
Specifications subject to change.
www.te.com/appliances

SIAMEZE Terminals (Continued)

250 Series (6.3 mm wide) FASTON Tab Terminals

Material
Brass



Type	Recommended Pocket[6]	Copper Magnet Wire Range AWG	Copper Magnet Wire Range mm	L Dim.	Tab Feature	Tab Size	Part Number Reeled	Part Number Loose
A Multi-Barb	1601425	27-36	0.36-0.13	.745 18.92	Hole	.250 x .032 6.35 x 0.81	1601118-2[3] 2-1601118-2[1,3]	4-1601118-2[3]
		18-34	1.02-0.16	.745 18.92	Hole	.250 x .032 6.35 x 0.81	1601002-2[3] 2-1601002-2[1,3]	4-1601002-2[3]
				.805 20.45	Hole	.250 x .032 6.35 x 0.81	1601028-2[3] 2-1601028-2[1,3]	4-1601028-2[3]
							1601028-1 2-1601028-1[1]	4-1601028-1
							284937-1[7] 2-284937-1[1,7]	—
					Dimple	.250 x .032 6.35 x 0.81	1601061-2[3] 2-1601061-2[1,3]	4-1601061-2[3]
				1.281 32.53	Hole	.250 x .032 6.35 x 0.81	1601052-2[2,4] 2-1601052-2[1,2,4]	4-1601052-2[2]
B Single Barb Medium Range	1601438	12-23	2.03-0.56	.778 19.76	—	.250 x .032 6.35 x 0.81	1601139-2[3] 2-1601139-2[1,3]	4-1601139-2[3]
C Single Barb Heavy Range	1601435	12-20	2.03-0.8	.885 22.48	Hole	.250 x .032 6.35 x 0.81	1601115-1 2-1601115-1[1]	4-1601115-1
		16-17[5]	1.27-1.15	.885 22.48	Hole	.250 x .032 6.35 x 0.81	1601159-1 2-1601159-1[1]	4-1601159-1
		14-15[5]	1.60-1.40	.885 22.48	Hole	.250 x .032 6.35 x 0.81	1601161-1 2-1601161-1[1]	4-1601161-1

1 Reverse Reeled –Consult TE drawing for orientation.
2 Finish is Pre-Plated Tin over Copper (Consult TE drawing for specifics).
3 Finish is Pre-Plated Tin (Consult TE drawing for specifics).
4 Double Carrier Strip.
5 Two magnet wires may be terminated in the same slot if diameters are equal.
6 Magnet wire 30 AWG [0.25 mm] and smaller also requires a wrap post per drawing 1601447.
7 Hole size and position complies with DIN standard.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

SIAMEZE Terminals (Continued)

Typical Plastic Cavity Pockets

Note: The overall dimensions shown on these pages are for general reference only. For design purposes refer to the TE Cavity Specification.

Plastic cavities, designed to TE specifications, may be molded as part of the coil bobbin or attached to a lamination stack in the area of the magnet wire coil.

Each cavity is a rectangular box with two narrow slots on opposing walls and a plastic cutoff or tie-off post.

During or after the winding process, the magnet wire is placed across the plastic cavities and into the slots, either manually or by coil winding equipment.

Unraveling is prevented by a slight friction fit, suitable bend or by wrapping the magnet wire around the wrap post.

During insertion, the insulation displacing terminal slot strip the film insulation from the magnet wire producing a stable electrical termination.

Terminal retention is retained in the plastic cavities by single or multiple barbs (Refer to Product Spec for force requirements).

Excess magnet wire is trimmed flush with the outside of the plastic cavity by a shear blade traveling with the terminal insertion ram.

TE can provide design and mold engineering resources to manufacture most specifically designed SIAMEZE cavity housings.



Cavity Specification 1601421



Cavity Specification 1601424



Cavity Specification 1601425



Cavity Specification 1601426



Cavity Specification 1601427



Cavity Specification 1601431

* Minimum dimension with Lead Lok slot.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

SIAMEZE Terminals (Continued)

Typical Plastic Cavity Pockets (Continued)



Cavity Specification 1601432



Cavity Specification 1601433



Cavity Specification 1601434



Cavity Specification 1601435



Cavity Specification 1601436



Cavity Specification 1601437



Cavity Specification 1601438



Cavity Specification 1601440



Wrap Post Specification 1601447



Cavity Specification 1601475

* Minimum dimension with Lead Lok slot.

MAG-MATE and SIAMEZE Application Tooling

MAG-MATE Product Terminator (MPT)

Product Facts

- **Single, dual and triple insertion**
- **Two-reel, two-product capability, with alternating feed capability**
- **Available as horizontal bench, vertical bench or independent module**
- **Module easily integrates into production lines using simple handshake signals**
- **Fine adjustment mechanism for insertion depth (.001 increments)**
- **Tube-type insertion tooling for standard MAG-MATE terminals**
- **Microprocessor controlled operation**
- **Holding fixture for bobbin can be designed and built by Tyco Electronics or the customer**

For quick, easy and reliable termination of magnet wire without pre-stripping the insulation or soldering, Tyco Electronics offers the MAG-MATE product family and the MPT-5 (MAG-MATE Product Terminator) air-operated insertion machine with micro-processor control. The MPT-5 machine inserts a MAG-MATE terminal into a customer-designed cavity in the coil bobbin or similar magnet-wire housing, terminating the wire and providing an I/O terminal or other connection. The MAG-MATE system can create a termination that is very close to the coil.

Dual reel capability of the MPT-5 allows insertion of two different MAG-MATE terminals, with the capability to alternate between inserting one and two terminals at a time. Two terminations per second are possible with dual insertion. Loaded with two different terminals, a single MPT-5 can cover a range of 8 AWGs.

A fifth generation machine, the MPT-5 is lighter and quieter than previous versions. The MPT-5 is available as a horizontal or vertical bench machine or as a discrete module for integration into automated lines. The discrete module also can be used to make a custom horizontal or vertical bench machine. A fixture to hold the coil assembly, which is required for bench operation, can be designed and built by Tyco Electronics or the customer.

The MPT-5 uses three or four air cylinders to feed terminals from one or both reels, cut terminals from the carrier strip, and insert terminals into the cavities. The display shows the operating conditions of the machine such as the batch count, total count, error messages, and ready state. The display also lets the operator step through the machine sequence or manually cycles the machine for set up or easy diagnosis of problems.

Solderless MAG-MATE Terminations:

- No need to pre-strip the magnet wire
- No wire embrittlements due to solder
- No soldering fumes
- Compact, clean termination
- Ideal for automation
- Fast magnet wire connections: Up to two per second with dual insertion



Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

MAG-MATE and SIAMEZE Application Tooling (Continued)

MPT-5S/L Machine for Mag Wire Coil Termination utilizing SIAMEZE and Lead Lok terminals



Product Facts

- **Single, dual and triple insertion**
- **Two-reel, two-product capability, with alternating feed capability**
- **Available as horizontal bench, vertical bench or independent module**
- **Module easily integrates into production lines using simple handshake signals**
- **Fine adjustment mechanism for insertion depth (.001 increments)**
- **Tube-type insertion tooling for standard SIAMEZE & Lead Lok terminals**
- **Microprocessor controlled operation**
- **Holding fixture for bobbin can be designed and built by Tyco Electronics or the customer**

For quick, easy and reliable termination of magnet wire without pre-stripping the insulation or soldering, Tyco Electronics offers the SIAMEZE terminals and Lead Lok product family and the MPT-5S/L (MAG-MATE Product Terminator) air-operated insertion machine with micro-processor control. The MPT-5S/L machine inserts a SIAMEZE terminal into a customer-designed cavity in the coil bobbin or similar magnet-wire housing, terminating the wire and providing an I/O terminal or other connection. The MPT-5S/L can insert both the SIAMEZE terminal for magnet wire termination and the Lead Lok terminal to assure your lead wire connection.

Dual reel capability of the MPT-5S/L allows insertion of two different SIAMEZE terminals, with the capability to alternate between inserting one and two terminals at a time. Two terminations per second are possible with dual insertion.

A fifth generation machine, the MPT-5s/L is lighter and quieter than previous versions. The MPT-5S/L is available as a horizontal or vertical bench machine or as a discrete module for integration into automated lines. The discrete module also can be used to make a custom horizontal or vertical bench machine. A fixture to hold the coil assembly, which is required for bench operation, can be designed and built by Tyco Electronics or the customer. The MPT-5S/L uses three or four air cylinders to feed terminals from one or both reels, cut terminals from the carrier strip, and insert terminals into the cavities. The display shows the operating conditions of the machine such as the batch count, total count, error messages, and ready state. The display also lets the operator step through the machine sequence or manually cycles the machine for set up or easy diagnosis of problems.

Solderless SIAMEZE terminations:

- No need to pre-strip the magnet wire
- No wire embrittlements due to solder
- No soldering fumes
- Compact, clean termination
- Ideal for automation
- Fast magnet and lead wire connections: Up to two per second with dual insertion

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

www.te.com/appliances

MAG-MATE and SIAMEZE Application Tooling (Continued)

Application Tooling for MAG-MATE Terminals

The Module

The MPT-5 insertion module is the cornerstone of Tyco Electronics magnet wire application tooling. A fifth generation machine, the MPT-5 module is used in conjunction with our bench machine, LPT-522, Rotary Index Table, and can also be order separately when using your equipment manufacture of choice. Electric, pneumatic and de-reeling controls are available allowing for easy integration in your production line. Experienced Tyco Electronics personnel will work with the customer and the equipment manufacturer to adapt the module to their automated assembly system.

Specifications

Electrical—120 VAC, 60 Hz, 5 A, 1 Ø, or 240 VAC, 50 Hz, 2 A, 1 Ø

Air—80 psi [5.52 bar], 3 scfm [0.00142 m^3/s]

Weight—Approx. 60 lb [27.2 kg]

Width—8 [204]

Depth—7 [178]

Height—30 [762]

Hand Tools

Part Number 274250-2
Poke-In Terminals

Part Number 274260-1
.187 [4.75] Tab Terminals

Part Number 274282-1
.250 [6.35] Tab Terminals

This insertion tool is capable of applying terminals furnished as loose piece parts. Use for prototype, production start-up and moderate volume production runs. Terminals can be inserted at rates up to 300 per hour.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

MAG-MATE and SIAMEZE Application Tooling (Continued)

Application Tooling for MAG-MATE Terminals

Rotary Index Table

Product Facts

- **High-volume rates, up to 600 assemblies per hour**
- **Handles Standard and Mini MAG-MATE terminals through interchangeable insertion modules**
- **Load-while-run feature increases productivity**
- **Fast, simple machine setup and changeover**
- **Versions to handle in-line, radial, and linear/angularly opposed cavities**
- **Easy programming through hand-held keypad/display**
- **Up to 30 insertion sequences stored in EEPROM memory**
- **Options include**
  - **Continuity test station**
  - **Bend station**
  - **Dual MAG-MATE modules**
  - **X- or Y-axis travel**
  - **Auto-change single/dual insertion modules**

The Rotary Index Table is a semiautomatic machine that automatically positions fixtured coils, bobbins, and field assemblies for insertion of MAG-MATE terminals. The table is used with MPT-5 insertion modules, which mount vertically above the table and insert terminals fed from a reel. Modules which are not included as part of the base machine, are available for the entire MAG-MATE line, including Standard and Mini MAG-MATE, SIAMEZE and Lead Lok products.

In operation, the operator places the coil/bobbin/field assembly on the worktable and cycles the machine. The table rotates 90˚ or 180˚ to position the assembly under the insertion module for processing. As each terminal is inserted, the machine automatically indexes to the next insertion position. While this assembly is being processed, the operator can remove the assembly processed during the previous cycle and load a new coil/bobbin/field assembly. This load-while-run feature helps maximize productivity. Assembly rates of up to 600 coils per hour (at six terminations per coil) are possible with dual insertion.

A hand-held operator's terminal contains a keypad and easy-to-read LCD display to allow quick, easy programming of machine functions, including insertion sequences. Up to 30 programs (insertion sequences) can be stored in the EEPROM internal memory.

The machine is available with any combination of one or two MPT-5 insertion modules that are fixed or indexing, with or without a rotating fixture for axial insertion. One version allows indexing only in the Y axis for processing in-line cavities. The other includes a rotary fixture that allows the coil/bobbin/field assembly to be rotated to process cavities radially or linear/angularly opposed.

Besides its fast production rates, the rotary table is also designed to enhance productivity through reliability and easy setup. The number of adjustments required for normal operation has been minimized, while the procedure for product changeovers takes only a few minutes. The result is a machine with little downtime.

Options include a continuity test station, a bend station that bends terminals up to 90˚ after insertion, dual modules that insert two identical or different terminals simultaneously, and X-axis travel.

Cost savings and productivity are enhanced with Tyco Electronics Field Engineering Service, which provides complete setup and installation assistance, operating and maintenance training, and continuing rapid response through the Toll-Free Technical Support Center at 1-800-522-6752.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

MAG-MATE and SIAMEZE Application Tooling (Continued)

LPT-522 Linear Product Terminator

Product Facts

- **Intermediate to high volume rates, up to 600 assemblies per hour**
- **Flexible platform accommodates secondary application modules**
- **Version to handle in-line, radial, and linear/angularly opposed cavities**
- **Programmable linear slide and rotary table**
- **Easy programming through keypad display**
- **Palletized fixture system for greater efficiency and production rates**
- **Microprocessor controlled**
- **Fine insertion depth adjustment (.001 increments)**
- **Two-reel, two-product capability with or without alternating feed**
- **Single, dual separate, and on-the-fly dual common insertion capability**

Specifications

Air — 10 scfm@80 psi minimum
Electrical — 110 VAC, 5 AMP
Footprint — 60"x 52"

The Linear Product Terminator-522 was designed for intermediate to high volume applications. It is also a very flexible platform since it can accommodate two secondary application modules. These can include, but are not limited to, special wrap-off post trim, continuity testing with defective coil identification, and tab bending.

The LPT-522 features our MPT-5 insertion module as well as a programmable linear slide and rotary table system. The flexible system can process coils that have cavity configurations in a linear pattern, axial pattern, or combination of both.

The LPT-522 machine is of a serial process design, which allows for a unique coil holding fixture. This fixture can be palletized to increase your efficiency and production rates. The palletized system allows the operator to load/unload a pallet of coils while a second pallet is processing on this machine, increasing the machine up time and decreasing non-productive labor.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

MAG-MATE and SIAMEZE Application Tooling (Continued)

LPT-522 Linear Product Terminator (Continued)



Rotary Index Insertion Process



Optional Continuity Test Station

Magnet Wire Termination Machines—Cost Comparison

Machine Attribute	Horizontal Bench Machine (HBM)	Vertical Bench Machine (VBM)	LPT-522 Insertion Machine	RIT Insertion Machine
Applications	● Single row bobbin ● Single terminal feed ● Bottom trim	● Single/Dual/Axial bobbin ● Single or dual feed ● Bottom or top trim	● Same as VBM plus: -Multiple bobbin capacity Auxiliary stations ● Serial Processing	● Same as LPT, plus: -Up to 3 different terminals ● Parallel processing
Machine Cost	■	■■	■■■	■■■■
Fixture Cost	■■	■■■	■	■■■■
Complexity	■	■■	■■■■	■■■■
Production Rate	■	■	■■■	■■■■
Cost / Insertion	■■■	■■■■	■■	■

[■ = lowest level] [■■ = mid level] [■■■ = high level] [■■■■ = highest level]

Note: All machine options work in conjunction with our MPT-5 module. The MPT-5 module can incorporate an on-the-fly feature, which allows for selection of dual common insertions. The MPT-5 module can also be incorporated in your automated line using your integrator of choice. Please call for details.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

AMPLIVAR Splices

Product Facts

- **Compression crimp eliminates cold solder points, weld burns and wire embrittlement usually connected with thermal-type terminations**
- **Excellent tensile strength—vibration resistant**
- **Provides a superior electrical connection that is free of many contaminants such as stripper residue and solder flux**
- **Precision formed, strip-fed splices terminated in AMP automatic machines for high production rates per hour**
- **High termination rates, low wire consumption and the elimination of rejects caused by solder flux or heat damage results in the lowest applied costs**
- **Precisely controlled crimp termination helps eliminate human error for maximum reliability**
- **Splice up to 3 magnet wires together with stranded lead in one barrel**

Applications

- **Motor windings and connections**
- **Coil connections**
- **Transformer windings and connections**
- **Solid wire connections**
- **Lighting ballasts**
- **Power supplies**
- **Starters and alternators**



Tyco Electronics offers a full selection of AMP AMPLIVAR splices that are specifically designed to terminate magnet wire to itself or in combination with standard solid or stranded lead wire.

AMPLIVAR splices have machined, sharp edged serrations inside the crimp barrels. These serrations, made by a special production process, pierce the insulating layer of magnet wires in a manner that provides a large contact area.

In a one-step operation the magnet wire is automatically multiple ring-stripped of its insulation as it is forced into the serrations during the precisely controlled crimp.

The resulting termination produces a high tensile strength, air-sealed connection that is as resistant to corrosion as the insulated conductor.

As many as three magnet wires can be terminated simultaneously in one splice. In addition, copper or aluminum magnet wire, or a combination of both, can be terminated.

When required, copper or aluminum magnet wire can be combined with standard, pre-stripped solid or stranded lead wires.

Depending on your specific application, AMPLIVAR splices are available in 5, 7 and 9 serration versions for terminations in the 100 to 22,000 CMA range as well as miniature and subminiature designs for terminations in the 100 to 1850 CMA range.

The crimping of AMPLIVAR splices is done by semi-automatic crimping machines for high output per hour production rates.



Section AA



Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

AMPLIVAR Splices (Continued)

Technical Features

Applicable Types of Wire — Cu, Al (Solid) together or in combination with stranded lead wire

Wire Size Range — from 300 to 13,000 CMA (0.1 mm^2 to 6.6 mm^2)

Terminal Base Material — Brass, phosphor bronze

Surface Finish — plain and tin plated except where noted

Temperature Range — –65°C to +150°C

Rated Current — according connected wire size

Rated Voltage — according terminated winding

Test Results

The AMPLIVAR products have been subjected to the following tests without significant millivolt losses.

Temperature Cycling — 25 cycles with each cycle consisting of 30 minutes at +125°C followed by 30 minutes at –65°C

Heat Age — 96 hours at +150°C

Thermal Shock — 25 cycles with each cycle consisting of 30 minutes at +150°C followed by 30 minutes at –65°C

Salt Spray — 96 hours at +35°C with a 5% salt solution spray

Humidity — 96 hours at 90–95% relative humidity and +40°C

Current Cycling — 10,000 cycles with each consisting of 3 minutes on and 3 minutes off at a current (25 A) which establishes a wire temperature

TYPICAL CURRENT CYCLING TEST RESULTS





Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

AMPLIVAR Splices (Continued)

General Application Guidelines

To assist you in obtaining the optimum AMPLIVAR termination, the following guidelines are recommended:

1. All magnet wires must be placed in the bottom of the wire barrel before crimping. If lead wire is to be crimped in the same termination, it should be placed on top of the magnet wires.
2. Wire barrels are designed to accept a maximum of three insulated magnet wires plus stranded lead wires.
3. The ratio of magnet wire diameters crimped in any wire barrel should not exceed 2:1. This ratio is approximately a range from the largest to the smallest magnet wire of six sizes.
4. The sum of the circular mil area (CMA) of the magnet wires and any lead wires should not exceed the capacity of the splice.
5. The sum of the diameters of the individual magnet wires plus twice the terminal stock thickness must be equal to or less than the crimp width.
6. Magnet wire of 26 AWG [0.40 mm] or smaller should be used with 7-serration splices having "shallow serrations," and magnet wire of 28 AWG [0.32 mm] or smaller should be used with 9-serration splices having "shallow serrations" (part numbers identified with asterisk [*] are in the tabular data on the following technical pages).
7. Magnet wire of 20 AWG [0.81 mm] or larger having an insulation thickness heavier than "single film coated," should not be used with splices having "shallow serrations" (those part numbers marked with an asterisk [*] in the tabular data on the following technical pages).
8. When aluminum magnet wire is used, splices and terminals must be tin plated.
9. Consult Tyco Electronics for splice and terminal selection and recommendations for all non-standard applications.

Technical Documents

Application Specifications describe requirements for using the product in its intended application and or crimping information. They are intended for the Packaging and Design Engineer and the Machine Setup Person.

114-2002	AMPLIVAR 7-Serration Pigtail Splices	114-2006	AMPLIVAR Subminiature Pigtail Splices
114-2003	AMPLIVAR 9-Serration Pigtail Splices	114-2009	AMPLIVAR 5-Serration Thru Splices
114-2005	AMPLIVAR Subminiature Thru Splices	114-2016	AMPLIVAR Miniature Pigtail Splices

Suggested Splice Selection Procedure

Use the following guide to help you to determine the proper splice for your application:

1. Use 9-serration splices, tin plated when terminating aluminum magnet wire or combinations with aluminum magnet wire.
2. Use 9-serration splices for hermetic and severe environment applications.
3. Use splices identified with an asterisk [*] when terminating 7-serration 26 AWG [0.40 mm] or smaller wires and 9-serration 28 AWG [0.32 mm] or smaller wires.
4. Calculate the total CMA of the magnet wires plus any lead wires to be terminated. Always use the coated magnet wire for CMA (see pages 94–96).
5. Calculate the total magnet wire diameters (see pages 94 and 95).
6. Select a splice for trial calculations. It should have the proper CMA range. Plating finish should be considered at this time.
7. Calculate the sum of the magnet wire diameters plus two splice stock thicknesses. If this total is less than the crimp width of the splice selected, it may be used. If the total is greater than the crimp width, a splice with a greater crimp width must be selected. Consult Tyco Electronics for special wide tooling recommendations.

Example:

■ Selection of a Pigtail Splice to terminate the following wires:

One 28 AWG [0.32 mm] copper magnet wire.
One 22 AWG [0.64 mm] aluminum magnet wire.
One 18 AWG [0.8–0.9 mm^2] 19-strand copper lead wire.

■ Calculate the total CMA (Procedure 4):

28 AWG [0.32 mm] coated magnet wire	= 185 CMA
22 AWG [0.64 mm] coated magnet wire	= 708 CMA
18 AWG [0.8–0.9 mm^2] stranded lead wire	= 1608 CMA
Total	**= 2501 CMA**

■ Calculate the sum of the magnet wire diameters (Procedure 5):

28 AWG [0.32 mm] coated magnet wire	= .0136 [0.35]
22 AWG [0.64 mm] coated magnet wire	= .0266 [0.68]
Total	**= .0402 [1.03]**

■ Select a terminal for trial calculations. Splice No. 62305-2, page 49 (Procedure 6):

CMA range	= 600–3000
Stock thickness	= .016 [0.41]
Crimp width	= .110 [2.79]

9-serration, tin plated for aluminum magnet wire (Procedure 1).

Splice identified with asterisk [*] for 28 AWG [0.32 mm] (Procedure 3).

■ Calculate the sum of the magnet wire diameters plus two splice stock thicknesses (Procedure 7):

.0402 + (.016 x 2) = .0722
[1.02 + (0.41 x 2) = 1.84

.0722 [1.84] is less than the splice crimp width of .110 [2.79]; therefore, Part No. 62305-2 may be used.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only.
Specifications subject to change.

www.te.com/appliances

AMPLIVAR Splices (Continued)

9 Serrations — Pigtail Type

Product Facts
(Plus All 7 Serration Facts)

- **Splice length is increased on larger CMA splices for improved performance**
- **Serration depths are varied within the splice to give optimum electrical/ mechanical performance on all wire sizes**
- **Serration sidewall angles are varied to allow better wire stripping and serration fill**
- **Flat bottom of splice helps keep magnet wires on bottom as required during crimping**
- **Magnet wires 28 AWG [0.32 mm] and larger may be terminated without requiring shallow serrations**
- **Additional serrations enhance stability of crimp**



AWG/ mm²	Wire Range Solid Dia.	Wire Range CMA	Stock Thickness	Crimp Width	Dim. L	Material	Part Number
24-18.5 0.26-0.80	**.020-.039** 0.55-1.00	400-1500	**.016** 0.41	**.080** 2.03	**.225** 5.72	Tin Plated Brass	62303-2*
22-15.5 0.38-1.54	**.028-.055** 0.70-1.40	600-3000	**.020** 0.51	**.110** 2.79	**.225** 5.72	Tin Plated Brass	62304-2
22-15.5 0.38-1.54	**.028-.055** 0.70-1.40	600-3000	**.016** 0.41	**.110** 2.79	**.225** 5.72	Tin Plated Brass	62305-2*
18.5-13.5 0.80-2.54	**.039-.071** 1.00-1.80	1500-5000	**.020** 0.51	**.110** 2.79	**.225** 5.72	Tin Plated Brass	62306-2
18.5-13.5 0.80-2.54	**.039-.071** 1.00-1.80	1500-5000	**.016** 0.41	**.110** 2.79	**.225** 5.72	Tin Plated Brass	62307-2*
15.5-12 1.54-3.46	**.055-.083** 1.40-2.10	3000-7000	**.020** 0.51	**.140** 3.56	**.265** 6.73	Tin Plated Brass	62308-2
13.5-10 2.54-4.90	**.071-.098** 1.80-2.50	5000-10,000	**.025** 0.64	**.180** 4.57	**.265** 6.73	Tin Plated Brass	62309-2
12-9 3.46-6.38	**.083-.112** 2.10-2.85	7000-13,000	**.025** 0.64	**.180** 4.57	**.265** 6.73	Tin Plated Brass	62310-2
10-8 4.90-8.60	**.098-.130** 2.50-3.31	10,000-17,000	**.030** 0.76	**.250** 6.35	**.340** 8.64	Tin Plated Brass	62311-2
9-6.5 7.07-9.45	**.118-.137** 3.00-3.47	14,000-22,000	**.030** 0.76	**.250** 6.35	**.340** 8.64	Tin Plated Brass	1742898-1

*These splices are recommended for applications using wire size 28 AWG [0.32 mm] or smaller.
[1] Special high force application equipment required.

7 Serrations — Pigtail Type

Product Facts

- **Taper on both crimper and anvil improves flex life of termination**
- **Longer "flat" on tooling improves electrical performance (.125 vs. .080 [3.18 vs. 2.03])**
- **Radius on wire entry end of splice helps prevent nicking wires and improves mechanical performance**
- **Serrations are offset to sheared end to place additional serrations in "electrical" portion of crimped splice**
- **Splice CMA ranges are overlapped so that two splices are available for any given CMA**



AWG/ mm²	Wire Range Solid Dia.	Wire Range CMA	Stock Thickness	Crimp Width	Dim. L	Material	Part Number
22-15.5 0.38-1.54	**.028-.055** 0.70-1.40	600-3000	**.020** 0.51	**.110** 2.79	**.225** 5.72	Brass	62000-1
22-15.5 0.38-1.54	**.028-.055** 0.70-1.40	600-3000	**.020** 0.51	**.110** 2.79	**.225** 5.72	Brass	62157-1*
22-15.5 0.38-1.54	**.028-.055** 0.70-1.40	600-3000	**.020** 0.51	**.110** 2.79	**.225** 5.72	Tin Plated Brass	62000-2
22-15.5 0.38-1.54	**.028-.055** 0.70-1.40	600-3000	**.020** 0.51	**.110** 2.79	**.225** 5.72	Tin Plated Brass	62157-2*
22-15.5 0.38-1.54	**.028-.055** 0.70-1.40	600-3000	**.020** 0.51	**.110** 2.79	**.225** 5.72	Tin Plated Brass	62200-2[1]
18.5-13.5 0.80-2.54	**.039-.071** 1.00-1.80	1500-5000	**.020** 0.51	**.110** 2.79	**.225** 5.72	Brass	62040-2
18.5-13.5 0.80-2.54	**.039-.071** 1.00-1.80	1500-5000	**.020** 0.51	**.110** 2.79	**.225** 5.72	Tin Plated Brass	62040-1
18.5-13.5 0.80-2.54	**.039-.071** 1.00-1.80	1500-5000	**.020** 0.51	**.110** 2.79	**.225** 5.72	Phosphor Bronze	964156-1
15.5-12 1.54-3.46	**.055-.083** 1.40-2.10	3000-7000	**.020** 0.51	**.140** 3.56	**.225** 5.72	Brass	62001-1
15.5-12 1.54-3.46	**.055-.083** 1.40-2.10	3000-7000	**.020** 0.51	**.140** 3.56	**.225** 5.72	Tin Plated Brass	62001-2
15.5-12 1.54-3.46	**.055-.083** 1.40-2.10	3000-7000	**.020** 0.51	**.140** 3.56	**.225** 5.72	Tin Plated Brass	62201-2[1]
12-10 2.10-6.0	**.085-.110** 2.10-2.85	7000-12,000	**.025** 0.64	**.250** 6.35	**.225** 5.72	Tin Plated Brass	62295-1
12-10 2.10-6.0	**.085-.110** 2.10-2.85	7000-12,000	**.025** 0.64	**.250** 6.35	**.225** 5.72	Brass	62295-2
12-9 2.10-6.38	**.085-.115** 2.10-3.47	7000-13,000	**.025** 0.64	**.180** 4.57	**.225** 5.72	Tin Plated Brass	62002-2

*These splices are recommended for applications using wire size 26 AWG [0.40 mm] or smaller.
[1] Flat bottom.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

AMPLIVAR Splices (Continued)

7 Serrations — Thru Type

Product Facts

- Crimp bellmouth provides retention in circular cavity slot in bobbin



AWG/ mm²	Wire Range Solid Dia.	Wire Range CMA	Stock Thickness	Crimp Width	Dim. L	Material	Part Number
22-15.5 0.38-1.54	**.028-.055** 0.70-1.40	600-3000	**.020** 0.51	**.110** 2.79	**.225** 5.72	Tin Plated Brass	1217384-1*

*These splices are recommended for applications using wire size 26 AWG [0.40 mm] or smaller.

5 Serrations — Thru Type

Product Facts

- Wide range of thru splices
- Serrations centered in splice to achieve optimum electrical and mechanical performance in a thru splice
- CMA range accepts a wide variety of wire sizes and combinations

A



B



Type	AWG/ mm²	Wire Range Solid Dia.	Wire Range CMA	Stock Thickness	Crimp Width	Dim. L	Material	Part Number
A	17-12.5 1.00-2.80	**.045-.075** 1.15-1.85	2000-5400	**.020** 0.51	**.110** 5.08	**.235** 5.97	Brass	63564-1
	10-8 5.00-8.00	**.100-.125** 2.55-3.20	10,000-16,000	**.032** 0.80	**.180** 4.57	**.267** 6.78	Tin Plated Brass	63561-1
	10-7.5 5.00-11.50	**.100-.150** 2.60-3.80	10,400-22,900	**.030** 0.76	**.300** 7.62	**.310** 7.87	Tin Plated Brass	63562-1
B	22-15.5 0.38-1.54	**.028-.055** 0.70-1.40	600-3000	**.020** 0.51	**.110** 2.79	**.225** 5.72	Brass	42076
	22-15.5 0.38-1.54	**.028-.055** 0.70-1.40	600-3000	**.020** 0.51	**.110** 2.79	**.225** 5.72	Brass	42192-1*
	22-15.5 0.38-1.54	**.028-.055** 0.70-1.40	600-3000	**.020** 0.51	**.110** 2.79	**.225** 5.72	Tin Plated Brass	42192-2*
	22-15.5 0.38-1.54	**.028-.055** 0.70-1.40	600-3000	**.020** 0.51	**.110** 2.79	**.225** 5.72	Brass	42778-1*[1]
	22-15.5 0.38-1.54	**.028-.055** 0.70-1.40	600-3000	**.020** 0.51	**.110** 2.79	**.225** 5.72	Tin Plated Brass	42778-2*[1]
	18.5-13.5 0.80-2.54	**.039-.071** 1.00-1.80	1500-5000	**.020** 0.51	**.110** 2.79	**.225** 5.72	Brass	41765
	18.5-13.5 0.80-2.54	**.039-.071** 1.00-1.80	1500-5000	**.020** 0.51	**.110** 2.79	**.225** 5.72	Tin Plated Brass	41899
	18.5-13.5 0.80-2.54	**.039-.071** 1.00-1.80	1500-5000	**.020** 0.51	**.110** 2.79	**.225** 5.72	Brass	42119-1*
	18.5-13.5 0.80-2.54	**.039-.071** 1.00-1.80	1500-5000	**.020** 0.51	**.110** 2.79	**.225** 5.72	Brass	42776-1*[1]
	18.5-13.5 0.80-2.54	**.039-.071** 1.00-1.80	1500-5000	**.020** 0.51	**.110** 2.79	**.225** 5.72	Tin Plated Brass	42776-2*[1]
	15.5-12 1.54-3.46	**.055-.083** 1.40-2.10	3000-7000	**.020** 0.51	**.140** 3.56	**.225** 5.72	Brass	41766
	15.5-12 1.54-3.46	**.055-.083** 1.40-2.10	3000-7000	**.020** 0.51	**.140** 3.56	**.225** 5.72	Tin Plated Brass	41900
	15.5-12 1.54-3.46	**.055-.083** 1.40-2.10	3000-7000	**.020** 0.51	**.140** 3.56	**.225** 5.72	Brass	42779-1[1]
	15.5-12 1.54-3.46	**.055-.083** 1.40-2.10	3000-7000	**.020** 0.51	**.140** 3.56	**.225** 5.72	Tin Plated Brass	42779-2[1]
	12-10 3.46-6.00	**.083-.110** 2.10-2.80	7000-12,000	**.025** 0.64	**.250** 6.35	**.225** 5.72	Tin Plated Brass	61074-1[1,2]
	12-9 3.46-6.38	**.083-.112** 2.10-2.85	7000-13,000	**.025** 0.64	**.180** 4.57	**.225** 5.72	Brass	41770
	12-9 3.46-6.38	**.083-.112** 2.10-2.85	7000-13,000	**.025** 0.64	**.180** 4.57	**.225** 5.72	Tin Plated Brass	41904
	12-9 3.46-6.38	**.083-.112** 2.10-2.85	7000-13,000	**.025** 0.64	**.180** 4.57	**.225** 5.72	Brass	42780-1[1]
	12-9 3.46-6.38	**.083-.112** 2.10-2.85	7000-13,000	**.025** 0.64	**.180** 4.57	**.225** 5.72	Tin Plated Brass	42780-2[1]

* These splices are recommended for applications using wire size 26 AWG [0.40 mm] or smaller.
[1] Increased terminal pitch.
[2] Increased U-diameter.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

www.te.com/appliances

AMPLIVAR Splices (Continued)

5 Serrations — Pigtail Type

Product Facts

- Serration depths are varied within the splice to give optimum electrical / mechanical performance on all wire sizes
- Flat bottom of splice helps keep magnet wires on bottom as required during crimping



AWG/ mm²	Wire Range Solid Dia.	Wire Range CMA	Stock Thickness	Crimp Width	Dim. L	Material	Part Number
20-17 0.50-1.00	**.030-.045** 0.80-1.15	1000-2000	**.016** 0.41	**.100** 2.54	**.225** 5.72	Tin Plated Brass	62670-2*[1]

*These splices are recommended for applications using wire size 26 AWG [0.40 mm] or smaller.
[1] Flat bottom.

Miniature Splice — Pigtail Type

Product Facts

- The Miniature AMPLIVAR splice was developed for crimping thinner copper magnet wires having a diameter between .003 and .016 [0.08 and 0.40 mm] and has to be connected with a stranded conductor
- The diameter of one conductor strand should not exceed the magnet wire diameter to be applied



AWG/ mm²	Wire Range Solid Dia.	Wire Range CMA	Stock Thickness	Crimp Width	Dim. L	Material	Part Number
27-21 0.10-0.40	**.014-.030** 0.35-0.75	200-850	**.012** 0.30	**.055** 1.40	**.195** 4.95	Tin Plated Brass	63431-1
25-18 0.16-0.90	**.015-.045** 0.45-1.10	300-1850	**.012** 0.30	**.070** 1.78	**.195** 4.95	Copper-Nickel	61166-1
24-18.5 0.20-0.75	**.020-.039** 0.55-1.00	480-1500	**.014** 0.36	**.080** 2.03	**.195** 4.95	Tin Plated Brass	62341-1
24-18.5 0.20-0.75	**.020-.039** 0.55-1.00	480-1500	**.014** 0.36	**.080** 2.03	**.195** 4.95	Brass	62341-2
24-18 0.20-0.80	**.020-.040** 0.55-1.00	480-1700	**.016** 0.41	**.070** 1.78	**.195** 4.95	Brass	62044-1

Subminiature Splice — Thru or Pigtail Type

Product Facts

- The compactness of these splices makes them ideal for use in small subfractional motors, transformers, relays, solenoids, indicator lamps and small appliance terminations
- These splices provide the same reliability as the larger AMPLIVAR splices



AWG/ mm²	Wire Range Solid Dia.	Wire Range CMA	Stock Thickness	Crimp Width	Dim. L	Material	Part Number
30-26 0.05-0.15	**.010-.015** 0.30-0.50	100-300	**.010** 0.25	**.042** 1.08	**.080** 2.03	Tin Plated Brass	63621-2
24-19 0.26-0.60	**.020-.035** 0.55-0.90	400-1300	**.016** 0.41	**.070** 1.78	**.100** 2.54	Tin Plated Brass	62194-2
24-19 0.26-0.60	**.020-.035** 0.55-0.90	400-1300	**.016** 0.41	**.070** 1.78	**.100** 2.54	Gold Plated Brass	62194-4

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

AMPLIVAR Terminals

Products Facts

- **Ring tongue terminals available for 2 to 3/8 stud diameters**
- **FASTON Tab terminals accept .125 [3.18], .187 [4.75] and .250 [6.35] receptacle terminals**
- **FASTON Receptacle terminals accept .187 [4.75] and .250 [6.35] tab terminals**
- **FASTON Stator Receptacle accept .250 x .032 [6.35 x 0.81] tab terminal**
- **Pin receptacle terminals accept .062 [1.57] and .090 [2.29] diameter pins**



Applications

- **Motor windings**
- **Transformers**
- **Power supplies**
- **Starters and alternators**

AMPLIVAR magnet wire terminals are designed to terminate copper and/or aluminum magnet wire.

Terminals are insulation displacing; therefore, magnet wires do not require a separate prestripping operation.

The unique wire barrel design, with serrations and burrs, produces a superior metal-to-metal compression crimp with excellent tensile strength.

Terminals are available in a variety of ring tongue, FASTON straight, flag and stator receptacles and tab quick-disconnect style terminals.

Direct connection to magnet wire eliminates the need for separate stranded wire terminal connection to input/output devices.

Matched with AMP automated application tooling allows high production rates for strip-form terminals.

Product Specifications describe the product qualification test results completed by Tyco Electronics for consideration of product use in a specific application. They are intended for the Design and Product Reliability Engineer.

108-16000 — AMPLIVAR Ring Tongue Terminals

108-1718 — AMPLIVAR .125 Blade Terminals [Type A]

Technical Documents

Application Specifications describe requirements for using the product in its intended application and or crimping information. They are intended for the Packaging and Design Engineer and the Machine Setup Person.

114-2145 AMPLIVAR .125 Blade Terminals

114-2146 AMPLIVAR FASTIN-FASTON Series 187 Tab Terminals

114-2070 AMPLIVAR FASTON Series 250 Tab Terminals

114-2144 AMPLIVAR FASTON Series .250 Straight Receptacle Terminals

114-2152 AMPLIVAR Flag FASTON Series 187 & 250 Receptacle Terminal

114-2080 AMPLIVAR Pin Receptacle Terminals [Type A]

114-2128 AMPLIVAR Stator Receptacle with FASTON Mating End

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

AMPLIVAR Terminals (Continued)

Ring Tongue Terminals

A



B



C



D



E



F



G



Wire Size Range 29–22 AWG [0.287–0.643 mm]

Type	Insulation Dia. Range	Hole Dia.	Stud Size	Stock Thk.	Material	Dimensions W	L	E	C	Part Number
B	**.040-.060** 1.02-1.52	**.197** 5	10	**.020** 0.51	Tin Plated Brass	**.342** 8.69	**.833** 21.16	**.662** 16.81	**.312** 7.92	63399-1

Wire Size Range 23–19 AWG [0.574–0.912 mm]

Type	Insulation Dia. Range	Hole Dia.	Stud Size	Stock Thk.	Material	Dimensions W	L	E	C	Part Number
B	**.100-.140** 2.54-3.56	**.171** 4.34	8	**.020** 0.51	Tin Plated Brass	**.342** 8.69	**.833** 21.16	**.662** 16.81	**.312** 7.92	60321-2
A	**.125-.165** 3.18-4.19	**.171** 4.34	8	**.020** 0.51	Tin Plated Brass	**.300** 7.62	**.700** 17.78	**.550** 13.97	**.230** 5.84	60323-2
B	**.100-.140** 2.54-3.56	**.197** 5	10	**.020** 0.51	Tin Plated Brass	**.342** 8.69	**.833** 21.16	**.662** 16.81	**.312** 7.92	60319-2
A	**.125-.165** 3.18-4.19	**.197** 5	10	**.020** 0.51	Tin Plated Brass	**.300** 7.62	**.695** 17.65	**.545** 13.84	**.230** 5.84	60325-2

Wire Size Range 22–18 AWG [0.643–1.024 mm]

Type	Insulation Dia. Range	Hole Dia.	Stud Size	Stock Thk.	Material	Dimensions W	L	E	C	Part Number
B	**.125-.165** 3.18-4.19	**.265** 6.73	1/4	**.025** 0.64	Tin Plated Brass	**.420** 10.67	**.872** 22.15	**.662** 16.81	**.312** 7.92	63612-1
E	—	**.145** 3.58	6	**.025** 0.64	Tin Plated Brass	**.290** 7.37	**.500** 12.7	**.355** 9.02	**.195** 4.95	63649-1
C	—	**.265** 6.73	1/4	**.025** 0.64	Tin Plated Brass	**.420** 10.67	**.702** 17.83	**.492** 12.5	**.312** 7.92	62835-1
E	—	**.171** 4.34	8	**.025** 0.64	Brass Tin Plated Brass	**.290** 7.37	**.500** 12.7	**.355** 9.02	**.195** 4.95	63446-1 63446-2

Wire Size Range 20–16 AWG [0.813–1.29 mm]

Type	Insulation Dia. Range	Hole Dia.	Stud Size	Stock Thk.	Material	Dimensions W	L	E	C	Part Number
A	**.125-.165** 3.18-4.19	**.171** 4.34	8	**.020** 0.51	Tin Plated Brass	**.300** 7.62	**.695** 17.65	**.545** 13.84	**.230** 5.84	60322-2
H	—	—	8	**.020** 0.51	Brass	**.340** 8.64	**1.220** 30.98	**.660** 16.76	**.500** 12.7	505071-1
L	—	—	3/8	**.020** 0.51	Brass	**.625** 15.88	**.939** 23.85	**.627** 15.93	**.467** 11.86	505075-1
M	—	—	3/8	**.020** 0.51	Brass	**.645** 16.38	**.950** 24.12	**.627** 15.93	**.467** 11.86	505072-1

Wire Size Range 18–14 AWG [1.024–1.628 mm]

Type	Insulation Dia. Range	Hole Dia.	Stud Size	Stock Thk.	Material	Dimensions W	L	E	C	Part Number
B	**.100-.140** 2.54-3.56	**.171** 4.34	8	**.020** 0.51	Brass	**.342** 8.69	**.833** 21.16	**.662** 16.81	**.312** 7.92	60320-1
	.100-.140 2.54-3.56	**.171** 4.34	8	**.020** 0.51	Tin Plated Brass	**.342** 8.69	**.833** 21.16	**.662** 16.81	**.312** 7.92	60320-2
	.100-.140 2.54-3.56	**.197** 5	10	**.020** 0.51	Brass	**.342** 8.69	**.833** 21.16	**.662** 16.81	**.312** 7.92	60318-1
D	**.080-.120** 2.03-3.05	**.173** 4.39	8	**.028** 0.71	Lu-Bronze[1]	**.370** 9.4	**.915** 23.24	**.730** 18.54	**.380** 9.65	485079-1
	.080-.120 2.03-3.05	**.185** 4.7	8	**.028** 0.71	Lu-Bronze[1]	**.365** 9.27	**.882** 22.4	**.700** 17.78	**.380** 9.65	485044-1

[1]High conductivity copper-tin-zinc alloy.

Wire Range 17–13.5 AWG [1.151–1.78 mm]

Type	Insulation Dia. Range	Hole Dia.	Stud Size	Stock Thk.	Material	Dimensions W	L	E	C	Part Number
F	—	—	8	**.020** 0.51	Brass	**.310** 7.87	**.692** 17.58	**.505** 12.83	**.312** 7.92	63147-1
	—	—	8	**.020** 0.51	Tin Plated Brass	**.310** 7.87	**.692** 17.58	**.505** 12.83	**.312** 7.92	63147-2*

*Available on request

Wire Size Range 14–12 AWG [1.628–2.05 mm] or (2) 15 AWG [1.45 mm]

Type	Insulation Dia. Range	Hole Dia.	Stud Size	Stock Thk.	Material	Dimensions W	L	E	C	Part Number
G	—	—	8	**.025** 0.64	Brass	**.342** 8.69	**.945** 24.00	**.750** 19.05	**.570** 14.48	62755-1

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

AMPLIVAR Terminals (Continued)

Stud Retaining Terminals

H



Wire Size Range 13–11 AWG [1.83–2.3 mm]

Type	Insulation Dia. Range	Hole Dia.	Stud Size	Stock Thk.	Material	Dimensions W	Dimensions L	Dimensions E	Dimensions C	Part Number
A	**.085-.150** 2.16-3.81	**.180** 4.57	8	**.025** 0.64	Brass	**.342** 8.69	**.833** 21.16	**.662** 16.81	**.312** 7.92	61710-1
C	—	**.180** 4.57	8	**.025** 0.64	Tin Plated Brass	**.342** 8.69	**.665** 16.89	**.495** 12.57	**.312** 7.92	350571-1
	—	**.197** 5.00	10	**.025** 0.64	Tin Plated Brass	**.342** 8.69	**.665** 16.89	**.495** 12.57	**.312** 7.92	640212-1

J



Wire Range (1) 18 AWG [1.024 mm] and (1) 20.5 AWG [0.768 mm]

Type	Insulation Dia. Range	Hole Dia.	Stud Size	Stock Thk.	Material	Dimensions W	Dimensions L	Dimensions E	Dimensions C	Part Number
J	—	—	8	**.020** 0.51	Brass	**.340** 8.64	**.955** 24.26	**.660** 16.76	**.500** 12.7	505044-1

K



Wire Range (2) 17 AWG [1.51 mm] or (2) 15 AWG [1.45 mm]

Type	Insulation Dia. Range	Hole Dia.	Stud Size	Stock Thk.	Material	Dimensions W	Dimensions L	Dimensions E	Dimensions C	Part Number
B	**.150-.190 or (2) .115** 3.18-4.83 or (2) 2.92	**.171** 4.34	8	**.025** 0.64	Tin Plated Brass	**.342** 8.69	**.827** 21.01	**.656** 16.66	**.312** 7.92	60752-2
	.150-.190 or (2) .115 3.18-4.83 or (2) 2.92	**.197** 5.00	10	**.025** 0.64	Tin Plated Brass	**.342** 8.69	**.827** 21.01	**.656** 16.66	**.312** 7.92	61151-1

L



Wire Range 16–13.5 AWG [1.29–1.78 mm]

Type	Insulation Dia. Range	Hole Dia.	Stud Size	Stock Thk.	Material	Dimensions W	Dimensions L	Dimensions E	Dimensions C	Part Number
K	—	—	10	**.020** 0.51	Brass	**.340** 8.64	**1.220** 30.99	**.660** 16.76	**.500** 12.7	505079-1

M



Wire Range 14.5 AWG [1.539 mm]

Type	Insulation Dia. Range	Hole Dia.	Stud Size	Stock Thk.	Material	Dimensions W	Dimensions L	Dimensions E	Dimensions C	Part Number
N	—	—	2	**.025** 0.64	Tin Plated Brass	**.240** 6.1	**.620** 15.75	**.500** 12.7	**.165** 4.19	505036-1
	—	—	2	**.025** 0.64	Brass	**.240** 6.1	**.620** 15.75	**.500** 12.7	**.165** 4.19	505036-3

Alternator Eyelet Terminal

N



Wire Range (2) 13 AWG [1.83 mm]

Type	Insulation Dia. Range	Hole Dia.	Stud Size	Stock Thk.	Material	Dimensions W	Dimensions L	Dimensions E	Dimensions C	Part Number
B	**.150-.190** 3.81-4.83	**.171** 4.34	8	**.025** 0.64	Tin Plated Brass	**.342** 8.69	**.827** 21.00	**.656** 16.66	**.312** 7.92	63864-1

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

AMPLIVAR Terminals (Continued)

125 Series Blade

Stock Thickness

A = .013 [0.33]
B = .020 [0.51]

Mates with Power Blade Receptacle terminals 61603-1, 61604-1, 770642-1 and 1217039-1

Housings

Contact Tyco Electronics Engineering for housing options available

A



B



Type	Magnet Wire Range				Material	Material Thickness	Part Number
	AWG	mm²	Solid Dia.	CMA			
A	27-20.5	0.10-0.45	**.015-.030** 0.35-0.75	200-850	Tin Plated Brass	**.013** 0.33	63871-1
	24-18	0.2-0.8	**.020-.040** 0.50-1.00	400-1600	Tin Plated Brass	**.013** 0.33	63889-1
	18.5-13.5	0.75-2.5	**.040-.070** 0.50-1.80	1500-5000	Tin Plated Brass	**.016** 0.41	63870
B	27-20.5	0.10-0.45	**.015-.030** 0.35-0.75	200-850	Tin Plated Brass	**.013** 0.33	1217072-1
	24-18	0.2-0.8	**.020-.040** 0.50-1.00	400-1600	Tin Plated Brass	**.020** 0.51	1217029-1
	18.5-13.5	0.75-2.5	**.040-.070** 0.50-1.80	1500-5000	Tin Plated Brass	**.020** 0.51	1217073-1

187 Series FASTON Tabs[1]

Board Thickness

A = .062–.072 [1.57–1.83]

Stock Thickness

A = .020 [0.51]
B = .032 [0.81]

A



B



Type	Wire Range		Material	Dim. L	Part Number
	AWG	mm²			
B	27-23	0.1-0.2	Tin Plated Brass	**.935** 23.75	63484-1[2]
A	24-21	0.2-0.4	Tin Plated Brass	**.935** 23.75	61440-3†
	22-16	0.3-1.4	Tin Plated Brass	**1.015** 25.78	62447-1
	15-13	1.6-2.6	Tin Plated Brass	**.935** 23.75	61442-3†
	15-12	1.6-3.0	Tin Plated Brass	**1.015** 25.78	62445-1

[2] Varnish resist coating.
† These part numbers are available upon special request, contact Tyco Electronics Engineering for details.

250 Series FASTON Tabs[1]

Stock Thickness

.032 [0.81]



Wire Range		Material	Part Number	Quick-Change Applicator[3]
AWG	mm²			
14-12	2.0-3.0	Tin Plated Brass	62922-1[2]	466510-1

[2] Varnish resist coating.
[3] Quick-Change Applicator for AMP-O-LECTRIC Machine 565435-5. For AMPOMATOR Machine and other machines not listed, contact Tyco Electronics.

[1]Mates with FASTON receptacles. See AMP Catalog 82004.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.
Dimensions are shown for reference purposes only. Specifications subject to change.
www.te.com/appliances

AMPLIVAR Terminals (Continued)

250 Series FASTON Tabs[1]
(Continued)

Stock Thickness
.032 [0.81]

Mates with FASTON receptacles.
See AMP Catalog 82004.



Wire Range AWG	Wire Range mm²	Material	Dimensions W	Dimensions L	Dimensions E	Dimensions T	Part Number
28-23.5	0.08-0.2	Tin Plated Brass	**.250** 6.35	**.580** 14.73	**.342** 8.69	45°	63136-1
25-19.5	0.16-0.6	Tin Plated Brass	**.250** 6.35	**.650** 16.51	**.450** 11.43	30°	63140-1
23-19	0.2-0.6	Tin Plated Brass	**.250** 6.35	**.225** 5.72	**.583** 14.81	15°	63165-1

250 Series FASTON Receptacles[1]

Stock Thickness
.016 [0.41]

Mates with FASTON tabs.
See AMP Catalog 82004.



Magnet Wire Range CMA	Magnet Wire Range mm² Dia.	Insulation Diameter	Mating Tab Thk.	Material	Material Thickness	Part Number	Applicator No.
24-19	0.51-0.98	**.050-.080** 1.30-2.00	**.020** 0.51	Brass / Tin Plated Brass	**.016** 0.41	63623-1[1] / 63623-2[1]	567451-2[2]
23-19 or (2) 24 or (2) 26	0.60-0.98 or (2) 0.57 or (2) 0.45	**.050-.100** 1.30-2.55	**.025** 0.64	Brass	**.016** 0.41	62069-1	567343-2[2]
20-16 or (2) 23 or (2) 20	0.85-1.37 or (2) 0.63 or (2) 0.88	**.100-.140 or (2) .060 Max.** 2.55-3.55	**.032** [0.81]	Brass / Tin Plated Brass	**.016** 0.41	60384-1 / 60384-2	466010-1[2]
20-16	0.85-1.37	**.100-.140** 2.55-3.55	**.020** 0.51	Brass	**.016** 0.41	62080-1	466010-1[2]
18-14 or (2) 17	1.02-1.71	**.120-.170 or (2) .060 Max.** 3.05-4.30	.032 [0.81]	Tin Plated Brass	**.016** 0.41	60385-2	466816-1[2]
18-14 or (2) 19	1.02-1.71	**.120-.170** 3.05-4.30	**.020** 0.51	Brass	**.016** 0.41	63622-1[1]	466816-1[2]
18-14 or (2) 19	1.02-1.71	**.120-.170** 3.05-4.30	**.020** 0.51	Brass	**.016** 0.41	1217835-1[1]	466816-1[2]

[1] Low insertion force
[2] Quick-Change Applicator for AMP-O-LECTRIC Machine 565435-5.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

AMPLIVAR Terminals (Continued)

187 Series FASTON Flag Receptacles

Stock Thickness

.016 [0.41]



Magnet Wire Range		Insulation Diameter	Mating Tab Thk.	Material	Material Thickness	Part Number	Applicator No.
CMA	mm² Dia.						
500-960	0.56-0.79	**.020-.040** 0.51-1.02	**.020** 0.51	Tin Plated Brass	**.016** 0.41	63942-1	566411-1[1]
24-20 AWG	0.51-0.81	**.020-.040** 0.51-1.02	**.032** 0.81	Tin Plated Brass	**.016** 0.41	1217624-1	566411-1[1]
1500-2350	0.99-1.22	**.020-.040** 0.51-1.02	**.020** 0.51	Tin Plated Brass	**.016** 0.41	63941-1	566410-1[1]
2000-4050	1.14-1.63	**.020-.040** 0.51-1.02	**.020** 0.51	Tin Plated Brass	**.016** 0.41	63940-1	680353-3[2]
2000-4050	1.14-1.63	**.020-.040** 0.51-1.02	**.032** 0.81	Tin Plated Brass	**.016** 0.41	1217417-1	680353-3[2]

[1] Standard Applicator for "G" Splice Terminator No. 356462-2.
[2] Quick-Change Applicator for "G" Splice Terminator No. 356462-1.

250 Series FASTON Flag Receptacles

Stock Thickness

.018 [0.45]



Magnet Wire Range		Insulation Diameter	Mating Tab Thk.	Material	Material Thickness	Part Number	Applicator No.
CMA	mm² Dia.						
16-12	1.29-2.13	**.120-.170** 3.05-4.32	**.032** 0.81	Tin Plated Phos Bronze	**.018** 0.45	63944-1	680421-3[1]

[1] Quick-Change Applicator for "G" Splice Terminator No. 356462-1.

Pin Receptacles

Stock Thickness

.016 [0.41]

A



B



Type	Wire Range		Insulation Dia. Range	Material	Dimensions			Part Number
	AWG	mm²			W Max.	L	C	
A	29-22	0.07-0.3	**.040-.060** 1.02-1.52	Tin Plated Brass	**.084** 2.13	**.590** 14.99	**.195** 4.95	63506-1
B	21-16	0.4-1.4	—	Tin Plated Phos. Bronze	**.235** 5.97	**.660** 16.76	**.250** 6.35	60177-2

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

AMPLIVAR Terminals (Continued)

250 Series Stator Receptacles — 7 Serrations





Magnet Wire Range				Mating Tab Thickness	Stock Thickness	Crimp Width	Material	Part Number
AWG	mm²	Solid Dia.	CMA					
27-22	0.10-0.3	**.014-.026** 0.35-0.66	200-700	**.032** 0.81	**.018** 0.44	**.070** 1.77	Tin Plated Brass	63480-1
21-15	0.4-1.6	**.028-.060** 0.71-1.52	800-3600	**.032** 0.81	**.018** 0.44	**.110** 2.79	Tin Plated Brass	62381-1
22-15.5	0.3-1.5	**.053-.086** 1.35-2.18	2800-7400	**.032** 0.81	**.018** 0.44	**.155** 3.94	Tin Plated Brass	63964-1

Stator Terminal — Receptacle .250 x .032 [6.35 x 0.81]

① **Stator Terminal** with Receptacle .250 x .032 [6.35 x 0.81]

② **Plastic Cavity**

Production only according to Tyco Electronics Specifications (Contact Tyco Electronics Engineering for details).

For design and material selection Tyco Electronics Engineering **has to be** contacted before decision.

The terminal is separated from the strip and placed automatically into the cavity.



③ **Wire Clamping Barrel**

The magnet wire is positioned via posts into the AMPLIVAR crimp barrel and fixed inside clamping barrel.

④ **AMPLIVAR Crimp**

The AMP application equipment crimps the AMPLIVAR connection and cuts the extending clamping barrel in one operation.



Additional versions upon request.

Application Tooling for Production Line Integrating available upon request.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

Cluster Blocks

Product Facts

- Connects to sealed hermetic headers
- Versions available to accept 2.29 [.090] and 3.18 [.125] header pins
- Accepts Lead wire range 18–16 AWG [0.8–1.4 mm^2] and 14–12 AWG [2.0–3.0 mm^2]
- AMPLIVAR versions accept up to 3 copper or aluminum magnet wires without the need to remove insulation
- Impervious to many oils and refrigerants
- Insulation compatibility
- Housings available to accept standard and reversed header pin layouts
- Housing versions available for compressor interior and exterior
- High-performance electrical and mechanical contact
- High-impact resistant
- Assemblies accept pins from one side only to prevent reversed polarity
- High-speed application of pin receptacle terminals with AMP automatic terminating machines and quick-change applicators for high volume production rates at the lowest installed cost
- Recognized under the Component Program of Underwriters Laboratories Inc., File No. E28476



TE features AMP cluster blocks that offer manufacturers of air conditioning and refrigeration products a low-cost, fully insulated, quick-connect means for electrically connecting sealed hermetic header pins on compressors.

Cluster blocks feature high impact resistance to shock and abuse, and long-life performance in the presence of oils and refrigerants. Since the connectors accept pins from only one side, the danger of reversing polarity at the time of installation is prevented.

The one-piece housings are molded from thermoplastic polyester. The connector accepts 2.29 [.090] and 3.18 [.125] diameter pin sizes in either standard or reverse pin layouts.

Housings accept both lead wire and AMPLIVAR direct connect pin receptacle terminals. These are precision formed and available on reels for highspeed application.

High retention pin receptacle terminals are available to provide optimum terminal retention housings.





Typical Assembly

PRODUCT SPECIFICATIONS:
108-2008,108-5205 &108-5541

APPLICATION SPECIFICATIONS:
114-2019 & 114-5235

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

Cluster Blocks 2.29 [.090] Pin Size (Lead Wire and Direct Connect)

Housings



Pin Location
A



Pin Location
B, C and D



Pin Location
E



C



A



D



B

E

Type	Header Pin Circle Dia.	Dim L	Dim W	Dim H	Dim K	Material / Use[1]	Accepts Receptacle Style	Part Number	Notes
	mm / inch	mm / inch	mm / inch	mm / inch	mm / inch				
A 2 Position with Standoff	13.46 [.530]	22.45 [.884]	21.08 [.830]	14.23 [.560]	N/A	PBT Interior	A, B & C	1969357-1	
B 3 Position Center Forward	13.46 [.530]	31.50 [1.240]	18.05 [.710]	8.15 [.320]	21.35 [.840]	PBT Interior	A, B & C	360050-1	
		31.00 [1.220]	17.65 [.695]	6.60 [.260]	20.85 [.820]	PBT Interior	A, B & C	521078-1	
		30.48 [1.200]	17.65 [.695]	7.87 [.310]	20.40 [.803]	PBT Exterior	A, B & C	1380145-1	2
		30.48 [1.200]	17.65 [.695]	7.87 [.310]	20.40 [.803]	PBT Exterior	A, B & C	1380145-2	3
		30.48 [1.200]	17.65 [.695]	9.70 [.382]	20.40 [.803]	PBT Exterior	A, B & C	2232327-1	3
		30.48 [1.200]	17.65 [.695]	9.70 [.382]	20.40 [.803]	PA6+GF Exterior	A, B & C	2232327-2	4
C 3 Position Center Back	13.46 [.530]	30.48 [1.200]	17.65 [.695]	9.70 [.382]	20.40 [.803]	PBT Exterior	A, B & C	2232326-1	3
		30.48 [1.200]	17.65 [.695]	9.70 [.382]	20.40 [.803]	PA6+GF Exterior	A, B & C	2232326-2	4
		30.80 [1.21]	17.80 [.701]	7.40 [.0291]	20.40 [.803]	PBT Exterior	A, B & C	235280-1	
		31.10 [1.225]	20.55 [.810]	8.15 [.320]	21.35 [.840]	PBT Interior	A, B & C	360033-1	
		30.50 [1.200]	17.65 [.695]	7.85 [.310]	20.40 [.805]	PBT Interior	A, B & C	281006-4	
		30.50 [1.200]	17.70 [.697]	7.90 [.311]	20.40 [.805]	PBT Exterior	A, B & C	880631-5	2
		30.50 [1.200]	17.70 [.697]	7.80 [.307]	20.40 [.805]	PA6+GF Exterior	A, B & C	1955415-1	4
D 3 Position Center Back Extra Wide	13.46 [13.46]	31.60 [1.244]	22.70 [.893]	9.30 [.366]	21.50 [.846]	PBT Filled Interior	D & E	171370-3	
		31.60 [1.244]	22.70 [.893]	9.30 [.366]	21.50 [.846]	PBT Filled Exterior	D & E	171370-5	3
E 4 Position	17.35 [.683]	37.85 [1.490]	22.85 [.900]	9.00 [.355]	21.45 [.845]	PBT Interior	A, B & C	1217262-1	

Notes: 1.Interior use designates that the material can be subjected to refrigerants and lubricants often found in a compressor. Consult TE Connectivity Product specification for additional information.
2.Flammability rating UL94 V-2
3.Flammability rating UL94 V-0
4.Flammability rating UL94 V-0. Glow Wire compliant to 750°C with No Flame per IEC 60335-1.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

Cluster Blocks 2.29 [.090] Pin Size (Lead Wire and Direct Connect)

Pin Receptacles



Lead Wire
Standard Retention

A



Lead Wire
High Retention

B



Lead Wire
Standard Retention

C



Lead Wire
Standard Retention

D



Lead Wire
Standard Retention

E

Type	Lead Wire Size	Magnet Wire Size	Crimp Width	Insulation Dia	Crimp Width	Material	Part Number	Notes
	mm² / AWG	mm² / CMA	mm / inch	mm / inch	mm / inch			
A Lead Wire Standard Retention	0.30 - .75 [22 - 18]		2.03 0.080	1.30 - 2.40 .051 - .095	3.05 0.120	Tin Plated Phos Bronze[1]	1599105-1	
	0.80 - 1.3 [18 - 16]		2.79 0.110	1.50 - 2.50 .060 - .100	3.56 0.140	Tin Plated Phos Bronze[1]	62131-3	
			2.79 0.110	2.30 - 4.30 .090 - .170	4.57 0.180	Tin Plated Phos Bronze[1]	63448-1	
B Lead Wire High Retention	0.30 - 2.08 [22 - 14]		2.54 0.100	2.00 - 3.80 .080 - .150	3.30 0.130	Tin Plated Phos Bronze[1]	1217264-1	
C Amplivar Direct Connect High Retention		0.26-0.77 [400 - 1600]	2.270 0.090	1.50 - 2.55 0.06 - .100	3.560 0.140	Tin Plated Phos Bronze[1]	1742981-1	
		0.77 - 2.43 [1600 - 4800]	2.79 0.110	1.90 - 3.20 .075 - .125	3.94 0.155	Tin Plated Phos Bronze[1]	1742964-1	3
D Lead Wire Oval Contact	0.50 - 1.25 [20 - 16]		2,29 0.090	2.00 - 3.40 .080 - .134	3.81 0.150	Tin Plated Phos Bronze[1]	170063-2	2
E Amplivar Short Barrel Oval Contact		0.11 - 0.73 [225 - 1445]	1.78 0.070	0.90 - 2.00 .035 - .079	3.3 0.130	Tin Plated Phos Bronze[1]	1123655-1	2, 4
		0.77 - 2.13 [1600 - 4200]	2.79 0.110	2.00 - 2.90 .080 - .114	3.81 0.150	Tin Plated Phos Bronze[1]	353937-1	2, 4

Notes: 1.May contain an equivalent Copper Alloy.
2.Requires Extra Wide type D housing.
3.Connects up to 3 Copper or Aluminum Magnet wires without stripping insulation.
4.Connects up to 2 Copper Magnets without stripping insulation.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

www.te.com/appliances

Cluster Blocks 3.18 [.125] Pin Size (Lead Wire and Direct Connect)

Housings



Pin Location
A and B



Pin Location
C and D



Pin Location
E



A



B



C



D



E

Type	Header Pin Circle Dia.	Dim L	Dim W	Dim H	Dim K	Material / Use'	Accepts Receptacle Style	Part Number
	mm / inch	mm / inch	mm / inch	mm / inch	mm / inch			
A 3 Position Center Forward	13.46 [.530]	44.60 [1.755]	19.45 [0.765]	11.95 [0.470]	31.17 [1.227]	PBT Interior	A, B, C & D	360052-1
		44.60 [1.755]	19.45 [0.765]	13.35 [.525]	31.17 [1.227]	PBT Interior	A, B, C & D	1217181-1
B 3 Position Center Back	13.46 [.530]	44.60 [1.755]	19.45 [0.765]	11.95 [0.470]	31.10 [1.225]	PBT Interior	A, B, C & D	360051-1
		47.25 [1.860]	19.45 [.765]	13.35 [.525]	31.10 [1.225]	PBT Interior	A, B, C & D	1217200-1
C 3 Position Center Forward	17.45 [.687]	40.50 [1.595]	22.75 [.895]	9.65 [.380]	27.45 [1.080]	PBT Interior	A, B, C & D	520995-1
		43.95 [1.730]	22.75 [.895]	15.60 [.615]	27.45 [1.080]	PBT Interior	A, B, C & D	1217186-1
D 3 Position Center Back	17.45 [.687]	47.00 [1.850]	22.75 [.895]	15.60 [.615]	31.10 [1.225]	PBT Interior	A, B, C & D	1217187-1
E 3 Position Center Forward	20.70 [.815]	50.15 [1.975]	25.80 [1.015]	15.00 [.590]	26.65 1.05	PBT Interior	A, B, C & D	1217261-1

Notes: 1.Interior use designates that the material can be subjected to refrigerants and lubricants often found in a compressor. Consult TE Connectivity Product specification for additional information.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

www.te.com/appliances

Cluster Blocks 3.18 [.125] Pin Size (Lead Wire and Direct Connect) (Continued)

Pin Receptacles



A
Lead Wire



B
Lead Wire



C
AMPLIVAR Direct Connect



D
AMPLIVAR Direct Connect

Type	Lead Wire Size	Magnet Wire Size	Crimp Width	Insulation Dia	Crimp Width	Material	Part Number	Notes
	mm² / AWG	mm² / CMA	mm / inch	mm / inch	mm / inch			
A Lead Wire Standard Retention	0.75 - 1.5 [18 - 16]		2.79 0.110	2.30 - 3.30 .090 - .130	3.94 0.155	Tin Plated Phos Bronze[1]	62244-3	2
	2.0 - 6.0 14 - 10		3.56 0.140	3.30 - 4.30 .130 - .170	4.57 0.180	Tin Plated Phos Bronze[1]	62243-3	2
B Lead Wire High Retention	0.32-0.82 or 2x0.32 [22-18 or 2x22]		2.29 0.090	2.79 or 2x2.29 Max .110 or 2x.090 Max	3.56 0.140	Tin Plated Phos Bronze[1]	1742657-1	2
	0.75 - 1.5 [18 - 16]		2.79 0.110	2.30 - 3.30 .090 - .130	3.94 0.155	Tin Plated Phos Bronze[1]	1217176-1	2
	2.0 - 6.0 [14 - 10]		3.56 0.140	3.30 - 4.30 .130 - .170	4.57 0.180	Tin Plated Phos Bronze[1]	1217175-1	2
C Amplivar Direct Connect Standard Retention		0.20 - 0.81 400 - 1600	2.27 0.090	1.50 - 2.55 .060 - .100	3.56 0.140	Tin Plated Phos Bronze[1]	63453-1	2, 4
		0.76 - 2.13 1500 - 4200	2.79 0.110	1.90 - 3.20 .075 - .125	3.94 0.155	Tin Plated Phos Bronze[1]	63454-1	2, 4
		2.00 - 4.30 4000 - 8500	3.56 0.140	2.30 - 4.30 .090 - .170	4.32 0.170	Tin Plated Phos Bronze[1]	63455-1	2, 4
D Amplivar Direct Connect High Retention		0.20 - 0.81 400 - 1600	2.27 0.090	1.50 - 2.55 .060 - .100	3.56 0.140	Tin Plated Phos Bronze[1]	1217172-1	2, 4
		0.76 - 2.13 1500 - 4200	2.79 0.110	1.90 - 3.20 .075 - .125	3.94 0.155	Tin Plated Phos Bronze[1]	1217174-1	2, 4
		2.00 - 4.30 4000 - 8500	3.56 0.140	2.30 - 4.30 .090 - .170	4.32 0.170	Tin Plated Phos Bronze[1]	1217173-1	2, 4

Notes: 1.Material shown is for reference only. May contain an equivalent Copper Alloy.
2.Receptacle must be contained in a housing listed on the previous page for proper performance.
3.Stand-alone receptacle can be used with or without a housing.
4.Connects up to 3 Copper or Aluminum Magnet wires without removing the insulation.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

www.te.com/appliances

AMPLIVAR and Cluster Blocks Application Tooling

AMPLIVAR Product Terminator (APT)

Product Facts

- **No need to strip magnet wire**
- **Connects up to 3 wires in 1 splice**
- **Crimp Quality Monitor (CQM) system measures crimp heights**
- **Machine shut height easily adjusts in .0005 [0.013] increments**
- **Quick-change tooling without major shut-height adjustments**

Specifications

Weight — Approximately 150 lb [68 kg] with CQM

Width — 38 [965] with CQM and product reel

Depth — 35 [889]

Height — 14 [356]

Electrical — 120 VAC, 60 Hz, 1 A, 1f, or 240 VAC, 50 Hz, .5 A, 1f

Air — 80-100 psi [5.52-7.59 bar], 22 scfm [0.000141 m3/s]



APT III A

For pigtail splices or direct connection of contacts to magnet wire, the AMPLIVAR Product Terminator (APT) and strip-form AMPLIVAR products offer a fast and efficient system, with no need to strip mag-wire insulation. To apply a splice or contact, simply place the wires in the target area and depress the foot switch. The machine automatically shears the splice or contact from the strip, crimps it, shears off excess wire, and advances the next splice or contact into position.

APT semi-automatic bench machines are available in two versions: the IIIA with automatic precision adjustment controlled by the Crimp Quality Monitor (CQM), and the IIE with manual precision adjustment.

With CQM, the APT IIIA assists in achieving 6-sigma processing capability. In addition to providing 100% inspection and automatic adjustment of crimp heights as needed, the CQM also evaluates the quality of each crimp. If a questionable crimp is detected, visual and audible alarms alert the operator.

For operations with multiple wire sizes, the APT IIIA provides programmable sequencing of different crimp-height settings, and it can store up to 2,000 different programs of 7 different settings each. The maximum time to auto-adjust between programmed crimp is 2 seconds.

The lower cost, manual adjust IIE is a simpler version without CQM capability, with the advantage of faster set-up times.

To avoid the need to change product reels when wire combinations are smaller than the CMA range of the splice or contact, an optional stuffer (part no. 679323-1 for APT IIIA, part no. 679323-2 for APT IIE.) inserts a stuffer wire into the splice or contact prior to crimping, increasing the total CMA to the recommended range. The wire stuffer unit is for pigtail splices only.

APT III A with vertical base (679984-1) for direct connect terminals



APT II E

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

AMPLIVAR and Cluster Blocks Application Tooling (Continued)

AMPLIVAR Product Terminator (APT) (Continued)

Machine Ordering Information

A "Base Part Number" is selected from the Basic Machine Part Numbers table. Then, a dash number or numbers are selected from one of the other two tables depending on the type of product to be applied.

Note: The wire stuffer is available for Pigtail-Type Splice only and may be added to the machine after installation.

679323-1 — APT IIIA

679323-2 — APT IIE



Extraction Tool Part No. 274186-1

Basic Machine Part Numbers

Machine Features				Base Part Number*	
Precision Adjust	Crimp Quality Monitor	Programmable Crimp-Height Sequencing	Model	Pigtail-type Splice	Direct Connect Contact
Manual	Not included	Not included	APT IIE**	□-1338906-□	□-1338907-□
Automatic	Included	Included	APT IIIA	□-679453-□	□-679457-□

*See tables below for suffix and prefix dash numbers which indicate product to be applied, product crimp width, and voltage requirement.

**Not upgradable to an APT IIIA

AMPLIVAR Pigtail-Type Splice Suffix and Prefix Dash Numbers

(Aluminum base 679984-1 not included)

Pigtail-type Splice Base Number	Crimp Width	120/240 VAC IIE Machine □-1338906-□	120/240 VAC IIIA Machine □-679453-□
42775 42776	.110 [2.79]	1-( )-1	3-( )-7
42777 42778	.110 [2.79]	1-( )-2	3-( )-8
42779	.140 [3.56]	( )-8	3-( )-4
62000	.110 [2.79]	1-( )-2	3-( )-8
62001	.140 [3.56]	( )-7	3-( )-3
62001	.180 [4.57]	( )-6	3-( )-2
62201	.140 [3.56]	( )-8	3-( )-4
62002	.180 [4.57]	( )-3	2-( )-9
62040	.110 [2.79]	1-( )-1	3-( )-7
62157 62200	.110 [2.79]	1-( )-2	3-( )-8
62295	.250 [6.35]	( )-1	2-( )-7
62303	.080 [2.03]	1-( )-3	3-( )-9
62304 62305	.110 [2.79]	1-( )-2	3-( )-8
62306	.140 [3.56]	1-( )-0	3-( )-6
62306 62307	.110 [2.79]	1-( )-1	3-( )-7
62308	.140 [3.56]	( )-9	3-( )-5
62308	.180 [4.57]	( )-6	3-( )-2
62309	.220 [5.59]	5-( )-4	5-( )-3
62309	.180 [4.57]	( )-5	3-( )-1
62310	.220 [5.59]	( )-2	2-( )-8
62310	.180 [4.57]	( )-4	3-( )-0
280002	.110 [2.79]	1-( )-1	3-( )-7
280004	.110 [2.79]	1-( )-2	3-( )-8
964156	.110 [2.79]	1-( )-1	3-( )-7

AMPLIVAR Direct Connect Contact Suffix and Prefix Dash Numbers

(Aluminum base 679984-1 included)

Direct Connect Contact Base Number	Crimp Width	120/240 VAC IIE Machine □-1338907-□	120/240 VAC IIIA Machine □-679457-□
63453	.090 [2.286]	( )-3	( )-8
63454	.110 [2.79]	( )-2	( )-7
63455	.140 [3.56]	( )-1	( )-6
63548	.090 [2.286]	( )-5	1-( )-0
63549	.110 [2.79]	( )-4	( )-9
63906	.140 [3.56]	( )-1	( )-6
63907	.110 [2.79]	( )-2	( )-7
63908	.090 [2.286]	( )-3	( )-8
1217122	.160 [4.064]	1-( )-1	1-( )-2
1217172	.090 [2.286]	( )-3	( )-8
1217173	.140 [3.56]	( )-1	( )-6
1217174	.110 [2.79]	( )-2	( )-7
1217670	.090 [2.286]	( )-3	( )-8
1217671	.110 [2.79]	( )-2	( )-7
1217672	.140 [3.56]	( )-1	( )-6

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

www.te.com/appliances

AMPLIVAR and Cluster Blocks Application Tooling (Continued)

AMP-O-LECTRIC Termination Machines

Model "G"

A totally new design of our most popular machine for bench-top operation. It features a quiet and highly-reliable direct motor drive, electronic controls for ease of setup and operation, and improved guarding and lighting for operator convenience and safety. All versions also include either manual or automatic precision adjustment for crimp height. For use with miniature style applicators only.

(Shown with optional Crimp Quality Monitor.)

Specifications

Weight — Approximately 240 lb [110 kg]
Height — 20 [508] without reel
Width — 18.7-25.3 [475-643] depending on type of applicator used
Depth — 21.5-28.1 [546-713] depending on type of applicator used
Electrical — 120 or 220 VAC, 50 or 60 Hz
Air — 90-110 psi [6.21-7.59 bar] when required for use with air-feed applicators

For complete information, request Catalog 65828.



Model "K"

These machines are used with standard style applicators, generally to apply one size and type of terminal without the need for frequent changeovers of applicators or adjustment of crimp height. The basic model is Part Number 1-471273-2. Part Number 1-471273-3 is equipped with a mechanical feed assembly for applicators requiring this type of feed for advancing the terminal strip.

Specifications

Weight — Approximately 230 lb [104 kg]
Height — 24 [610] without reel
Width — 21 [533]
Depth — 20 [508]
Electrical — 120 VAC, 60 Hz, 6 A
Air — 90-110 psi [6.21-7.59 bar] when required for use with air-feed applicators

Crimp Quality Monitor

This unique system provides 100% on-the-fly crimp inspection. It measures the crimp height of each termination, and evaluates the quality of each crimp. If a crimp is questionable, the monitor alerts the operator with both visual and audible alarms. It also provides ports for printing and networking.

When used with AMP-O-LECTRIC Model "G" Termination Machines, the monitor is mounted to the machine. When used with AMPOMATOR CLS IV Lead Making Machines, it is integrated into the machine's operating system, with the information displayed on the machine's touch screen.

Specifications

Height — 4.5 [114]
Width — 8.5 [216]
Depth — 9 [229]
Electrical — 120 VAC, 50 or 60 Hz, or 220 VAC, 50 or 60 Hz
Printer Port — Serial Interface

For further information, request Catalog 82275.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

AMPLIVAR and Cluster Blocks Application Tooling (Continued)

Model G Splice Terminating Machine, P/N 356462-2 & Applicator

Semiautomatic bench machine crimps reeled splice product. Uses Standard G Splice Applicators to provide access to both sides of the splice product. Features a quiet, reliable motor drive, microprocessor controls for ease of setup and operation and guarding and lighting designed for operator convenience. Manual precision crimp height adjust is standard and machine-mounted sensors are available for crimp quality monitoring.

Specifications

AMP-O-LECTRIC Model "G" Thru Splice Terminator

Capacity — 5 000 lb [2 224 N] max. crimp force

Deflection — .003 [0.076] max. per 1 000 lb [445 N] crimp force

Noise — 76 dB max. at 5 000 lb [2 224 N] full capacity

Weight — Approx. 240 lb [109 kg]

Height — 20 [508]

Electrical — 120/220 VAC, 50/60 Hz; Avg. 2.6 A at 120 VAC when used as a bench-top unit at 2 000 cycles per hour operating rate

Air — 90-110 psi [6.21-7.58 bar], 6 scfm [0.00283 m^3/s] (when required for use with air-feed applicators)

For more information, order Catalog 889021.

Standard G Splice Applicator
Available for the AMP-O-LECTRIC Model G splice terminator only.

Two-piece applicator for crimping end- or side-feed reeled splice products. Provides access to both sides of splice for increased ease of use and productivity. Applicators use an air feed mechanism.

Entry Level Terminator (ELT), 1338600-(x)



Semiautomatic Bench Terminator for side- and end-feed reeled terminals and contacts. The ELT uses a DC motor with gear box drive. The result is a small-footprint design that is fast and quiet. Cycle time is less than 0.400 sec. with an operation sound level of 76dBa. With a crimp force capacity of 3,000 pounds, the ELT is available for all but the highest crimp force applications. Optional equipment is also available to meet your specific application requirements.

Specifications

Width—16.8 [427]

Depth—20.6 [523]

Height—20 [510] w/o reel support

Weight—approx. 150 lb [68 kg]

Electrical—100-240 VAC, 50/60 Hz, 6 A *(Note: Avg <1 A at 120 VAC when used as a bench-top unit at 2,000 cycles per hour operating rate)*

Air—90-100 psi [6.21-6.90 bar], 6 scfm [0.00282 m^3/s] when required for use with air-feed applicators *(Note: Optional Air Feed Valve Assembly Required)*

Wire Range—Up to 14 AWG [2.5 mm^2]

For more information, request catalog 1308382.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

www.te.com/appliances

AMPLIVAR and Cluster Blocks Application Tooling (Continued)

Applicators

End- and Side-Feed Heavy-Duty Miniature (HDM) Applicators

AMP applicators are designed to exacting specifications to produce consistent, high-quality terminations.

HDM applicators are quickly interchangeable and easily repaired. They feature simple dial-in settings for adjusting crimp height for terminating different wire combinations within the designated CMA range.

These applicators are used with both bench machines and fully-automatic lead makers. They can also be used for crimp quality monitoring on systems equipped with the CQM G-Adapter. Call the AMP Tooling Assistance Center at 1-800-722-1111 for further information.



Standard (STD) Applicators

Standard style applicators are generally used for long production runs using dedicated equipment, or when splicing a coil, for example, that needs to be positioned close to the crimping area in the applicator. The crimp height can be adjusted by raising or lowering the base mount.



Standard Style Applicator for Large CMA Splice, Part Number 566372-2

This applicator was designed specifically to apply AMP 5 000-16 000 CMA Splice, Part Number 63625-1. It features a highly-visible, close-up crimp area—less than 1 [25] from the front of the guard. You can easily splice multiple wires by simply rotating them down through the front of the guard into the crimp area.

It is an air-feed applicator, and can be used with Model “K” Part Number 1-471273-3.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

www.te.com/appliances

AMPLIVAR and Cluster Blocks Application Tooling (Continued)

AMPOMATOR CLS IV+ Lead-Making Machines, 356500-1, -2

Fully-automatic machines that measure, cut, strip and terminate single leads. Microprocessor-controlled, and programmed and operated using an easy-to-follow, menu-driven touchscreen. Features include direct-drive terminating units with precision crimp height adjustment, fully programmable setups, wire runout and splice detection, and motorized pre-feed with wire straightener. Crimp quality monitoring is also available.

Specifications

Width—159 [4 040]

Depth—68 [1 730]

Height—86 [2 185] with 24 [610] dia. reel

Weight—2 000 lb [907 kg]

Electrical—220 VAC, 50 or 60 Hz, single phase, 25 A, with neutral and ground

Air—90 psi [6.21 bar], 15 scfm [0.0071 m^3/s] sustained

Wire Range—26-10 AWG [0.12-6 mm^2] stranded, 26-16 AWG [0.12-1.4 mm^2] solid

Lead Lengths—3-90 [76.2-2 285], 90-1 000 [2 285-25 400] with long lead conveyors

For more information, request Catalog **124324**.

Gamma 333 PC Lead-Making Machine, Three Stations, 1-528324-1



With its capacity to accommodate an additional processing station on side 1, the Gamma 333 PC can perform a number of new processes. It can produce two-ended crimp leads, process double crimp connections with three different terminals or apply seals on one end of the wire. Tinning and ink jet marking are two further options. Process monitoring is integrated into the system, for accurate trimming and stripping of the wires.

Specifications

Length—125 [3137]

Width—54.2 [1377]

Height—70.5 [1790]

Length Range— 2.36 in-32.8 ft [60-10,000] (optional 30mm)

Cross-Section Range — AWG 26-AWG 10 [0.125mm^2-5mm^2]

Noise Level—<76dB (without crimping modules)

Electrical—3x208 - 480V, 50-60Hz; 6kVA

Compressed Air—5-6 bar

Air Consumption—6.5m^3/h

Weight—1850 lbs [840 kg] with two crimping modules

For more information, request Catalog **1307901**.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

www.te.com/appliances

MTM Crimpband Splices

Product Facts

- Made from a continuous coil of “Ribbon Connector” material
- Magnet wires MTM Crimpband splices have machine-piercing serrations designed for displacing magnet wire insulation.
- Available in brass, tin-plated brass, and copper-nickel alloy material
- Make parallel or pigtail connections on same machine
- 100% of Crimpband material is used in scrap free terminations
- Crimpband material coupled with appropriate toolsets accommodate specific CMA ranges
- Produced in Tyco Electronics equipment on your production floor
- Meets UL 486C crimp tensile requirements

Applications

- Motors windings and connections
- Coil connections
- Transformer windings and connections
- Lighting ballasts
- Power supplies



Tyco Electronics features the AMP MTM Crimpband system that is comprised of two key features: the semi-automatic termination machine and a reel of MTM Crimpband material.

In a one-step crimping operation, the machine feeds, cuts, forms and crimps the material to provide a low-cost, high reliability crimp connection.

The MTM Crimpband splices are formed during the crimping process from machined longitudinal grooved material that pierces magnet wire varnish film insulation during crimping.

MTM Crimpband splices are specifically designed to terminate magnet wire to itself or in combination with standard solid or stranded lead wire.

Three magnet wires maximum can be terminated together with stranded lead wire in one splice.

Tyco Electronics provides a wide range of toolset types and Crimpband splices to meet various production requirements.

Depending on your specific application, MTM Crimpband splices are available in 7, 9, 11 and 13 serration versions for terminations in the 400 to 13,000 CMA range.

When aluminum magnet wire is used, MTM Crimpband splices must be tin plated.





Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

MTM Crimpband Splices (Continued)

MTM Crimpband Interconnection System

How the System Operates

① **Feed (Magnet Wire Connector Material)**
Machine feeds strip until the strip hits the wire stop.

② **Shear (Blank Length)**
The strip is cut by the cutter block former bar insert tooling.

③ **Bend (Crimp Formed)**
The former bar drives the cut strip over the anvil, bending the cut strip into an upside down "U".

④ **Wire (Placement)**
In Pigtail and Parallel (Thru) splices magnet wires must be placed on top of the lead wire.

⑤ **Crimp (Crimp Formed)**
The anvil retracts as the driver takes the formed strip down into the clincher.

Notes: To insure that the proper Crimpband splice is chosen, Tyco Electronics recommends the following:
1. Submit 10 samples of wire combinations and/or components to be crimped with any special requirements to your Tyco Electronics sales representative.
2. Pull-out force and/or millivolt drop tests will be performed to insure that the proper Crimpband material, toolset and crimp heights are recommended.
3. Tooling and testing will be documented on a Material & Tooling Sheet (M & T sheet).
4. Crimpband material quotes, tooling quotes and samples will be submitted to the customer.



Connector Specification Code

Machine Basis	See Figure 1 and/or Legend below				
	B.L. Dim. Tooling Size	W Dim. Connector Width	T Dim. Material Thickness	Finish	Material Code
L	092	6R	20	T	B

Splice No. Example: L 092 6R 20 T B

Legend

Machine Basis		
L	P	G*
Leased	Purchase	General

* Customer has their own Tooling

Tooling Size Code	Blank Length B/L (Nom.)
032	.167
032/036	.228
036	.224
045	.246
051	.267
061	.292
061/076	.324
076	.339
076/092	.361
092	.379
092/125	.413
125	.446
125/160	.485
125/165	.506
165	.546

Note: For B/L above, .546 consult Tyco Electronics for tooling size code.

Connector Width Code		W
4R	5 Serrations	.138
6R	7 Serrations	.154
8R	9 Serrations	.194
10R	11 Serrations	.234

Material Thickness Code	T±.002 Dim.	D Serration Depth
12	.012	.005
14	.014	.005
16	.016	.007
20	.020	.007
25	.025	.007

Material Code	Material/Finish
B	CDA 260 Brass
A	CDA 725 Copper/ Nickel Alloy
TB	Pre-Tin over CDA 260 Brass

Wire Size AWG	UL486C Pull Out Force Requirements Underwriters Laboratory (lbs.)
26	3
24	5
22	8
20	10
18	10
16	15
14	25
12	35
10	40

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

MTM Crimpband Splices (Continued)

11 Serrations



AWG/ mm²	Wire Range Solid Dia.	CMA Range	Stock Thk. (T)	Mat'l Width (W)	Material	Toolset	Part Number	Descriptive X-ref
14½-11½ 1.80-4.00	**.059-.087** 1.50-2.21	3500-7500	**.025** 0.64	**.234** 5.94	Brass	125/165	1601842-1	P125/ 16510R25B
14½-11½ 1.80-4.00	**.059-.087** 1.50-2.21	3500-7500	**.025** 0.64	**.234** 5.94	Tin Plated Brass	125/165	1601705-1	L125/ 16510R25TB
13½-10½ 2.54-4.50	**.071-.097** 1.70-2.46	4500-9500	**.025** 0.64	**.234** 5.94	Brass	165/200	1601847-1	P165/ 20010R25B
13½-10½ 2.54-4.50	**.071-.097** 1.70-2.46	4500-9500	**.025** 0.64	**.234** 5.94	Tin Plated Brass	165/200	1601848-1	P165/ 20010R25TB

9 Serrations



AWG/ mm²	Wire Range Solid Dia.	CMA Range	Stock Thk. (T)	Mat'l Width (W)	Material	Toolset	Part Number	Descriptive X-ref
24-20 0.20-0.50	**.020-.033** 0.51-0.84	400-1100	**.016** 0.41	**.194** 4.93	Tin Plated Brass	032/036	1601794-1†	P032/ 0368R16TB
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.018** 0.46	**.194** 4.93	Tin Plated Brass	061	1601607-1†	L0618R16TB
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.018** 0.46	**.194** 4.93	Brass	061	1601608-1	L0618R20B
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.018** 0.46	**.194** 4.93	Tin Plated Brass	061	1601814-1†	P0618R20TB
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1600-4000	**.016** 0.41	**.194** 4.93	Tin Plated Brass	076	1601824-1	P0768R16TB
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1600-4000	**.020** 0.51	**.194** 4.93	Tin Plated Brass	076	1601857-1	PO768R20TB
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1800-4600	**.020** 0.51	**.194** 4.93	Brass	076/092	1601823-1	P076/ 0928R20B
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1800-4600	**.020** 0.51	**.194** 4.93	Tin Plated Brass	076/092	1601639-1	L076/ 0928R20TB
16-12 1.30-3.46	**.051-.078** 1.29-1.98	2600-6100	**.020** 0.51	**.194** 4.93	Brass	092/125	1601833-1	P092/ 1258R20B
16-12 1.30-3.46	**.051-.078** 1.29-1.98	2600-6100	**.020** 0.51	**.194** 4.93	Tin Plated Brass	092/125	1601677-1	L092/ 1258R20TB
16-12 1.30-3.46	**.051-.078** 1.29-1.98	2600-6100	**.025** 0.64	**.194** 4.93	Brass	092/125	1601678-1†	L092/ 1258R25B
16-12 1.30-3.46	**.051-.078** 1.29-1.98	2600-6100	**.025** 0.64	**.194** 4.93	Tin Plated Brass	092/125	1601835-1†	P092/ 1258R25TB
15½-12 1.54-3.46	**.055-.082** 1.40-2.10	3000-6750	**.016** 0.41	**.194** 4.93	Brass	125	1601717-1†	L1258R16B
15½-12 1.54-3.46	**.055-.082** 1.40-2.10	3000-6750	**.016** 0.41	**.194** 4.93	Tin Plated Brass	125	1601718-1	L1258R16TB
15½-12 1.54-3.46	**.055-.082** 1.40-2.10	3000-6750	**.020** 0.51	**.194** 4.93	Brass	125	1601846-1	P1258R20B
15½-12 1.54-3.46	**.055-.082** 1.40-2.10	3000-6750	**.025** 0.64	**.194** 4.93	Brass	125	1601719-1	L1258R25B
14½-11½ 1.80-4.00	**.059-.087** 1.50-2.21	3500-7500	**.025** 0.64	**.194** 4.93	Brass	125/165	1601706-1	L125/ 1658R25B
14½-11½ 1.80-4.00	**.059-.087** 1.50-2.21	3500-7500	**.025** 0.64	**.194** 4.93	Tin Plated Brass	125/165	1601707-1	L125/ 1658R25TB
14-11 2.00-4.20	**.063-.092** 1.60-2.34	4000-8500	**.025** 0.64	**.194** 4.93	Tin Plated Brass	165	1601750-1†	L1658R25TB
11½-9 4.00-6.50	**.084-.114** 2.13-2.90	7000-13000	**.025** 0.64	**.194** 4.93	Tin Plated Brass	200/202	1601761-1	L200/ 2028R25TB

† These part numbers are available upon special request; contact Tyco Electronics Engineering for details.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

MTM Crimpband Splices (Continued)

7 Serrations



AWG/ mm²	Wire Range Solid Dia.	CMA Range	Stock Thk. (T)	Mat'l Width (W)	Material	Toolset	Part Number	Descriptive X-ref
27½-21 0.09-0.40	**.013-.028** 0.33-0.71	170-800	**.012** 0.30	**.154** 3.91	Brass	032	1601800-1	P0326R12BUF[1]
24-20 0.20-0.50	**.020-.033** 0.51-0.84	400-1100	**.012** 0.30	**.154** 3.91	Brass	032/036	1601539-1	L032/ 0366R12B
24-20 0.20-0.50	**.020-.033** 0.51-0.84	400-1100	**.012** 0.30	**.154** 3.91	Cu Ni	032/036	1601538-1	L032/ 0366R12AUF[1]
24-20 0.20-0.50	**.020-.033** 0.51-0.84	400-1100	**.016** 0.41	**.154** 3.91	Brass	032/036	1601540-1	L032/ 0366R16B
24-20 0.20-0.50	**.020-.033** 0.51-0.84	400-1100	**.016** 0.41	**.154** 3.91	Tin Plated Brass	032/036	1601793-1	P032/ 0366R16TB
22-19 0.38-0.60	**.024-.036** 0.70-0.91	600-1300	**.016** 0.41	**.154** 3.91	Brass	045	1601559-1	L0456R16B
22-19 0.38-0.60	**.024-.036** 0.70-0.91	600-1300	**.020** 0.51	**.154** 3.91	Brass	045	1601560-1†	L0456R20B
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.016** 0.41	**.154** 3.91	Brass	061	1601604-1	L0616R16B
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.016** 0.41	**.154** 3.91	Tin Plated Brass	061	1601606-1	L0616R16TB
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1600-4000	**.016** 0.41	**.154** 3.91	Brass	076	1601644-1	L0766R16B
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1600-4000	**.016** 0.41	**.154** 3.91	Tin Plated Brass	076	1601646-1†	L0766R16TB
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1600-4000	**.020** 0.51	**.154** 3.91	Brass	076	1601647-1†	L0766R20B
17½-13½ 0.95-2.54	**.042-.068** 1.07-1.80	1800-4600	**.016** 0.41	**.154** 3.91	Brass	076/092	1601637-1	L076/ 0926R16BX
16½-13 1.10-2.60	**.047-.072** 1.19-1.83	2200-5200	**.016** 0.41	**.154** 3.91	Tin Plated Brass	092	1601683-1	L0926R16TB
16-12 1.30-3.46	**.051-.078** 1.29-1.98	2600-6100	**.016** 0.41	**.154** 3.91	Tin Plated Brass	092/125	1601675-1	L092/ 1256R16TB
16-12 1.30-3.46	**.051-.078** 1.29-1.98	2600-6100	**.020** 0.51	**.154** 3.91	Brass	092/125	1601832-1	P092/ 1256R20B
15½-12 1.54-3.46	**.055-.082** 1.40-2.10	3000-6750	**.012** 0.30	**.154** 3.91	Brass	125	1601844-1	P1256R12B
15½-12 1.54-3.46	**.055-.082** 1.40-2.10	3000-6750	**.016** 0.41	**.154** 3.91	Brass	125	1601845-1	P1256R16B
15½-12 1.54-3.46	**.055-.082** 1.40-2.10	3000-6750	**.016** 0.41	**.154** 3.91	Tin Plated Brass	125	1601716-1†	L1256R16TB

[1] UF designates Ultra-Fine serrations which are recommended for applications using wire size 28 AWG [0.32 mm] or smaller.
† These part numbers are available upon special request; contact Tyco Electronics Engineering for details.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.
Dimensions are shown for reference purposes only. Specifications subject to change.
www.te.com/appliances

RTM Crimpband Splices

Product Facts

- Made from a continuous coil of "Ribbon Connector" material
- RTM Crimpband have grooved serrations for improved axial retention.
- Available in brass, tin-plated brass and copper-nickel alloy (CA725) material
- Make parallel or pigtail connections on same machine
- Used for electrical and non-electrical connections.
- 100% of RTM Crimpband material is used in scrap free terminations
- Crimpband material coupled with appropriate toolsets accommodate specific CMA ranges
- Produced in Tyco Electronics equipment on your production floor
- Meets UL 486C crimp tensile requirements

Applications

- Stranded and solid wire-to-wire connections
- Light bulb LED assembly
- Switch lead assembly
- Resistor lead assembly
- Printed circuit board lead assembly
- Flex-film lead assembly
- Glass reed switch lead assembly



Mod I Mod III

Tyco Electronics features the AMP RTM Crimpband system that is comprised of two key features: the semi-automatic termination machine and a reel of RTM Crimpband material.

In a one-step crimping operation, the machine feeds, cuts, forms and crimps the material to provide a low-cost, high reliability crimp connection.

The RTM Crimpband splices are formed during the crimping process from milled longitudinal groove material that produce rolled, rounded serrations.

They are designed to terminate pre-stripped stranded and solid wire conductors together as well as wire conductors to switch tabs, resistors, printed circuit board, flex circuit and light bulb LED and glass reed switch assemblies, etc.

The flexibility of the RTM Crimpband system provides opportunity for use in custom applications for either electrical and / or mechanical connections.

Tyco Electronics provides a wide range of toolset types and crimpband splices to meet various production requirements.

Depending on your specific application, RTM Crimpband splices are available in 3, 6, 7, 8, 9, 10 14 and 20 ridge serration versions for terminations in the 170 to 13,000 CMA range.





Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

RTM Crimpband Splices (Continued)

RTM Crimpband Interconnection System

How the System Operates

① **Feed (Ribbon Connector Material)**
Machine feeds strip until the strip hits the wire stop.

② **Shear (Blank Length)**
The strip is cut by the cutter block former bar insert tooling.

③ **Bend (Crimp Formed)**
The former bar drives the cut strip over the anvil, bending the cut strip into an upside down "U".

④ **Wire (Placement)**
Pigtail and Parallel (Thru) splice terminations are made on the same machine.

⑤ **Crimp (Crimp Formed)**
The anvil retracts as the driver takes the formed strip down into the clincher.

Notes: To insure that the proper Crimpband splice is chosen, Tyco Electronics recommends the following:

1. Submit 10 samples of wire combinations and/or components to be crimped with any special requirements to your Tyco Electronics sales representative.
2. Pull-out force and/or millivolt drop tests will be performed to insure that the proper Crimpband material, toolset and crimp heights are recommended.
3. Tooling and testing will be documented on a Material & Tooling Sheet (M & T sheet).
4. Crimpband material quotes, tooling quotes and samples will be submitted to the customer.



Connector Specification Code

Machine Basis	See Figure 1 and/or Legend below			
	B.L. Dim. Tooling Size	W Dim. Connector Width	T Dim. Material Thickness	Material
L	092	F	20	TCRS

Splice No. Example: L 092 F 20 TCRS

Legend

Machine Basis	
L	P
Leased	Purchase

Tooling Size Code	Blank Length B/L (Nom.)
032	.167
032/036	.228
036	.224
045	.246
051	.267
061	.292
061/076	.324
076	.339
076/092	.361
092	.379
092/125	.413
125	.446
125/160	.485
125/165	.506
165	.546

Note: For B/L above, .546 consult factory for tooling size code

Connector Width Code	W Dim.	N No. of Ridges
B	.076	3
C	.138	6
D	.154	7
E	.185	8
F	.216	9
G	.234	10
H	.247	10
L	.086	3
M	.330	14
N	.500	20
P	.114	5

Material Thickness Code	T±.002 Dim.
12	.012
16	.016
18	.018
20	.020
22	.022
24	.024
25	.025

Material Code	Material/Finish
B	CDA 260 Brass
A	CDA 725 Copper/ Nickel Alloy
TB	Pre-Tin over CDA 260 Brass
TCRS	1010 Cold Rolled Steel, Tin Plated
SS	301 or 302 Stainless Steel
ST	Stainless Steel, Tin Plated

Wire Size AWG	UL486C Pull Out Force Requirements Underwriters Laboratory (lbs.)
26	3
24	5
22	8
20	10
18	10
16	15
14	25
12	35
10	40

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

www.te.com/appliances

RTM Crimpband Splices (Continued)

20 Ridges



AWG/ mm²	Wire Range Solid Dia.	CMA Range	Stock Thk. (T)	Mat'l Width (W)	Material	Toolset	Part Number	Descriptive X-ref
11½-9 4.00-6.50	**.084-.114** 2.13-2.90	7000-13000	**.020** 0.51	**.500** 12.70	Tin Plated Brass	200/202	1601771-1	L200/202N20TB

14 Ridges



AWG/ mm²	Wire Range Solid Dia.	CMA Range	Stock Thk. (T)	Mat'l Width (W)	Material	Toolset	Part Number	Descriptive X-ref
22-19 0.38-0.60	**.024-.036** 0.61-0.91	600-1300	**.012** 0.30	**.330** 8.38	Cu Ni	045	1601577-1†	L045M12A
22-19 0.38-0.60	**.024-.036** 0.61-0.91	600-1300	**.012** 0.30	**.330** 8.38	Brass	045	1601578-1	L045M12B

† These part numbers are available upon special request; contact Tyco Electronics Engineering for details.

10 Ridges



AWG/ mm²	Wire Range Solid Dia.	CMA Range	Stock Thk. (T)	Mat'l Width (W)	Material	Toolset	Part Number	Descriptive X-ref
22-19 0.38-0.60	**.024-.036** 0.61-0.91	600-1300	**.012** 0.30	**.234** 5.94	Brass	045	1601575-1	L045G12B
21-18½ 0.40-0.75	**.028-.039** 0.71-0.99	800-1500	**.016** 0.41	**.234** 5.94	Cu Ni	051	1601593-1†	L051G16A
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.012** 0.30	**.234** 5.94	Brass	061	1601632-1†	L061G12B
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.020** 0.51	**.234** 5.94	Brass	061	1601633-1	L061G20B
11½-9 4.00-6.50	**.084-.114** 2.13-2.90	7000-13000	**.020** 0.51	**.234** 5.94	Brass	200/202	1601853-1	P200/ 202G20B
11½-9 4.00-6.50	**.084-.114** 2.13-2.90	7000-13000	**.025** 0.64	**.234** 5.94	Brass	200/202	1601769-1	L200/ 202G25BX

† These part numbers are available upon special request; contact Tyco Electronics Engineering for details.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

RTM Crimpband Splices (Continued)

9 Ridges



AWG/ mm²	Wire Range Solid Dia.	CMA Range	Stock Thk. (T)	Mat'l Width (W)	Material	Toolset	Part Number	Descriptive X-ref
22-19 0.38-0.60	**.024-.036** 0.61-0.91	600-1300	**.012** 0.30	**.216** 5.49	Stainless Steel	045	1601807-1	P045F12SS
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.012** 0.30	**.216** 5.49	Stainless Steel	061	1601520-1	G061F12SS

8 Ridges



AWG/ mm²	Wire Range Solid Dia.	CMA Range	Stock Thk. (T)	Mat'l Width (W)	Material	Toolset	Part Number	Descriptive X-ref
24-20 0.20-0.50	**.020-.033** 0.51-0.84	400-1100	**.012** 0.30	**.185** 4.70	Cu Ni	032/036	1601553-1	L032/ 036E12A
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1600-4000	**.018** 0.46	**.185** 4.70	Tin Plated CRS	076	1601669-1	L076E18TCRS
11½-9 4.00-6.50	**.084-.114** 2.13-2.90	7000-13000	**.024** 0.61	**.185** 4.70	Brass	200/202	1601768-1	L200/ 202E24B

7 Ridges



AWG/ mm²	Wire Range Solid Dia.	CMA Range	Stock Thk. (T)	Mat'l Width (W)	Material	Toolset	Part Number	Descriptive X-ref
24-20 0.20-0.50	**.020-.033** 0.51-0.84	400-1100	**.012** 0.30	**.154** 3.91	Brass	032/036	1601550-1	L032/ 036D12B
24-20 0.20-0.50	**.020-.033** 0.51-0.84	400-1100	**.016** 0.41	**.154** 3.91	Cu Ni	032/036	1601551-1	L032/ 036D16A
24-20 0.20-0.50	**.020-.033** 0.51-0.84	400-1100	**.016** 0.41	**.154** 3.91	Brass	032/036	1601797-1	P032/ 036D16B
24-20 0.20-0.50	**.020-.033** 0.51-0.84	400-1100	**.016** 0.41	**.154** 3.91	Tin Plated Brass	032/036	1601798-1	P032/ 036D16TB
22-19 0.38-0.60	**.024-.036** 0.61-0.91	600-1300	**.012** 0.30	**.154** 3.91	Brass	045	1601572-1	L045D12B
22-19 0.38-0.60	**.024-.036** 0.61-0.91	600-1300	**.016** 0.41	**.154** 3.91	Cu Ni	045	1601573-1	L045D16A

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

RTM Crimpband Splices (Continued)

7 Ridges (Continued)



AWG/ mm²	Wire Range Solid Dia.	CMA Range	Stock Thk. (T)	Mat'l Width (W)	Material	Toolset	Part Number	Descriptive X-ref
22-19 0.38-0.60	**.024-.036** 0.61-0.91	600-1300	**.016** 0.41	**.154** 3.91	Brass	045	1601507-1†	G045D16B
21-18½ 0.40-0.75	**.028-.039** 0.71-0.99	800-1500	**.012** 0.30	**.154** 3.91	Brass	051	1601587-1	L051D12B
21-18½ 0.40-0.75	**.028-.039** 0.71-0.99	800-1500	**.016** 0.41	**.154** 3.91	Brass	051	1601588-1	L051D16B
21-18½ 0.40-0.75	**.028-.039** 0.71-0.99	800-1500	**.020** 0.51	**.154** 3.91	Nickel Plated Steel	051	1601591-1	L051D20NPS
21-18½ 0.40-0.75	**.028-.039** 0.71-0.99	800-1500	**.020** 0.51	**.154** 3.91	Tin Plated CRS	051	1601811-1†	P051D20TCRS
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.012** 0.30	**.154** 3.91	Cu Ni	061	1601818-1†	P061D12A
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.012** 0.30	**.154** 3.91	Brass	061	1601620-1†	L061D12B
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.012** 0.30	**.154** 3.91	Tin Plated Brass	061	1601514-1†	G061D12TB
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.016** 0.41	**.154** 3.91	Cu Ni	061	1601819-1	P061D16A
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.016** 0.41	**.154** 3.91	Brass	061	1601820-1	P061D16B
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.016** 0.41	**.154** 3.91	Tin Plated Brass	061	1601623-1	L061D16TB
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.018** 0.46	**.154** 3.91	Brass	061	1601625-1	L061D18B
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.018** 0.46	**.154** 3.91	Tin Plated Brass	061	1601628-1	L061D18TB
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.020** 0.51	**.154** 3.91	Cu Ni	061	1601629-1	L061D20A
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.020** 0.51	**.154** 3.91	Brass	061	1601630-1	L061D20B
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.020** 0.51	**.154** 3.91	Tin Plated Brass	061	1601631-1	L061D20TBX
20-15 0.60-1.60	**.033-.057** 0.84-1.45	1100-3200	**.016** 0.41	**.154** 3.91	Brass	061/076	1601601-1	L061/076D16B
19½-14½ 0.60-1.80	**.035-.061** 0.89-1.54	1200-3700	**.016** 0.41	**.154** 3.91	Brass	061/092	1601603-1	L061/092D16B
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1600-4000	**.012** 0.30	**.154** 3.91	Cu Ni	076	1601828-1	P076D12A
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1600-4000	**.012** 0.30	**.154** 3.91	Brass	076	1601655-1†	L076D12B
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1600-4000	**.016** 0.41	**.154** 3.91	Cu Ni	076	1601656-1	L076D16A
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1600-4000	**.016** 0.41	**.154** 3.91	Brass	076	1601829-1	P076D16B
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1600-4000	**.016** 0.41	**.154** 3.91	Tin Plated Brass	076	1601658-1	L076D16TB
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1600-4000	**.018** 0.46	**.154** 3.91	Cu Ni	076	1601660-1	L076D18AX
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1600-4000	**.018** 0.46	**.154** 3.91	Brass	076	1601661-1	L076D18B
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1600-4000	**.018** 0.46	**.154** 3.91	Tin Plated Brass	076	1601664-1	L076D18TB
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1600-4000	**.020** 0.51	**.154** 3.91	Brass	076	1601665-1	L076D20B
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1600-4000	**.020** 0.51	**.154** 3.91		076	1601667-1	L076D20TCRS
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1600-4000	**.024** 0.61	**.154** 3.91	Brass	076	1601668-1	L076D24B

† These part numbers are available upon special request; contact Tyco Electronics Engineering for details.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

www.te.com/appliances

RTM Crimpband Splices (Continued)

7 Ridges (Continued)



AWG/ mm²	Wire Range Solid Dia.	CMA Range	Stock Thk. (T)	Mat'l Width (W)	Material	Toolset	Part Number	Descriptive X-ref
17½-13 0.95-2.54	**.042-.068** 1.07-1.80	1800-4600	**.016** 0.41	**.154** 3.91	Brass	076/092	1601642-1	L076/ 092D16BX
16½-13 1.10-2.60	**.047-.072** 1.19-1.83	2200-5200	**.016** 0.41	**.154** 3.91	Cu Ni	092	1601689-1	L092D16ASP
16½-13 1.10-2.60	**.047-.072** 1.19-1.83	2200-5200	**.016** 0.41	**.154** 3.91	Brass	092	1601691-1	L092D16B
16½-13 1.10-2.60	**.047-.072** 1.19-1.83	2200-5200	**.016** 0.41	**.154** 3.91	Tin Plated Brass	092	1601693-1	L092D16TB
16½-13 1.10-2.60	**.047-.072** 1.19-1.83	2200-5200	**.018** 0.46	**.154** 3.91	Cu Ni	092	1601694-1	L092D18A
16½-13 1.10-2.60	**.047-.072** 1.19-1.83	2200-5200	**.018** 0.46	**.154** 3.91	Brass	092	1601695-1	L092D18B
16½-13 1.10-2.60	**.047-.072** 1.19-1.83	2200-5200	**.018** 0.46	**.154** 3.91	Tin Plated Brass	092	1601841-1	P092D18TB
16½-13 1.10-2.60	**.047-.072** 1.19-1.83	2200-5200	**.020** 0.51	**.154** 3.91	Brass	092	1601528-1†	G092D20B
16-12 1.30-3.46	**.051-.078** 1.29-1.98	2600-6100	**.020** 0.51	**.154** 3.91	Cu Ni	092/125	1601680-1	L092/ 125D20A
16-12 1.30-3.46	**.051-.078** 1.29-1.98	2600-6100	**.020** 0.51	**.154** 3.91	Brass	092/125	1601681-1	L092/ 125D20B
16-12 1.30-3.46	**.051-.078** 1.29-1.98	2600-6100	**.020** 0.51	**.154** 3.91	Tin Plated CRS	092/125	1601682-1	092/ 125D20TCRS
15½-12 1.54-3.46	**.055-.082** 1.40-2.10	3000-6750	**.016** 0.41	**.154** 3.91	Brass	125	1601529-1	G125D16B
15½-12 1.54-3.46	**.055-.082** 1.40-2.10	3000-6750	**.018** 0.46	**.154** 3.91	Cu Ni	125	1601531-1	G125D18A
15½-12 1.54-3.46	**.055-.082** 1.40-2.10	3000-6750	**.018** 0.46	**.154** 3.91	Brass	125	1601726-1	L125D18B
15½-12 1.54-3.46	**.055-.082** 1.40-2.10	3000-6750	**.018** 0.46	**.154** 3.91	Tin Plated Brass	125	1601729-1	L125D18TBX
15½-12 1.54-3.46	**.055-.082** 1.40-2.10	3000-6750	**.020** 0.51	**.154** 3.91	Brass	125	1601730-1	L125D20B
15½-12 1.54-3.46	**.055-.082** 1.40-2.10	3000-6750	**.020** 0.51	**.154** 3.91	Tin Plated Brass	125	1601731-1	L125D20TB
15½-12 1.54-3.46	**.055-.082** 1.40-2.10	3000-6750	**.020** 0.51	**.154** 3.91		125	1601733-1	L125D20TCRS
14½-11½ 1.80-4.00	**.059-.087** 1.50-2.21	3500-7500	**.018** 0.46	**.154** 3.91	Tin Plated Brass	125/165	1601709-1	L125/ 165D18TB
14½-11½ 1.80-4.00	**.059-.087** 1.50-2.21	3500-7500	**.020** 0.51	**.154** 3.91	Cu Ni	125/165	1601710-1	L125/ 165D20A
14½-11½ 1.80-4.00	**.059-.087** 1.50-2.21	3500-7500	**.020** 0.51	**.154** 3.91	Brass	125/165	1601711-1	L125/ 165D20B
14½-11½ 1.80-4.00	**.059-.087** 1.50-2.21	3500-7500	**.020** 0.51	**.154** 3.91	Tin Plated Brass	125/165	1601712-1	L125/ 165D20TB
14-11 2.00-4.20	**.063-.092** 1.60-2.34	4000-8500	**.020** 0.51	**.154** 3.91	Cu Ni	165	1601754-1†	L165D20A
14-11 2.00-4.20	**.063-.092** 1.60-2.34	4000-8500	**.020** 0.51	**.154** 3.91	Brass	165	1601755-1	L165D20B
13½-10½ 2.54-4.50	**.071-.097** 1.70-2.46	4500-9500	**.020** 0.51	**.154** 3.91	Brass	165/200	1601532-1	G165/ 200D20B
11½-9 4.00-6.50	**.084-.114** 2.13-2.90	7000-13000	**.016** 0.41	**.154** 3.91	Brass	200/202	1601764-1	L200/ 202D16B
11½-9 4.00-6.50	**.084-.114** 2.13-2.90	7000-13000	**.020** 0.51	**.154** 3.91	Cu Ni	200/202	1601765-1	L200/ 202D20A
11½-9 4.00-6.50	**.084-.114** 2.13-2.90	7000-13000	**.020** 0.51	**.154** 3.91	Brass	200/202	1601852-1	P200/ 202D20B
11½-9 4.00-6.50	**.084-.114** 2.13-2.90	7000-13000	**.020** 0.51	**.154** 3.91	Tin Plated Brass	200/202	1601766-1	L200/ 202D20TB

† These part numbers are available upon special request; contact Tyco Electronics Engineering for details.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

www.te.com/appliances

RTM Crimpband Splices (Continued)

6 Ridges



AWG/ mm²	Wire Range Solid Dia.	CMA Range	Stock Thk. (T)	Mat'l Width (W)	Material	Toolset	Part Number	Descriptive X-ref
24-20 0.20-0.50	**.020-.033** 0.51-0.84	400-1100	**.012** 0.30	**.138** 3.51	Tin Plated Brass	032/036	1601548-1	L032/ 036C12TB
24-20 0.20-0.50	**.020-.033** 0.51-0.84	400-1100	**.016** 0.41	**.138** 3.51	Brass	032/036	1601549-1	L032/ 036C16B
22-19 0.38-0.60	**.024-.036** 0.61-0.91	600-1300	**.012** 0.30	**.138** 3.51	Brass	045	1601566-1	L045C12B
22-19 0.38-0.60	**.024-.036** 0.61-0.91	600-1300	**.016** 0.41	**.138** 3.51	Cu Ni	045	1601569-1	L045C16A
22-19 0.38-0.60	**.024-.036** 0.61-0.91	600-1300	**.016** 0.41	**.138** 3.51	Brass	045	1601571-1	L045C16B
21-18½ 0.40-0.75	**.028-.039** 0.71-0.99	800-1500	**.012** 0.30	**.138** 3.51	Brass	051	1601808-1†	P051C12B
21-18½ 0.40-0.75	**.028-.039** 0.71-0.99	800-1500	**.016** 0.41	**.138** 3.51	Cu Ni	051	1601809-1	P051C16A
21-18½ 0.40-0.75	**.028-.039** 0.71-0.99	800-1500	**.016** 0.41	**.138** 3.51	Brass	051	1601810-1	P051C16B
21-18½ 0.40-0.75	**.028-.039** 0.71-0.99	800-1500	**.018** 0.46	**.138** 3.51	Brass	051	1601586-1†	L051C18B
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.016** 0.41	**.138** 3.51	Cu Ni	061	1601614-1	L061C16A
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.016** 0.41	**.138** 3.51	Brass	061	1601511-1	G061C16B
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.016** 0.41	**.138** 3.51	Tin Plated Brass	061	1601617-1	L061C16TB
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.018** 0.46	**.138** 3.51	Cu Ni	061	1601618-1	L061C18AX
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.018** 0.46	**.138** 3.51	Brass	061	1601619-1	L061C18B
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.020** 0.51	**.138** 3.51	Brass	061	1601513-1†	G061C20B
20-15 0.60-1.60	**.033-.057** 0.84-1.45	1100-3200	**.016** 0.41	**.138** 3.51	Brass	061/076	1601597-1	L061/ 076C16B
20-15 0.60-1.60	**.033-.057** 0.84-1.45	1100-3200	**.016** 0.41	**.138** 3.51	Tin Plated Brass	061/076	1601599-1	L061/ 076C16TB
20-15 0.60-1.60	**.033-.057** 0.84-1.45	1100-3200	**.018** 0.46	**.138** 3.51	Brass	061/076	1601600-1†	L061/ 076C18B
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1600-4000	**.016** 0.41	**.138** 3.51	Cu Ni	076	1601650-1	L076C16A
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1600-4000	**.016** 0.41	**.138** 3.51	Brass	076	1601651-1	L076C16B
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1600-4000	**.018** 0.46	**.138** 3.51	Cu Ni	076	1601652-1†	L076C18A
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1600-4000	**.018** 0.46	**.138** 3.51	Brass	076	1601827-1	P076C18B
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1600-4000	**.018** 0.46	**.138** 3.51		076	1601654-1†	L076C18TCRS
17½-13 0.95-2.54	**.042-.068** 1.07-1.80	1800-4600	**.016** 0.41	**.138** 3.51	Brass	076/092	1601640-1	L076/ 092C16B
16½-13 1.10-2.60	**.047-.072** 1.19-1.83	2200-5200	**.016** 0.41	**.138** 3.51	Cu Ni	092	1601837-1	P092C16AX
16½-13 1.10-2.60	**.047-.072** 1.19-1.83	2200-5200	**.016** 0.41	**.138** 3.51	Brass	092	1601687-1	L092C16B
15½-12 1.54-3.46	**.055-.082** 1.40-2.10	3000-6750	**.016** 0.41	**.138** 3.51	Tin Plated Brass	125	1601721-1	L125C16TB
15½-12 1.54-3.46	**.055-.082** 1.40-2.10	3000-6750	**.018** 0.46	**.138** 3.51	Cu Ni	125	1601722-1	L125C18A
15½-12 1.54-3.46	**.055-.082** 1.40-2.10	3000-6750	**.018** 0.46	**.138** 3.51	Brass	125	1601723-1	L125C18B

† These part numbers are available upon special request; contact Tyco Electronics Engineering for details.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

www.te.com/appliances

RTM Crimpband Splices (Continued)

3 Ridges



AWG/ mm²	Wire Range Solid Dia.	CMA Range	Stock Thk. (T)	Mat'l Width (W)	Material	Toolset	Part Number	Descriptive X-ref
27½-21 0.09-0.40	**.013-.028** 0.33-0.71	170-800	**.012** 0.30	**.076** 1.93	Brass	032	1601555-1	L032B12B
24-20 0.20-0.50	**.020-.033** 0.51-0.84	400-1100	**.012** 0.30	**.076** 1.93	Cu Ni	032/036	1601542-1	L032/ 036B12A
24-20 0.20-0.50	**.020-.033** 0.51-0.84	400-1100	**.012** 0.30	**.076** 1.93	Brass	032/036	1601795-1	P032/ 036B12B
24-20 0.20-0.50	**.020-.033** 0.51-0.84	400-1100	**.016** 0.41	**.076** 1.93	Brass	032/036	1601545-1	L032/ 036B16B
24-20 0.20-0.50	**.020-.033** 0.51-0.84	400-1100	**.016** 0.41	**.076** 1.93	Tin Plated Brass	032/036	1601546-1	L032/ 036B16TB
24-20 0.20-0.50	**.020-.033** 0.51-0.84	400-1100	**.018** 0.46	**.076** 1.93	Brass	032/036	1601547-1†	L032/ 036B18B
22-19 0.38-0.60	**.024-.036** 0.61-0.91	600-1300	**.016** 0.41	**.076** 1.93	Cu Ni	045	1601503-1	G045B16A
22-19 0.38-0.60	**.024-.036** 0.61-0.91	600-1300	**.016** 0.41	**.076** 1.93	Brass	045	1601562-1	L045B16B
22-19 0.38-0.60	**.024-.036** 0.61-0.91	600-1300	**.016** 0.41	**.076** 1.93	Tin Plated Brass	045	1601504-1†	G045B16TB
22-19 0.38-0.60	**.024-.036** 0.61-0.91	600-1300	**.016** 0.41	**.076** 1.93	Tin Plated Brass	045	1601564-1	L045B16TBSP
21-18½ 0.40-0.75	**.028-.039** 0.71-0.99	800-1500	**.016** 0.41	**.076** 1.93	Cu Ni	051	1601580-1†	L051B16A
21-18½ 0.40-0.75	**.028-.039** 0.71-0.99	800-1500	**.016** 0.41	**.076** 1.93	Brass	051	1601582-1†	L051B16B
21-18½ 0.40-0.75	**.028-.039** 0.71-0.99	800-1500	**.016** 0.41	**.076** 1.93	Tin Plated Brass	045	1601583-1†	L051B16TB
21-18½ 0.40-0.75	**.028-.039** 0.71-0.99	800-1500	**.020** 0.51	**.076** 1.93	Brass	051	1601584-1	L051B20B
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.016** 0.41	**.076** 1.93	Tin Plated Brass	061	1601612-1†	L061B16TB
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.016** 0.41	**.076** 1.93	Cu Ni	061	1601610-1	L061B16A
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.016** 0.41	**.076** 1.93	Brass	061	1601611-1	L061B16B
20½-16 0.45-1.30	**.030-.051** 0.76-1.29	900-2600	**.016** 0.41	**.076** 1.93	Brass	061	1601635-1	L061L16B
20-15 0.60-1.60	**.033-.057** 0.84-1.45	1100-3200	**.016** 0.41	**.076** 1.93	Tin Plated Brass	061/076	1601596-1	L061/ 076B16TBX
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1600-4000	**.016** 0.41	**.076** 1.93	Brass	076	1601825-1	P076B16B
18-14 0.80-2.00	**.040-.063** 1.02-1.60	1600-4000	**.020** 0.51	**.076** 1.93	Brass	076	1601649-1	L076B20B

† These part numbers are available upon special request; contact Tyco Electronics Engineering for details.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

www.te.com/appliances

Crimpband Application Tooling

Product Facts

- **High Speed Operation — Many times faster than soldering, up to 2,000 crimps per hour**
- **Reliable — Creates uniform connection, unlike soldering**
- **Dependable — The connection is stronger than the wires being crimped**
- **Clean — No heat or noxious solder fumes**
- **Scrap Free — No leftover scrap material**
- **Easy Operation — Simple operator training**
- **Economical — Proven reduction in assembly costs**



Mod I



Mod III

Tyco Electronics offers solderless crimping systems to handle a wide range of wire connections including solid and stranded lead wire, insulated magnet wire, and component leads. Each system is comprised of continuous, serrated Crimpband material and a crimping machine. The Tyco Electronics solution allows the flexibility to create a shape and size, which optimizes the crimp's electrical and mechanical performance.

The Tyco Electronics crimping system produces a very economical and reliable interconnection. Utilizing a continuous Crimpband material the machine will feed, cut form, and crimp your application resulting in a very strong and uniform interconnect crimp.

Whether your application required a wire-to-wire, wire to component leads, wire to terminals, or magnet wire splice termination, the very flexible and dependable crimping machine will provide high-speed scrap free interconnects.

Substantial increase in production interconnection rates can be realized versus traditional soldering. Not to mention it completely eliminates the noxious fumes.

The Mod I crimping system is used when running standard RTM and MTM Crimpband product. In addition, left and right horn termination machines are available when your application requires additional working envelope. The Mod III crimping system is used when stainless steel splices or when large wire gauge applications warrant additional force requirements.

Tooling and Equipment Selector

Volume To Be Crimped		Recommended Equipment	
CMA	in^2/mm^2	Toolset Size	Machine
140-800	**.003-.016** 0.07 - 0.40	032	Mod I
400-1200	**.008-.024** 0.20 - 0.60	032/036	Mod I
600-1600	**.012-.032** 0.30 - 0.81	045	Mod I
900-2600	**.018-.052** 0.45 - 1.31	061	Mod I
1600-4000	**.032-.080** 0.81 - 2.02	076	Mod I
2200-5200	**.044-.104** 1.11 - 2.63	092	Mod I
3000-6750	**.060-.135** 1.52 - 3.42	125	Mod I
4000-8500	**.080-.170** 2.02 - 4.31	165	Mod III
5000-11000	**.010-.219** 2.53 - 5.57	200	Mod III
6000-13000	**.120-.259** 3.04 - 6.58	200/202	Mod III

1. Calculate the combined volume of the wires or components in a crimp.
2. Select Tooling and Machine.
3. Submit samples for test and equipment conditioning.
4. Toolsets are easily interchangeable within same machine type.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

Power Splice

Product Facts

- **Compression crimp eliminates cold solder points, weld burns and wire enbrittlement usually connected with thermal-type terminations**
- **Precisely controlled crimp termination helps eliminate human error, for maximum reliability**
- **Excellent tensile strength, up to 90 lbs axial retention, vibration resistant**
- **Provides a superior electrical connection that is free of many contaminates such as stripper residue and solder flux**
- **8000 - 38,000 CMA nominal capacity**
- **Accepts up to six magnet wires and two standard solid or stranded lead wires**
- **Superior test results: low resistance, high stability**
- **High termination rates, low wire consumption and the elimination of rejects caused by solder flux or heat damage results in the lowest applied costs**

Applications

- **Hermetic/Compressor motors**
- **Squirrel Cage DC motors**
- **Capacitor Start motors**
- **Gear & Traction motors**
- **Power supplies**
- **Liner, Torroid & RF transformers**
- **Circuit breakers & welders**



Tyco Electronics features the AMP Power Splice terminal that is specifically designed to terminate a wide range of lead and magnet wire combinations.

The splice contains two cavities that separate and cradle magnet wire and stripped lead wires prior to crimping.

The outer saddle accepts up to six-magnet wire allowing for a CMA range of 15,000 to 30,000.

The inner saddle accepts pre-stripped lead wires that total up to 10,900 CMA.

In a one step automatic operation, the magnet wire film insulation is multiple ring-stripped as it is forced into the serrations while the lead wire is simultaneously terminated during the precisely controlled crimp

The outer saddle has machined, sharp edges made by a special production process that pierces the insulating layer of the magnet wire in a manner that provides a large contact area.

The resulting termination produces a high tensile strength, air sealed connection that is as resistant to corrosion as the insulated conductor with up to 90 lbs axial retention.

As many as six magnet wires can be terminated simultaneously in one splice in combination with up to two pre-stripped standard solid or stranded lead wire.

A semi-automatic machine provides high output per hour terminations.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

Power Splice (Continued)



Type	Magnet Wire Range CMA	Lead Wire Range CMA	Part Number Reeled
A	15,000-30,000	4200-10,900	1601953-1[1]

[1] Total combined CMA not to exceed 38000.





Part Number 111-000-001

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

Power Splice Application Tooling

Power Splice Machine for Mag Wire/Lead Wire Pigtail Splice Termination

Product Facts

- **Terminate Mag Wire and Lead Wire Together**
- **Maximum 38,000 CMA Crimp**
- **Servo-Driven 5-Ton Terminator**
- **Heavy Duty Air-Feed Applicator**
- **One Control Cabinet Operates 2 Terminators**
- **Programmable Crimping Ram Stroke**
- **Hand Held Control Pendent**
- **Crimp Force Monitoring**
- **Crimp Height Sequencing**



For quick, easy and reliable pigtail splice termination of magnet wire and solid or stranded lead wire, Tyco Electronics offers the new Power Splice terminator and applicator.

The Power Splice terminator and applicator will terminate pigtail splices consisting up to two (2) solid or stranded copper lead wires in wire size from 10-14 AWG and having a Circular Mil Area (CMA) of 4,200-10,000. The splice will simultaneously accept combinations of multiple copper magnet wires in a range of 11-20 AWG. Total magnet wire CMA can fall in the range of 8,000-30,000. Total CMA capable of being crimped in the Power Splice terminal is between 8,000-38,000.

The Power Splice terminator incorporates a servo motor drive 5-ton terminator with an air feed applicator to create a high quality crimp. The application equipment is controlled through a handheld pendent and incorporates crimp force monitoring, crimp height sequencing, and a programmable ram stroke. A special machine guard to facilitate proper wire placement into the terminal is also provided to ease terminal loading and provide operator safety.

Solderless Pigtail Splice Terminations

- No need to pre-strip the magnet wire
- No wire embrittlement due to solder
- No Solder fumes
- Compact clean termination

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

Technical Information

Tensile Strength of Magnet Wire[1]

Wire Size	Nominal Dia. Copper (lbs.)	Nominal Dia. Aluminum (lbs.)
8	438	142
9	340	113
10	269	89
11	213	71
12	189	56
13	134	44
14	106	35
15	84	28
16	66	22
17	53	17
18	42	14
19	33	11
20	6	8
21	21	7
22	16	5
23	13	4
24	10	3
25	8	2.7
26	6	2.1
27	5	1.7
28	4	1.3
29	3	1.1
30	2	.86
31	2	.68
32	1	.55
33	1	.43
34	1	.34
35	.81	.27
36	.65	.21
37	.65	.21
38	.42	.13
39	.32	.10
40	.25	.083
41	.20	.067
42	.16	.054
43	.12	.041
44	.10	.034
45	.08	.027
46	.06	.022
47	.05	.017
48	.04	.013
49	.03	.010
50	.02	.009
51	.02	.007
52	.01	.005

[1] Magnet wire tensile will change as the psi of magnet wire changes.

Note: Copper magnet wire is calculated at 33,000 psi. Aluminum magnet wire is calculated at 11,000 psi (EC grade). Magnet wire should be tensiled on each coil. After termination of the AMPLIVAR splice, the tensile strength will be 70% (min.) of the original magnet wire tensile values.

C.	F.	C.	F.	C.	F.	C.	F.
–80	–112.0	9	48.2	47	116.6	85	185.0
–70	–94.0	10	50.0	48	118.4	86	186.8
–60	–76.0	11	51.8	49	120.2	87	188.6
–50	–58.0	12	53.6	50	122.0	88	190.4
–45	–49.1	13	55.4	51	123.8	89	192.2
–40	–40.0	14	57.2	52	125.6	90	194.0
–35	–31.0	15	59.0	53	127.4	91	195.8
–30	–22.0	16	60.8	54	129.2	92	197.6
–25	–13.0	17	62.6	55	131.0	93	199.4
–20	– 4.0	18	64.4	56	132.8	94	201.2
–19	– 2.2	19	66.2	57	134.6	95	203.0
–18	– .4	20	68.0	58	136.4	96	204.8
–17	1.4	21	69.8	59	138.2	97	206.6
–16	3.2	22	71.6	60	140.0	98	208.4
–15	5.0	23	73.4	61	141.8	99	210.2
–14	6.8	24	75.2	62	143.6	100	212.0
–13	8.6	25	77.0	63	145.4	110	230.0
–12	10.4	26	78.8	64	147.2	120	248.0
–11	12.2	27	80.6	65	149.0	130	266.0
–10	14.0	28	82.4	66	150.8	140	284.0
– 9	15.8	29	84.2	67	152.6	150	302.0
– 8	17.6	30	86.0	68	154.4	160	320.0
– 7	19.4	31	87.8	69	156.2	170	338.0
– 6	21.2	32	89.6	70	158.0	180	356.0
– 5	23.0	33	91.4	71	159.8	190	374.0
– 4	24.8	34	93.2	72	161.6	200	392.0
– 3	26.6	35	95.0	73	163.4	220	428.0
– 2	8.4	36	96.8	74	165.2	240	464.0
– 1	30.2	37	98.6	75	167.0	260	500.0
0	32.0	38	100.4	76	168.8	280	536.0
1	33.8	39	102.2	77	170.6	300	572.0
2	35.6	40	104.0	78	172.4	400	752.0
4	39.2	42	107.6	80	176.0	600	1112.0
5	41.0	43	109.4	81	177.8	700	1292.0
6	42.8	44	111.2	82	179.6	800	1472.0
7	44.6	45	113.0	83	181.4	900	1652.0
8	46.4	46	114.8	84	183.2	1000	1832.0

C = 5/9 (F. ☒32)
F = 9/5C. + 32

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

Technical Information (Continued)

Circular Mil Area (CMA) and Diameter for Magnet Wires (AWG Wire Size Range 52–25½)

AWG Bare Wire	Bare Wire Dia.		CMA Bare	Single Film Coated Dia.		CMA Single Film Coated	Heavy Film Coated Dia.		CMA Heavy Film Coated
	in.	mm		in.	mm		in.	mm	
52	.0008	.020	0.6	.0010	.025	1.0	.0011	.028	1.2
51	.0009	.023	0.8	.0011	.028	1.2	.0012	.031	1.5
50	.0010	.025	1.0	.0012	.031	1.5	.0013	.033	1.7
49	.0011	.028	1.2	.0013	.033	1.7	.0014	.035	2.0
48	.0012	.031	1.5	.0014	.035	2.0	.0015	.038	2.2
47	.0014	.035	2.0	.0016	.040	2.5	.0018	.045	3.1
46	.0016	.040	2.5	.0017	.043	2.9	.0019	.048	3.6
45	.0018	.045	3.1	.0019	.048	3.6	.0021	.053	4.4
44	.0020	.050	4.0	.0022	.056	4.8	.0025	.063	6.2
43	.0022	.056	4.8	.0025	.063	6.2	.0027	.069	7.3
42	.0025	0.06	6.3	.0028	0.07	8	.0030	0.08	9
41	.0028	0.07	7.8	.0031	0.08	10	.0034	0.09	12
40	.0031	0.08	9.6	.0035	0.09	12	.0038	0.10	14
39	.0035	0.09	12	.0039	0.10	15	.0043	0.11	18
38	.0040	0.10	16	.0045	0.11	20	.0049	0.12	24
37	.0045	0.11	20	.0050	0.13	25	.0055	0.14	30
36	.0050	0.13	25	.0056	0.14	31	.0060	0.15	36
35	.0056	0.14	31	.0062	0.16	38	.0067	0.17	45
35	.0056	0.14	31	.0062	0.16	38	.0067	0.17	45
34	.0063	0.16	40	.0069	0.18	48	.0075	0.19	56
33	.0071	0.18	50	.0077	0.20	59	.0085	0.22	72
32	.0080	0.20	64	.0084	0.21	71	.0095	0.24	90
31	.0089	0.23	79	.0092	0.23	85	.0105	0.27	110
30½	.0095	0.24	90	.0099	0.25	98	.0111	0.28	123
30	.0100	0.25	100	.0106	0.27	112	.0116	0.29	135
29½	.0107	0.27	115	.0114	0.29	130	.0123	0.31	151
29	.0113	0.29	128	.0120	0.30	144	.0130	0.33	169
28½	.0120	0.30	144	.0126	0.32	159	.0137	0.35	187
28	.0126	0.32	159	.0136	0.35	185	.0144	0.37	207
27½	.0134	0.34	180	.0144	0.37	207	.0153	0.39	234
27	.0142	0.36	202	.0152	0.39	231	.0161	0.41	259
26½	.0151	0.38	225	.0160	0.41	256	.0170	0.43	289
26	.0159	0.40	258	.0170	0.43	289	.0179	0.45	320
25½	.0169	0.43	289	.0180	0.46	324	.0190	0.48	361

Technical Information (Continued)

Circular Mil Area (CMA) and Diameter for Magnet Wires (AWG Wire Size Range 25–8)

AWG Bare Wire	Bare Wire Dia.		CMA Bare	Single Film Coated Dia.		CMA Single Film Coated	Heavy Film Coated Dia.		CMA Heavy Film Coated
	in.	mm		in.	mm		in.	mm	
25	.0179	0.45	320	.0190	0.48	361	.0200	0.51	400
24 1/2	.0190	0.48	361	.0200	0.51	400	.0212	0.54	449
24	.0201	0.51	404	.0213	0.54	455	.0223	0.57	497
23 1/2	.0214	0.54	458	.0226	0.57	511	.0236	0.60	557
23	.0226	0.57	511	.0238	0.60	566	.0249	0.63	620
22 1/2	.0240	0.61	576	.0252	0.64	635	.0263	0.67	692
22	.0253	0.64	640	.0266	0.68	708	.0277	0.70	767
21 1/2	.0269	0.68	724	.0282	0.72	795	.0293	0.74	858
21	.0285	0.72	812	.0298	0.76	888	.0310	0.79	961
20 1/2	.0303	0.77	918	.0315	0.80	992	.0328	0.83	1,076
20	.0320	0.81	1,024	.0334	0.85	1,116	.0346	0.88	1,197
19 1/2	.0340	0.86	1,156	.0353	0.90	1,246	.0365	0.93	1,340
19	.0359	0.91	1,289	.0373	0.95	1,391	.0386	0.98	1,490
18 1/2	.0381	0.97	1,452	.0395	1.00	1,560	.0409	1.04	1,673
18	.0403	1.02	1,624	.0418	1.06	1,747	.0431	1.09	1,858
17 1/2	.0428	1.09	1,832	.0443	1.13	1,962	.0456	1.16	2,079
17	.0453	1.15	2,052	.0468	1.19	2,190	.0482	1.22	2,323
16 1/2	.0481	1.22	2,314	.0496	1.26	2,460	.0510	1.30	2,601
16	.0508	1.29	2,581	.0524	1.33	2,746	.0583	1.37	2,894
15 1/2	.0540	1.37	2,916	.0560	1.42	3,136	.0570	1.45	3,249
15	.0571	1.45	3,260	.0587	1.49	3,446	.0602	1.53	3,624
14 1/2	.0606	1.54	3,672	.0622	1.58	3,869	.0639	1.62	4,082
14	.0641	1.63	4,109	.0658	1.67	4,330	.0675	1.71	4,556
13 1/2	.0681	1.73	4,638	.0698	1.77	4,872	.0711	1.81	5,055
13	.0720	1.83	5,184	.0738	1.87	5,446	.0749	1.90	5,670
12 1/2	.0764	1.94	5,837	.0783	1.99	6,131	.0793	2.01	6,188
12	.0808	2.05	6,529	.0827	2.10	6,839	.0838	2.13	7,090
11 1/2	.0858	2.18	7,362	.0877	2.23	7,691	.0888	2.26	7,885
11	.0907	2.30	8,226	.0927	2.35	8,593	.0938	2.38	8,892
10 1/2	.0963	2.35	9,274	.0983	2.50	9,663	.0994	2.52	9,880
10	.1019	2.59	10,384	.1040	2.64	10,820	.1050	2.67	11,151
9	.1144	2.91	13,087	.1166	2.96	13,600	.1177	2.99	13,971
8	.1285	3.26	16,512	.1307	3.32	17,080	.1318	3.35	17,530

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

Technical Information (Continued)

Circular Mil Area (CMA) and Diameter for Lead Wires (AWG Wire Size Range 30–8)

Wire Size	Strands		Wire Area in Circ. Mils
	No.	Dia. (Mils)	
30	7	4.0	112
30	1	10.0	100
28	7	5.0	175
28	19	3.1	181
28	1	12.6	159
27	7	5.6	219
27	1	14.2	202
26	6	6.3	238
26	10	5.0	250
26	16	4.0	256
26	8	5.6	251
26	1	15.9	253
26	26	3.1	250
26	7	6.3	278
26	3	10.0	300
26 AN	12	5.0	300
25	10	5.6	314
25	8	6.3	318
25	1	17.9	320
24	10	6.3	397
24	8	7.1	403
24	16	5.0	400
24	4	10.0	400
24	1	20.1	404
24	26	4.0	416
24	13	5.6	408
24	7	8.0	448
24	56	2.8	439
24 AN	19	5.0	475
23	10	7.1	504
23	8	8.0	512
23	1	22.6	511
—	21	5.0	525
22	6	10.0	600
22	8	8.9	634
22	16	6.3	635
22	10	8.0	640
22	1	25.3	640
22	7	10.0	700
22 AN	19	6.3	754
20	10	10.0	1,000
20	1	10.0	1,024
20	26	6.3	1,032
20	7	12.6	1,111
20 AN	19	7.9	1,186
18	19	9.2	1,608
—	16	10.0	1,600
18	1	40.3	1,624
18	7	15.2	1,617
18	65	5.0	1,625
18	7	15.3	1,639

Wire Size	Strands		Wire Area in Circ. Mils
	No.	Dia. (Mils)	
—	41	6.3	1,627
—	7	16.0	1,792
18 AN	19	10.0	1,900
18 AN	19	11.3	2,426
16	7	19.2	2,580
16	1	50.8	2,581
16	65	6.3	2,580
16	19	11.7	2,601
16	105	5.0	2,625
—	26	10.0	2,600
16	7	20.0	2,800
14 AN	19	14.2	3,831
14	37	10.5	4,079
14	7	24.2	4,099
14	19	14.7	4,106
14	1	64.4	4,109
—	41	10.0	4,100
14	105	6.3	4,167
14	168	5.0	4,200
14	84	71	4,234
—	7	25.3	4,481
12	19	17.9	6,088
12 AN	19	17.9	6,088
12	259	5.0	6,475
12	19	18.5	6,503
12	7	30.5	6,512
12	37	13.3	6,545
12	1	80.8	6,529
12	165	6.3	6,549
12	84	8.9	6,654
10	7	36.0	9,072
—	37	16.0	9,472
10	414	5.0	10,350
10	37	16.7	10,319
10	1	101.9	10,384
10	7	38.5	10,376
10	19	23.4	10,404
—	41	15.9	10,365
10	105	10.0	10,500
9	7	43.0	12,943
9	1	114.4	13,087
9	525	5.0	13,125
8	7	45.0	14,175
8	133	11.1	16,386
8	37	21.1	16,472
8	1	128.5	16,512
8	7	48.6	16,533
8	19	29.5	16,534
8	49	18.4	16,589
8 AN	133	11.3	16,982

Terminal Stud Hole Size

Use to Select Proper Size Terminal

The chart shows sizes and dimensions of various studs and the corresponding terminal stud hole sizes used with AMP devices.

For example, with stud #5 (.125 [3.18] Diameter), use AMP device listed for #5 stud (.129 [3.28] Hole Diameter).

Terminal stud hole sizes may easily be checked by fitting sample terminal to black circle.

Stud Size		Stud Dia.	Minimum Terminal Hole Diameter
U.S. Cust.	Metric		
#0		.060	.064
#1		.073	.077
#2	M2	.086	.090
#3		.099	.103
#4		.112	.116
#5	M3	.125	.129
#6	M3.5	.138	.142
#8	M4	.164	.168
#10		.190	.194
#12		.216	.220
#14		.242	.247
1/4"	M6	.250	.260
5/16"	M8	.312	.323
3/8"		.375	.385
7/16"		.437	.448
1/2"	M12	.500	.510

Stud Size		Stud Dia.	Minimum Terminal Hole Diameter
U.S. Cust.	Metric		
5/8"	M16	.625	.651
3/4"		.750	.776
7/8"	M22	.875	.901
1"		1.000	1.026
1-1/8"		1.125	1.151
1-1/4"		1.250	1.276

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

Engineering Notes

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

Engineering Notes

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

Engineering Notes

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

FOR MORE INFORMATION

te.com

TE Technical Support Center

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

Part numbers in this brochure are RoHS Compliant*, unless marked otherwise.
*as defined www.te.com/leadfree

te.com/appliances

© 2014 Tyco Electronics Corporation a TE Connectivity Ltd, Company. All Rights Reserved.
82221 CS 01/2014
MAG-MATE, SIAMEZE, AMPLIVAR, TE Connectivity, TE connectivity (logo) and TE (logo) are trademarks.
Other logos, product and Company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE connectivity