

4		3		2		1		
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION				
© COPYRIGHT - By -				ALL RIGHTS RESERVED.				
						REVISIONS		
P		LTR		DESCRIPTION		DATE	DWN	APVD
		G1		REVISED PER ECO-16-014993		19OCT2016	RS	DR
INSULATION SERRATIONS SLEEVE 3 EQUALLY SPACED STRIPES COLOR CODE BLUE BODY Ø5.00±0.07 [Ø.197±.003] FOR #10 STUD 7.92 [.312] 7.13 [.281] MIN 17.83 [.702] MAX 21.84 [.860] MAX .787 [.031] MIN 6						1 MUST BE CRIMPED WITH A 22-18 OR 22-16 PIDG (RED) TOOL. 2 WIRE INSULATION DIA: 0.79-1.34[.031-.055.] 3 TONGUE MATERIAL THK: 0.69±0.05[.027±.002.] 4 BODY & SLEEVE: TIN 0.00254[.000100] MIN THK PER ASTM B545. 5 MATERIAL: BODY & SLEEVE- CU PER ASTM B152 INSULATION - NYLON PER ASTM D4066 COLOR - YELLOW. 6 APPLIES FROM EDGE OF METAL BARREL TO THE CENTER OF STUD HOLE. 7 MEETS M7928/1-10, CLASS 1 & 2.		
						1000	LOOSE PIECE	53057
						QTY	PACKAGE TYPE	PART NO.
CUSTOMER SERVICE SYSTEMS				MAX RECOMMENDED OPERATING TEMPERATURE: 105°C[221°F] MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 300 V MAX		DWN JR RUTH 14JAN10		
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 0.10-0.26mm²[202-509] STRANDED		CHK T MICHIELUTTI 15JAN10		
FOR ORDER ENTRY		1-800-526-5142				APVD T MICHIELUTTI 15JAN10		
				DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		
						0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH		
				MATERIAL		PRODUCT SPEC		
				4		APPLICATION SPEC		
				5		WEIGHT		
						CUSTOMER DRAWING		
						SCALE 5:1		
						SHEET 1 OF 1		
						REV G1		
						RESTRICTED TO		
						SIZE A3		
						CAGE CODE 00779		
						DRAWING NO C-53057		
						NAME		
						TE Connectivity		
						TERMINAL, RING TONGUE, PIDG, INSULATION RESTRICTING WIRE SIZE: 24 AWG		