



REVISIONS				DOC. NO. SPC-F004 * Effective: 7/8/02 * DCP No: 1398					
DCP #	REV	DESCRIPTION		DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1857	D	RoHS Added		DCM	12/12/05	JWM	3/17/08	JWM	3/17/08
2041	E	Storage Life Added		JN	04/22/08	JWM	04/22/08	JWM	04/22/08

The FPF series heat shrink tubing is a general purpose tubing which has been specially engineered for superior flame resistance. FPF tubing can withstand elevated temperatures to 135°C (275°F) for brief periods, is split resistant, mechanically tough and resists cold flow.

Shrink Ratio: 2:1 Shrink Temp.: 100°C (212°F) Operating Temp.: -55°C~135°C (-67°F~274°F)

Dimensions				Standard Packages (Color: Black)					
Size	Expanded I.D. (Min)	Recovered I.D. (Max.)	Recovered Nominal Wall Thickness	4 Foot Lengths (+1", -0")			6 Inch Lengths (±.125")		
				Type No.	Pcs.	Total Footage	Type No.	Pcs	Total Footage
3/64"	.046"	.023"	.016"	FPF-003-4025-BLK	25	100 FT	FPF-003-6040-BLK	40	20 FT
1/16"	.063"	.031"	.017"	FPF-004-4025-BLK	25	100 FT	FPF-004-6036-BLK	36	18 FT
3/32"	.093"	.046"	.020"	FPF-006-4025-BLK	25	100 FT	FPF-006-6032-BLK	32	16 FT
1/8"	.125"	.062"	.020"	FPF-008-4025-BLK	25	100 FT	FPF-008-6028-BLK	28	14 FT
3/16"	.187"	.093"	.020"	FPF-012-4025-BLK	25	100 FT	FPF-012-6024-BLK	24	12 FT
1/4"	.250"	.125"	.025"	FPF-016-4025-BLK	25	100 FT	FPF-016-6020-BLK	20	10 FT
3/8"	.375"	.187"	.025"	FPF-024-4025-BLK	25	100 FT	FPF-024-6016-BLK	16	8 FT
1/2"	.500"	.250"	.025"	FPF-032-4005-BLK	5	20 FT	FPF-032-6014-BLK	14	7 FT
3/4"	.750"	.375"	.030"	FPF-048-4005-BLK	5	20 FT	FPF-048-6012-BLK	12	6 FT
1"	1.000"	.500"	.035"	FPF-064-4005-BLK	5	20 FT	FPF-064-6008-BLK	8	4 FT
1 1/2"	1.500"	.750"	.040"	FPF-096-4005-BLK	5	20 FT	FPF-096-6005-BLK	5	2.5 FT
2"	2.000"	1.000"	.045"	FPF-128-4005-BLK	5	20 FT	FPF-128-6003-BLK	3	1.5 FT
3"	3.000"	1.500"	.050"	FPF-192-4002-BLK	2	8 FT	FPF-192-6003-BLK	3	1.5 FT

TYPICAL PROPERTIES

Physical

Tensile Strength 2400 PSI
 Ultimate Elongation 400 %
 Longitudinal Change +1 %, -10%
 Secant Modulus (2 %) 13,000 PSI
 Heat Aging Elongation 175 %
 (168 hrs @ 175°C)
 Heat Shock (4 hrs @ 250°C) No dripping,
 cracking, passes mandrel wrap test
 Low Temp Flexibility No cracking
 (4 hrs @ -55°C)
 *Flexibility: 3
 Flammability: Self-extinguishing,
 meets UL 224 VW-1 test

Shelf Life: 10 years in humidity controlled storage
 (10°C/50°F to 27°C/80°F & <75 % RH)

*Flexibility: The materials are rated on a scale

Electrical

Dielectric Strength 900 V/mil
 Volume Resistivity 10¹⁵ ohm-cm



RoHS
Compliant

Chemical

Corrosive Effect Non-corrosive
 Water Absorption 0.2 %
 Solvent Resistance

Tensile Strength 1000PSI
 Dielectric Strength 400 V/mil
 Fungus Resistance Non-nutrient
 Applicable Specifications: MIL-DTL-23053/5 Class 3



The technical information provided consists of typical product data and should not be used for specification purposes. Unless otherwise noted, all tests are performed at room temperature.

SPC-F004.DWG

of 1~10. (1=most flexible and 10=most rigid)

TOLERANCES: UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	DRAWN BY:	DATE:	DRAWING TITLE:			
	JAP	1/17/92	FPF Series-Flame Retardant Flexible Polyolefin Tubing			
	CHECKED BY:	DATE:	SIZE	DWG. NO.	ELECTRONIC FILE	REV
	JC	7/13/92	A	TA-411	TA-411.dwg	E
	APPROVED BY:	DATE:	SCALE: NTS		U.O.M.: INCHES [mm]	SHEET: 1 OF 1
	JL	7/14/92				

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY. DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.