

SPECIFICATION FOR APPROVAL

CUSTOMER: JAMES

PART NO: 2099121

MODEL NO: 5.5x2.1 AWG#18 6FT

DESIGNED NO: T0210 RoHS

REVISION: 1-1

CATEGORY: DC CORD

DATE SUBMITTED: 2014.11.21

SAMPLE SUBMITTED SAMPLE 0 SPECIFICATION 1	CONCLUSION	APPROVED
		REJECTED
		CONDITION APP'D

CUSTOMER'S SIGNATURE:

浩源實業有限公司
HAWK'S AIM INDUSTRIAL CO., LTD.
高雄市前鎮區新衙路 286-8 號 5F-2
5F-2, No.286-8, Shin-Ya Road, Chien-Chen
District, Kaohsiung, Taiwan 806
Tel:07-8418448 Fax:07-8419997

MODEL NO: 5.5x2.1 AWG#18 6FT
CUSTOMER P/N: 2099121
DESCRIPTION: DC CORD
ISSUED DATE: 2014.11.21
REVISION: 1-1

TABLE OF CONTENTS

1.0 APPEARANCE DIMENSION


REV	DESCRIPTION	DATE
1-0	INITIAL RELEASED	2009.09.22
1-1	CHANGE HAWK'S AIM	2014.11.21

APP.BY _____

CHK.BY _____

PRE.BY _____

1.0 APPEARANCE DIMENSIONS: (UNIT:mm)



BLACK WIRE —●— LETTERED WIRE

BLACK WIRE —●— LETTERED WIRE

(1) MAXIMUM VOLTAGE RATING: 300V

(2) MAXIMUM CURRENT RATING: 2.5Amp

FUNCTION TEST: No open, no reversed polarity, no short-circuit, no INT

CABLE ASSEMBLY SHALL BE IN COMPLIANCE WITH RoHS REQUIREMENT.

HI-POT: 600VAC, 0.5mA, 1Second

APP.BY _____

CHK.BY _____

PRE.BY _____