



**NOTES, UNLESS OTHERWISE SPECIFIED:**

STEEL TOOL CASE INCLUDED WITH  
CT-980CH TOOL.

TOOL OUTPUT: 5.5 METRIC TONS/6.2 SHORT TONS.

TOOL INPUT: 10,000 PSI

APPLICABLE CONNECTOR RANGE: 4AWG-750MCM COPPER  
COMPRESSION LUGS AND SPLICES.  
6AWG-500MCM ALUMINUM  
COMPRESSION LUGS AND SPLICES.

CONNECTIONS MADE WITH PANDUIT COPPER  
COMPRESSION CONNECTORS ARE U.L. LISTED.

PANDUIT CT-901 HYDRAULIC PUMP SYSTEM  
MATCHED TO TOOL HEAD.

TOOL WEIGHT: 6.81bs/3.1Kg.

TOOL DIMENSIONS: 12.0 x 5.3 x 2.50 IN.  
305 x 135 x 65mm.

TOOL CAN BE USED WITH COMPATABLE  
HYDRAULIC PUMP SYSTEM DEVELOPING  
10,000 PSI.

DO NOT USE TOOL ON LIVE ELECTRICAL CIRCUITS.

MINIMUM JAW OPENING AT FULLY RETRACTED POSITION: 1.46 IN. (37.084 mm).

©