





PRODUCT NUMBER	ROW	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32
75860-X01	a	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X
	b	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X
	c	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X
75860-X02	a	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X
	b	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X
	c	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X



NOTE:-

1. THE "LF" PRODUCTS MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
2. LEAD FREE OR RoHS DIRECTIVE LABELLING TO BE PROVIDED AS PER GS-14-920 FOR LEAD FREE VERSION.

NOTES:

- 1.MATERIAL HOUSING: THERMOPLASTIC POLYESTER 30% GLASS FILLED, FLAME RETARDANT PER UL-94-V0
COLOUR HOUSING: GREY, COLOUR COVER: BLACK
- 2.MATERIAL CONTACT: PHOSPHOR BRONZE
- 3.CAN BE MATED WITH 3 ROW MALE CONNECTOR CONFORM DIN 41612 - FORM C
- 4."LF" SUFFIX TO THE PRODUCT NUMBER FOR LEAD FREE OR RoHS COMPATIBLE PRODUCTS.
- 5.PIERCE AREA PLATING SPEC: $0.1-0.2\mu\text{mNi}$

Part Number	Performance Class
75860-4YY	2.0um Aumin over 3um Ni in contact area
75860-0YY	3.0um Aumin over 3um Ni in contact area
75860-1YY	DIN 41612 CLASS 1
75860-2YY	DIN 41612 CLASS 2

mat'l. code	see table	surface	ISO 1912	tolerance	ISO 486	ISO 1912	projection	product family
lit. len. no. dr. date								BACKPANEL
K H20166 MVI	1992-03-31	angles	linear	mm				title
L 105-0123 MNI	2008-07-27							64 Pos. P.L. ASSEMBLY
M 108-0082 MNI	2008-08-01							dwg no
N 108-0078 JOHN	2008-08-28							75860
								sheet 1 of 1
								A2
								type
								CUSTOMER Drawing
sheet index	revision	N	1					