


High Precision Wraparound - High Temperature (230 °C) Thin Film Chip Resistors




INTRODUCTION

For applications such as down hole applications, the need for parts able to withstand very severe conditions (temperature as high as 215 °C powered or up to 230 °C un-powered) has leaded Vishay Sfernice to push out the limit of the thin film technology.


Designers might read the application note: Power Dissipation Considerations in High Precision Vishay Sfernice Thin Film Chip Resistors and Arrays (P, PRA etc...) (High Temperature Application) www.vishay.com/doc?53047 in conjunction with this datasheet to help them to properly design their PCBs and get the best performances of the PHT. Vishay Sfernice R&D engineers will be willing to support any customer design considerations.

DIMENSIONS in millimeters (inches)



CASE SIZE	A	B	C	D/E	
	MAX. TOL. + 0.152 (+ 0.006) MIN. TOL. - 0.152 (- 0.006)	MAX. TOL. + 0.127 (+ 0.005) MIN. TOL. - 0.127 (- 0.005)		NOMINAL	TOLERANCE
	NOMINAL	NOMINAL			
0603	1.52 (0.060)	0.85 (0.033)	0.5 (0.02) ± 0.127 (0.005)	0.38 (0.015)	0.13 (0.005)
0805	1.91 (0.075)	1.27 (0.050)		0.40 (0.016)	
1206	3.06 (0.120)	1.60 (0.063)		0.48 (0.019)	
2010	5.08 (0.200)	2.54 (0.100)			

** Please see document "Vishay Material Category Policy": www.vishay.com/doc?99902

SUGGESTED LAND PATTERN (to IPC-7351A)


CHIP SIZE	DIMENSIONS (in millimeter)		
	Z _{max.}	G _{min.}	X _{max.}
0603	2.37	0.35	0.98
0805	2.76	0.74	1.40
1206	3.91	1.85	1.73
2010	5.93	3.71	2.67

STANDARD ELECTRICAL SPECIFICATIONS		
TEST	SPECIFICATIONS	CONDITIONS
Series	0603, 0805, 1206, 2010	
Ohmic Range ⁽¹⁾	10R to 7M6 (depending on series)	
Temperature Coefficient ⁽²⁾	25 ppm/°C, 50 ppm/°C, 100 ppm/°C	- 55 °C; + 215 °C
Tolerance	0.05 %, 0.1 %, 0.5 %, 1 %	
Power Rating (Pn) ⁽³⁾	12.5 mW to 100 mW	215 °C
Operating Temperature Range	- 55 °C; + 215 °C	
Limiting Voltage ⁽³⁾	75 V to 300 V	
Load Life Stability	0.50 %	1000 h/215 °C (ambient) at Pn
Storage Temperature Range	- 55 °C; + 230 °C	
Shelf Life Stability	0.7 % typ. (1 % max.)	8000 h/230 °C

Notes

(1) Please refer to table 3 for TCR versus ohmic values

(2) See table 2

(3) See table 1

Caution:

Performances obtained with following mounting conditions:

PCB: Polyimide

Solder paste: PbSnAg (93.5/5/1.5)

TABLE 1

SIZE	POWER RATING ⁽¹⁾	LIMITING VOLTAGE
0603	12.5 mW	75 V
0805	20 mW	150 V
1206	33 mW	200 V
2010	100 mW	300 V

Note

⁽¹⁾ For power handling improvement, please refer to application note 53047: Power Dissipation Considerations in High Precision Vishay Sfernice Thin Film Chip Resistors and Arrays (High Temperature Applications) www.vishay.com/doc?/53047 and consult Vishay Sfernice

TABLE 2 - TEMPERATURE COEFFICIENT

Y	10 ppm/°C	- 55 °C; + 155 °C
	25 ppm/°C	- 55 °C; + 215 °C
E	25 ppm/°C	- 55 °C; + 155 °C
	50 ppm/°C	- 55 °C; + 215 °C
H	50 ppm/°C	- 55 °C; + 155 °C
	100 ppm/°C	- 55 °C; + 215 °C

TABLE 3

SERIES	OHMIC RANGE ⁽²⁾			
	CT: Y		CT: E/H	
	Min.	Max.	Min.	Max.
0603	39 Ω	320K	10 Ω	320K
0805	39 Ω	511K	10 Ω	725K
1206	39 Ω	1M8	10 Ω	2M7
2010	39 Ω	5M	10 Ω	7M6

Note

⁽²⁾ Best tolerance possible:


0.5 %: 10 Ω to < 20 Ω

0.1 %: 20 Ω to < 39 Ω

0.05 %: 39 Ω to max. value

PHT STABILITY CURVE

High Temperature Drift vs. Time

**Note**

- Stability will be dependent on resistivity of resistor. Above curves are worst case.

MECHANICAL SPECIFICATIONS

Substrate	Alumina
Resistive Element	Nichrome (NiCr)
Passivation	Silicon nitride (Si_3N_4)
Protection	Epoxy + Silicone
Terminations	Gold (< 1 μm) over nickel barrier

Note

- For other terminations, please consult

POPULAR OPTIONS

It is recommended to consult Vishay Sfernice for availability first.


Option: Enlarged terminations:

For stringent and special power dissipation requirements, the thermal resistance between the resistive layer and the solder joint can be reduced using enlarged terminations chip resistors which are soldered on large and thick copper pads acting as heatsink (see application note: 53048 Power Dissipation in High Precision Vishay Sfernice Chip Resistors and Arrays (P Thin Film, PRA Arrays, CHP Thick Film) www.vishay.com/doc?53048).


Option to order: 0063 (applies to size 1206/2010).

DIMENSIONS (Option 0063) in millimeters

Bottom view for mounting



CASE SIZE	A	B	E	D	F		
	MAX. TOL. + 0.152	MAX. TOL. + 0.127	MAX. TOL. + 0.13	MAX. TOL. + 0.13			
	NOMINAL	NOMINAL	NOMINAL	NOMINAL	NOMINAL	MIN.	MAX.
1206	3.06	1.60	0.40	1.215	0.63	0.50	0.76
2010	5.08	2.54	0.48	2.25			

SUGGESTED LAND PATTERN (Option 0063)


CHIP SIZE	DIMENSIONS (in millimeter)		
	Z _{max}	G _{min}	X _{max}
1206	3.91	0.50	1.73
2010	5.93		2.67

PACKAGING

ESD packaging available: waffle-pack, and plastic tape and reel (low conductivity). Paper tape available upon request (ESD only).

SIZE	MOQ	NUMBER OF PIECES PER PACKAGE			TAPE WIDTH
		WAFFLE PACK 2" x 2"		TAPE AND REEL	
		MIN.	MAX.		
0603	100	100	100	4000	8 mm
0805					
1206					
2010					

Note

(1) 12 mm on request

PACKAGING RULES**Waffle Pack**

Can be filled up to maximum quantity indicated in the table here above, taking into account the minimum order quantity. When quantity ordered exceeds maximum quantity of a single waffle pack, the waffle packs are stacked up on the top of each other and closed by one single cover.

To get "not stacked up" waffle pack in case of ordered quantity > maximum number of pieces per package:
Please consult Vishay Sfernice for specific ordering code

Tape and Reel

Can be filled up to maximum quantity indicated in the table here above, taking into account the minimum order quantity. When quantity ordered is between the MOQ and the maximum reel capacity, only one reel is provided.

When several reels are needed for ordered quantity within MOQ and maximum reel capacity: Please consult Vishay Sfernice for specific ordering code

GLOBAL PART NUMBER INFORMATION

Global Part Numbering: PHT1206Y1001BGT063

P	H	T	1	2	0	6	Y	1	0	0	1	B	G	T	0	6	3
GLOBAL MODEL	SIZE	TCR	VALUE			TOLERANCE	TERMINATION			PACKAGING			OPTION				
PHT	0603 0805 1206 2010	Y E H	The first three digits are significant figures and the last digit specifies the number of zeros to follow, R designates decimal point			W = 0.05 % B = 0.1 % D = 0.5 % F = 1 %	G = Gold N = Tin/silver (2)			T = Tape and reel Blank = Waffle pack			Leave blank if no option				
			10R0 = 10 Ω 3901 = 3900 Ω 1004 = 1 MΩ														

Note

(2) For usage at temperatures up to 200 °C maximum N (tin/silver termination are available upon request)

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.