





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		D2	REVISED PER ECO-11-004917	11MAR11	RK	HMR

MATERIAL:
HOUSING: THERMOPLASTIC, UL94V-0 BLACK.
TERMINALS: BRIGHT TIN PLATED, COPPER ALLOY.
SCREWS: #6-32, STEEL, ZINC PLATED WITH CLEAR CHROMATE.

ELECTRICAL:
CURRENT RATING UL/CSA:
CLASS C: 25A, 300V.
CLASS D: 5A, 600V.
WIRE RANGE: 12-22 AWG

MECHANICAL:
RECOMMENDED TORQUE: 7 IN-LB.
OPERATING TEMP.: 105°C MAX.

- 1
- SCREWS ARE NICKEL PLATED BRASS.
- 2
- SEE FIGURE.
- 3
- MARK WITH WHITE PERMANENT INK.
- 4
- ALL SCREWS BOTTOMED.
- 5
- OBSOLETE PARTS: OBSOLETE CIS
STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED PCB LAYOUT



10.875	11.311	28	6PCV-28-009	4-1546686-2
10.500	10.936	27	6PCV-27-009	4-1546686-1
10.125	10.561	26	6PCV-26-009	4-1546686-0
9.750	10.186	25	6PCV-25-009	3-1546686-9
9.375	9.811	24	6PCV-24-009	3-1546686-8
9.000	9.436	23	6PCV-23-009	3-1546686-7
8.625	9.061	22	6PCV-22-009	3-1546686-6
8.250	8.686	21	6PCV-21-009	3-1546686-5
7.875	8.311	20	6PCV-20-1362	7-1546158-9
7.875	8.311	20	6PCV-20-1361	7-1546158-8
7.875	8.311	20	6PCV-20-009	3-1546686-4
7.500	7.936	19	6PCV-19-009	3-1546686-3
7.125	7.561	18	6PCV-18-009	3-1546686-2
6.750	7.186	17	6PCV-17-009	3-1546686-1
6.375	6.811	16	6PCV-16-009	3-1546686-0
6.000	6.436	15	6PCV-15-009	2-1546686-9
5.625	6.061	14	6PCV-14-009	2-1546686-8
5.250	5.686	13	6PCV-13-009	2-1546686-7
4.875	5.311	12	6PCV-12-009	6-1546158-6
4.500	4.936	11	6PCV-11-009	2-1546686-6
4.125	4.561	10	6PCV-10-009	2-1546686-5
3.750	4.186	9	6PCV-09-009	2-1546686-4
3.375	3.811	8	6PCV-08-1188	1-1437653-6
3.375	3.811	8	6PCV-08-009	1-1437653-2
3.000	3.436	7	6PCV-07-009	5-1546158-8
2.625	3.061	6	6PCV-06-009	1-796988-1
2.250	2.686	5	6PCV-05-009	5-1546158-2
1.875	2.311	4	6PCV-04-009	7-1437652-0
1.500	1.936	3	6PCV-03-009	796988-5
1.125	1.561	2	6PCV-02-009	3-1437652-8
DIM B	DIM A	NO OF POS.	CATALOG NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	S SCHLEGEL	8/19/03	TE Connectivity			
		CHK	S YODER	8/19/03				
		APVD	S YODER	8/19/03	NAME			
		PRODUCT SPEC			6PCV-XX-009 ASSEMBLY			
		APPLICATION SPEC						
		WEIGHT			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		-			A3	00779	C-796988-5	-
		CUSTOMER DRAWING			SCALE	NTS	SHEET	REV
							1 OF 2	D2

4		3		2		1		
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION				
© COPYRIGHT - By -				ALL RIGHTS RESERVED.				
LOC FT		DIST 0		REVISIONS				
P		LTR		DESCRIPTION		DATE	DWN	APVD
		-		SEE SHEET 1		-	-	-

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16

17

18

19

20

7-1546158-8

20

19

18

17

16

15

14

13

12

11

10

9

8

7

6

5

4

3

2

1

7-1546158-9

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± .02
3 PLC ± .010
4 PLC ± -
ANGLES ± 1°

MATERIAL

-

FINISH

-

DWN
S SCHLEGEL
8/19/03

CHK
S YODER
8/19/03

APVD
S YODER
8/19/03

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

TE Connectivity

NAME
6PCV-XX-009 ASSEMBLY

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-796988-5

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
NTS

SHEET
2 OF 2

REV
D2

1470-19 (3/11)