

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0923181612

Status:

Active

Overview:

Picoflex Ribbon-Cable Connectors

Description:

Picoflex PF-50 IDT-to-Board-in Z-Style, 16 Circuits, 0.12m Length

Documents:

Drawing (PDF)

Product Specification PS-99020-0011-001 (PDF)

RoHS Certificate of Compliance (PDF)

Application tooling part link

Application Tooling Part Link

Application Tooling Part Link

62100-6000

62100-6010

General

Product Family

Series

Assembly Configuration

Connector to Connector

Overview

Product Name

UPC

Cable Assemblies

92318

Dual Ended Connectors

Picoflex PCB-to-IDT

Picoflex Ribbon-Cable Connectors

Picoflex

822350944687

Physical

Cable Length

Circuits (Loaded)

Color - Resin

Gender

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Packaging Type

Pitch - Mating Interface

Plating min - Mating

Plating min - Termination

Single Ended

Termination Interface: Style

Waterproof / Dustproof

Wire Insulation Diameter

Wire Size AWG

Wire/Cable Type

0.12m

16

Natural

Female-Female

None

Phosphor Bronze

Tin

Tin

Polyester

2.060/g

2

Bag

1.27mm

2.032µm

2.032µm

No

IDT or Pierce, Through Hole - Kinked Pin

No

N/A

28

PVC, Ribbon Cable

Electrical

Current - Maximum per Contact

Shielded

Voltage - Maximum

1.2A

No

250V

Material Info


Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-99020-0011-001

SD-92318-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

Green Image

REACH SVHC

Not Contained Per

-ED/01/2018 (15

January 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit

Contact US

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

92318 Series

Mates With

Picoflex PF-50 Header

90325 , 90800 ,

90779 , 90715 , 90814

Application Tooling | FAQ

Tooling specifications and manuals are

found by selecting the products below.

Crimp Height Specifications are then

contained in the Application Tooling

Specification document.

Global

Description

Product #

Extractor Tool for

Connectors

621006000

This document was generated on 09/13/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION