

DRAWING MADE IN THIRD ANGLE PROJECTION

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

, 19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.


LOC	DIST	P	F	ZONE	LTR	REVISIONS	DATE	APPD
G	14				A	REVISED PER 0720-0230-93	2/28/94	DAP

METRIC

DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	UL E13288 Listed
12-10 AWG STRANDED	12-10 AWG STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

△ STAMP AMP 12-10* APPROX AS SHOWN

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMSFOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTSPRODUCT INFORMATION CENTER
1-800-522-6752FOR APPLICATION
TOOLING INFORMATIONTOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:

170°C MAX

VOLTAGE RATING:

NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:
2.62-6.64mm² [5,180-13,100] CIR MILS
STRANDEDTHIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING BUSINESS ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLC DEC ± -
3 PLC DEC ± -
ANGLES ± -MATERIAL
COPPER PER
ASTM B-152
ANNEALEDFINISH
TIN PLATE
0.00254 [0.000100] MIN
THK PER MIL-T-10727DR 2-8-93
TA BRINKMANCHK 2-8-93
DA PATTERSONAPPD 2-8-93
DE MILLERAPPD 2-8-93
JL MECKLEY

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

324910

PART NO

AMP

AMP Incorporated
Harrisburg, PA 17105-3608NAME
TERMINAL, RING TONGUE,
BUDGET

SIZE

C

CAGE CODE

00779

DRAWING NO

C-324910

SCALE 10:1

SHEET

1 OF 1

CUSTOMER DRAWING

AMP 1471-B REV 3-92

28-FEB-94 14:38:13 amp26463 /files/dept1123/dwg1123/u.bodies/u.12-10