

EPIC® H-D 8


Multi-pole inserts for machined crimp contacts

The powerful and compact standard insert has PE contacts with screw termination and is suitable, for example, for control systems.

Info

Compact, powerful standard insert

For machined contacts for fast processing with the crimping tool



Robust



Space requirement



Mechanical and plant engineering

Benefits

Small, high-performance connector

High performance crimping contacts

PE contact with screw connection

Application range

Machine and equipment manufacturing

Control engineering

EPIC® H-D 8

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000438 ETIM 5.0 Class-Description: Contact insert for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000438 ETIM 6.0 Class-Description: Contact insert for industrial connectors
Rated voltage (V):	IEC: 24 V (AC)/60 V (DC) metal housing; 250 V thermoplastic housing; UL: 250 V
Rated impulse voltage:	2.5 kV
Rated current (A):	IEC: 10 A UL: 10 A
Pollution degree:	3
Flammability:	UL94 V-0
Contact resistance:	< 2 mOhm
Contacts:	Copper alloy, hard silver/gold-plated
Number of contacts:	8
Termination methods:	Crimp termination: 0.14 - 2.5 mm ²
Material:	PBT Polyester
Cycle of mechanical operation:	100
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40°C to +100°C, short-term up to +125°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-D 8

Article number	Article description	Contact type	Number of operating contacts
11252500	H-D 8 SCM	male	1 - 8
11253500	H-D 8 BCM	female	1 - 8

Last Update (23.02.2018)

©2018 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16