






LOC		DIST		REVISIONS					
CM	00	P	LTR	DESCRIPTION		DATE	DWN	APVD	
				0	REVISED PER 063B-0087-04	01MAY04	KW	SR	
				01	REVISED PER ECO-05-001793	21MAY05	KW	SR	
				02	REVISED PER ECO-09-025699	11DEC09	KK	AEG	




1. PARTS COMPLY TO AMP SOLDERABILITY SPECIFICATION 109-11-3.
2. CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.
3. DIMENSIONS IN BRACKETS ARE IN INCHES.
4. IDENTIFICATION WILL APPEAR AT CIRCUIT NO. 1, OTHERS OPTIONAL.
5. CONTACT IS PLATED WITH 0.00127 [0.00050] NICKEL, THEN 0.000075 [0.00030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.
6. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI




SCALE 4:1



SECTION B-B



SECTION A-A
SCALE 10:1



Ø1.78±0.07
[0.070±.003]
5 PLC

RECOMMENDED MOUNTING HOLE PATTERN
FOR 1.57 [0.062] THICK P.C. BOARD

6	OBSOLETE	PHOSPOR BRONZE, GOLD 5	NYLON, UL94V-2,NATURAL	1586134-2
		PHOSPOR BRONZE, PRE-TIN	NYLON, UL94V-2,NATURAL	1586134-1
		PIN CONTACT MATERIAL AND FINISH	HOUSING MATERIAL AND COLOR	PART NUMBER

DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN R. WHITAKER 07MAY04		Tyco Electronics Corporation Harrisburg, PA 17105-3608	
9 PLC ±		1 PLC ±		CHK S. RIDGILL 07MAY04		NAME	
3 PLC ±		5 PLC ±		APVD S. RIDGILL 07MAY04		PRODUCT SPEC	
4 PLC ±		FINISH		APPLICATION SPEC		SIZE CAGE CODE DRAWING NO	
MATERIAL SEE TABLE		SEE TABLE		WEIGHT		A1 00779 C=1586134	
				CUSTOMER DRAWING		RESTRICTED TO	

