


LOC	DIST	REVISIONS					
G	14	P	LTR	DESCRIPTION	DATE	DWN	APVD
			H1	REVISED PER ECO-11-004917	11MAR11	RK	HMR



AMP WIRE RANGE	E13288 Listed
16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED

LR7189 Certified	MILITARY P/N AND CLASS
16-14 AWG SOLID OR STRANDED	M7928/7-10 CLASS 2 P/N 34126 & 2-34126-2 ONLY

- 1 STAMP AMP 16-14* APPROX AS SHOWN
- 2 TIN PLATE 0.00254 [$.000100$] MIN THK PER ASTM B-545.
- 3 GOLD PLATE 0.00127 [$.000050$] MIN THK PER MIL-G-45204 OVER NICKEL PLATE 0.00076 [$.000030$] MIN THK PER QQ-N-290.
- 4 PRELIMINARY - NOT FOR PRODUCTION

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170° C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
		WIRE CROSS SECTIONAL AREA RANGE: $1.04-2.62\text{mm}^2$ [$2,050-5,180$] CIR MILS SOLID OR STRANDED
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.
FOR ORDER ENTRY	1-800-526-5142	

3	----	LOOSE PIECE	4	2-34126-1
2	100	LOOSE PIECE, BOX		8-34126-1
2	5000	ON TAPE		2-34126-2
2	---	LOOSE PIECE		34126
FINISH	QUANTITY	PACKAGING TYPE	PART NO	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-17-93	 TE Connectivity				
DIMENSIONS: INCHES		CHK DA PATTERSON 3-17-93					
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD DE MILLER 3-17-93	NAME TERMINAL, RING TONGUE, SOLISTRAND™			
			PRODUCT SPEC —				
			APPLICATION SPEC —				
			WEIGHT —				
MATERIAL COPPER PER ASTM B-152 ANNEALED		FINISH SEE TABLE	SIZE A2		CAGE CODE 00779	DRAWING NO C-34126	RESTRICTED TO —
			CUSTOMER DRAWING		SCALE 8:1	SHEET 1 of 1	REV H1