

GENERAL DESCRIPTION

The SP339 is an advanced multiprotocol transceiver supporting RS-232, RS-485, and RS-422 serial standards in a 40 pin QFN package. Integrated cable termination and four configuration modes allow all three protocols to be used interchangeably over a single cable or connector with no additional switching components. Full operation requires only four external charge pump capacitors.

The RS-485/422 modes feature one driver and one receiver (1TX/1RX) in both half and full duplex configurations. The RS-232 mode (3TX/5RX) provides full support of all eight signals commonly used with the DB9 RS-232 connector. A dedicated diagnostic loopback mode is also provided.

The high speed drivers operate up to 20Mbps in RS-485/422 modes, and up to 1Mbps in RS-232 mode. All drivers can be slew limited to 250kbps in any mode to minimize electromagnetic interference (EMI).

All transmitter outputs and receiver inputs feature robust electrostatic discharge (ESD) protection to $\pm 15\text{kV}$ IEC-61000-4-2 Air Gap, $\pm 8\text{kV}$ IEC-61000-4-2 Contact, and $\pm 15\text{kV}$ Human Body Model (HBM). Each receiver output has full fail-safe protection to avoid system lockup, oscillation, or indeterminate states by defaulting to logic-high output level when the inputs are open, shorted, or terminated but undriven. No external biasing resistors are required.

The RS-232 receiver inputs include a $5\text{k}\Omega$ pull-down to ground. The RS-485/422 receiver inputs are high impedance ($>96\text{k}\Omega$ when termination is disabled), allowing up to 256 devices on a single communication bus (1/8th unit load).

The SP339 operates from a single power supply, either 3.3V or 5V, with low idle current (2mA typical in all modes). The shutdown mode consumes less than 10 μA for low power standby operation.

FEATURES

- Pin selectable Cable Termination
- No external resistors required for RS-485/422 termination and biasing
- 3.3V or 5V Single Supply Operation
- Robust ESD Protection on bus pins
 - $\pm 15\text{kV}$ IEC 61000-4-2 (Air Gap)
 - $\pm 8\text{kV}$ IEC 61000-4-2 (Contact)
 - $\pm 15\text{kV}$ Human Body Model (HBM)
- Max Data Rate of 20Mbps in RS-485/422 Modes and up to 1Mbps in RS-232 Modes
- Pin selectable 250kbps Slew Limiting
- 3 Drivers, 5 Receivers RS-232/V.28
- 1 Driver, 1 Receiver RS-485/422
 - Full and Half Duplex Configuration
 - 1/8th Unit Load, up to 256 receivers on bus
- RS-485/422 Enhanced Failsafe for open, shorted, or terminated but idle inputs
- Space saving 6mm x 6mm QFN-40 Package
- Pin compatible with SP338E

TYPICAL APPLICATIONS

- Dual Protocol Serial Ports (RS-232 or RS-485/422)
- Industrial Computers
- Industrial and Process Control Equipment
- Point-Of-Sale Equipment
- Networking Equipment
- HVAC Controls Equipment
- Building Security and Automation Equipment

ORDERING INFORMATION

PART NUMBER	PACKAGE	OPERATING TEMPERATURE RANGE	DEVICE STATUS
SP339EER1-L	40-pin QFN	-40°C to +85°C	Active
SP339EER1-L/TR	40-pin QFN	-40°C to +85°C	Active
SP339ECR1-L	40-pin QFN	0°C to +70°C	Active
SP339ECR1-L/TR	40-pin QFN	0°C to +70°C	Active

Note: -L = Green / RoHS Compliant, /TR = Tape and Reel

ABSOLUTE MAXIMUM RATINGS

These are stress ratings only and functional operation of the device at these ratings or any other above those indicated in the operation sections to the specifications below is not implied. Exposure to absolute maximum rating conditions for extended periods of time may affect reliability and cause permanent damage to the device.

Supply Voltage V_{CC}	-0.3V to +6.0V
Receiver Input Voltage (from Ground)	$\pm 18V$
Driver Output Voltage (from Ground)	$\pm 18V$
Short Circuit Duration, TX out to Ground	Continuous
Voltage at TTL Input Pins	-0.3V to $(V_{CC} + 0.5V)$
Storage Temperature Range	-65°C to +150°C
Lead Temperature (soldering, 10s)	+300°C
Power Dissipation 40-pin QFN (derate 17mW/°C above +70°C)	500mW

CAUTION:

ESD (ElectroStatic Discharge) sensitive device. Permanent damage may occur on unconnected devices subject to high energy electrostatic fields. Unused devices must be stored in conductive foam or shunts. Personnel should be properly grounded prior to handling this device. The protective foam should be discharged to the destination socket before devices are removed.

ESD PROTECTION

		MIN.	TYP.	MAX.	UNITS	
R1-R9	Tx Output & Rx Input Pins		± 15		kV	Human Body Model (HBM)
			± 8		kV	IEC 61000-4-2 (Contact)
			± 15		kV	IEC 61000-4-2 (Air Gap)
	All Other Pins		± 4		kV	Human Body Model (HBM)

PIN DESCRIPTIONS BY MODE (MODE1, MODE0)

Pin	Name	00, Figure 1	01, Figure 2	10, Figure 3	11, Figure 4
1	L1	R1 Output		1	1
2	L2	R2 Output		R1 Output	R1 Output
3	L3	T1 Input		T1 Input	T1 Input
4	L4	T2 Input			
5	L6	R3 Output		1	1
6	L7	T3 Input			
7	L8	R4 Output		1	1
8	L9	R5 Output		1	1
9	VCC		V _{CC}		
10	GND		Ground		
11	SLEW		SLEW = V _{CC} enables 250kbps slew limiting		
12	DIR1			T1 Enable, R1 Disable	T1 Enable
13	N/C		This pin is not used and is not connected internally		
14	MODE0	0	1	0	1
15	MODE1	0	0	1	1
16	N/C		This pin is not used and is not connected internally		
17	TERM			Enables RS-485/422 receiver termination	
18	N/C		This pin is not used and is not connected internally		
19	ENABLE		ENABLE = V _{CC} for operation, ENABLE = 0V for shutdown		
20	VCC		V _{CC}		

SP339E
RS-232/RS-485/RS-422 TRANSCEIVER WITH INTERNAL TERMINATION
PIN DESCRIPTIONS BY MODE (MODE1, MODE0)

Pin	Name	00, Figure 1	01, Figure 2	10, Figure 3	11, Figure 4
21	R9		R5 Input		
22	R8		R4 Input		
23	GND		Ground		
24	R7		T3 Output		
25	R6		R3 Input		
26	GND		Ground		
27	R4		T2 Output		R1 Input B
28	R3		T1 Output		R2 Input A
29	GND		Ground		
30	R2		R2 Input	R1 Input A, T1 Out A	T1 Out A
31	R1		R1 Input	R1 Input B, T1 Out B	T1 Out B
32	VCC	V_{CC} - 1.0 μ F to ground recommended for supply decoupling			
33	VSS	V_{SS} - Charge pump negative supply, 0.1 μ F from ground			
34	C2-	C_{2+} - Charge pump cap 2 negative lead			
35	C1-	C_{1-} - Charge pump cap 1 negative lead			
36	GND	Ground			
37	C1+	C_{1+} - Charge pump cap 1 positive lead, 0.1 μ F			
38	VCC	V_{CC}			
39	C2+	C_{2+} - Charge pump cap 2 positive lead, 0.1 μ F			
40	VDD	V_{DD} - Charge pump positive supply, 0.1 μ F to ground			

ELECTRICAL CHARACTERISTICS

UNLESS OTHERWISE NOTED:

$V_{CC} = +3.3V \pm 5\%$ or $+5.0V \pm 5\%$, $C1-C4 = 0.1\mu F$; $T_A = T_{MIN}$ to T_{MAX} . Typical values are at $V_{CC} = 3.3V$, $T_A = +25^\circ C$.

SYMBOL	PARAMETERS	MIN.	TYP.	MAX.	UNITS	CONDITIONS
DC CHARACTERISTICS						
I_{CC}	Supply Current (RS-232)		2	8	mA	No load, idle inputs
I_{CC}	Supply Current (RS-485)		2	8	mA	No load, idle inputs
I_{CC}	V _{CC} Shutdown Current		1	10	μA	ENABLE = 0V
TRANSMITTER and LOGIC INPUT PINS: Pins 3, 4, 6, 11, 12, 14, 15, 17-19						
V_{IH}	Logic Input Voltage High	2.0			V	$V_{CC} = 3.3V$
V_{IH}	Logic Input Voltage High	2.4			V	$V_{CC} = 5.0V$
V_{IL}	Logic Input Voltage Low			0.8	V	
I_{IL}	Logic Input Leakage Current Low			1	μA	Input Low ($V_{IN} = 0V$)
I_{IH}	Logic Input Leakage Current High			1	μA	Input High ($V_{IN} = V_{CC}$), pins 3, 4 and 6
I_{PD}	Logic Input Pull-down Current			50	μA	Input High ($V_{IN} = V_{CC}$), pins 11, 12, 14, 15, 17-19
V_{HYS}	Logic Input Hysteresis		200		mV	
RECEIVER OUTPUTS: Pins 1, 2, 5, 7, 8						
V_{OH}	Receiver Output Voltage High	$V_{CC}-0.6$			V	$I_{OUT} = -1.5mA$
V_{OL}	Receiver Output Voltage Low			0.4	V	$I_{OUT} = 2.5mA$
I_{OSS}	Receiver Output Short Circuit Current		± 20	± 60	mA	$0 \leq V_O \leq V_{CC}$
I_{OZ}	Receiver Output Leakage Current		± 0.1	± 1	μA	$0 \leq V_O \leq V_{CC}$, Receivers disabled

SP339E

RS-232/RS-485/RS-422 TRANSCEIVER WITH INTERNAL TERMINATION

ELECTRICAL CHARACTERISTICS (Continued)

UNLESS OTHERWISE NOTED:

$V_{CC} = +3.3V \pm 5\%$ or $+5.0V \pm 5\%$, $C1-C4 = 0.1\mu F$; $T_A = T_{MIN}$ to T_{MAX} . Typical values are at $V_{CC} = 3.3V$, $T_A = +25^\circ C$.

SYMBOL	PARAMETERS	MIN.	Typ.	MAX.	UNITS	CONDITIONS
SINGLE-ENDED RECEIVER INPUTS (RS-232)						
V_{IN}	Input Voltage Range	-15		+15	V	
V_{IL}	Input Threshold Low	0.6	1.2		V	$V_{CC} = 3.3V$
		0.8	1.5		V	$V_{CC} = 5.0V$
V_{IH}	Input Threshold High		1.5	2.0	V	$V_{CC} = 3.3V$
			1.8	2.4	V	$V_{CC} = 5.0V$
V_{HYS}	Input Hysteresis		0.3		V	
R_{IN}	Input Resistance	3	5	7	k Ω	$-15V \leq V_{IN} \leq +15V$
SINGLE-ENDED DRIVER OUTPUTS (RS-232)						
V_O	Output Voltage Swing	± 5.0	± 5.5		V	Output loaded with $3k\Omega$ to Gnd
				± 7.0	V	No load output
I_{SC}	Short Circuit Current			± 60	mA	$V_O = 0V$
R_{OFF}	Power Off Impedance	300	10M		Ω	$V_{CC} = 0V$, $V_O = \pm 2V$

ELECTRICAL CHARACTERISTICS (Continued)

UNLESS OTHERWISE NOTED:

$V_{CC} = +3.3V \pm 5\%$ or $+5.0V \pm 5\%$, $C1-C4 = 0.1\mu F$; $T_A = T_{MIN}$ to T_{MAX} . Typical values are at $V_{CC} = 3.3V$, $T_A = +25^\circ C$.

SYMBOL	PARAMETERS	MIN.	TYP.	MAX.	UNITS	CONDITIONS
DIFFERENTIAL RECEIVER INPUTS (RS-485 / RS-422)						
R_{IN}	Receiver Input Resistance	96			$k\Omega$	$TERM = 0V$, $-7V \leq V_{IN} \leq +12V$
V_{TH}	Receiver Differential Threshold Voltage	-200	-125	-50	mV	
ΔV_{TH}	Receiver Input Hysteresis		25		mV	$V_{CM} = 0V$
I_{IN}	Receiver Input Current			125	μA	$V_{IN} = +12V$
				-100	μA	$V_{IN} = -7V$
R_{TERM}	Termination Resistance	100	120	155	Ω	$TERM = V_{CC}$, Figure 5 $-7V \leq V_{CM} \leq +12V$
R_{TERM}	Termination Resistance	100	120	140	Ω	$TERM = V_{CC}$, Figure 5 $V_{CM} = 0V$
DIFFERENTIAL DRIVER OUTPUTS (RS-485 / RS-422)						
V_{OD}	Differential Driver Output	2		V_{CC}	V	$R_L = 100\Omega$ (RS-422), Figure 6
		1.5		V_{CC}	V	$R_L = 54\Omega$ (RS-485), Figure 6
		1.5		V_{CC}	V	$-7V \leq V_{CM} \leq +12V$, Figure 7
				V_{CC}	V	No Load
ΔV_{OD}	Change In Magnitude of Differential Output Voltage	-0.2		+0.2	V	$R_L = 54\Omega$ or 100Ω , Figure 6
V_{CM}	Driver Common Mode Output Voltage			3	V	$R_L = 54\Omega$ or 100Ω , Figure 6
ΔV_{CM}	Change In Magnitude of Common Mode Output Voltage			0.2	V	$R_L = 54\Omega$ or 100Ω , Figure 6
I_{OSD}	Driver Output Short Circuit Current	-250		250	mA	$-7V \leq V_O \leq +12V$, Figure 8
I_O	Driver Output Leakage Current			100	μA	$DIR1 = 0V$ in Mode 11, or $ENABLE = 0V$, $V_O = +12V$, $V_{CC} = 0V$ or $5.25V$
				-100	μA	$DIR1 = 0V$ in Mode 11, or $ENABLE = 0V$, $V_O = -7V$, $V_{CC} = 0V$ or $5.25V$

TIMING CHARACTERISTICS

UNLESS OTHERWISE NOTED:

$V_{CC} = +3.3V \pm 5\%$ or $+5.0V \pm 5\%$, $C1-C4 = 0.1\mu F$; $T_A = T_{MIN}$ to T_{MAX} . Typical values are at $V_{CC} = 3.3V$, $T_A = +25^\circ C$.

SYMBOL	PARAMETERS	MIN.	TYP.	MAX.	UNITS	CONDITIONS
ALL MODES						
t_{ENABLE}	Enable from Shutdown		1000		ns	
$t_{SHUTDOWN}$	Enable to Shutdown		1000		ns	
RS-232, DATA RATE = 250kbps (SLEW = V_{cc}), ONE TRANSMITTER SWITCHING						
	Maximum Data Rate	250			kbps	$R_L = 3k\Omega$, $C_L = 1000pF$
t_{RHL} , t_{RLH}	Receiver Propagation Delay		100		ns	$C_L = 150pF$, Figure 9
$ t_{RHL}-t_{RLH} $	Receiver Propagation Delay Skew			100	ns	
t_{DHL} , t_{DLH}	Driver Propagation Delay		1400		ns	$R_L = 3k\Omega$, $C_L = 2500pF$, Figure 10
$ t_{DHL}-t_{DLH} $	Driver Propagation Delay Skew			600	ns	
t_{SHL} , t_{SLH}	Transition Region Slew Rate from +3.0V to -3.0V or -3.0V to +3.0V	4		30	V/ μ s	$V_{CC} = 3.3V$, $R_L = 3k\Omega$ to $7k\Omega$, $C_L = 150pF$ to $2500pF$, Figure 10
t_{SHL} , t_{SLH}	Transition Region Slew Rate from +3.0V to -3.0V or -3.0V to +3.0V	6		30	V/ μ s	$V_{CC} = 3.3V$, $R_L = 3k\Omega$ to $7k\Omega$, $C_L = 150pF$ to $2500pF$, $T_A = 25^\circ C$, Figure 10
RS-232, DATA RATE = 1Mbps (SLEW = 0V), ONE TRANSMITTER SWITCHING						
	Maximum Data Rate	1			Mbps	$R_L = 3k\Omega$, $C_L = 250pF$
t_{RHL} , t_{RLH}	Receiver Propagation Delay		100		ns	$C_L = 150pF$, Figure 9
$ t_{RHL}-t_{RLH} $	Receiver Propagation Delay Skew			100	ns	
t_{DHL} , t_{DLH}	Driver Propagation Delay		300		ns	$R_L = 3k\Omega$, $C_L = 1000pF$, Figure 10
$ t_{DHL}-t_{DLH} $	Driver Propagation Delay Skew			150	ns	
t_{SHL} , t_{SLH}	Transition Region Slew Rate from +3.0V to -3.0V or -3.0V to +3.0V	15		150	V/ μ s	$V_{CC} = 3.3V$, $R_L = 3k\Omega$ to $7k\Omega$, $C_L = 150pF$ to $1000pF$, Figure 10
t_{SHL} , t_{SLH}	Transition Region Slew Rate from +3.0V to -3.0V or -3.0V to +3.0V	24		150	V/ μ s	$V_{CC} = 3.3V$, $R_L = 3k\Omega$ to $7k\Omega$, $C_L = 150pF$ to $1000pF$, $T_A = 25^\circ C$, Figure 10

TIMING CHARACTERISTICS (Continued)

UNLESS OTHERWISE NOTED:

$V_{CC} = +3.3V \pm 5\%$ or $+5.0V \pm 5\%$, $C1-C4 = 0.1\mu F$; $T_A = T_{MIN}$ to T_{MAX} . Typical values are at $V_{CC} = 3.3V$, $T_A = +25^\circ C$.

SYMBOL	PARAMETERS	MIN.	TYP.	MAX.	UNITS	CONDITIONS
RS-485/RS-422, DATA RATE = 250kbps (SLEW = Vcc), ONE TRANSMITTER SWITCHING						
	Maximum Data Rate	250			kbps	$R_L = 54\Omega$, $C_L = 50pF$
t_{RPHL}, t_{RPLH}	Receiver Propagation Delay		50	150	ns	$C_L = 15pF$, Figure 11
$ t_{RPHL}-t_{RPLH} $	Receiver Propagation Delay Skew			20	ns	
t_{DPHL}, t_{DPLH}	Driver Propagation Delay		500	1000	ns	$R_L = 54\Omega$, $C_L = 50pF$, Figure 12
$ t_{DPHL}-t_{DPLH} $	Driver Propagation Delay Skew			100	ns	
t_{DR}, t_{DF}	Driver Rise and Fall Time	300	650	1200	ns	
RS-485/RS-422, DATA RATE = 20Mbps (SLEW = 0V), ONE TRANSMITTER SWITCHING						
	Maximum Data Rate	20			Mbps	$R_L = 54\Omega$, $C_L = 50pF$
t_{RPHL}, t_{RPLH}	Receiver Propagation Delay		50	150	ns	$C_L = 15pF$, Figure 11
$ t_{RPHL}-t_{RPLH} $	Receiver Propagation Delay Skew			10	ns	
t_{DPHL}, t_{DPLH}	Driver Propagation Delay		30	100	ns	$R_L = 54\Omega$, $C_L = 50pF$, Figure 12
$ t_{DPHL}-t_{DPLH} $	Driver Propagation Delay Skew			10	ns	
t_{DR}, t_{DF}	Driver Rise and Fall Time		10	20	ns	
RS-485/RS-422, DATA RATE = 20Mbps (SLEW = 0V), ONE TRANSMITTER SWITCHING						
	Receiver Output Enable Time			200	ns	$C_L = 15pF$, Figure 13
t_{RHZ}, t_{RLZ}	Receiver Output Disable Time			200	ns	
t_{DZH}, t_{DZL}	Driver Output Enable Time			1000	ns	$R_L = 500\Omega$, $C_L = 50pF$, Figure 14
t_{DHZ}, t_{DLZ}	Driver Output Disable Time			200	ns	

SP339E

RS-232/RS-485/RS-422 TRANSCEIVER WITH INTERNAL TERMINATION

BLOCK DIAGRAM BY MODE (MODE1, MODE0)

FIGURE 1. MODE 00 - LOOPBACK





FIGURE 2. MODE 01 - RS-232



SP339E

RS-232/RS-485/RS-422 TRANSCEIVER WITH INTERNAL TERMINATION

FIGURE 3. MODE 10 - RS-485 HALF DUPLEX






FIGURE 4. MODE 11 - RS-485/422 FULL DUPLEX



SP339E
RS-232/RS-485/RS-422 TRANSCEIVER WITH INTERNAL TERMINATION
TEST CIRCUITS
FIGURE 5. RS-485/422 RECEIVER TERMINATION RESISTANCE


Termination is enabled in RS-485/422 modes when the TERM pin is held high (V_{CC}).




FIGURE 6. RS-485/422 DIFFERENTIAL DRIVER OUTPUT VOLTAGE

FIGURE 7. RS-485/422 DIFFERENTIAL DRIVER OUTPUT VOLTAGE OVER COMMON MODE

FIGURE 8. RS-485/422 DRIVER OUTPUT SHORT CIRCUIT CURRENT


FIGURE 9. RS-232 RECEIVER PROPAGATION DELAY





FIGURE 10. RS-232 DRIVER PROPAGATION DELAY



SP339E

RS-232/RS-485/RS-422 TRANSCEIVER WITH INTERNAL TERMINATION

FIGURE 11. RS-485/422 RECEIVER PROPAGATION DELAY




FIGURE 12. RS-485/422 DRIVER PROPAGATION DELAY AND RISE/FALL TIMES




FIGURE 13. RS-485/422 RECEIVER OUTPUT ENABLE/DISABLE TIMES





FIGURE 14. RS-485/422 DRIVER OUTPUT ENABLE/DISABLE TIMES



PRODUCT SUMMARY

The SP339 is an advanced multiprotocol transceiver supporting RS-232, RS-485, and RS-422 serial standards in a 40 pin QFN package. Integrated cable termination and four configuration modes allow all three protocols to be used interchangeably over a single cable or connector with no additional switching components. The RS-485/422 modes feature one driver and one receiver (1TX/1RX) in both half and full duplex configurations. The RS-232 mode (3TX/5RX) provides full support of all eight signals commonly used with the DB9 RS-232 connector. A dedicated mode is also available for diagnostic loopback testing.

INTERNAL SWITCHED CABLE TERMINATION

Enabling and disabling the RS-485/422 termination resistor is one of the largest challenges system designers face when sharing a single connector or pair of lines across multiple serial protocols. A termination resistor may be necessary for accurate RS-485/422 communication, but must be removed when the lines are used for RS-232. SP339 provides an elegant solution to this problem by integrating the termination resistor and switching control, and allowing it to be switched in and out of the circuit with a single pin. No external switching components are required.

ENHANCED FAILSAFE

Ordinary RS-485 differential receivers will be in an indeterminate state whenever the data bus is not being actively driven. The enhanced failsafe feature of the SP339 guarantees a logic-high receiver output when the receiver inputs are open, shorted, or terminated but idle/undriven. The enhanced failsafe interprets 0V differential as a logic high with a minimum 50mV noise margin, while maintaining compliance with the EIA/TIA-485 standard of $\pm 200mV$. No external biasing resistors are required, further easing the usage of multiple protocols over a single connector.

$\pm 15kV$ ESD PROTECTION

ESD protection structures are incorporated on all pins to protect against electrostatic discharges encountered during handling and assembly. The bus pins (driver outputs and receiver inputs) have extra protection structures, which have been tested up to $\pm 15kV$ without damage. These structures withstand high ESD in all states: normal operation, shutdown and powered down.

ESD protection is be tested in various ways. Exar uses the following methods to qualify the protection structures designed into SP339:

- $\pm 15kV$ using the Human Body Model (HBM)
- $\pm 8kV$ using IEC 61000-4-2 Contact Discharge
- $\pm 15kV$ using IEC 61000-4-2 Air Gap Discharge

The IEC 61000-4-2 standard is more rigorous than HBM, resulting in lower voltage levels compared with HBM for the same level of ESD protection. Because IEC 61000-4-2 specifies a lower series resistance, the peak current is higher than HBM. The SP339 has passed both HBM and IEC 61000-4-2 testing without damage.

DIAGNOSTIC LOOPBACK MODE

The SP339 includes a diagnostic digital loop back mode for system testing as shown in [Figure 1](#). The loopback mode connects the TTL driver inputs to the TTL receiver outputs, bypassing the analog driver and receiver circuitry. The analog/bus pins are internally disconnected in this mode.

PACKAGE DRAWINGS

FIGURE 15. QFN-40 PACKAGE DRAWING




FIGURE 16. QFN-40 PACKAGE DIMENSIONS


32LD 5x5 QFN (Option 1) JEDEC MO-220 Variation VWD-0							
DIMENSIONS IN MM (Control Unit)				DIMENSIONS IN INCH (Reference Unit)			
SYMBOLS	MIN	NOM	MAX	SYMBOLS	MIN	NOM	MAX
A	0.80	0.90	1.00	0.032	0.036	0.039	
A1	0.80	0.92	0.95	0.001	0.002	0.003	
A3	0.10	0.12	0.15	0.008	0.010	0.012	
b	0.18	0.25	0.30	0.007	0.010	0.012	
D	5.90	6.00	6.10	0.19	0.20	0.21	
D2	3.00	3.10	3.20	0.118	0.122	0.126	
E	5.00	5.10	5.20	0.178	0.182	0.186	
E2	3.00	3.10	3.20	0.118	0.122	0.126	
e	0.90	0.95	1.00	0.020	0.020	0.020	
L	0.35	0.40	0.45	0.014	0.016	0.018	
K	0.20	—	—	0.008	—	—	
0	0°	—	14°	0°	—	14°	
N	3.2	3.2	3.2	—	—	—	
ND	8	8	8	—	—	—	
NE	8	8	8	—	—	—	
32LD 5x5 QFN (Option 2) JEDEC MO-220 Variation VWD-0							
DIMENSIONS IN MM (Control Unit)				DIMENSIONS IN INCH (Reference Unit)			
SYMBOLS	MIN	NOM	MAX	SYMBOLS	MIN	NOM	MAX
A	0.80	0.90	1.00	0.032	0.036	0.039	
A1	0.80	0.90	1.00	0.032	0.036	0.039	
A3	0.10	0.12	0.15	0.001	0.002	0.003	
b	0.18	0.25	0.30	0.007	0.010	0.012	
D	5.00	5.10	5.20	0.19	0.20	0.21	
D2	3.00	3.10	3.20	0.148	0.150	0.152	
E	5.00	5.10	5.20	0.197	0.200	0.203	
E2	3.00	3.10	3.20	0.148	0.150	0.152	
e	0.90	0.95	1.00	0.020	0.020	0.020	
L	0.35	0.40	0.45	0.014	0.016	0.018	
K	0.20	—	—	0.008	—	—	
0	0°	—	14°	0°	—	14°	
N	3.2	3.2	3.2	—	—	—	
ND	8	8	8	—	—	—	
NE	8	8	8	—	—	—	
32LD 5x5 QFN (Option 3) JEDEC MO-220 Variation VWD-0							
DIMENSIONS IN MM (Control Unit)				DIMENSIONS IN INCH (Reference Unit)			
SYMBOLS	MIN	NOM	MAX	SYMBOLS	MIN	NOM	MAX
A	0.80	0.90	1.00	0.032	0.036	0.039	
A1	0.80	0.90	1.00	0.032	0.036	0.039	
A3	0.10	0.12	0.15	0.001	0.002	0.003	
b	0.18	0.25	0.30	0.007	0.010	0.012	
D	5.00	5.10	5.20	0.197	0.200	0.203	
D2	3.00	3.10	3.20	0.148	0.150	0.152	
E	5.00	5.10	5.20	0.197	0.200	0.203	
E2	3.00	3.10	3.20	0.148	0.150	0.152	
e	0.90	0.95	1.00	0.020	0.020	0.020	
L	0.35	0.40	0.45	0.014	0.016	0.018	
K	0.20	—	—	0.008	—	—	
0	0°	—	14°	0°	—	14°	
N	3.2	3.2	3.2	—	—	—	
ND	8	8	8	—	—	—	
NE	8	8	8	—	—	—	
40LD 6x6 QFN (Option 1) JEDEC MO-220 Variation VWD-5							
DIMENSIONS IN MM (Control Unit)				DIMENSIONS IN INCH (Reference Unit)			
SYMBOLS	MIN	NOM	MAX	SYMBOLS	MIN	NOM	MAX
A	0.80	0.90	1.00	0.032	0.036	0.039	
A1	0.80	0.90	1.00	0.032	0.036	0.039	
A3	0.10	0.12	0.15	0.001	0.002	0.003	
b	0.18	0.25	0.30	0.008	0.012	0.016	
D	5.00	5.10	5.20	0.197	0.200	0.203	
D2	3.00	3.10	3.20	0.148	0.150	0.152	
E	5.00	5.10	5.20	0.197	0.200	0.203	
E2	3.00	3.10	3.20	0.148	0.150	0.152	
e	0.90	0.95	1.00	0.020	0.020	0.020	
L	0.35	0.40	0.45	0.014	0.016	0.018	
K	0.20	—	—	0.008	—	—	
0	0°	—	14°	0°	—	14°	
N	4.0	4.0	4.0	—	—	—	
ND	10	10	10	—	—	—	
NE	10	10	10	—	—	—	
40LD 6x6 QFN (Option 2) JEDEC MO-220 Variation VWD-5							
DIMENSIONS IN MM (Control Unit)				DIMENSIONS IN INCH (Reference Unit)			
SYMBOLS	MIN	NOM	MAX	SYMBOLS	MIN	NOM	MAX
A	0.80	0.90	1.00	0.032	0.036	0.039	
A1	0.80	0.90	1.00	0.032	0.036	0.039	
A3	0.10	0.12	0.15	0.001	0.002	0.003	
b	0.18	0.25	0.30	0.008	0.012	0.016	
D	5.00	5.10	5.20	0.197	0.200	0.203	
D2	3.00	3.10	3.20	0.148	0.150	0.152	
E	5.00	5.10	5.20	0.197	0.200	0.203	
E2	3.00	3.10	3.20	0.148	0.150	0.152	
e	0.90	0.95	1.00	0.020	0.020	0.020	
L	0.35	0.40	0.45	0.014	0.016	0.018	
K	0.20	—	—	0.008	—	—	
0	0°	—	14°	0°	—	14°	
N	6.4	6.4	6.4	—	—	—	
ND	16	16	16	—	—	—	
NE	16	16	16	—	—	—	
40LD 6x6 QFN (Option 3) JEDEC MO-220 Variation VWD-5							
DIMENSIONS IN MM (Control Unit)				DIMENSIONS IN INCH (Reference Unit)			
SYMBOLS	MIN	NOM	MAX	SYMBOLS	MIN	NOM	MAX
A	0.80	0.90	1.00	0.032	0.036	0.039	
A1	0.80	0.90	1.00	0.032	0.036	0.039	
A3	0.10	0.12	0.15	0.001	0.002	0.003	
b	0.18	0.25	0.30	0.008	0.012	0.016	
D	5.00	5.10	5.20	0.197	0.200	0.203	
D2	3.00	3.10	3.20	0.148	0.150	0.152	
E	5.00	5.10	5.20	0.197	0.200	0.203	
E2	3.00	3.10	3.20	0.148	0.150	0.152	
e	0.90	0.95	1.00	0.020	0.020	0.020	
L	0.35	0.40	0.45	0.014	0.016	0.018	
K	0.20	—	—	0.008	—	—	
0	0°	—	14°	0°	—	14°	
N	4.8	4.8	4.8	—	—	—	
ND	12	12	12	—	—	—	
NE	12	12	12	—	—	—	
40LD 6x6 QFN (Option 4) JEDEC MO-220 Variation VWD-5							
DIMENSIONS IN MM (Control Unit)				DIMENSIONS IN INCH (Reference Unit)			
SYMBOLS	MIN	NOM	MAX	SYMBOLS	MIN	NOM	MAX
A	0.80	0.90	1.00	0.032	0.036	0.039	
A1	0.80	0.90	1.00	0.032	0.036	0.039	
A3	0.10	0.12	0.15	0.001	0.002	0.003	
b	0.18	0.25	0.30	0.008	0.012	0.016	
D	7.00	7.00	7.00	0.276	0.276	0.276	
D2	5.50	5.50	5.50	0.217	0.222	0.228	
E	7.00	7.00	7.00	0.276	0.276	0.276	
E2	5.50	5.50	5.50	0.217	0.222	0.228	
e	0.90	0.95	1.00	0.020	0.020	0.020	
L	0.35	0.40	0.45	0.014	0.016	0.018	
K	0.20	—	—	0.008	—	—	
0	0°	—	14°	0°	—	14°	
N	4.8	4.8	4.8	—	—	—	
ND	12	12	12	—	—	—	
NE	12	12	12	—	—	—	

REV.	DISCUSSION	REVISION HISTORY	DATE	APP'D
A	DRAWING DISCUSSION - ECN# 1342-03	10/17/13	AD	
B	UPDATE FORMAT TO COMBINE ALL QFN PACKAGE OUTLINE DIMMERS INTO POD-000-0000003.	10/29/13	AD	

EXAR	
A New Direction in Mixed-Signal	
EXAR CORPORATION	
QFN PACKAGE OUTLINE	
A New Direction in Mixed-Signal	
By AD	Date: 10/29/13
Revision: B	Sheet: 3 OF 3

NOTE: For SP339E package dimensions, refer to 40LD 6x6 (Option 1) table.

FIGURE 17. RECOMMENDED PCB LAND PATTERN



REVISION HISTORY

DATE	REVISION	DESCRIPTION
October 2011	1.0.0	Production Release
December 2011	1.0.1	Added C_L and R_L test conditions to figures 13 and 14 on page 9 Absolute max rating $\pm 18V$ on page 2 Text edits in product summary on page 19
February 2013	1.0.2	Clarified test conditions for Driver Output Leakage Current on page 7 Added $\pm 15kV$ Air Gap ESD per PCN 12-1009-01 Added $\pm 4kV$ HBM ESD to non-bus pins per PCN 12-1009-01
November 2013	1.0.3	Added recommended PCB land pattern drawing. ECN:1348-11

NOTICE

EXAR Corporation reserves the right to make changes to the products contained in this publication in order to improve design, performance or reliability. EXAR Corporation assumes no responsibility for the use of any circuits described herein, conveys no license under any patent or other right, and makes no representation that the circuits are free of patent infringement. Charts and schedules contained here in are only for illustration purposes and may vary depending upon a user's specific application. While the information in this publication has been carefully checked; no responsibility, however, is assumed for inaccuracies.

EXAR Corporation does not recommend the use of any of its products in life support applications where the failure or malfunction of the product can reasonably be expected to cause failure of the life support system or to significantly affect its safety or effectiveness. Products are not authorized for use in such applications unless EXAR Corporation receives, in writing, assurances to its satisfaction that: (a) the risk of injury or damage has been minimized; (b) the user assumes all such risks; (c) potential liability of EXAR Corporation is adequately protected under the circumstances.

Copyright 2013 EXAR Corporation

Datasheet November 2013.

For technical support please email Exar's Serial Technical Support group at: serialtechsupport@exar.com.

Reproduction, in part or whole, without the prior written consent of EXAR Corporation is prohibited.