

LOC		DIST		REVISIONS				
P	LYR	DESCRIPTION			DATE	DWN	APVD	
	B2	REVISED PER ECO-12-011334			28SEP2012	KH	JE	

- 2

PHOSPHOR BRONZE
- 3

LCP, UL94V-0
- 4

FINISH:
CONTACT MATING AREA MEETS THE PERFORMANCE REQUIREMENTS OF
TE CONNECTIVITY PRODUCT SPECIFICATION 108-1957; BASED ON
TELCORDIA GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
COMPLIANT PIN AREA: 0.5µm MIN MATTE TIN OVER BASE PLATING.
- 5

CONNECTOR MARKED WITH PART NUMBER AND DATE CODE
- 6






REFERENCE APPLICATION SPEC 114-13020 FOR RECOMMENDED
PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.
- 7

APPLICATION SEATING HEIGHT TO PRINTED CIRCUIT BOARD
- 8

DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
- 9

LUBRICATE CONTACT AREA WITH BELLCORE APPROVED LUBRICANT
TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995
- 10

HOLE DIAMETER SHPULD BE 3.10 WHEN USING FEED THROUGH GUIDE PIN P/N 120759
CLEARANCE FOR A M3x0.5 THREAD



5.50	9.7	5120662-2
5.50	8.2	5120662-1
M	L	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. CARBO	06DEC04	NAME HEADER ASSEMBLY, 50 POSITION, LEFT HAND, 10 ROW, Z-PACK HS3		
		CHK R. PATTERSON	06DEC04			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SIZE		
mm		0 PLC ± 1 PLC ± 2 PLC ±0.13 3 PLC ±0.05 4 PLC ± ANGLES ± FINISH -		CAGE CODE		RESTRICTED TO
MATERIAL HOUSING: 3		WEIGHT -		DRAWING NO		
CONTACTS: 2		SIGNAL CONTACT: 4		A1 00779 ©=5120662		
		CUSTOMER DRAWING		SCALE 5:1		SHEET 1 OF 1 REV B2