

8

7

6


5

4


3

2


1




3 PIN




4 PIN



5 PIN




6 PIN



7 PIN

NOTES:

1. ALL DIMENSIONS REF. UNLESS OTHERWISE SPECIFIED.



STANDARD SERIES

SCREW - STAINLESS STEEL
HOUSING - ZINC, NICKEL PLATED
SOLDER TERMINAL - BRASS, ELECTRO TIN PLATED
INSULATOR - POLYESTER, GREEN (UL94V-0)
CONTACT PIN - BRASS, SILVER PLATED

D

M

CONTACT PLATING
BLANK = SILVER (STANDARD)
AU = GOLD

HOUSING FINISH
BLANK = NICKEL PLATE (STANDARD)
B = BLACK
S = SANDED

NO. OF CONTACTS:
3 = 3 CONTACTS
4 = 4 CONTACTS
5 = 5 CONTACTS
6 = 6 CONTACTS
7 = 7 CONTACTS


PROFESSIONAL SERIES

SAME AS ABOVE EXCEPT
CONTACT PIN - PHOSPHOR BRONZE, GOLD OVER NICKEL



QGP

63

NO. OF CONTACTS:
3 = 3 CONTACTS
4 = 4 CONTACTS
5 = 5 CONTACTS
6 = 6 CONTACTS
7 = 7 CONTACTS



RECOMMENDED
PANEL CUT-OUT



CUSTOMER DRAWING

G	20745	2-22-96	SG	SG	★ STAR SYMBOL DENOTES CRITICAL DIMENSION UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES - TWO PLACE DECIMALS ±0.01 - THREE PLACE DECIMALS ±0.005 - ANGLES ±1° - ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R. 2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002 3. REMOVE ALL BURRS DO NOT SCALE DRAWING	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.								
F	20627	1-31-96	SG	SG		SIZE	WIDTH		MULT	LBS/M		TEMPER		
E	20543	1-5-96	SG	RB		FINISH	MATERIAL							
						SPEC No.						SPEC No.		
K	22838	10-1-99	JL	DG		FIRST USED ON			SCALE 2:1		Switchcraft®			
J	21070	1-15-97	SG	KS		DATE DRAWN	BY	CHKD	APVD					
H	21035	1-15-97	SG	KS		00-000-90	SG	8-15-94	GHJ 8-15-94					
REV	ECO NUMBER	DATE	BY	APVD		NAME		PART No.					REV	
REVISIONS						D SERIES MALE QG		D_M SERIES					K	