

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E3	REVISED PER ECO-13-005147	27MAR13	KH	DR
	E4	REVISED PER ECO-17-007400	23NO2017	RS	DR

- 1

WIRE INSUL $\varnothing$ 3.810-5.842[$\varnothing$.150-.230]
- 2

MATERIAL: BODY — CU PER ASTM B152
SLEEVE — CU PER ASTM B152
INSULATION — NYLON ASTM D4066, TYPE 1
- 3

FINISH: BODY & SLEEVE: TIN PER ASTM B-545
INSULATION — COLOR: YELLOW
- 4


APPLIES FROM THE EDGE OF METAL BARREL
TO THE CENTER OF THE STUD HOLE.
- 5

BODY MATERIAL THICKNESS: 0.991 ± 0.051 [$.039\pm.002$]
- 6

STAMP AMP 12-10* APPROX AS SHOWN.

 WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
12-10 AWG SOLID OR STRANDED	12-10 AWG SOLID OR STRANDED	12-10 AWG SOLID OR STRANDED

2000	ON TAPE	2-320634-1
500	LOOSE PIECE	320634
QTY	PACKAGE TYPE	PART NO

MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F] VOLTAGE RATING: 300 V MAX CIRCULAR MIL AREA: 2.62–6.64mm ² [5,180–13,100] SOLID OR STRANDED	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr_ruth 12JUN09		TE Connectivity			
	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK TOM MICHIELUTTI 12JUN09					
		0 PLC ± – 1 PLC ± – 2 PLC ± – 3 PLC ± 0.127[.005] 4 PLC ± – ANGLES ± 5°	APVD TOM MICHIELUTTI 12JUN09	NAME TERMINAL, PIDG, RING TONGUE, WIRE SIZE: 12–10				
		MATERIAL 	FINISH 					PRODUCT SPEC UL 486 A–B APPLICATION SPEC 114–2157 WEIGHT –
			SIZE A3	CAGE CODE 00779	DRAWING NO C=320634	RESTRICTED TO –		
CUSTOMER DRAWING					SCALE 5:1	SHEET 1 OF 1	REV E4	