

Characteristics

C_N	Δ	3x 33,2 μ F $\pm$ 5 %
U_N		AC 800 V
f_N		50 Hz 60 Hz
Q_N		20 kvar 24 kvar
I_N		3x 14,5 A 17,4 A

$\tan \delta_0$ 0,2 W/kvar (dielectric)

Maximum ratings

$U_{\max}$	AC 880 V, 8 h daily AC 1040 V, 1 min
$I_{\max}$	3x 35 A ($\Theta_A = 40^\circ\text{C}$, U_N)
I_s	4600 A
$(du/dt)_{\max}$	32 V/ μ s
$(du/dt)_s$	80 V/ μ s

Test data

U_{TT}	AC 1720 V, 10 s
U_{TC}	AC 6000 V, 10 s

$\tan \delta$ (50 Hz) $\leq$ 0,4 W/kvar (total)

Climatic category -40/D


$\Theta_{\min}$	-40 °C
$\Theta_{\max}$	+55 °C
Humidity	Max. relative Humidity $\leq$ 95 %
Θ_{stg}	-55 bis +70 °C

Life expectancy

t_{LD}	130 000 h
----------	-----------

Remarks

Natural cooling



Design data

Dimensions $\phi \times l$	142 x 200 mm (5,59 x 7,87 in)
Approx. weight	2 kg (4,4 lb)
Impregnation	Gas
Fixing	Threaded bolt M12
Mounting hole	14 mm (0,55 in)
Max. torque	10 Nm
Terminals	Isolated terminal, IP20
Max. torque	1,2 Nm
Terminal cross section	16 mm ² (5 AWG)
Creepage distance	12,7 mm (0,50 in)
Clearance	9,6 mm (0,38 in)
Overpressure disconnecter	
Any mounting position possible	