


DIMENSIONS AND PERMISSIBLE RIPPLE CURRENT



Lead Spacing and Diameter (mm)

øD	4	5	6.3	8
P	1.5	2.0	2.5	3.5
ød	0.45	0.50	0.50	0.50

Value (µF)	Working Voltage (WV); Dimensions: D x H (mm); Ripple Current: mA/RMS @ 120Hz, 85°C													
	6.3		10		16		25		35		50		63	
	D x L	mA	D x L	mA	D x L	mA	D x L	mA	D x L	mA	D x L	mA	D x L	mA
0.1											4 x 7	2	4 x 7	2
0.15													4 x 7	2
0.22											4 x 7	3	4 x 7	3
0.33											4 x 7	4	4 x 7	4.4
0.47											4 x 7	5	4 x 7	7.9
0.68													4 x 7	6
1											4 x 7	10	4 x 7	11
1.5													4 x 7	11
2.2											4 x 7	15	4 x 7	17
3.3											4 x 7	18	4 x 7	21
4.7									4 x 7	22	4 x 7	22	5 x 7	26
6.8							4 x 7	16	5 x 7	16	6 x 7	23		
10					4 x 7	25	4 x 7	26	4 x 7	26	5 x 7	31	6.3 x 7	40
15					4 x 7	21	5 x 7	24	5 x 7	29				
22	4 x 7	31	4 x 7	32	4 x 7	33	4 x 7	34	6.3 x 7	47	6.3 x 7	53	8 x 7	70
33	4 x 7	32	4 x 7	35	5 x 7	43	6.3 x 7	53	8 x 7	83	6.3 x 7	65		
47	4 x 7	38	4 x 7	39	5 x 7	49	6.3 x 7	65	8 x 9	63	8 x 7	85		
68	5 x 7	48	6 x 7	58	6 x 7	53	8 x 9	51						
100	5 x 7	63	6.3 x 7	80	6.3 x 7	90	8 x 7	125						
150	6 x 7	99	8 x 9	84										
220	6.3 x 7	99	8 x 7	140	8 x 7	146								